

Enclosed Switching AC-to-DC Power Supplies

4 LEVELS OF SAVINGS			
NAME BRANDS	HOUSE BRANDS	FACTORY OVERRUN	DOLLAR SALE

Jameco carries the full line of Mean Well Power products. For additional products visit www.Jameco.com/meanwellproducts



Enclosed Switching AC-to-DC Power Supplies (Continued)



SP-200

* Web Code: EPS

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L"xW"xH")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	Additional Info (Pg 120)†	Certification	Pricing		
			Voltage @ Current (min-max)	Power							1	5	25
Single Output (Continued)													
1585709	Mean Well	RSP-1000-27	+27V @ 0-37.0A	999W	11.6x5.0x1.6	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	\$319.95	\$299.95	\$279.95
2102983	Mean Well	PB-120N-27C#	+27.6V @ 0-4.3A	118.7W	7.1x3.8x1.9	150	\$	\$	—	UL/CUL/TUV/CE/CB	69.95	62.95	56.95
2102473	Mean Well	SP-240-30	+30V @ 0-8A	240W	7.5x3.7x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	55.95
2101024	Mean Well	HRP-75-36	+36V @ 0-2.1A	75.6W	5.1x3.9x1.5	200	0.5	0.2	3	UL/CUL/TUV/CE/CB	56.95	51.95	46.95
2101753	Mean Well	HRPG-600-36	+36V @ 0-17.5A	630W	8.6x4.1x2.5	200	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	189.95	174.95	164.95
693206	Mean Well	RS-25-48	+48V @ 0-0.57A	27.4W	3.1x2.0x1.1	200	0.5	0.5	1	UL/CUL/TUV/CE/CB	19.95	16.49	13.95
693249	Mean Well	RS-50-48	+48V @ 0-1.1A	52.8W	3.9x3.8x1.4	200	0.5	0.5	1	UL/CUL/TUV/CE/CB	23.95	19.95	16.95
216805	Mean Well	SP-75-48	+48V @ 0-1.6A	76.8W	7.0x3.9x1.3	100	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	36.95	31.95	29.95
216793	Mean Well	S-100F-48	+48V @ 0-2.2A	105.6W	7.8x3.9x1.5	150	0.5	0.5	2	UL/TUV/CE/CB	32.95	26.95	23.95
167346	Mean Well	S-150-48	+48V @ 0-3.2A	153.6W	7.0x4.3x2.0	240	0.2	0.2	2	UL/CUL/TUV/CE/CB	34.95	32.49	29.95
201929	Mean Well	SP-150-48	+48V @ 0-3.2A	154W	7.0x3.9x2.0	250	0.5	0.5	3	UL/CUL/TUV/CE	24.95	22.49	19.95
201930	Mean Well	SP-150-48	+48V @ 0-3.2A	153.6W	7.0x3.9x2.0	250	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	56.95	49.95	44.95
323863	Mean Well	RS-150-48	+48V @ 0-3.3A	158.4W	7.8x3.9x1.5	200	0.5	0.5	1	UL/CUL/TUV/CE/CB	31.95	28.49	26.49
202068	Mean Well	SP-200-48	+48V @ 0-4.2A	201.6W	7.0x3.9x2.0	250	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	54.95	49.95	44.95
2102481	Mean Well	SP-240-48	+48V @ 0-5A	240W	7.5x3.7x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	55.95
207191	Mean Well	S-320-48	+48V @ 0-6.5A	312W	8.5x4.5x2.0	240	0.5	0.5	2	UL/CUL	69.95	62.95	58.95
244770	Mean Well	SP-320-48	+48V @ 0-6.7A	321.6W	8.5x4.5x2.0	240	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	54.95
2105164	Mean Well	SE-450-48	+48V @ 0-9.4A	451.2W	8.9x4.9x2.0	200	0.5	0.2	8	UL/CUL	99.95	92.95	86.95
301402	Mean Well	SP-480-48	+48V @ 0-11A	480W	10.9x5.0x1.7	240	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	144.95	134.95	124.95
161796	Mean Well	SP-500-48	+48V @ 0-10A	480W	6.7x4.7x3.7	300	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	159.95	139.95	129.95
190749	Mean Well	PSP-500-48	+48V @ 0-10.5A	504W	10.9x5.1x7.5	200	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	179.95	165.95	139.95
295929	Mean Well	SE-600-48	+48V @ 0-12.5A	600W	9.7x5.0x2.5	200	0.5	0.5	8	UL/CUL	119.95	109.95	99.95
374249	Mean Well	PSP-600-48	+48V @ 0-12.5A	600W	6.7x4.7x3.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	149.95	134.95	119.95
217350	Mean Well	PSP-1000-48	+48V @ 0-19.0A	912W	10.9x5.1x5.0	200	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	299.95	279.95	259.95
1585725	Mean Well	RSP-1000-48	+48V @ 0-21.0A	1008W	11.6x5.0x1.6	150	0.5	0.5	5	UL/CUL/TUV/CE/CB	319.95	299.95	279.95
231722	Mean Well	PSP-1500-48	+48V @ 0-28.5A	1368W	10.9x5.1x7.5	200	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	299.95	284.95	269.95
694954	Mean Well	RSP-1500-48	+48V @ 0-32.0A	1536W	10.9x5.0x3.3	200	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	389.95	369.95	349.95
2108921	Mean Well	RSP-3000-48	+48V @ 0-62.5A	3000W	10.9x7.0x2.5	200	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	579.95	539.95	499.95
Double Output													
323362	Mean Well	RD-35A	+5V @ 0.3-4A; +12V @ 0.2-1A	32W	3.9x3.2x1.4	80	0.5	0.5	1	UL/CUL/TUV/CE/CB	\$26.95	\$22.95	\$18.95
323380	Mean Well	RD-35B	+5V @ 0.3-4A; +24V @ 0.2-1.3A	51.2W	3.9x3.2x1.4	80	0.5	0.5	1	UL/CUL/TUV/CE/CB	26.95	22.95	18.95
323425	Mean Well	RD-50A	+5V @ 0.3-6A; +12V @ 0.3-3A	54W	3.9x3.8x1.4	80	0.5	0.5	1	UL/CUL/TUV/CE/CB	27.95	24.95	21.95
323433	Mean Well	RD-50B	+5V @ 0.3-6A; +24V @ 0.2-2A	53.6W	3.9x3.8x1.4	80	0.5	0.5	1	UL/CUL/TUV/CE/CB	27.95	24.95	21.95
123458	Mean Well	D-60A	+5V @ 0.3-4A; +12V @ 0.2-3A	56W	6.3x3.8x1.5	75	0.5	0.5	2	UL/CUL/TUV/CE/CB	32.95	26.95	22.95
123466	Mean Well	D-60B	+5V @ 0.3-3A; +24V @ 0.2-1.8A	58W	6.3x3.8x1.5	75	0.5	0.5	2	UL/CUL/TUV/CE/CB	32.95	26.95	22.95
323505	Mean Well	RD-65A	+5V @ 0.3-8A; +12V @ 0.2-4A	66W	5.1x3.9x1.5	80	0.5	0.5	1	UL/CUL/TUV/CE/CB	26.95	23.95	22.49
323513	Mean Well	RD-65B	+5V @ 0.3-8A; +24V @ 0.2-3A	68W	5.1x3.9x1.5	80	0.5	0.5	1	UL/CUL/TUV/CE/CB	26.95	23.95	22.49
323628	Mean Well	RD-85A	+5V @ 2.0-10A; +12V @ 0.3-5A	88W	6.3x3.8x1.5	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	51.95	48.95	45.95
132410	Mean Well	D-120A	+5V @ 2.0-12A; +12V @ 0.5-5A	120W	7.0x3.9x2.0	60	0.5	0.5	2	UL/CUL/TUV/CE/CB	44.95	37.95	34.95
132397	Mean Well	D-120B	+5V @ 2.0-6A; +24V @ 0.4-4A	126W	7.0x3.9x2.0	60	0.5	0.5	2	UL/CUL/TUV/CE/CB	44.95	37.95	34.95
323741	Mean Well	RD-125A	+5V @ 2.0-15A; +12V @ 0.5-10A	130.9W	7.8x3.9x1.5	80	3.0	1.0	1	UL/CUL/TUV/CE/CB	53.95	49.95	46.95
323759	Mean Well	RD-125B	+5V @ 2.0-10A; +24V @ 0.4-5A	133.4W	7.8x3.9x1.5	80	3.0	1.0	1	UL/CUL/TUV/CE/CB	53.95	49.95	46.95
2106124	Mean Well	RD-125-1224	+12V @ 1.0-3.7A; +24V @ 0.4-3.7A	133.2W	7.8x3.9x1.5	120	1.0	0.5	1	UL/CUL/TUV/CE/CB	53.95	49.95	46.95
Triple Output													
201989	Mean Well	T-40A	+5V @ 0.6-3A; +12V @ 0.2-2A; -5V @ 0.1-0.5A	41.5W	5.1x3.9x1.5	100	0.5	0.5	2	CSA/CE	\$31.95	\$26.95	\$22.95
201997	Mean Well	T-40B	+5V @ 0.6-3A; +12V @ 0.2-2A; -12V @ 0.1-0.5A	45W	5.1x3.9x1.5	100	0.5	0.5	2	CSA/CE	31.95	26.95	22.95
202009	Mean Well	T-40C	+5V @ 0.6-3A; +15V @ 0.2-1.5A; -15V @ 0.1-0.5A	45W	5.1x3.9x1.5	100	0.5	0.5	2	CSA/CE	31.95	26.95	22.95
323442	Mean Well	RT-50A	+5V @ 0.5-5A; +12V @ 0.2-2.5A; -5V @ 0.5-5A	46.5W	3.9x3.8x1.4	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	24.95	22.95	19.95
323460	Mean Well	RT-50B	+5V @ 0.5-5A; +12V @ 0.2-2.5A; -12V @ 0.1-1A	50W	3.9x3.8x1.4	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	33.95	31.95	29.95
323468	Mean Well	RT-50C	+5V @ 0-5A; +15V @ 0.2-2A; -15V @ 0.1-1A	50W	3.9x3.8x1.4	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	33.95	31.95	29.95
323476	Mean Well	RT-50D	+5V @ 0.5-5A; +12V @ 0.1-1A; +24V @ 0.2-1.5A	51W	3.9x3.8x1.4	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	33.95	31.95	29.95
123482	Mean Well	T-60B	+5V @ 0.5-5A; +12V @ 0.2-2.5A; -12V @ 0-0.5A	61W	6.3x3.8x1.5	100	1.0	0.5	2	UL/CUL/TUV/CE/CB	34.95	28.95	23.95
123491	Mean Well	T-60C	+5V @ 0.5-5A; +15V @ 0.2-2A; -15V @ 0-0.5A	62.5W	6.3x3.8x1.5	100	1.0	0.5	2	UL/CUL/TUV/CE/CB	34.95	28.95	23.95
323540	Mean Well	RT-65B	+5V @ 0.5-8A; +12V @ 0.2-3.5A; -12V @ 0-1A	64.6W	5.1x3.9x1.5	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	38.95	35.95	33.95
323548	Mean Well	RT-65C	+5V @ 0.5-8A; +15V @ 0.2-3A; -15V @ 0-1A	65.5W	5.1x3.9x1.5	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	38.95	35.95	33.95
323555	Mean Well	RT-65D	+5V @ 0.5-8A; +12V @ 0.1-1A; +24V @ 0.2-2A	68W	5.1x3.9x1.5	80	1.0	0.5	1	UL/CUL/TUV/CE/CB	38.95	35.95	33.95
213794	Mean Well	TP-100A	+5V @ 3-10A; +12V @ 0.4-4A; -5V @ 0-0.6A	100W	7.8x3.9x2.0	100	3.0	1.0	3	UL/CUL/TUV/CE/CB/PFC	49.95	47.95	45.95

* Primary Output # See complete specs on page 129 \$ Load line regulation is dependent on battery current requirement

More Enclosed Switching Power Supplies on page 119-121 & 123-124

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 180.