



Open-Frame Switching AC-to-DC Power Supplies

- Universal AC input/full range
- Two-year warranty
- Short-circuit, overload and overvoltage protection
- PFC Model: Built-in active Power Factor Correction function, power factor >0.93
- Three-year warranty

* Web Code: OSP



Complete specifications available online

Part No.	Manufacturer	Mfr. Part No.	Output		Input (VAC @ Hz)	Size (L"xW"xH")	Mounting Holes (L"xW"xDia.)	Ripple & Noise (mV p-p)*	Load Reg. (%)	Line Reg. (%)	PFC	Certification	Pricing	
			Voltage @ Current (min-max)	Power									1	10
Single Output														
2188692	TDK-Lambda	ZWS5-5	+5V @ 1A	5W	85-265 @ 47-440	3.8x1.8x0.8	3.6x1.5x0.1	120	2.0	1.0	—	UL/CSA/TUV/CE	\$10.95	\$9.95
2188730	Phihong	PSA-10L-050	+5V @ 2A	10W	85-264 @ 47-440	4.0x1.8x0.8	3.8x1.6x0.3	80	2.0	1.0	—	UL/CSA/TUV	12.95	11.95
229042	Phihong	PSA15LN3-050	+5V @ 0-3A	15W	90-264 @ 47-63	4.3x1.6x0.9	4.0x1.3x0.2	50	2.0	1.0	—	UL/CUL/TUV/CE	18.95	17.25
212354	Mean Well	PS-25-5	+5V @ 0-5A	25W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	80	2.0	0.5	—	UL/CUL/TUV/CE	11.95	10.49
217332	Mean Well	PS-45-5	+5V @ 0-8A	40W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.2	100	3.0	1.0	—	UL/CUL/TUV/CE	12.49	11.49
201938	Mean Well	PS-65-5	+5V @ 0-13.8A	60W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	100	1.0	4.0	—	UL/CUL/TUV/CE	13.95	12.95
392826	Mean Well	PS-25-7.5	+7.5V @ 3.3A	24.8W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.14	80	2.0	0.5	—	UL/TUV/EN	11.95	10.49
2188772	UMEC	UP0401S-09	+9V @ 4.4A	40W	90-264 @ 47-63	4.0x3.0x1.0	3.6x2.6x0.2	100	1.0	1.0	—	UL/CSA/TUV	12.95	11.95
2105666	Mean Well	PS-15-12	+12V @ 0-1.25A	15W	85-264 @ 47-63	3.7x1.9x1.0	3.4x1.9x0.1	150	0.5	0.5	—	CB/CE	7.95	6.95
148604	Mean Well	PS-25-12	+12V @ 0-2.1A	25.2W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	100	2.0	0.3	—	UL/CUL/TUV/CE	11.95	10.49
213728	Mean Well	PS-45-12	+12V @ 0-3.7A	44.4W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.2	100	2.0	1.0	—	UL/CUL/TUV/CE	12.49	11.49
2205413	Astrodyne	ASM60-1380	+12V @ 0-5A	60W	100-240 @ 50-60	4.0x2.0x1.7	3.7x1.7x0.1	100	3.0	1.0	—	UL/CUL/TUV/CE	12.95	11.95
148639	Mean Well	PS-65-12	+12V @ 0-5.2A	62.4W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.15	100	2.0	1.0	—	UL/CUL/TUV/CE	13.95	12.95
2099981	ITE	SBU60-105	+12V @ 5.25A	63W	90-264 @ 47-63	5.0x3.0x1.1	4.6x2.6x0.15	120	3.0	0.5	—	UL/CUL/CE	8.95	7.95
374089	Mean Well	PPS-125-12	+12V @ 0-8.5A	126W	90-264 @ 47-63	5.0x3.0x1.4	4.6x2.6x0.14	100	1.0	0.5	✓	UL/CUL/TUV/CE	45.95	40.49
213681	Mean Well	LPP-150-12	+12V @ 0-12.5A	150W	85-264 @ 47-63	8.7x2.4x1.6	8.3x2.6x0.15	100	1.0	0.5	✓	UL/CUL/TUV/CE	37.95	34.95
374380	Mean Well	PS-65-13.5	+13.5V @ 0-5.4A	63.5W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.16	100	2.0	1.0	—	UL/CUL/TUV/CE/CB	13.95	12.95
2105674	Mean Well	PS-15-15	+15V @ 0-1A	15W	85-264 @ 47-63	3.7x1.9x1.0	3.4x1.6x0.1	120	1.0	1.0	—	UL/TUV/CB/CE	4.95	4.49
216769	Mean Well	PS-25-15	+15V @ 0-1.7A	25.5W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	100	2.0	0.3	—	UL/CUL/TUV/CE	11.95	10.49
216751	Mean Well	PS-65-15	+15V @ 0-4.2A	63W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	100	2.0	1.0	—	UL/CUL/TUV/CE	13.95	12.95
216670	Mean Well	LPP-100-15	+15V @ 6.7A	100W	85-264 @ 47-63	8.7x2.4x1.3	8.3x2.0x0.14	100	0.5	0.5	✓	UL/CUL/TUV/CE	34.95	31.95
2122491	Mean Well	PLP-20-24	+24V @ 0-0.8A	19.2W	90-277 @ 47-63	5.5x1.3x0.8	5.2x1.0x0.1	300	10.0	3.0	✓	UL/CUL/TUV/CE	14.95	12.95
212346	Mean Well	PS-25-24	+24V @ 0-1A	24W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	240	2.0	0.2	—	UL/CUL/TUV/CE	11.95	10.49
1919035	Mean Well	PS-35-24	+24V @ 0-1.5A	36W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	240	2.0	0.2	—	UL/CUL/TUV/CE	12.49	11.49
213720	Mean Well	PS-45-24	+24V @ 0-1.9A	45.6W	90-264 @ 47-440	4.0x2.0x0.9	3.8x1.8x0.1	200	0.5	0.5	—	UL/CUL/TUV/CE/CB	12.49	11.49
148647	Mean Well	PS-65-24	+24V @ 0-2.7A	64.8W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	100	2.0	1.0	—	UL/CUL/TUV/CE	13.95	12.95
2129633	Elpac	MS6524F	+24V @ 2.7A	65W	100-240 @ 50-60	5.0x3.0x1.2	4.5x2.5x0.2	100	5.0	5.0	—	UL/CSA/TUV/CE	5.95	4.95
244727	Mean Well	LPS-75-24	+24V @ 0-3.5A	76.8W	90-264 @ 47-63	8.7x2.2x1.2	8.4x1.8x0.2	120	1.0	1.0	✓	UL/CUL/TUV/CE	14.95	13.95
173463	Mean Well	LPS-100-24	+24V @ 0-4.2A	100.8W	88-264 @ 47-63	8.7x2.4x1.3	8.4x2.1x0.1	150	0.5	0.5	✓	UL/CUL/TUV/CE	31.95	28.95
2129684	Elpac	MSM7524	+24V @ 4.6A	110.0W	100-240 @ 50-60	5.7x3.4x1.6	5.2x3.4x1.5	240	3.0	1.0	—	UL/CUL/CE	13.95	12.49
301429	Mean Well	PPS-125-24	+24V @ 0-5.2A	124.8W	90-264 @ 47-63	5.0x3.0x1.4	4.6x2.6x0.1	150	1.0	0.5	✓	UL/CUL/TUV/CE	45.95	40.49
213672	Mean Well	LPP-150-24	+24V @ 0-6.3A	150W	85-264 @ 47-63	8.7x2.4x1.6	8.3x2.6x0.2	150	0.5	0.5	✓	UL/CUL/TUV/CE	37.95	34.95
668730	Mean Well	PPS-200-24	+24V @ 0-8.3A	199.2W	90-264 @ 47-63	5.0x3.0x1.4	3.7x7.8x0.14	150	1.0	0.5	✓	UL/CUL/TUV/CE	64.95	54.95
201954	Mean Well	PS-65-48	+48V @ 0-1.5A	64.8W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.16	100	2.0	1.0	—	UL/CUL/TUV/CE/CB	13.95	12.95
Double Output														
2188617	Powdec	CML0522	+5V @ 0-1.5A; +12V @ 0-0.6A	15W	100-240 @ 50-60	3.5x2.3x1.1	3.1x2.0x0.1	50	4.0	2.0	—	UL/CSA/TUV/CE	\$11.95	\$10.95
212312	Mean Well	PD-2505	+5V @ 0.1-3A; -5V @ 0.1-2.5A	25W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.08x0.1	50	4.0	1.0	—	UL/CUL/TUV/CE	16.95	14.95
212338	Mean Well	PD-25A	+5V @ 0.2-2.5A; +12V @ 0.1-1.5A	25W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.08x0.1	50	1.0	0.5	—	UL/CUL/TUV/CE	13.95	12.49
212330	Mean Well	PD-25B	+5V @ 0.2-2A; +24V @ 0.1-1A	25.2W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	50	1.0	0.5	—	UL/CUL/TUV/CE	13.95	12.49
194862	Mean Well	PD-45A	+5V @ 0.4-3.2A; +12V @ 0.2-2	40W	90-264 @ 47-440	5.0x2.5x1.5	4.5x2.5x0.2	50	3.0	1.0	—	UL/CSA	14.95	13.49
2197741	Skyenet	SNP-N563	+5V @ 1.0-8A; +3.3V @ 0.5-6A	60W	85-264 @ 47-63	5.0x3.0x1.1	4.6x2.6x0.2	50	3.0	1.0	—	UL	11.95	10.95
194889	Mean Well	PD-65A	+5V @ 0.4-7A; +12V @ 0.2-3.2A	61.1W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	50	3.0	1.0	—	UL/CUL/TUV/CE	14.49	13.49
692377	Autec	UPS65-1002	+5V @ 0.5-3.5A; +12V @ 0.1-4A	65W	90-260 @ 47-63	6.0x3.5x1.5	4.8x3.2x0.2	50	2.0	0.5	—	UL/CSA/TUV	13.95	11.95
194897	Mean Well	PD-65B	+5V @ 0.4-3.5A; +24V @ 0.2-2A	65.5W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	50	3.0	1.0	—	UL/CUL/TUV/CE	16.95	14.95
148690	Mean Well	PD-2512	+12V @ 0.1-1.2A; -12V @ 0.1-1A	24W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	50	3.0	0.5	—	UL/CUL/TUV/CE	13.95	12.49
2100857	Mean Well	PD-25-15	+15V @ 1A, -5V @ 1A	25W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	50	3.0	0.5	—	UL/CUL/TUV/CE	13.95	12.49
Triple Output														
2081617	Artesyn	NFN40-7607	+5V @ 3A; +12V @ 2A; -5V @ 0.35A	40W	85-264 @ 47-440	5.0x3.0x1.2	4.6x2.6x0.15	50	2.0	1.0	—	UL/CSA/TUV	\$7.95	\$6.95
2129676	Elpac	MSM40D	+5.1V @ 4A; +24V @ 1A; -12V @ 0.4A	40W	100-240 @ 50-60	5.0x3.0x1.1	4.6x2.5x0.2	50	5.0	5.0	—	UL/CUL/CSA/CE	10.95	9.95
229122	Phihong	PSA4531	+5V @ 0-4A; +12V @ 0-1.5A; -12V @ 0-0.5A	44W	90-264 @ 47-63	5.0x3.0x1.2	4.6x2.6x0.2	50	2.0	1.0	—	UL/CSA/TUV/CE	33.95	31.49
88402	Mean Well	PT-45B	+5V @ 0.4-3A; +12V @ 0.2-2A; -12V @ 0-0.3A	45W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.2	50	3.0	1.0	—	UL/CUL/TUV/CE	16.95	14.95
216734	Mean Well	PT-65B	+5V @ 0.4-5.5A; +12V @ 0.2-2.5A; -12V @ 0-0.5A	63.5W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.2	50	3.0	1.0	—	UL/CUL/TUV/CE	17.95	16.49
216726	Mean Well	PT-65C	+5V @ 0.4-5.5A; +15V @ 0.2-2A; -15V @ 0-0.5A	65W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.2	50	3.0	1.0	—	UL/CUL/TUV/CE	17.95	16.49
215707	Mean Well	PT-65D	+5V @ 0.5-5A; +12V @ 0.2-4A; +24V @ 0.2-1.3A	68W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.2	50	2.0	1.0	—	UL/CUL/TUV/CE	17.95	16.49

* Primary Output

** Medical rated

RoHS compliant product. Jameco obtains RoHS compliance status information from its suppliers solely and does not verify or confirm such status.