

Enclosed Switching AC-to-DC Power Supplies

3 LEVELS OF SAVINGS		
NAME BRANDS	HOUSE BRANDS	SPECIAL BUY



Enclosed Switching AC-to-DC Power Supplies (Continued)

- 100% full-load burn-in test
- Wide AC input range
- Manufacturer warranty varies



SP-200



*Web Code: EPS

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%)§	PFC	Certification	Pricing	
			Voltage @ Current (min-max)	Power								1	10
Single Output (Continued)													
173404	Mean Well	SP-150-24	+24V @ 0-6.25A	150W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	\$42.95	\$38.95
2147971	Mean Well	HLG-150H-24	+24V @ 0-6.3A	151.2W	9.0 x 2.7 x 1.5	150	0.5	0.5	93	✓	UL/CSA/EN/IP/TUV	65.95	59.95
123450	Mean Well	S-150-24	+24V @ 0-6.5A	156W	7.0 x 4.3 x 2.0	240	0.2	0.2	85	—	UL/CUL/TUV/CE/CB	34.95	31.95
323855	Mean Well	RS-150-24	+24V @ 0-6.5A	156W	7.8 x 3.9 x 1.5	120	0.5	0.5	86	—	UL/CUL/TUV/CE/CB	22.49	20.49
2135523	TDK/Lambda	HWS150-24/A	+24V @ 0-6.5A	156W	6.3 x 1.7 x 3.2	150	0.5	0.3	85	—	UL/CSA/CE/EN/IEC	44.95	41.95
2101868	Mean Well	HRP-150-24	+24V @ 0-6.5A	156W	6.3 x 3.8 x 1.5	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	54.95	49.95
2094864	Mean Well	HRPG-150-24	+24V @ 0-6.5A	156W	6.3 x 3.8 x 1.5	150	0.5	0.3	87	✓	UL/CUL/TUV/CE/CB	63.95	57.95
2205173	Globtek	SP-200-24M	+24V @ 0-8.4A	200W	7.8 x 3.9 x 1.9	150	0.5	0.3	95	—	UL/TUV/CE	44.95	39.95
194782	Mean Well	SP-200-24	+24V @ 0-8.4A	201.6W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	49.95	44.95
2172341	Mean Well**	MSP-200-24	+24V @ 0-8.4A	201.6W	7.8 x 3.9 x 1.5	150	0.5	0.2	88	✓	ANSI/AAMI/IEC	89.95	79.95
2101518	Mean Well	SP-240-24	+24V @ 0-10A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	49.95	44.95
196657	Mean Well	S-320-24	+24V @ 0-12.5A	300W	8.5 x 4.5 x 2.0	150	0.5	0.5	86	—	UL/CUL	64.95	59.95
2122714	Mean Well	SPV-300-24	+24V @ 0-12.5A	300W	8.5 x 4.5 x 1.9	150	0.5	0.2	85	✓	EN/TUV/UL	98.95	88.95
244752	Mean Well	SP-320-24	+24V @ 0-13A	312W	8.5 x 4.5 x 2.0	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	61.95	55.95
2102220	Mean Well	HRP-300-24	+24V @ 0-14A	336W	7.7 x 4.1 x 1.6	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	76.95	69.95
2094881	Mean Well	HRPG-300-24	+24V @ 0-14A	336W	7.8 x 4.1 x 1.6	150	0.5	0.3	87	✓	UL/CUL/TUV/CE/CB	89.95	79.95
2166055	Mean Well**	MSP-300-24	+24V @ 0-14A	336W	7.8 x 4.1 x 1.6	150	0.5	0.2	87	✓	ANSI/AAMI/IEC	104.95	94.95
2146564	Mean Well	SE-350-24	+24V @ 0-14.6A	350.4W	8.5 x 4.5 x 2.0	150	0.5	0.5	87	—	UL/CUL	43.95	39.95
2101606	Mean Well	SE-450-24	+24V @ 0-18.8A	451.2W	8.9 x 4.9 x 2.0	200	0.5	0.2	86	—	UL/CUL	64.95	58.95
2122335	Mean Well	HRP-450-24	+24V @ 0-18.8A	451.2W	8.6 x 4.1 x 1.6	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	114.95	104.95
2193379	Mean Well**	MSP-450-24	+24V @ 0-18.8A	451.2W	8.6 x 4.1 x 1.6	150	0.5	0.2	88	✓	UL/CUL/CB/CE	149.95	134.95
301322	Mean Well	SP-480-24	+24V @ 0-22A	480W	10.9 x 5.0 x 1.7	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	129.95	114.95
147054	Mean Well	SP-500-24	+24V @ 0-20A	480W	6.7 x 4.7 x 3.7	240	0.5	0.5	85.5	✓	UL/CUL/TUV/CE/CB	149.95	134.95
295902	Mean Well	SE-600-24	+24V @ 0-25A	600W	9.7 x 5.0 x 2.5	150	0.5	0.5	87	—	UL/CUL	84.95	77.95
374231	Mean Well	PSP-600-24	+24V @ 0-25A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	86	✓	UL/CUL/TUV/CE/CB	129.95	119.95
2204787	Mean Well**	MSP-600-24	+24V @ 0-27A	648W	8.6 x 4.1 x 2.5	150	0.5	0.2	88	✓	UL/CUL/CB/CE	159.95	144.95
320048	Mean Well	SP-750-24	+24V @ 0-31.3A	750W	10.9 x 5.0 x 2.5	120	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	199.95	179.95
2172121	Mean Well	RSP-750-24	+24V @ 0-31.3A	751.2W	9.8 x 5.0 x 1.6	150	0.5	0.5	90.5	✓	EN/TUV/UL	179.95	164.95
1585717	Mean Well	RSP-1000-24	+24V @ 0-40A	960W	11.6 x 5.0 x 1.6	150	0.5	0.5	88	✓	UL/CUL/TUV/CE/CB	249.95	229.95
2101569	Mean Well	SE-1000-24	+24V @ 0-41.7A	1000.8W	10.9 x 5.0 x 2.5	200	0.5	0.5	88	—	UL/CUL	174.95	159.95
694938	Mean Well	RSP-1500-24	+24V @ 0-63A	1512W	10.9 x 5.0 x 3.3	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	339.95	314.95
2106714	Mean Well	RSP-2400-24	+24V @ 0-100A	2400W	10.9 x 7.0 x 2.5	150	0.5	0.5	90	✓	EN/TUV/UL	454.95	414.95
2106749	Mean Well	RSP-3000-24	+24V @ 0-125A	3000W	10.9 x 7.0 x 2.5	150	0.5	0.5	90	✓	EN/TUV/UL	499.95	449.95
693513	Mean Well	SP-150-27	+27V @ 0-5.6A	151.2W	7.8 x 3.9 x 2.0	15	0.5	0.5	84	—	UL/CUL/TUV/CE/CB/PFC	42.95	38.95
693548	Mean Well	SP-200-27	+27V @ 0-7.5A	202.5W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	49.95	44.95
693628	Mean Well	SP-320-27	+27V @ 0-11.7A	315.9W	8.5 x 4.5 x 2.0	200	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	61.95	55.95
190706	Mean Well	SP-500-27	+27V @ 0-18A	486W	6.7 x 4.7 x 3.7	200	0.5	0.5	86.5	✓	UL/CUL/TUV/CE/CB	149.95	134.95
295911	Mean Well	SE-600-27	+27V @ 0-22.2A	599.4W	9.7 x 5.0 x 2.5	150	0.5	0.5	87	—	UL/CUL	84.95	77.95
374257	Mean Well	PSP-600-27	+27V @ 0-22.2A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	86	✓	UL/CUL/TUV/CE/CB	134.95	119.95
374038	Mean Well	SP-750-27	+27V @ 0-27.8A	750W	10.9 x 5.0 x 2.5	120	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	174.95	159.95
1585709	Mean Well	RSP-1000-27	+27V @ 0-37.0A	999W	11.6 x 5.0 x 1.6	150	0.5	0.5	88	✓	UL/CUL/TUV/CE/CB	239.95	214.95
694946	Mean Well	RSP-1500-27	+27V @ 0-56A	1512W	10.9 x 5.0 x 3.3	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	32.95	29.95
2102983	Mean Well	PB-120N-27C#	+27.6V @ 0-4.3A	118.7W	7.1 x 3.8 x 1.9	150	£	£	79	—	UL/CUL/TUV/CE/CB	44.95	39.95
2146118	Mean Well	AD-155B	+27.6V @ 0-5.5A	152W	7.8 x 4.3 x 2.0	150	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	54.95	48.95
2102473	Mean Well	SP-240-30	+30V @ 0-8A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	49.95	44.95
2101024	Mean Well	HRP-75-36	+36V @ 0-2.1A	75.6W	5.1 x 3.9 x 1.5	200	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	40.95	36.95
2102730	Mean Well	SP-320-36	+36V @ 0-8.8A	316.8W	8.5 x 4.5 x 2.0	220	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	61.95	55.95
2102318	Mean Well	HRP-300-36	+36V @ 0-14A	324W	7.8 x 4.1 x 1.6	250	0.5	0.2	88	✓	EN/TUV/UL	76.95	69.95
2104524	Mean Well	SE-600-36	+36V @ 0-16.6A	598W	9.7 x 5.0 x 2.5	200	0.5	0.5	87	—	UL/CUL	84.95	77.95
2101753	Mean Well	HRPG-600-36	+36V @ 0-17.5A	630W	8.6 x 4.1 x 2.5	200	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	134.95	119.95
693206	Mean Well	RS-25-48	+48V @ 0-0.57A	27.4W	3.1 x 2.0 x 1.1	200	0.5	0.5	85	—	UL/CUL/TUV/CE/CB	11.49	10.49
693249	Mean Well	RS-50-48	+48V @ 0-1.1A	52.8W	3.9 x 3.8 x 1.4	200	0.5	0.5	86	—	UL/CUL/TUV/CE/CB	13.95	12.95
693290	Mean Well	RS-100-48	+48V @ 0-2.3A	110.4W	6.3 x 3.8 x 1.5	200	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	22.95	20.95
167346	Mean Well	S-150-48	+48V @ 0-3.2A	153.6W	7.0 x 4.3 x 2.0	240	0.2	0.2	83	—	UL/CUL/TUV/CE/CB	32.95	29.95
201930	Mean Well	SP-150-48	+48V @ 0-3.2A	153.6W	7.0 x 3.9 x 2.0	250	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	42.95	38.95
323863	Mean Well	RS-150-48	+48V @ 0-3.3A	158.4W	7.8 x 3.9 x 1.5	200	0.5	0.5	87	—	UL/CUL/TUV/CE/CB	23.95	21.95
202068	Mean Well	SP-200-48	+48V @ 0-4.2A	201.6W	7.0 x 3.9 x 2.0	250	0.5	0.5	84	✓	UL/CUL/TUV/CE/CB	49.95	44.95
2102481	Mean Well	SP-240-48	+48V @ 0-5A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	49.95	44.95
2197855	TDK Lambda	SWS300-48	+48V @ 0-6.7A	321.6W	7.8 x 4.0 x 2.0	240	0.1	0.2	86	✓	UL/CSA/CE	49.95	44.95

*Primary Output **Medical rated § Efficiency # See complete specs on page 115 £ Load/line regulation is dependent on battery current requirement

