

Customer Number



Like our catalog, we have even more products on our website

Scan on your smartphone with a code reader app.

If you would like to unsubscribe from Jameco's catalog please visit www.Jameco.com/CatalogUnsubscribe

Printed in USA

Great Products, Awesome Prices, Reach for Jameco First!



Medical AC-to-DC Table-Top Power Supplies

*Web Code: WBM



These table-top power supplies are very reliable, accurate and approved to satisfy the demands of various kinds of medical electrical devices.

- Medical standard: 2XMDPP
- Universal AC input/full range
- Three-year warranty
- Protection: short circuit/overload/over voltage



2196318



2213915

Part No.	Mfr. Part No.	Output		Load Regulation	Line Regulation	Efficiency	Pricing	
		Voltage @ Current	Power				1	10
2196318	GSM06U05-P1J	5V @ 1.2A	6W	±0.5%	±5%	68%	\$9.95	\$8.95
2213915	GSM18B12-P1J	12V @ 1.5A	18W	±3.0%	±1%	85%	12.95	11.49
2214070	GSM36B12-P1J	12V @ 3A	36W	±3.0%	±1%	86%	14.49	12.95
2214230	GSM60B12-P1J	12V @ 5A	60W	±3.0%	±1%	88%	21.95	19.95
2210466	GSM90B12-P1M	12V @ 6.67A	80.04W	±5.0%	±1%	88%	31.95	28.95
2214029	GSM25B24-P1J	24V @ 1.04A	25W	±2.0%	±1%	87%	13.49	11.95
2214184	GSM40B24-P1J	24V @ 1.67A	40W	±2.5%	±1%	90%	18.95	17.49
2214310	GSM120B24-R7B	24V @ 5A	120W	±3.0%	±1%	90%	49.95	44.95



Industrial AC-to-DC Switching Power Supplies



This high efficiency power supplies have a state of the art design that can withstand harsh environmental conditions being fully potted by silicone and enclosed with an aluminum case. If reliability and durability are your concerns, this power supply will more than suit your needs.

- Built-in active PFC function
- Protections: short circuit/overload/over voltage
- Fanless design, cooling by free air convection
- LED indicator for power on
- Five-year warranty
- Output voltage and output current can be adjusted with internal potentiometer
- Size: 11"L x 5.6"W x 1.9"H

*Web Code: EPS



Part No.	Mfr. Part No.	Output		Load Regulation	Line Regulation	Efficiency	Pricing	
		Voltage @ Current	Power				1	10
2218741	HEP-600-12	12V @ 40A	480W	±2.0%	±0.5%	93%	\$210.95	\$189.95
2218775	HEP-600-24	24V @ 25A	600W	±0.5%	±0.5%	95%	210.95	189.95
2218812	HEP-600-48	48V @ 12.5A	600W	±0.5%	±0.5%	96%	210.95	189.95



AC-to-DC LED Switching Power Supplies

*Web Code: LPP



These waterproof and energy efficient power supplies are exactly what you need for all kinds of outdoor or indoor LED lighting applications.

- Universal AC Input/full range
- IP67 rated protection level
- Cooled by free air convection
- Built-in active PFC function
- Protections: Short circuit/overload/over voltage/over temperature

Part No.	Mfr. Part No.	Output		Load Regulation	Line Regulation	Efficiency	Pricing	
		Voltage @ Current	Power				1	10
2164121	APV-35-12*	12V @ 3A	36W	±2.0%	±1.0%	83.0%	\$11.95	\$10.96
2218329	HLG-600H-12B	12V @ 40A	480W	±2.0%	±0.5%	92.0%	194.95	169.95
2165861	LPF-25D-24	24V @ 1.05A	25W	±0.5%	±0.5%	85.5%	25.95	23.49
2215030	NPF-90-24	24V @ 3.75A	90W	±0.5%	±0.5%	91.0%	38.95	35.95
2215128	PWM-90-48	48V @ 1.88A	90W	±0.5%	±0.5%	90.5%	47.95	43.95
2215216	OWA-90U-54	54V @ 1.67A	90.24W	±0.5%	±0.5%	91.0%	43.95	38.95

* Does not have active PFC or IP67 level

CONTACT INFORMATION

Order Desk

Phone: 1-800-831-4242

Fax: 1-800-237-6948

E-mail: Sales@Jameco.com

Technical Support

Phone: 1-800-831-4242

E-mail: Tech@Jameco.com

Customer Service

Phone: 1-800-536-4316

E-mail: CustService@Jameco.com

Credit Department

Phone: 650-592-8097

Fax: 650-802-1583

E-mail: Credit@Jameco.com

International Order Desk

Phone: 650-592-8097

Fax: 650-592-2503

E-mail: International@Jameco.com

Feedback

E-mail: Feedback@Jameco.com

The Jameco RobotStore

Website: www.RobotStore.com

Club Jameco

Website: www.ClubJameco.com



2165861

2215128

2218329