

AC-to-DC Regulated Wall Adapters

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **SPECIAL BUY**

Energy Star Worldwide Interchangeable AC-to-DC Regulated Switching Wall Adapters

Meets US and European Energy Star compliance. Approved for European high-efficiency power applications.

- Field changeable AC plug clips (**sold separately, unless noted**)
- Regulated output • Double insulated
- Input voltage: 90-264VAC @ 47-63Hz • Power-on LED
- Output connector: **2.1mm x 5.5mm female center positive**; (except where noted, see footnotes **, #, ✓, ## below)
- Load regulation: ±5% • Class B EMI • 6" black cord
- Applications: wireless communications, portable equipment, digital camera, peripherals and networking

NEW
 MARKED IN PINK



* Web Code: NBH



Phihong & Mean Well AC Plug Clips (below)

Part No.	Manufacturer	Product No.	Output Volt. (VDC)	Current (A)	Power (W)	Ripple (mVp-p)	Line Regulation	Efficiency (%)	Dimensions (L" x W" x H")	Pricing		
										1	10	50
228785	Phihong	PSA11R-033	3.3	2.0	6	50	±5%	70	3.3 x 1.8 x 1.3	\$10.95	\$9.95	\$8.95
2202888	Phihong	PSA21R-033	3.3	3.0	10	50	±1%	70	3.9 x 2.3 x 1.2	12.95	11.95	10.95
2144809	Phihong	PSA08R-0501#	5	1.0	5	50	±1%	70	2.8 x 1.8 x 1.0	8.95	7.95	6.95
2202829	Phihong	PSA08R-050-1.3**	5	1.0	5	50	±1%	70	2.8 x 1.8 x 1.0	9.95	8.95	7.95
2202790	Cincon	TR10R050-1*	5	1.6	8	50	±1%	65	2.8 x 1.7 x 1.3	11.95	10.95	9.95
2197812	Cincon	TR10R050 ✓*	5	1.6	8	50	±1%	65	2.8 x 1.7 x 1.3	11.95	10.95	9.95
2158240	Phihong	PSM11R-050##	5	2.0	10	100	±5%	70	2.8 x 1.7 x 1.2	9.95	8.95	7.95
2202853	Phihong	PSA10R-090	9	1.1	10	90	±1%	65	3.4 x 2.0 x 1.3	10.95	9.95	8.95
2202896	Phihong	PSA21R-090	9	1.67	15	90	±1%	70	3.9 x 2.3 x 1.2	11.95	10.95	9.95
2082311	Mean Well	GE18I09-P1J	9	2.0	18	100	±5%	75	3.2 x 1.7 x 1.6	12.49	11.49	9.95
2138951	Phihong	PSA11R-120	12	0.83	10	120	±1%	65	2.8 x 1.8 x 1.2	9.95	8.95	7.95
2108656	Phihong	PSC12R-120	12	1.0	12	240	±5%	78	2.8 x 1.8 x 1.2	14.95	13.95	12.95
2154986	ReliaPro	FW75550/12*	12	1.25	15	150	±5%	80	3.5 x 2.0 x 1.3	15.95	14.95	13.95
2210693	Asian Power Devices	WA-18H12§	12	1.5	18	120	±2%	80	3.0 x 1.9 x 1.4	14.95	13.95	12.95
228849	Phihong	PSA21R-120	12	1.67	20	120	±1%	70	3.9 x 2.3 x 1.2	16.95	14.95	13.49
2100179	Phihong	PSAA20R-120	12	1.67	20	120	±5%	81	2.8 x 2.0 x 1.3	17.95	16.95	14.49
2102094	Mean Well	GE24I12-P1J	12	2.0	24	120	±1%	78	3.2 x 1.7 x 1.6	14.95	13.49	11.95
228822	Phihong	PSA11R-150	15	.67	10	150	±5%	70	3.4 x 2.0 x 1.3	16.95	14.95	13.49
2205632	CUI	EMS240025-PSP-SZ*	24	0.25	6	240	±1%	80	2.5 x 1.6 x 1.2	8.95	7.95	6.95
2082345	Mean Well	GE12I24-P1J	24	0.63	15	240	±3%	80	2.8 x 1.6 x 1.5	9.49	8.49	7.95
2192528	Edac	EA1024KR*	24	1.25	30	240	±1%	80	2.8 x 1.6 x 1.3	24.95	22.95	19.95

Input plugs: † Includes US AC plug clip only § Includes US and European plug clips *Kit includes US, UK, EU, AUS plugs
 Output connectors: ** 1.3mm x 3.5mm female plug # 2.5mm x 5.5mm female plug ✓ 2.5mm x 5.5mm right angle female plug ## Mini USB plug

Phihong AC Plug Clips (sold separately, required for above adapters)

Part No.	Mfr. P/N	Description (see above for photos)	1	10	50	100
229155	RPA	US AC plug only	\$1.25	\$1.19	\$1.09	\$.99
229163	RPE	European AC plug only	1.25	1.19	1.09	.99
229171	RPK	United Kingdom AC plug only	1.49	1.35	1.19	1.09
2081422	RPS	Australia AC plug only	1.25	1.19	1.09	.99
229181	RPKIT	Kit includes US, EU, UK & AU clips (4)	4.79	4.39	3.95	3.49

Mean Well AC Plug Clips (sold separately, required for above adapters)

Part No.	Mfr. P/N	Description (see above for photos)	1	10	50	100
2082353	AC-Plug-US	US AC plug only	\$1.19	\$1.09	\$.99	\$.89
2082361	AC-Plug-EU	European AC plug only	1.19	1.09	.99	.89
2082370	AC-Plug-UK	United Kingdom AC plug only	1.39	1.25	1.09	.99
2082388	AC-Plug-AU	Australia AC plug only	1.19	1.09	.99	.89
2082396	AC-Plug-MIX	Kit includes US, EU, UK & AU clips (4)	4.59	4.19	3.79	3.39

AC-to-DC Regulated Linear Wall Adapters

We specialize in Wall Adapters – Call for additional OEM PRICING.

We are happy to change any listed DC wall adapter power plug to a connector of your choice (see pg 99) for just \$2.50 each. Overmolding also available @ \$4.00 each. A 100 pc. minimum order applies.



* Web Code: WAZ

♦ Polarity 1 (+) (-) (center negative)
 Polarity 2 (-) (+) (center positive)
 Female(F) Male(M)

Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ♦	Input VAC @ Hz	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VDC)	Current (mA)								1	10	50	100
164101	ReliaPro	GPU410500500W000	5	500	2.1mm x 5.5mm F 2	120 @ 60	3.1 x 2.1 x 1.7	Black	6'	0.6	UL/CUL	\$10.95	\$9.95	\$8.95	\$7.95
319986	ReliaPro	DV-580R	5	800	2.5mm x 5.5mm F 2	120 @ 60	3.2 x 2.2 x 1.9	Black	6'	1.0	UL/CUL	7.49	6.49	5.49	4.49
1953612	ReliaPro	DDU050100	5	1000	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.2 x 1.8	Black	6'	1.2	UL/CUL	10.95	9.95	8.95	7.95
168605	ReliaPro	DBU0501000	5	1000	2.5mm x 5.5mm F 2	120 @ 60	3.3 x 2.2 x 1.9	Black	6'	1.2	UL/CUL	10.95	9.95	8.95	7.95
190512	ReliaPro	DBU60020-H3570	6	200	2.1mm x 5.5mm F 2	120 @ 60	2.2 x 1.7 x 1.5	Black	6'	0.4	UL/CUL	9.95	8.95	7.95	6.95
283573	ReliaPro	ADR-6V500MA-2.1	6	500	2.1mm x 5.5mm F 2	120 @ 60	3.1 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	10.95	9.95	8.95	7.95
190529	ReliaPro	AD9123	9	250	2.5mm x 5.5mm right angle F 2	120 @ 60	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CUL	9.95	8.95	7.95	6.95
1953639	ReliaPro	DCU09050	9	500	2.1mm x 5.5mm F 2	120 @ 60	3.4 x 2.0 x 1.6	Black	6'	0.9	UL/CUL	10.95	10.49	9.95	8.95
1953647	ReliaPro	SF41-0900500RU	9	500	2.5mm x 5.5mm F 2	120 @ 60	3.0 x 2.0 x 1.6	Black	6'	0.9	UL/CUL	10.95	10.49	9.95	8.95
220898	ReliaPro	DCU120020	12	200	2.1mm x 5.5mm F 1	120 @ 60	2.5 x 2.0 x 1.7	Black	6'	0.5	UL/CUL	8.95	7.95	6.95	6.25
162996	ReliaPro	DDU120050	12	500	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
170245	ReliaPro	RDU120100	12	1000	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.3 x 2.0	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95
1953663	ReliaPro	DCU1201000	12	1000	2.5mm x 5.5mm F 2	120 @ 60	3.3 x 2.3 x 2.0	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95
174861	ReliaPro	DFU240050	24	500	2.1mm x 5.5mm F 2	120 @ 60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	14.95	13.49	11.95	10.95
174879	ReliaPro	DCU090025	24	500	2.5mm x 5.5mm F 2	120 @ 60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	14.95	13.49	11.95	10.95

More AC-to-DC Wall Adapters listed on pages 90-91 & 93-94