

# AC-DC Regulated Switching Table-Top Power Supplies

| 3 LEVELS OF SAVINGS |              |             |
|---------------------|--------------|-------------|
| NAME BRANDS         | HOUSE BRANDS | SPECIAL BUY |



## AC-to-DC Regulated Switching Table-Top Power Supplies

We are happy to change the power plug on any listed table-top power supply to a connector of your choice (see pg 99) for just \$2.50 ea. Overmolding also available @ \$4.00 ea. A 100 pc. minimum order applies.

2135515



2172771




2099294



2139006



2172789



Female (F)

Female Right Angle

DIN (M)

4-Pin Molex



See page 102 for International Power Cords

| Part No.   | Manufacturer    | Product No.     | Output Volts (VDC)/ Current (A) | Output Connector ID x OD/F = female; M = male; Polarity ◆ | Input VAC@Hz         | Output Power (W) | LED Ind. | Size (L" x W" x H") | Cords* (DC/AC) | Wt. (lbs.) | Agency Approvals             | Pricing |                        |  |
|--|-----------------|-----------------|---------------------------------|---|----------------------|------------------|----------|---------------------|----------------|------------|------------------------------|---------|------------------------|--|
|  |                 |                 |                                 |   |                      |                  |          |                     |                |            |                              | 1       | 10                     |  |
| <b>3-Wire AC Input – Regulated Switching Table-Top – Single Output (Continued)</b> |                 |                 |                                 |   |                      |                  |          |                     |                |            |                              |         | <b>* Web Code: DDZ</b> |  |
| 1940416  | Mean Well       | GS18A12-P1JU    | +12/1.5                         | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 18               | Yes      | 3.7 x 2.1 x 1.4     | 6/6'           | 0.5        | UL/CUL/TUV/CE                | \$13.95 | \$12.95                |  |
| 2213915  | Mean Well       | GSM18B12-P1J    | +12/1.5                         | 2.1mm x 5.5mm F 2   | 80-264@47-63         | 18               | Yes      | 3.1 x 2.1 x 1.3     | 6/1'           | 0.4        | UL/CUL/CE/FCC/TUV/CB         | 12.95   | 11.49                  |  |
| 2135507  | SPC Technology  | SA121A6F-11     | +12/1.6                         | 2.1mm x 5.5mm F 2   | 100-250@47-63        | 19               | No       | 3.2 x 2.2 x 1.9     | 6/2'           | 0.2        | UL/CUL/TUV/CE                | 8.95    | 7.95                   |  |
| 2197601  | Delta           | EADP-24KBB      | +12/2.0                         | 2.1mm x 5.5mm F 2 †                                       | 100-240@50-60        | 24               | No       | 4.7 x 2.0 x 1.2     | 7/2'           | 0.5        | UL/CUL/CE                    | 9.95    | 8.95                   |  |
| 2190047  | Mean Well       | GS25A12-P1J     | +12/2.08                        | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 25               | Yes      | 3.7 x 2.1 x 1.4     | 4/2'           | 0.46       | UL/CUL/TUV/CE                | 11.95   | 10.95                  |  |
| 1940601  | Mean Well       | GS25A12-P1JU    | +12/2.08                        | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 25               | Yes      | 3.7 x 2.1 x 1.4     | 4/6'           | 0.5        | UL/CUL/TUV/CE                | 13.95   | 12.95                  |  |
| 2213991  | Mean Well       | GSM25B12-P1J    | 12/2.08                         | 2.1mm x 5.5mm F 2   | 80-264@47-63         | 25               | Yes      | 3.1 x 2.1 x 1.3     | 6/1'           | 0.5        | UL/CUL/CE/FCC/TUV/CB         | 13.49   | 11.95                  |  |
| 2154978  | ReliaPro        | GQ65120250-E1   | +12/2.5                         | 2.5mm x 5.5mm F 2   | 100-240@50-60        | 30               | No       | 3.6 x 1.9 x 1.3     | 6/2'           | 0.5        | TUV(US)/CE                   | 10.49   | 9.49                   |  |
| 2214070  | Mean Well       | GSM36B12-P1J    | +12/3.0                         | 2.1mm x 5.5mm F 2   | 80-264@47-63         | 36               | Yes      | 3.1 x 2.1 x 1.3     | 6/1'           | 0.5        | UL/CUL/CE/FCC/TUV/CB         | 14.49   | 12.95                  |  |
| 2129158  | Sparkle Power   | FSP040-DGAA1    | +12/3.33                        | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 40               | Yes      | 4.3 x 2.0 x 1.2     | 5/2'           | 0.5        | UL/CUL/TUV/CE                | 20.95   | 18.95                  |  |
| 1952345  | Mean Well       | GS40A12-P1J     | +12/3.34                        | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 40               | Yes      | 4.9 x 2.0 x 1.3     | 4/2'           | 0.7        | UL/CUL/TUV/CE                | 15.95   | 14.49                  |  |
| 2079357  | Mean Well       | GS40A12-P1M     | +12/3.34                        | 2.5mm x 5.5mm F 2   | 90-264@47-63         | 40               | Yes      | 4.9 x 2.0 x 1.3     | 4/2'           | 0.7        | UL/CUL/TUV/CE                | 16.95   | 15.49                  |  |
| 2214150  | Mean Well       | GSM40B12-P1J    | +12/3.34                        | 2.1mm x 5.5mm F 2   | 80-264@47-63         | 40               | Yes      | 1.25 x 1.9 x 4.95   | 3.3/1'         | 0.63       | UL/CUL/CE/FCC/TUV/CB         | 18.95   | 17.49                  |  |
| 1940264  | ReliaPro        | EA1050E         | +12/3.5                         | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 42               | Yes      | 4.7 x 2.4 x 1.4     | 4/2'           | 0.6        | UL/CUL/TUV/CE                | 14.49   | 13.49                  |  |
| 1940272  | ReliaPro        | GQ65-120416-EI  | +12/4.16                        | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 50               | Yes      | 4.5 x 1.9 x 1.4     | 4/2'           | 0.6        | TUV(US)/CE                   | 15.95   | 14.95                  |  |
| 2158485  | Power-One       | 3F42050         | +12/4.2                         | 2.1mm x 5.5mm F 2 †                                       | 100-240@50-60        | 50               | Yes      | 4.7 x 2.4 x 1.4     | 6/6'           | —          | UL/CUL/CE                    | 11.95   | 10.95                  |  |
| 2129609  | Phihong         | PSA65U-120      | +12/5.0                         | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 60               | No       | 5.9 x 2.8 x 1.5     | 3.3/2'         | 1.0        | UL/CUL/CE                    | 14.95   | 13.49                  |  |
| 2172771  | ReliaPro        | EA1050A-120     | +12/5.0                         | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 60               | Yes      | 4.7 x 2.4 x 1.4     | 4/2'           | 0.7        | UL/CUL/TUV/CE                | 15.95   | 14.49                  |  |
| 1952370  | Mean Well       | GS60A12-P1J     | +12/5.0                         | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 60               | Yes      | 4.9 x 1.9 x 1.2     | 4/2'           | 0.7        | UL/CUL/TUV/CE                | 17.95   | 15.95                  |  |
| 2214230  | Mean Well       | GSM60B12-P1J    | +12/5.0                         | 2.1mm x 5.5mm F 2   | 80-264@47-63         | 60               | Yes      | 1.25 x 1.9 x 4.95   | 3.3/1'         | 0.7        | UL/CUL/CE/FCC/TUV/CB         | 21.95   | 19.95                  |  |
| 2099420  | Sparkle Power   | AD060DBAEI-J25R | +12/5.0                         | 2.5mm x 5.5mm F 2 †                                       | 100-240@50-60        | 60               | Yes      | 4.3 x 2.4 x 1.2     | 5/2'           | 0.5        | UL/CUL/TUV/CE                | 27.95   | 24.95                  |  |
| 2078291  | Mean Well       | GS90A12-P1M     | +12/6.67                        | 2.5mm x 5.5mm F 2   | 100-240@50-60        | 80               | Yes      | 5.7 x 2.3 x 1.3     | 4/2'           | 0.9        | UL/CUL/TUV/CE                | 28.95   | 25.95                  |  |
| 2210466  | Mean Well       | GSM90B12-P1M    | +12/6.67                        | 2.5mm x 5.5mm F 2   | 80-264@47-63         | 80               | Yes      | 5.71 x 2.36 x 1.26  | 3.3/1'         | 0.99       | UL/CUL/CE/FCC/TUV            | 31.95   | 28.95                  |  |
| 221429   | Mean Well       | U65S105-P2JU    | +12/6.7                         | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 80               | Yes      | 6.6 x 3.1 x 1.8     | 6/6'           | 2.0        | UL/CUL/TUV/CE                | 41.95   | 38.95                  |  |
| 2129211  | Mean Well       | GS120A12-R7B    | +12/8.5                         | 4-pin DIN M   | 85-264@47-63         | 102              | Yes      | 6.6 x 2.6 x 1.4     | 4/2'           | 1.4        | UL/CUL/TUV/CE                | 42.95   | 38.95                  |  |
| 2214281  | Mean Well       | GSM120B12-R7B   | +12/8.5                         | 4-pin DIN   | 80-264@113-370       | 102              | Yes      | 6.6 x 2.7 x 1.4     | 3.3/1'         | 1.3        | UL/CUL/CE/FCC/TUV/CB         | 49.95   | 44.95                  |  |
| 2205165  | ReliaPro        | EA11011H-120    | +12/10                          | 4-pin DIN M   | 100-240@47-63        | 120              | Yes      | 5.4 x 2.3 x 1.3     | 4/2'           | 2.4        | UL/CUL/CB/CE                 | 39.95   | 36.95                  |  |
| 2122183  | Mean Well       | GS160A12-R7B    | +12/11.5                        | 4-pin DIN M   | 85-264@47-63         | 138              | Yes      | 6.9 x 2.8 x 1.4     | 4'             | 0.94       | UL/TUV/BSMI/CCC              | 50.95   | 45.95                  |  |
| 2099294  | Mean Well       | GS220A12-R7B    | +12/15                          | 4-pin DIN M   | 90-264/127-370@47-63 | 180              | Yes      | 8.3 x 3.4 x 1.8     | 3.3/2'         | 1.0        | UL/CUL/TUV/CE                | 74.95   | 67.95                  |  |
| 2139006  | ENG Electric    | 3G-301DN13      | +13.5/2.2                       | 4-pin Molex   | 100-240@50-60        | 30               | No       | 4.6 x 1.9 x 1.2     | 2'6/5'         | 0.8        | UL/CUL                       | 7.95    | 6.95                   |  |
| 1940432  | Mean Well       | GS18A15-P1J     | +15/1.2                         | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 18               | Yes      | 3.7 x 2.1 x 1.4     | 6/2'           | 0.5        | UL/CUL/TUV/CE                | 10.95   | 9.95                   |  |
| 1940619  | Mean Well       | GS25A15-P1J     | +15/1.66                        | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 25               | Yes      | 3.7 x 2.1 x 1.4     | 6/2'           | 0.5        | UL/CUL/TUV/CE                | 11.95   | 10.95                  |  |
| 2202554  | Phihong         | PSA30U-150      | +15/2.0                         | 2.1mm x 5.5mm F 2 †                                       | 100-240@47-63        | 30               | No       | 4.4 x 2.4 x 1.4     | 6/2'           | 0.5        | UL/TUV/CSA                   | 14.95   | 13.49                  |  |
| 221577   | Mean Well       | GS40A15-P1J     | +15/2.67                        | 2.1mm x 5.5mm F 2   | 90-264@50-60         | 40               | Yes      | 4.9 x 2.0 x 1.3     | 6/2'           | 0.8        | UL/CUL/TUV/CE                | 15.95   | 14.49                  |  |
| 2171559  | Mean Well       | GS40A15-P1JU    | +15/2.67                        | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 40               | Yes      | 4.9 x 2.0 x 1.2     | 3.3/6'         | 0.6        | UL/CUL/TUV/CE                | 17.95   | 15.49                  |  |
| 1954295  | Mean Well       | GS60A15-P1J     | +15/4.0                         | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 60               | Yes      | 4.9 x 2.0 x 1.2     | 4/2'           | 0.7        | UL/CUL/TUV/CE                | 17.95   | 15.95                  |  |
| 2078320  | Mean Well       | GS90A15-P1M     | +15/6.0                         | 2.5mm x 5.5mm F 2   | 100-240@50-60        | 90               | Yes      | 5.7 x 2.3 x 1.3     | 3.3/2'         | 0.8        | UL/CUL/TUV/CE                | 24.95   | 22.95                  |  |
| 2210474  | Mean Well       | GSM90B15-P1M    | +15/6.0                         | 2.5mm x 5.5mm F 2   | 80-264@47-63         | 90               | Yes      | 5.71 x 2.36 x 1.26  | 3.3/1'         | 0.99       | UL/CUL/CE/FCC/TUV            | 31.95   | 28.95                  |  |
| 2100785  | Mean Well       | GS220A15-R7B    | +15/13.4                        | 4-pin DIN M   | 90-264@47-63         | 201              | Yes      | 8.3 x 3.3 x 1.8     | 3'             | 0.94       | CE/CUL/TUV/UL                | 74.95   | 67.95                  |  |
| 2145107  | SYN Electronics | SYS-1097-4018   | +18/2.2                         | 2.1mm x 5.5mm F 2   | 100-240@47-63        | 40               | Yes      | 4.7 x 2.4 x 1.3     | 4/2'           | 0.7        | UL/TUV/CE                    | 10.95   | 9.95                   |  |
| 2102756  | Mean Well       | GS40A18-P1J     | +18/2.22                        | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 39.6             | Yes      | 5 x 2 x 1.3         | 6/2'           | 0.6        | UL/CUL/TUV/BSMI/CCC/BSR/CCCE | 15.95   | 14.49                  |  |
| 2154951  | Mean Well       | GS60A18-P1JU    | +18/3.33                        | 2.1mm x 5.5mm F 2   | 90-264@50-60         | 60               | Yes      | 4.9 x 2.0 x 1.2     | 6/6'           | 0.8        | UL/CUL/TUV/CE                | 19.95   | 17.95                  |  |
| 2101841  | Mean Well       | GS90A19-P1M     | +19/4.74                        | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 90               | Yes      | 5.7 x 2.3 x 1.3     | 4/2'           | 0.94       | UL/TUV/BSMI/CCC              | 28.95   | 25.95                  |  |
| 1940459  | Mean Well       | GS18A24-P1J     | +24/0.75                        | 2.1mm x 5.5mm F 2   | 100-240@50-60        | 18               | Yes      | 3.7 x 2.1 x 1.4     | 6/2'           | 0.5        | UL/CUL/TUV/CE                | 11.95   | 10.95                  |  |
| 2213940  | Mean Well       | GSM18B24-P1J    | +24/0.75                        | 2.1mm x 5.5mm F 2   | 80-264@47-63         | 18               | Yes      | 3.1 x 2.1 x 1.3     | 6'             | 0.4        | UL/CUL/CE/FCC/TUV/CB         | 12.95   | 11.49                  |  |
| 2190346  | Mean Well       | GS25A24-P1J     | +24/1.04                        | 2.1mm x 5.5mm F 2   | 90-264@47-63         | 25               | Yes      | 3.7 x 2.1 x 1.4     | 6/1'           | 0.46       | UL/CUL/TUV/CE                | 11.95   | 10.95                  |  |

\* See accessory table-top power cord chart on page 94 when AC cord needed; refer to 1, 2 or 3 in "Cord (DC/AC)" column above for correct power cord

\*\* Medical (2-wire)

† Right angle  
 cec