

Flat Ribbon & Ethernet Network Cable

3 LEVELS OF SAVINGS		
NAME BRANDS	HOUSE BRANDS	SPECIAL BUY

JAMECO ValuePro 28 AWG (7 x 36) Gray and Multicolor Flat Ribbon Cable

See page 56 for IDC Connectors

Gray Cable

*Web Code: WBX

- Insulation: polyvinyl chloride (PVC)
- Single edge red stripe for pin 1 orientation
- Center spacing: 0.05"



Part No.	Cross Ref. No.	Conductors	Length	1	5	25
643794	171-10-10	10	10'	\$3.95	\$3.55	\$3.19
643807	171-10-25	10	25'	6.95	5.95	4.95
643815	171-10-100	10	100' reel	21.95	19.95	17.95
643831	171-16-10	16	10'	4.95	4.49	3.95
643840	171-16-25	16	25'	10.95	9.95	8.95
643858	171-16-100	16	100' reel	34.95	31.49	27.95
643874	171-20-10	20	10'	5.95	5.49	4.95
643891	171-20-100	20	100' reel	44.95	39.95	35.95
643911	171-25-10	25	10'	7.95	6.95	5.95
643938	171-25-100	25	100' reel	49.95	46.95	43.95
643962	171-26-10	26	10'	8.49	7.49	6.75
643989	171-26-100	26	100' reel	59.95	53.95	48.95
644033	171-34-10	34	10'	9.95	8.95	7.95
644076	171-37-10	37	10'	10.95	9.95	8.95
644092	171-37-100	37	100' reel	59.95	53.95	49.95
644121	171-40-25	40	25'	29.95	26.95	23.95
644130	171-40-100	40	100' reel	79.95	69.95	62.95
644172	171-50-100	50	100' reel	89.95	79.95	74.95
644199	171-60-10	60	10'	9.95	8.95	7.95

Multicolor Cable

- Standard 10-color repeat sequence
- Voltage rating: 300V
- Center spacing: 0.05"
- Temperature rating: -20°C to +80°C
- Stranded copper wire



*Web Code: WCF

Part No.	Cross Ref. No.	Conductors	Length	1	5	25
639672	28RC10-10	10	10'	\$5.95	\$5.49	\$4.95
643508	28RC10-25	10	25'	12.95	11.49	10.49
643516	28RC10-100	10	100' reel	39.95	35.95	32.49
643532	28RC16-10	16	10'	7.95	6.95	6.25
643559	28RC16-100	16	100' reel	59.95	53.95	48.95
643575	28RC20-10	20	10'	10.95	9.95	8.95
643583	28RC20-25	20	25'	21.95	19.95	17.95
643591	28RC20-100	20	100'	74.95	67.49	59.95
643639	28RC25-100	25	100' reel	89.95	79.95	74.95
643698	28RC40-10	40	10'	26.95	23.95	21.95

JAMECO ValuePro Ethernet Network Cable Assemblies

Category 5e

- 8P8C
- 4 pair
- Unshielded Twisted Pair (UTP)
- 350 MHz
- "Snagless" boot
- 24 AWG (7 x 43) stranded
- T568B color coded for easy wire tracing

Part No.	Length	Color	1	10	100	Part No.	Length	Color	1	10	100
168292	3 ft.	Gray	\$1.49	\$1.25	\$0.99	1945381	5 ft.	Blue	\$1.95	\$1.75	\$1.65
2258494	7 ft.	Gray	2.75	2.49	2.25	2138708	7 ft.*	Blue	.99	.89	.75
201697	3 ft.	Black	1.75	1.59	1.39	201742	7 ft.	Blue	2.75	2.49	2.25
201700	7 ft.	Black	2.75	2.49	2.25	201751	15 ft.	Blue	3.95	3.55	2.95
201718	15 ft.	Black	3.95	3.55	2.95	201814	3 ft.	Yellow	1.75	1.59	1.39
201726	25 ft.	Black	6.49	5.95	5.49	201822	7 ft.	Yellow	2.49	2.25	1.95
201734	3 ft.	Blue	1.75	1.59	1.39						

Category 6

- Gold over nickel contacts
- 550 MHz
- With RJ45 plugs and molded strain reliefs
- Assembled using ETL verified 24AWG stranded cable
- Exceeds performance levels as specified in TIA/EIA 568B.2-1 category 6

*Web Code: BBK

Part No.	Length	Color	1	10	100
219707	3 ft.	Gray	\$2.25	\$1.95	\$1.75
219918	7 ft.	Red	3.25	2.95	2.49

JAMECO ValuePro Cat 5e Network Crossover Cable

*Web Code: CAE

Category 5e - 350MHz

- Connect 2 PCs without a hub
- 24AWG (7 x 43) stranded
- UTP
- Strain relief RJ45 connectors
- 4-pair
- 8P8C

Part No.	Length	Color	1	10	100
302041	7 ft.	Gray	\$2.95	\$2.59	\$2.29

5-Port Industrial Ethernet Switch

- Auto MDI/MDI-X crossover for plug-and-play
- IEEE 802.3, 802.3u, 802.3x
- DIN rail mountable
- Supports 10/100Mbps auto negotiatic..
- LED indicators for power, 10/100M, Link/Act

*Web Code: CAK

Part No.	Mfr. Part No.	1	5
2129019	NS-205	\$99.95	\$89.95

JAMECO ValuePro 10-Conductor Flat Ribbon Cable - Gray

.100" (2.54mm) - 24AWG

*Web Code: WBX

- Capacitance: 31pF/m
- Insulation resis.: 100MΩ
- Temperature rating: 105°C
- Insulation material: 7mm polyvinyl chloride (PVC) gray
- 10' roll



Part No.	Cross Ref. No.	Conductor	Length	1	5	25
363813	H24G-10-10	10	10'	\$9.95	\$8.95	\$7.95

EDUP electric imp WiFi Modules and Adapters

Add wireless connectivity to your computer or electronics project.

- 2.4GHz 802.11 b/g/n
- WEP/WPA security
- FCC approved

2189610

2223953

Part No.	Manufacturer	Description	Price
2223953	EDUP	USB WiFi adapter, plug-n-play, RTL8188CU	\$12.95
2189610	Electric Imp	ImpCard WiFi module in SD card form factor	24.95
2189636	Electric Imp	April breakout board (SD socket) required for ImpCard	11.95

JAMECO ValuePro Bulk Category 5e Network Cable



*Web Code: KCG



Blue



Gray

24 AWG UTP Category 5e Enhanced - 350MHz (Non-Plenum)

Part No.	Cross Ref. No.	Length	Color	Description	1	5
644615	10X5-804TH-100	100'	Blue	Stranded	\$16.95	\$15.95
644623	10X5-804TH-1000	1000'	Blue	Stranded	129.95	119.95
644594	10X5-801TH-1000	1000'	Gray	Stranded	129.95	119.95

ETHERNET NETWORK INSTALLER TOOLS

Must have tools for any network technician. Whether you're making new cable runs or are testing or tracing lines, these are the tools you need.

174676: Ratcheting modular cut/crimp/strip tool

- For RJ11 (6P) and RJ45 (8P)
- Includes cutting and stripping blade

2130749: LAN cable tester

- Networks: RJ45, 10BaseT, Token Ring, RJ11/12 cables
- Tests: Continuity, open, shorted and cross-wired pairs
- Max cable run testing: 984 feet



2130749

Part No.	Mfr.	Mfr. Part No.	Price
174676	BenchPro	TTK-070	\$27.95
2130749	Velleman	VTLAN4	17.95