

# Enclosed Switching AC-to-DC Power Supplies

3 LEVELS OF SAVINGS  
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



## Enclosed Switching AC-to-DC Power Supplies

- 100% full-load burn-in test
- Wide AC input range
- Manufacturer warranty varies

Complete specifications available online



SP-150



HRPG-150



HRP-300



RSP-1500



NES-75



SE-600

\* 2.5-4.2V Web Code: ENT

\* 5-9V Web Code: ENF

\* 12-13.8V Web Code: ENW

\* 15-20V Web Code: ENI

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%)§	PFC	Certification	Pricing		
			Voltage @ Current (min-max)	Power								1	10	
<b>Single Output</b>														
2106685	Mean Well	RS-15-3.3	+3.3V @ 0-3A	9.9W	2.5 x 2.0 x 1.1	80	2.0	0.5	72	—	UL/CUL/TUV/CE/CB	\$7.95	\$7.15	
1919043	Mean Well	RS-15-5	+5V @ 0-3A	15W	2.5 x 2.0 x 1.1	80	1.5	0.5	77	—	UL/CUL/TUV/CE/CB	7.95	7.15	
323282	Mean Well	RS-25-5	+5V @ 0-5A	25W	3.1 x 2.0 x 1.1	80	1.0	0.5	77	—	UL/CUL/TUV/CE/CB	10.25	8.95	
323329	Mean Well	RS-35-5	+5V @ 0-7A	35W	3.9 x 3.2 x 1.4	80	1	0.5	77	—	UL/CUL/TUV/CE	12.95	11.95	
323388	Mean Well	RS-50-5	+5V @ 0-10A	50W	3.9 x 3.8 x 1.4	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	14.49	12.95	
194791	Mean Well	SP-100-5	+5V @ 0-20A	100W	7.0 x 3.9 x 1.8	100	1.0	0.5	76	✓	UL/CUL/TUV/CE/CB	38.95	31.95	
323821	Mean Well	RS-150-5	+5V @ 0-26A	130W	7.8 x 3.9 x 1.5	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	23.95	20.95	
123394	Mean Well	S-150-5	+5V @ 0-30A	150W	7.0 x 4.3 x 2.0	150	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	34.95	31.95	
201912	Mean Well	SP-150-5	+5V @ 0-30A	150W	7.0 x 3.9 x 2.0	100	1.0	0.5	75	✓	UL/CUL/TUV/CE/CB	42.95	37.95	
202042	Mean Well	SP-200-5	+5V @ 0-40A	200W	7.0 x 3.9 x 2.0	100	1.0	0.5	71	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
244735	Mean Well	SP-320-5	+5V @ 0-55A at 230VAC; 0-44A at 115VAC	275W	8.5 x 4.5 x 2.0	150	1.0	0.5	79	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
2172068	Mean Well	RSP-320-5	+5V @ 0-60A	300W	8.5 x 4.5 x 1.2	150	1.0	0.5	85	✓	UL/CUL/TUV/CE/CB	47.95	40.95	
2219794	Mean Well	LRS-350-5	+5V @ 0-60A	300W	8.5 x 4.5 x 1.2	150	2	0.5	83.5	—	UL/CUL	34.95	29.95	
2149562	Mean Well	SE-350-5	+5V @ 0-60A	300W	8.5 x 4.5 x 2.0	150	2.0	0.5	78	—	UL/CUL	43.95	38.95	
374002	Mean Well	SE-600-5	+5V @ 0-100A	500W	9.7 x 5.0 x 2.5	150	2.0	0.5	78	—	UL/CUL	75.95	66.95	
394215	Mean Well	SP-320-7.5	+7.5V @ 0-40A	300W	8.5 x 4.5 x 2.0	150	1.0	0.5	83	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
1919051	Mean Well	RS-15-12	+12V @ 0-1.3A	15.6W	2.5 x 2.0 x 1.1	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	7.95	7.15	
323300	Mean Well	RS-25-12	+12V @ 0-2.1A	25.2W	3.0 x 2.0 x 1.1	120	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	10.25	8.95	
123255	Mean Well	S-25-12	+12V @ 0-2.1A	25.2W	3.9 x 3.8 x 1.4	100	0.5	0.5	76	—	UL/TUV/CE	18.95	16.95	
323337	Mean Well	RS-35-12	+12V @ 0-3A	36W	3.9 x 3.2 x 1.4	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	12.49	10.49	
323396	Mean Well	RS-50-12	+12V @ 0-4.2A	50.4W	3.9 x 3.8 x 1.4	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	13.95	11.95	
123335	Mean Well	S-60-12	+12V @ 0-5A	60W	6.3 x 3.8 x 1.5	120	0.5	0.5	76	—	UL/CUL/TUV/CE/CB	24.95	22.49	
323599	Mean Well	RS-75-12	+12V @ 0-6A	72W	5.1 x 3.9 x 1.5	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	16.49	14.25	
2105017	Mean Well	NES-100-12	+12V @ 0-8.5A	102W	6.3 x 3.8 x 1.5	120	0.5	0.5	83	—	UL/CUL/CE/CB	20.95	18.95	
123386	Mean Well	S-100F-12	+12V @ 0-8.5A	102W	7.8 x 3.9 x 1.5	125	0.5	0.5	80	—	UL/TUV/CE/CB	27.95	25.95	
323716	Mean Well	RS-100-12	+12V @ 0-8.5A	102W	6.3 x 3.8 x 1.5	120	0.5	0.5	81	✓	UL/CUL/TUV/CE/CB	22.95	20.95	
194803	Mean Well	SP-100-12	+12V @ 0-8.5A	102W	7.0 x 3.9 x 1.8	100	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	38.95	31.95	
2257723	Mean Well	LRS-150-12	+12V @ 0-12.5A	150W	6.0 x 3.8 x 1.2	150	0.5	0.5	87.5	—	UL/CUL/TUV/CE	19.95	17.49	
2257782	Mean Well	LRS-150F-12	+12V @ 0-12.5A	150W	6.3 x 3.8 x 1.2	150	0.5	0.5	87.5	—	UL/CUL/TUV/CE/CB	22.49	18.95	
323839	Mean Well	RS-150-12	+12V @ 0-12.5A	150W	7.8 x 3.9 x 1.5	120	0.5	0.5	83	—	UL/CUL/TUV/CE/CB	23.95	20.95	
123423	Mean Well	S-150-12	+12V @ 0-12.5A	150W	7.0 x 4.3 x 2.0	180	0.3	0.3	82	—	UL/CUL/TUV/CE/CB	36.95	32.95	
173421	Mean Well	SP-150-12	+12V @ 0-12.5A	150W	7.0 x 3.9 x 2.0	100	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	42.95	37.95	
194774	Mean Well	SP-200-12	+12V @ 0-16.7A	200.4W	7.0 x 3.9 x 2.0	100	0.5	0.5	79	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
2219727	Mean Well	LRS-200-12	+12V @ 0-17A	204W	8.5 x 4.5 x 1.2	150	1	0.5	87.5	—	UL/CUL	26.95	22.49	
2101497	Mean Well	SP-240-12	+12V @ 0-20A	240W	7.5 x 3.7 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	49.95	44.95	
244743	Mean Well	SP-320-12	+12V @ 0-25A at 230VAC; 0-20A @ 115VAC	300W	8.5 x 4.5 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
2102203	Mean Well	HRP-300-12	+12V @ 0-27A	324W	7.8 x 4.1 x 1.6	120	0.5	0.3	88	✓	UL/CUL/TUV/CE/CB	71.95	60.95	
2219807	Mean Well	LRS-350-12	+12V @ 0-29A	348W	8.5 x 4.5 x 1.2	150	1.0	0.5	85	—	UL/CUL	32.95	27.95	
2149503	Mean Well	SE-350-12	+12V @ 0-29A	348W	8.5 x 4.5 x 2.0	150	1.0	0.5	83	—	UL/CUL	43.95	38.95	
2094928	Mean Well	SE-450-12	+12V @ 0-37.5A	450W	8.9 x 4.9 x 2.0	200	1.0	0.5	83	✓	UL/CUL	61.95	54.95	
374011	Mean Well	SE-600-12	+12V @ 0-50A	600W	9.7 x 5.0 x 2.5	150	0.5	0.5	83	—	UL/CUL	75.95	66.95	
374214	Mean Well	PSP-600-12	+12V @ 0-50A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	84	✓	UL/CUL/TUV/CE/CB	125.95	111.95	
2101542	Mean Well	SE-1000-12	+12V @ 0-83.3A	999.6W	10.9 x 5.0 x 2.5	150	0.5	0.5	85	—	UL/CUL	165.95	146.95	
694911	Mean Well	RSP-1500-12	+12V @ 0-125A	1500W	10.9 x 5.0 x 3.3	150	0.5	0.5	87	✓	EN/TUV/UL	303.95	270.95	
202025	Mean Well	S-150-13.5	+13.5V @ 0-11.2A	151.2W	7.0 x 4.3 x 2.0	180	0.3	0.3	77	—	UL/CUL/TUV/CE/CB	26.95	24.95	
212410	Mean Well	SP-200-13.5	+13.5V @ 0-14.9A	201.1W	7.0 x 3.9 x 2.0	100	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
693599	Mean Well	SP-320-13.5	+13.5V @ 0-22A	297W	8.5 x 4.5 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
2106079	Mean Well	PSP-600-13.5	+13.5V @ 0-44.5A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	85	✓	UL/CUL/TUV/CE/CB	125.95	111.95	
2105439	Mean Well	AD-155A†	+13.8V @ 0-11.5A or 13.3V @ 0-0.5A	145W	7.8 x 4.3 x 2.0	150	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	46.95	42.95	
323302	Mean Well	RS-25-15	+15V @ 0-1.7A	25.5W	3.0 x 2.0 x 1.1	120	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	10.25	8.95	
323345	Mean Well	RS-35-15	+15V @ 0-2.4A	36W	3.9 x 3.2 x 1.4	120	0.5	0.5	83	—	UL/CUL/TUV/CE/CB	12.49	10.95	
323602	Mean Well	RS-75-15	+15V @ 0-5A	75W	5.1 x 3.9 x 1.5	120	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	16.49	14.25	

\* Applies only to primary output † UPS function § Efficiency