

Enclosed Switching AC-to-DC Power Supplies

Jameco carries the full line of Mean Well Power products. For additional products visit www.Jameco.com/meanwellproducts



Enclosed Switching AC-to-DC Power Supplies (Continued)


• 100% full-load burn-in test • Wide AC input range • Manufacturer warranty varies



RS-25

* 15-20V Web Code: ENI

* 24-30V Web Code: ENE



Part No.	Manufacturer	Mfr. Part No.	Output		Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%) §	PFC	Certification	Pricing		
			Voltage @ Current (min-max)	Power								1	10	
Single Output (Continued)														
323724	Mean Well	RS-100-15	+15V @ 0-7A	105W	6.3 x 3.8 x 1.5	120	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	\$22.95	\$19.95	
323847	Mean Well	RS-150-15	+15V @ 0-10A	150W	7.8 x 3.9 x 1.5	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	23.95	20.95	
123432	Mean Well	S-150-15	+15V @ 0-10A	150W	7.0 x 4.3 x 2.0	180	0.3	0.3	85	—	UL/CUL/TUV/CE/CB	36.95	32.95	
173412	Mean Well	SP-150-15	+15V @ 0-10A	150W	7.0 x 3.9 x 2.0	100	0.5	0.5	86.5	✓	UL/CUL/TUV/CE/CB	42.95	37.95	
202060	Mean Well	SP-200-15	+15V @ 0-13.4A	201W	7.0 x 3.9 x 2.0	100	0.5	0.5	81	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
693610	Mean Well	SP-320-15	+15V @ 0-20A	300W	8.5 x 4.5 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
2219815	Mean Well	LRS-350-15	+15V @ 0-23.2A	348W	8.5 x 4.5 x 1.2	150	0.5	0.5	86	—	UL/CUL	32.95	27.95	
291522	Mean Well	SE-600-15	+15V @ 0-40A	600W	9.7 x 5.0 x 2.5	150	0.5	0.5	84	—	UL/CUL	75.95	66.95	
694920	Mean Well	RSP-1500-15	+15V @ 0-100A	1500W	10.9 x 5.0 x 3.3	150	0.5	0.5	87	✓	UL/CUL/TUV/CE/CB	303.95	270.95	
1919078	Mean Well	RS-15-24	+24V @ 0-0.625A	15W	2.5 x 2.0 x 1.1	200	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	7.95	7.15	
323311	Mean Well	RS-25-24	+24V @ 0-1.1A	26.4W	3.0 x 2.0 x 1.1	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	10.25	8.95	
123272	Mean Well	S-25-24	+24V @ 0-1.1A	26.4W	3.9 x 3.8 x 1.4	100	0.5	0.5	80	—	UL/TUV/CE	18.95	16.95	
323353	Mean Well	RS-35-24	+24V @ 0-1.5A	36W	3.9 x 3.2 x 1.4	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	11.49	10.49	
123319	Mean Well	S-40-24	+24V @ 0-1.8A	43W	5.1 x 3.9 x 1.5	100	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	19.95	18.95	
323417	Mean Well	RS-50-24	+24V @ 0-2.2A	52.8W	3.9 x 3.8 x 1.4	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	14.49	12.95	
123352	Mean Well	S-60-24	+24V @ 0-2.5A	60W	6.3 x 3.8 x 1.5	150	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	24.95	22.49	
323620	Mean Well	RS-75-24	+24V @ 0-3.2A	76.8W	5.1 x 3.9 x 1.5	120	0.5	0.5	85	—	UL/CUL/TUV/CE/CB	16.49	14.25	
323732	Mean Well	RS-100-24	+24V @ 0-4.5A	108W	6.3 x 3.8 x 1.5	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	23.95	21.95	
201971	Mean Well	S-100F-24	+24V @ 0-4.5A	108W	7.8 x 3.9 x 1.5	150	0.5	0.5	83	—	UL/TUV/CE/CB	29.95	27.95	
173404	Mean Well	SP-150-24	+24V @ 0-6.25A	150W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	42.95	37.95	
2257740	Mean Well	LRS-150-24	+24V @ 0-6.5A	156W	6.0 x 3.8 x 1.2	200	0.5	0.5	89	—	UL/CUL/TUV/CE	18.95	15.95	
2257803	Mean Well	LRS-150F-24	+24V @ 0-6.5A	156W	6.3 x 3.8 x 1.2	200	0.5	0.5	89	—	UL/CUL/TUV/CE/CB	21.49	17.95	
323855	Mean Well	RS-150-24	+24V @ 0-6.5A	156W	7.8 x 3.9 x 1.5	120	0.5	0.5	86	—	UL/CUL/TUV/CE/CB	24.95	22.49	
123450	Mean Well	S-150-24	+24V @ 0-6.5A	156W	7.0 x 4.3 x 2.0	240	0.2	0.2	85	—	UL/CUL/TUV/CE/CB	36.95	32.95	
2094864	Mean Well	HRPG-150-24	+24V @ 0-6.5A	156W	6.3 x 3.8 x 1.5	150	0.5	0.3	87	✓	UL/CUL/TUV/CE/CB	51.95	45.95	
194782	Mean Well	SP-200-24	+24V @ 0-8.4A	201.6W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
2101518	Mean Well	SP-240-24	+24V @ 0-10A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	49.95	44.95	
196657	Mean Well	S-320-24	+24V @ 0-12.5A	300W	8.5 x 4.5 x 2.0	150	0.5	0.5	86	—	UL/CUL	64.95	59.95	
244752	Mean Well	SP-320-24	+24V @ 0-13A	312W	8.5 x 4.5 x 2.0	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
2102220	Mean Well	HRP-300-24	+24V @ 0-14A	336W	7.7 x 4.1 x 1.6	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	71.95	60.95	
2094881	Mean Well	HRPG-300-24	+24V @ 0-14A	336W	7.8 x 4.1 x 1.6	150	0.5	0.3	87	✓	UL/CUL/TUV/CE/CB	81.95	72.95	
2219823	Mean Well	LRS-350-24	+24V @ 0-14.6A	350.4W	8.5 x 4.5 x 1.2	150	0.5	0.5	88	—	UL/CUL	31.95	26.95	
2146564	Mean Well	SE-350-24	+24V @ 0-14.6A	350.4W	8.5 x 4.5 x 2.0	150	0.5	0.5	87	—	UL/CUL	43.95	38.95	
2101606	Mean Well	SE-450-24	+24V @ 0-18.8A	451.2W	8.9 x 4.9 x 2.0	200	0.5	0.2	86	—	UL/CUL	61.95	54.95	
2122335	Mean Well	HRP-450-24	+24V @ 0-18.8A	451.2W	8.6 x 4.1 x 1.6	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	110.95	93.95	
301322	Mean Well	SP-480-24	+24V @ 0-20A	480W	10.9 x 5.0 x 1.7	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	136.95	115.95	
147054	Mean Well	SP-500-24	+24V @ 0-20A	480W	6.7 x 4.7 x 3.7	240	0.5	0.5	85.5	✓	UL/CUL/TUV/CE/CB	152.95	134.95	
2197994	Mean Well	RSP-500-24	+24V @ 0-21A	504W	9.1 x 5.0 x 1.6	150	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	88.95	77.95	
295902	Mean Well	SE-600-24	+24V @ 0-25A	600W	9.7 x 5.0 x 2.5	150	0.5	0.5	87	—	UL/CUL	75.95	66.95	
374231	Mean Well	PSP-600-24	+24V @ 0-25A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	86	✓	UL/CUL/TUV/CE/CB	125.95	111.95	
2100961	Mean Well	HRP-600-24	+24V @ 0-27A	648W	8.6 x 4.1 x 2.5	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	114.95	101.95	
2204787	Mean Well	MSP-600-24**	+24V @ 0-27A	648W	8.6 x 4.1 x 2.5	150	0.5	0.2	88	✓	UL/CUL/CB/CE	153.95	129.95	
2172121	Mean Well	RSP-750-24	+24V @ 0-31.3A	751.2W	9.8 x 5.0 x 1.6	150	0.5	0.5	90.5	✓	EM/TUV/UL	168.95	142.95	
320048	Mean Well	SP-750-24	+24V @ 0-31.3A	751.2W	10.9 x 5.0 x 2.5	120	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	204.95	179.95	
1585717	Mean Well	RSP-1000-24	+24V @ 0-40A	960W	11.6 x 5.0 x 1.6	150	0.5	0.5	88	✓	UL/CUL/TUV/CE/CB	206.95	175.95	
2101569	Mean Well	SE-1000-24	+24V @ 0-41.7A	1000.8W	10.9 x 5.0 x 2.5	200	0.5	0.5	88	—	UL/CUL	165.95	146.95	
694938	Mean Well	RSP-1500-24	+24V @ 0-63A	1512W	10.9 x 5.0 x 3.3	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	303.95	270.95	
693513	Mean Well	SP-150-27	+27V @ 0-5.6A	151.2W	7.8 x 3.9 x 2.0	15	0.5	0.5	84	—	UL/CUL/CE/CB/PFC	42.95	37.95	
693548	Mean Well	SP-200-27	+27V @ 0-7.5A	202.5W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
693628	Mean Well	SP-320-27	+27V @ 0-11.7A	315.9W	8.5 x 4.5 x 2.0	200	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	62.95	47.95	
2149520	Mean Well	SE-350-27	+27V @ 0-13A	351W	8.5 x 4.5 x 3.3	200	0.5	0.5	88	—	UL/CUL	43.95	38.95	
190706	Mean Well	SP-500-27	+27V @ 0-18A	486W	6.7 x 4.7 x 3.7	200	0.5	0.5	86.5	✓	UL/CUL/TUV/CE/CB	152.95	134.95	
295911	Mean Well	SE-600-27	+27V @ 0-22.2A	599.4W	9.7 x 5.0 x 2.5	150	0.5	0.5	87	—	UL/CUL	75.95	66.95	
374257	Mean Well	PSP-600-27	+27V @ 0-22.2A	599.4W	6.7 x 4.7 x 3.7	240	0.5	0.5	86	✓	UL/CUL/TUV/CE/CB	125.95	111.95	
1585709	Mean Well	RSP-1000-27	+27V @ 0-37.0A	999W	11.6 x 5.0 x 1.6	150	0.5	0.5	88	✓	UL/CUL/TUV/CE/CB	206.95	175.95	
694946	Mean Well	RSP-1500-27	+27V @ 0-56A	1512W	10.9 x 5.0 x 3.3	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	303.95	270.95	
2146118	Mean Well	AD-155B	+27.6V @ 0-5.5A or 27.1V @ 0-0.5A	152W	7.8 x 4.3 x 2.0	150	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	46.95	42.95	
2102473	Mean Well	SP-240-30	+30V @ 0-8A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	49.95	44.95	

* Applies only to primary output

** Medical rated

§ Efficiency

Continued on next page

* For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com