

# Enclosed Switching AC-to-DC Power Supplies

3 LEVELS OF SAVINGS  
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



## Enclosed Switching AC-to-DC Power Supplies (Continued)

• 100% full-load burn-in test • Wide AC input range • Manufacturer warranty varies



SP-200



\* 36-54V Web Code: ENH

\* Multiple Output WC: ENM

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%)§	PFC	Certification	Pricing	
			Voltage @ Current (min-max)	Power								1	10
<b>Single Output (Continued)</b>													
2102730	Mean Well	SP-320-36	+36V @ 0-8.8A	316.8W	8.5 x 4.5 x 2.0	220	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	\$62.95	\$47.95
693206	Mean Well	RS-25-48	+48V @ 0-0.57A	27.4W	3.1 x 2.0 x 1.1	200	0.5	0.5	85	—	UL/CUL/TUV/CE/CB	10.25	8.95
693290	Mean Well	RS-100-48	+48V @ 0-2.3A	110.4W	6.3 x 3.8 x 1.5	200	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	23.95	21.95
201930	Mean Well	SP-150-48	+48V @ 0-3.2A	153.6W	7.0 x 3.9 x 2.0	250	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	42.95	37.95
323863	Mean Well	RS-150-48	+48V @ 0-3.3A	158.4W	7.8 x 3.9 x 1.5	200	0.5	0.5	87	—	UL/CUL/TUV/CE/CB	24.95	22.49
202068	Mean Well	SP-200-48	+48V @ 0-4.2A	201.6W	7.0 x 3.9 x 2.0	250	0.5	0.5	84	✓	UL/CUL/TUV/CE/CB	49.95	42.95
2102481	Mean Well	SP-240-48	+48V @ 0-5A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	49.95	42.95
2229466	Arndt	SP-300-48	+48V @ 0-6.25A	300W	8.1 x 4.5 x 2.0	240	0.5	0.2	85	✓	UL/CUL/TUV/CE	39.95	35.95
244770	Mean Well	SP-320-48	+48V @ 0-6.7A	321.6W	8.5 x 4.5 x 2.0	240	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	62.95	47.95
2219840	Mean Well	LRS-350-48	+48V @ 0-7.3A	350W	8.5 x 4.5 x 1.2	200	0.5	0.5	89	—	UL/CUL	32.95	27.95
2149554	Mean Well	SE-350-48	+48V @ 0-7.3A	350W	8.5 x 4.5 x 2.0	240	0.5	0.5	87.5	—	UL/CUL	43.95	38.95
2105164	Mean Well	SE-450-48	+48V @ 0-9.4A	451.2W	8.9 x 4.9 x 2.0	200	0.5	0.2	88	—	UL/CUL	61.95	54.95
301402	Mean Well	SP-480-48	+48V @ 0-11A	528W	10.9 x 5.0 x 1.7	240	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	136.95	115.95
161796	Mean Well	SP-500-48	+48V @ 0-10A	480W	6.7 x 4.7 x 3.7	300	0.5	0.5	87	✓	UL/CUL/TUV/CE/CB	152.95	134.95
295929	Mean Well	SE-600-48	+48V @ 0-12.5A	600W	9.7 x 5.0 x 2.5	200	0.5	0.5	88	—	UL/CUL	75.95	66.95
374249	Mean Well	PSP-600-48	+48V @ 0-12.5A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	87	✓	UL/CUL/TUV/CE/CB	125.95	111.95
2101577	Mean Well	SE-1000-48	+48V @ 0-20.8A	998.4W	10.9 x 5.0 x 2.5	200	0.5	0.5	89	—	UL/CUL	165.95	146.95
1585725	Mean Well	RSP-1000-48	+48V @ 0-21.0A	1008W	11.6 x 5.0 x 1.6	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	206.95	175.95
694954	Mean Well	RSP-1500-48	+48V @ 0-32.0A	1536W	10.9 x 5.0 x 3.3	200	0.5	0.5	91	✓	UL/CUL/TUV/CE/CB	303.95	270.95
2108921	Mean Well	RSP-3000-48	+48V @ 0-62.5A	3000W	10.9 x 7.0 x 2.5	200	0.5	0.5	90.5	✓	UL/CUL/TUV/CE/CB	417.95	407.95
<b>Double Output</b>													
323362	Mean Well	RD-35A	+5V @ 0.3-4A; +12V @ 0.2-1A	32W	3.9 x 3.2 x 1.4	80	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	\$13.49	\$12.95
323380	Mean Well	RD-35B	+5V @ 0.3-4A; +24V @ 0.2-1.3A	51.2W	3.9 x 3.2 x 1.4	80	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	13.49	12.95
323425	Mean Well	RD-50A	+5V @ 0.3-6A; +12V @ 0.3-3A	54W	3.9 x 3.8 x 1.4	80	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	14.49	12.95
323433	Mean Well	RD-50B	+5V @ 0.3-6A; +24V @ 0.2-2A	54W	3.9 x 3.8 x 1.4	80	0.5	0.5	80	—	UL/CUL/TUV/CE/CB	14.49	12.95
323505	Mean Well	RD-65A	+5V @ 0.3-8A; +12V @ 0.2-4A	66W	5.1 x 3.9 x 1.5	80	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	15.95	14.49
323513	Mean Well	RD-65B	+5V @ 0.3-8A; +24V @ 0.2-3A	68W	5.1 x 3.9 x 1.5	80	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	15.95	14.49
132397	Mean Well	D-120B	+5V @ 2.0-6A; +24V @ 0.4-4A	126W	7.0 x 3.9 x 2.0	60	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	39.95	36.95
323741	Mean Well	RD-125A	+5V @ 2.0-15A; +12V @ 0.5-10A	130.9W	7.8 x 3.9 x 1.5	80	3.0	1.0	82	—	UL/CUL/TUV/CE/CB	24.95	22.95
2106124	Mean Well	RD-125-1224	+12V @ 1.0-3.7A; +24V @ 0.4-3.7A	133.2W	7.8 x 3.9 x 1.5	120	1.0	0.5	85	—	UL/CUL/TUV/CE/CB	24.95	22.95
323759	Mean Well	RD-125B	+5V @ 2.0-10A; +24V @ 0.4-5A	133.4W	7.8 x 3.9 x 1.5	80	3.0	1.0	82	—	UL/CUL/TUV/CE/CB	24.95	22.95
<b>Triple Output</b>													
323460	Mean Well	RT-50B	+5V @ 0.5-5A; +12V @ 0.2-2.5A; -12V @ 0.1-1A	50W	3.9 x 3.8 x 1.4	80	1.0	0.5	77	—	UL/CUL/TUV/CE/CB	\$15.95	\$14.95
323468	Mean Well	RT-50C	+5V @ 0.5-5A; +15V @ 0.2-2A; -15V @ 0.1-1A	50W	3.9 x 3.8 x 1.4	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	15.95	14.95
323476	Mean Well	RT-50D	+5V @ 0.5-5A; +12V @ 0.1-1A; +24V @ 0.2-1.5A	51W	3.9 x 3.8 x 1.4	80	1.0	0.5	80	—	UL/CUL/TUV/CE/CB	15.95	14.95
123482	Mean Well	T-60B	+5V @ 0.5-5A; +12V @ 0.2-2.5A; -12V @ 0-0.5A	61W	6.3 x 3.8 x 1.5	100	1.0	0.5	72	—	UL/CUL/TUV/CE/CB	29.95	26.95
323540	Mean Well	RT-65B	+5V @ 0.5-8A; +12V @ 0.2-3.5A; -12V @ 0-1A	64.6W	5.1 x 3.9 x 1.5	80	1.0	0.5	77	—	UL/CUL/TUV/CE/CB	17.49	16.49
323548	Mean Well	RT-65C	+5V @ 0.5-8A; +15V @ 0.2-3A; -15V @ 0-1A	65.5W	5.1 x 3.9 x 1.5	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	17.49	16.49
323555	Mean Well	RT-65D	+5V @ 0.5-8A; +12V @ 0.1-1A; +24V @ 0.2-2A	68W	5.1 x 3.9 x 1.5	80	1.0	0.5	79	—	UL/CUL/TUV/CE/CB	17.49	16.49
323775	Mean Well	RT-125B	+5V @ 2-15A; +12V @ 0.5-6A; -12V @ 0.1-1A	132W	7.8 x 3.9 x 1.5	80	1.0	0.5	80	—	UL/CUL/TUV/CE/CB	28.95	26.95
323783	Mean Well	RT-125C	+5V @ 2-15A; +15V @ 0.5-6A; -15V @ 0.1-1A	132.5W	7.8 x 3.9 x 1.5	80	1.0	0.5	81	—	UL/CUL/TUV/CE/CB	28.95	26.95
323792	Mean Well	RT-125D	+5V @ 2-15A; +12V @ 0.1-2A; +24V @ 0.4-4A	136W	7.8 x 3.9 x 1.5	80	1.0	0.5	82	—	UL/CUL/TUV/CE/CB	28.95	26.95
<b>Quad Output</b>													
323484	Mean Well	RQ-50B	+5V @ 0.5-6A; +12V @ 0.2-1.5A; -5V @ 0-1A; -12V @ 0-1A	45.5W	3.9 x 3.8 x 1.4	80	0.5	0.5	74	—	UL/CUL/TUV/CE/CB	\$19.95	\$17.95
323564	Mean Well	RQ-65B	+5V @ 0.5-8A; +12V @ 0.2-3A; -5V @ 0.1-1.5A; -12V @ 0-1A	62.5W	5.1 x 3.9 x 1.5	80	0.5	0.5	76	—	UL/CUL/TUV/CE/CB	18.49	17.49
323572	Mean Well	RQ-65D	+5V @ 0.5-8A; +12V @ 0.2-3A; +24V @ 0.1-1.5A; -12V @ 0-1A	68W	5.1 x 3.9 x 1.5	80	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	18.49	17.49
323812	Mean Well	RQ-125D	+5V @ 2-12A; +12V @ 0.5-4A; +24V @ 0.1-2.5A; -12V @ 0-1A	124W	7.8 x 3.9 x 1.5	80	1.0	0.5	82	—	UL/CUL/TUV/CE/CB	28.95	26.95
213648	Mean Well	QP-150F	+5V @ 3-15A; +15V @ 0-5A; +24V @ 0.4-3A; -15V @ 0-1A	152W	7.8 x 3.9 x 1.5	120	2.0	1.0	78	✓	UL/CUL/TUV/CE/CB	86.95	79.95
213752	Mean Well	QP-200D	+5V @ 3-20A; +12V @ 0-6A; +24V @ 0.4-5A; -12V @ 0-1A	204.9W	7.8 x 3.9 x 2.0	100	2.0	1.0	75	✓	UL/CUL/TUV/CE/CB	99.95	89.95
668764	Mean Well	QP-320D	+5V @ 2.5-20A; +12V @ 0-10A; +24V @ 0.2-5A; -12V @ 0.2-2A	316W	8.5 x 4.5 x 2.0	100	2.0	1.0	83	✓	UL/CUL/TUV/CE	103.95	98.95

\*Applies only to primary output

§ Efficiency