

DIN-Rail UPS Module & DC-to-DC Power Converters

Jameco carries the full line of Mean Well Power products. For additional products visit www.Jameco.com/meanwellproducts



40A DC DIN-Rail UPS Module

* Web Code: DTF

Part No.	Mfr. Part No.	Description	DC Input/DC BUS	Output Voltage @ Current	Charge Current	Certification	1	10
2103273	DR-UPS40	Battery controller for UPS	24-29V @ 40A	21-29VDC @ 0-40A	2A	CE	\$39.95	\$34.95



15 to 201-Watt Enclosed Converters

* 5-9V Web Code: IDF

* 12V Web Code: IDW

* 15-24V Web Code: IDR

* 30-48V Web Code: IDO

- 2:1 wide input range
- Working temp.: -10°C to +60°C
- 100% burn-in tes
- Protection: short-circuit, overload and overvoltage

- SD-15 Series** • Built-in EMI filter, low ripple noise • One-year warranty
- SD-25/SD-50/SD-150 Series** • Isolation voltage: 1500VDC • Built-in EMI filter, low ripple noise • One-year warranty
- SD-200 Series** • Isolation voltage: 1500VDC • Cooling by free air convection • Fixed switching freq @ 83kHz • One-year warranty



Part No.	Mfr. Part No.	Input Range	Output		Size (L" x W" x H")	Pins	Line Reg. (±%)	Load Reg. (±%)	Ripple & Noise (mV p-p)	Certification	Pricing	
			Voltage @ Current	Power (W)							1	10
1953778	SD-15A-5	9.2-18V	+5V @ 3.0A	15	3.1 x 2.0 x 1.1	5	0.5	0.5	100	CE	\$11.95	\$10.75
1953786	SD-15B-5	18-36V	+5V @ 3.0A	15	3.1 x 2.0 x 1.1	5	0.5	0.5	100	CE	11.95	10.75
175662	SD-25A-5	9-18V	+5V @ 5.0A	25	3.9 x 3.8 x 1.4	5	0.5	0.5	100	CE	20.95	18.95
212549	SD-50A-5	9-18V	+5V @ 10A	50	6.3 x 3.8 x 1.5	5	0.5	0.5	100	CE	24.95	22.49
1953823	SD-15B-12	18-36V	+12V @ 1.25A	15	3.1 x 2.0 x 1.1	5	0.3	0.3	120	CE	11.95	10.75
1953840	SD-15C-12	36-72V	+12V @ 1.25A	15	3.1 x 2.0 x 1.1	5	0.3	0.3	120	CE	11.95	10.75
175805	SD-25A-12	9-18V	+12V @ 2.1A	25.2	3.9 x 3.8 x 1.4	5	0.3	0.3	120	CE	20.95	18.95
1537483	SD-50A-12	9.2-18V	+12V @ 4.2A	50.4	6.3 x 3.8 x 1.5	5	0.3	0.3	120	CE	24.95	22.49
212531	SD-50B-12	19-36V	+12V @ 4.2A	50.4	6.3 x 3.8 x 1.5	5	0.3	0.3	120	CE	24.95	22.49
212506	SD-50C-12	36-72V	+12V @ 4.2A	50.4	6.3 x 3.8 x 1.5	5	0.3	0.3	120	CE	24.95	22.49
217270	SD-150B-12	19-36V	+12V @ 12.5A	150	7.8 x 4.3 x 2.0	7	0.5	0.5	120	CE	41.95	37.95
175813	SD-25A-24	9-18V	+24V @ 1.1A	26.4	3.9 x 3.8 x 1.4	5	0.2	0.2	150	CE	20.95	18.95
2107266	SD-50A-24	9.2-18V	+24V @ 2.1A	50.4	6.3 x 3.8 x 1.5	5	0.2	0.2	150	CE	24.95	22.49
2107039	SD-100C-24	36-72V	+24V @ 4.2A	100.8	7.8 x 3.9 x 1.6	7	0.2	0.2	150	CE	31.95	27.95
2107098	SD-150C-24	36-72V	+24V @ 6.3A	151.2	7.8 x 4.3 x 2.0	7	0.3	0.3	150	CE	41.95	37.95
1953954	SD-200B-24	19-36V	+24V @ 8.4A	201.6	8.5 x 4.5 x 2.0	9	0.5	1.0	150	CE	69.95	61.95

Encapsulated DC-to-DC Converters

* 3.3-9V Web Code: IEF

* 12-13.5V Web Code: IEW

* 15-24V Web Code: IEO

- 1000VDC I/O isolation
- Short-circuit/overload protection
- Shield metal case
- 2:1 wide input range
- Cooling by free air convection
- One-year warranty



Part No.	Mfr. Part No.	Input Range	Output		Size (L" x W" x H")	Pins	Line Reg. (±%)	Load Reg. (±%)	Ripple & Noise (mV p-p)	Certification	Pricing	
			Voltage @ Current	Pwr (W)							1	10
213234	SLW05C-05*	36-72V	+5V @ 1A	5	2.0 x 1.0 x 0.44	5	1.0	0.2	100	CE	\$11.95	\$10.95
216937	SLW05B-05*	18-36V	+5V @ 1A	5	2.0 x 1.0 x 0.44	5	1.0	0.2	100	CE	11.95	10.95
216962	SKE10A-05*	9-18V	+5V @ 2A	10	2.0 x 1.0 x 0.44	5	0.3	1.0	50	CE	17.95	16.49
155716	SKE15A-05*	9-18V	+5V @ 3A	15	2.0 x 2.0 x 0.43	5	0.3	0.5	50	CE	18.95	16.95
155708	SKE15A-12*	9-18V	+12V @ 1.25A	15	2.0 x 2.0 x 0.43	5	0.3	0.5	60	CE	16.49	15.49
155695	SKE15A-24*	9-18V	+24V @ 0.625A	15	2.0 x 2.0 x 0.43	5	0.3	0.5	80	CE	18.95	16.95
161702	DCW03A-12**	9-18V	±12V @ 0.125A	15	1.25 x 0.8 x 0.48	10	1.0	0.5	100	CE	9.95	8.95
217092	DKE10A-12**	9-18V	±12V @ 0.42A	5.04	2.0 x 1.0 x 0.44	5	0.3	0.5	60	CE	18.95	17.49
217112	DKE10A-15**	9-18V	±15V @ 0.333A	5.0	2.0 x 1.0 x 0.44	5	0.3	0.5	60	CE	18.95	17.49

* Single output ** Double output

DC-to-AC Inverters Pure and Modified Sine Waves

* Web Code: XEL

NEW MARKED IN PINK

Part No.	Mfr. Part No.	Input Range (VDC)	Output (VAC)	Wattage (W)	Efficiency (%)	LED Indicator	Size (L" x W" x H")	Pricing	
								1	10
277181	A-301-150-B2	10-15	120	150	78	Yes	4.8 x 2.9 x 1.8	\$32.95	\$29.95
2228316	PWR118012S	10-16.2	120	180	90	Yes	5.9 x 3.2 x 1.5	24.95	22.49
2108445	TS-200-112A	10.5-15	120	200	86	Yes	8.0 x 6.2 x 2.3	114.95	104.95



POWER SUPPLIES AND WALL ADAPTERS — GREAT PRICES ON SPECIAL BUYS

Part No.	Type	Voltage @ Current	Power	Price	Part No.	Type	Voltage @ Current	Power	Price
2188730	Open	+5V @ 2A	10W	\$4.95	2188705	Wall	+12V @ 1.5A	18W	\$9.95
2208981	Table	+5V @ 4A	20W	6.95	2230256	Table	+12V @ 3A	36W	15.95
2230272	Wall	+12V @ 50mA	0.6W	3.95	2149546	Enclosed	+36V @ 9.7A	349.2W	43.95
2229503	Wall	+5V @ 1.2A	6W	7.95	2229247	Table	+12V @ 4A	48W	10.95
2258380	Table	+12V @ 2.5A	30W	10.95	2257168	Table	+5V @ 4A	20W	12.19
2202618	Table	+15V @ 1.2A	18W	5.95	2258443	Wall	+12V @ 1A	12W	8.95



* For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com 109