

Test Leads, Cables, Plugs, Clips & Posts

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **SPECIAL BUY**

Test Leads and Cables



*Web Code: RAC



Part No.	Manufacturer	Product No.	Description	Size (L')	1	10	25
159871	Pomona	2249-C-36	BNC male to male cable, RG58C/U, 50Ω, 20 AWG, black	36	\$18.95	\$17.95	\$16.95
2113877	Pomona	3957	BNC male to Multi-Stacking banana plugs (2nd End)	1.55	18.95	16.95	14.95
176971	Pomona	4532-C-36	BNC male to Mini alligator clips w/ strain relief, RG58C/U, 50Ω, 20AWG, blk	36	23.95	21.49	19.49
2218901	BenchPro	11384	BNC male to alligator clips, RG58C/U, 18AWG, 1 black, 1 red	20	4.95	4.49	3.95
11464	BenchPro	05-A-078-R	BNC male to Mini-clip test lead, RG174A/U, black	39	5.49	4.95	4.49
11422	BenchPro	05-A-081-R	BNC male to Micro-clip test lead, RG174A/U, black	39	5.49	4.95	4.49
2097150	Pomona	5187-C-36	BNC male to MiniGrabber test leads, RG58C/U 50Ω, 20 AWG, black	36	21.95	20.95	19.95
176954	Pomona	5187-K-36	BNC male to MiniGrabber test leads, RG174/U 50Ω, 26 AWG, black	36	33.95	29.95	26.95
256832	BenchPro	CBB-069	BNC female to pigtail, 20 AWG, 2 wire, 1 black, 1 red	7	6.15	5.49	4.95
2097168	Pomona	4969	BNC female to pigtail, 20 AWG, 2 wire, 1 black	9	9.95	8.95	7.95
2097555	BenchPro	CBB-070	BNC male to pigtail, 20 AWG, 2 wire, 1 black, 1 red	9	5.95	4.95	4.49
2113869	Pomona	3788	BNC female Minigrabber test clips (2nd end)	2.56	12.95	12.49	11.95
2113885	Pomona	5051	BNC female to #8 spade lugs	5.4	9.95	8.95	7.95
2158477	BenchPro	FC16A	Probes w/ right angle banana, screw on alligator clips, 1 black, 1 red	40	8.95	7.95	6.95
2211055	Arndt	TP9238	Probes, R/A with screw on alligator clip, 24 AWG, red/black	36	6.95	6.25	5.49
212222	Probe Master	8043S	Softie test probe leads, 10-pc. set, interchangeable tips, 18 AWG, 1 blk, 1 red	48	34.95	32.95	29.95
174625	Probe Master	8150	Micro-tip test probe leads rt. angle (w/10 plunger type tips), 1 blk, 1 red	39	44.95	42.95	39.95
168516	BenchPro	GA-5010	Universal test lead kit w/ 12 interchangeable tips, 1 black, 1 red	36	9.95	8.95	7.95
2113914	Pomona	5953A	Adjustable tip test probe set, tip adjusts up to 3", 1 black, 1 red	48	27.95	26.95	24.95
2212306	Velleman	TLM4	Banana plug, rt. angle to probe insulated leads, 1 black, 1 red	48	2.75	2.49	2.25
155951	Pomona	5519A	Banana plug rt. angle to probe, insulated leads, 18 AWG 1 blk, 1 red	48	18.95	16.95	14.95
77738	BenchPro	GF19-R	Protected banana style multimeter test leads, 1 black, 1 red	40	4.95	4.49	3.95
77746	BenchPro	FC-15B-R	Standard banana style multimeter test probes, 1 black, 1 red	42	6.95	6.25	5.59
10444	BenchPro	GAL01	Alligator clip test leads, 24 AWG (19/36), 10-pc. assorted colors	21	5.95	5.39	4.79
2185483	BenchPro	GAL02	Alligator clip test leads, 24 AWG, 1 black, 1 red	21	1.95	1.75	1.49
2210239	BenchPro	GAL1016	Alligator clip test leads, 16 AWG, 2 sets, 5 colors	21	9.95	8.95	7.95
2210247	BenchPro	GAL0216	Alligator clip test leads, 16 AWG, 1 set (red/black)	21	5.95	5.39	4.75
159901	Pomona	B-24-02	Stackable banana patch cords, 18 AWG, 1 black, 1 red	24	11.95	11.49	10.95
159919	Pomona	B-36-02	Stackable banana patch cords, 18 AWG, 1 black, 1 red	36	11.95	11.49	10.95
2208884	BenchPro	CRF-TS0284TS-XX-250MM	Stackable banana patch cords, 16 AWG, 2 ea. (black,red,blue,white,yellow)	9.8	24.95	22.95	19.95
77842	BenchPro	CRF-TS0284TS-XX-330MM	Stackable banana patch cords, 16 AWG, 2 ea. (black,red,blue,white,yellow)	13	27.95	24.95	22.49
1814137	Pomona	1166-12-0	Alligator clip to stackable banana plug, 18 AWG, black	12	6.95	6.25	5.59
1814145	Pomona	1166-12-2	Alligator clip to stackable banana plug, 18 AWG, red	12	6.95	6.25	5.59
2212293	Velleman	TLM3	Alligator clip to banana plug, 18 AWG*	35.4	2.75	2.49	2.25
1814153	Pomona	1166-48-0	Multi-stacking banana plug to alligator clip, black	48	7.95	6.95	6.25
1814161	Pomona	1166-48-2	Alligator clip to stackable banana plug, 18 AWG, red	48	7.95	6.95	6.25
2218919	BenchPro	ACBP-20AWG1000-RB	Alligator clip to stackable banana plug, 20AWG, 1 black, 1 red	20	8.95	7.95	6.95
2224930	BenchPro	GCA340-SM	Alligator clip to stackable double banana plug, 18AWG	36	5.95	4.95	4.49
21857	BenchPro	05-A-082-R	Mini-clip to stackable banana test leads, black	39	4.95	4.49	3.95
21865	BenchPro	05-A-079-R	Mini-clip to stackable banana test leads, red	39	4.95	4.49	3.95
2189601	BenchPro	3782-36-02JVP	Mini-clip to stackable banana test leads, 1 black/ 1 red	39	7.95	6.95	6.25
159899	Pomona	3782-36-02	Mini-clip w/ stackable banana test leads, 20 AWG, 1 black, 1 red	36	13.95	13.49	12.95
135299	BenchPro	SF-207A-R	Mini-clip test leads, 26 AWG, 5 sets (blue, black, yellow, red, green)	14	11.25	10.25	8.95
156495	Pomona	5523-R	MiniGrabber™ test clip patch cord, 20 AWG 10-pc. assorted colors	24	49.95	44.95	39.95
155985	Pomona	2708B	9 slot test lead holder, accepts RG213 & RG214 wire sizes (blue)	11	15.95	14.49	12.95
155977	Pomona	4408	10 slot test lead holder, accepts RG59 & RG108 wire sizes (black)	11	11.95	11.49	10.49
155969	Pomona	1508	14 slot test lead holder, accepts RG58 & RG142 wire sizes (orange)	11	14.95	13.95	12.95

*Black, red, yellow



Test Clips, Plugs and Posts

*Web Code: TLC



Part No.	Manufacturer	Product No.	Description	Size (in.)	1	10	100
71240	BenchPro	GIP-003-R	Binding post, screw type, chassis mount 1 black, 1 red	1.0 L x .50 Dia.	\$2.05	\$1.75	\$1.49
77691	BenchPro	GIP-001-R	Binding post, screw type, chassis mount 1 black, 1 red	1.8 L x .50 Dia.	1.95	1.75	1.49
1818779	Pomona	3760-0	Binding post, accepts banana, wire, or spade lug, black	1.78 L x .44 Dia.	4.49	3.95	3.59
1818787	Pomona	3760-5	Binding post, accepts banana, wire, or spade lug, green	1.78 L x .44 Dia.	4.49	3.95	3.59
2127742	Pomona	3760-2	Binding post, accepts banana, wire, or spade lug, red	1.78 L x .44 Dia.	3.95	3.69	3.35
2205755	BenchPro	WTA-60R-4PK	Binding post 4-pack, chassis mount, red/black/green/yellow	1.1 L x .30 Dia.	3.95	3.59	3.29



Test Clips, Plugs & Posts continued on next page