

# Crimpers, Strippers, Cutters & Miscellaneous Tools

3 LEVELS OF SAVINGS  
**NAME BRANDS** **HOUSE BRANDS** **SPECIAL BUY**

Xcelite®

JAMECO  
BenchPro



Wire Cutters/Strippers/Crimpers

EXIMCORP



\*Web Code: GBU



Part No.	Manufacturer	Mfr. P/N	Description	Functions			Size (L" x W")	Pricing	
				Cut	Strip	Crimp		1	5
179902	BenchPro	GPL-171	4" leaf spring cutters w/ flush side cutting, forged steel, cushion grip	✓			4.0 x 2.6	\$3.95	\$3.59
2123320	BenchPro	GPL-101	4.5" spring return cutters w/ flush side cutting, carbon steel, vinyl grip	✓			4.5 x 2.6	4.95	4.49
35482	BenchPro	AX103	4.3" Diagonal wire cutters, rubber handles, 0.5" cutting blade, 45° angle	✓			4.3 x 2.1	7.95	6.95
2203750	Plato	175LX	5.6" Ergonomic, ESD-safe shear lead cutter with guard, blue grips	✓			5.6 x 2.0	7.95	6.95
146712	Xcelite	170M	5" general purpose shearcutters, flush cutting, red cushioned grips	✓			5.0 x 2.5	9.95	8.95
161411	Pro's Kit	1PK-717	5" Diagonal wire cutters, insulated handles, cuts 0.08mm fine wire	✓			5.0 x 1.8	6.95	6.25
217921	Xcelite	MS54J	4" oval head-flush diagonal cutters, flush cut, green cushioned grips	✓			4.3 x 1.8	22.95	20.95
217904	Xcelite	MS549JV	4" tapered head diagonal cutters, flush cut, green cushioned grips	✓			4.2 x 1.8	23.95	21.49
2112292	BenchPro	TTK-061	UTP/STP wire stripper, 3-24 AWG, shielded/unshielded/twisted pair cable		✓		3.5 x 1.3	1.95	1.75
159185	Hanlong	HT-332D	2-blade rotary coax cable strippers, 4 settings for cable sizes 4-12mm		✓		3.9 x 0.7	11.95	10.95
114535	Hanlong	HT-336G	Ratcheted BNC crimper, for RG58, RG59, RG62, RG174, and fiber optic			✓	8.5 x 2.5	25.95	23.49
78992	Hanlong	HT-108	5" cutter/strippers, 10-30 AWG, spring return, screw-adjustable wire gauge	✓	✓		5.0 x 3.0	5.95	5.49
215889	BenchPro	JE-2022C	5" cutter/strippers, 10-24 AWG, spring return, dial to adjust wire gauge	✓	✓		5.0 x 3.0	5.95	4.95
159274	Hanlong	HT-1091	5" cutter/strippers, 20-24 AWG, spring-loaded, insulated grips, 45° angle	✓	✓		5.0 x 3.0	4.95	4.49
2112284	BenchPro	GTA-002	Automatic wire strippers, 10-24 AWG, spring-loaded handle w/ wire stopper	✓	✓		6.8 x 3.2	9.95	8.95
159291	Hanlong	HT-5023	6.6" cutter/strippers, 20-30 AWG, cuts steel wire, scale markings in AWG/mm	✓	✓		6.6 x 2.0	10.95	9.95
99443	Hanlong	HT-202A	Non-insulated terminal crimper, for D-sub and non-insulated connectors	✓		✓	7.3 x 1.5	9.95	8.95
159266	Hanlong	HT-213	D-sub crimper, crimps D-sub pins and sockets, works with 20-28 AWG wire	✓		✓	7.0 x 4.0	15.95	14.49
161218	Ideal	45-121	6" cutter/strippers, strips 16-26 AWG stranded, 14-24 AWG solid, plier nose	✓	✓		6.0 x 2.0	17.95	15.95
175098	BenchPro	GTA-006H	Automatic strippers, 8-22 AWG, spring-loaded handle with wire stopper	✓	✓		7.0 x 3.5	18.95	16.49
18797	Hanlong	HT-1041	7-in-1 wire-handling tool, 10-18 AWG, steel wire cutter, wire loop, red	✓	✓	✓	6.6 x 3.0	6.95	6.25
127862	Hanlong	HT-1042	7-in-1 wire-handling tool, 16-26 AWG, steel wire cutter, wire loop, blue	✓	✓	✓	6.6 x 3.0	7.95	6.95
127871	Hanlong	HT-1043	7-in-1 wire-handling tool, 22-30 AWG, steel wire cutter, wire loop, orange	✓	✓	✓	6.6 x 3.0	7.95	6.95
2153078	BenchPro	GRK-42N	8.5" cutter/crimper/stripper, ergonomic grip, 10-22 AWG, wire gauge markings	✓	✓	✓	8.5 x 3.0	5.95	5.49
2192376	BenchPro	HT-N5684	7.5" modular crimping tool, 8P8C/RJ45, 6P6C/RJ12, 6P4C/RJ11, 4P4C and 4P2C	✓	✓	✓	7.5 x 3.0	15.95	14.49

Test/Tools

JAMECO  
BenchPro

## 100-Piece Professional Electronics Tool Kit

- Kit includes:
  - Soldering iron
  - 12 screwdrivers
  - 7-piece hex key set
  - Extractor
  - 4 Pliers
  - Adjustable wrench
  - Crimper/Stripper
  - 6-piece screwdriver set
  - 3-piece soldering aid kit
  - Flashlight
  - Multimeter
  - Tweezers
  - 5-piece file set
  - Desoldering pump
  - Voltage tester
  - Vacuum cleaner
  - Cordless screwdriver kit (bits included)
  - Aluminum case features removable pallets, surface-type locks, and black plastic handle
  - Size: 18.0"L x 14.0"W x 6.0"H • Weight: 20 lbs.



Part No.	Description	1	5
242851	100-piece tool kit	\$159.95	\$149.95

## 116-Piece Tech Service Tool Kit

- Kit includes:
  - Storage box
  - 8 pliers
  - Tweezers
  - Spring hook
  - 3-piece soldering aid kit
  - Desoldering pump
  - 3-piece alignment tool set
  - Diagonal cutter
  - Soldering iron
  - Forceps
  - 9-piece screwdriver set
  - Brush
  - Wire stripper
  - 5-piece file set
  - Flashlight
  - 3-prong holder
  - PVC insulated tape
  - Heat sink
  - Measuring tape
  - 6-piece electronic screwdriver set
  - 40-piece socket & screwdriver set
  - 10-piece electronic wrench set
  - Drill
  - Desoldering wick
  - Brush
  - Crimping tool
  - Extractor
  - 7-piece hex key set
  - Hammer
  - Solder core
  - Wrist strap
  - Inspection Mirror
- Size: 18.5"L x 13.8"W x 6.7"H • Weight: 22.8 lbs.



Part No.	Description	1	5
149024	116-piece tool kit	\$299.95	\$289.95

## molex Hand Tools for Mini-Fit™ Jr.



- 304928:**
  - Accepts wire range from 14-24 AWG
  - Insulated small handle spread design
  - Great for open-barrel terminals
- 304936:**
  - For the removal of Mini-Fit Jr™ crimped terminals series from their housings

Part No.	Mfr. Part No.	Description	1	5
304928	63811-1000	Crimp tool	\$54.95	\$49.95
304936	11-03-0044	Extraction tool	27.95	24.95

\*Crimping Tools — Enter Web Code GBU

\*Tool Kits — Enter Web Code CAA

JAMECO  
BenchPro

## Pocket Screwdriver

Phillips & Flat head

- Pen clip for pocket storage



Part No.	Description	1	10	100
127271	6"L pocket screwdriver	\$1.95	\$1.59	\$1.39