

# Magnifying Lamps & Anti-Static Products

## 22"L Anti-Static Plastic DIP IC Storage Rails & Rubber Rail Stops



**29524** (ICs not included) **29583**

**29516:** .300" rail fits 8, 14, 16, 18, 20 and 22-pin ICs  
**29524:** .600" rail fits 24, 28, 36 and 40-pin ICs  
**29583:** Rubber stops used to plug plastic rail ends

**Note: previously used** \* Order in multiples of 10

Part No.	Product No.	Description	1	10	100
<b>29516</b>	RIC20	.300"W rail	\$.29	\$.25	\$.22
<b>29524</b>	RIC220	.600"W rail	.29	.25	.22
<b>29583</b>	RRS	Rubber stop	*.09	.07	

## DIGITAL LUX METER

Measure local area brightness over your workstation with one touch.

- 1999 count display w/ low bat.
- Light pocket-sized model
- Measure intensity from 0.1 to 50,000 lux



Part No.	Description	1	5
<b>2175306</b>	DVM1300	\$39.95	\$37.95

## ANTI-STATIC DESOLDERING PRODUCTS

In addition to having a static-free work surface, your tools can have the same protection.



Part No.	Mfr. P/N	Description	Price
<b>2203784</b>	1822-5F	0.075" x 5' desolder braid	\$3.49
<b>2131215</b>	VTD3	Desolder pump w/ 0.8" tip	7.95

## Anti-Static Heel Strap

- Discharges static without restricting your mobility
- Ground strap length: 24"L



Part No.	Description	1	10	25
<b>2204437</b>	Strap w/ 1MΩ resistor	\$3.95	\$3.59	\$3.29

## Anti-Static Work Mats

These mats are made of attractive semi-conductive vinyl that provide adequate discharging yet will not short leads or pins.



Part No.	Dimensions	Wt. (lbs.)	1	10	25
<b>10576</b>	11.3" x 22"	0.7	\$9.95	\$8.95	\$7.95
<b>10584</b>	19.5" x 23.5"	1.1	13.95	12.49	10.95
<b>2130853</b>	19.7" x 23.6"	1.1	14.95	13.95	12.95
<b>2152075</b>	24" x 48"	3.9	69.95	64.95	59.95

## Field Service Static Kit

- 4 pocket for ESD safe storage
- 10' ground strap and 6' wrist strap share on one ground point
- Size: 2' x 2.13'



Part No.	Cross Ref. No.	1	5	25
<b>2113720</b>	8PK-AS07-1	\$14.95	\$13.95	\$12.95

## Visor Magnifier w/ Light

- Power supply: 4 AAA batteries (not included)
- Adjustable diopter: 1.8/2.3/3.7/4.8
- Size: 7.9"L x 2.4"W x 5.5"H



Part No.	Mfr. Part No.	Wt. (oz.)	1	10
<b>2131119</b>	VTMG6	5.3	\$8.95	\$7.95

## Anti-Static Wrist Straps

- Comfortable, adjustable black Velcro wrist strap
- The coiled grounding cord has banana plug and alligator clips
- Extended cord: 9'L (2131266: 6'L)



Part No.	Mfr.	Color	1	10	100
<b>34552</b>	BenchPro	Black/yellow	\$6.49	\$5.95	\$5.49
<b>2131266</b>	Velleman	Black/yellow ...	4.49	3.95	3.49
<b>2202087</b>	3M	Disposable	1.95	1.75	1.49

## Conductive Anti-Static Bags and Foam

Don't get zapped!

13864

Protect your investment with these inexpensive bags and ensure a safe work area with our conductive anti-static foam.

**13864:** 24"L x 12"W x 0.25"H

Part No.	Description	1	10	100
<b>249519</b>	4" x 6" anti-static bags, pink	\$.25	\$.19	\$.12
<b>249527</b>	5" x 7" anti-static bags, pink	.25	.19	.12
<b>2202247</b>	5" x 7" anti-static zip, gray	.39	.29	.19
<b>78650</b>	8" x 10" anti-static bags, gray	.39	.29	.25
<b>13864</b>	24" x 12" anti-static foam	12.95	11.95	10.95
<b>2237896</b>	12" x 16" anti-static foam	3.95	3.49	2.95

\*Anti-Static — Enter Web Code XAA

## PLCC & DIP IC Extractors

\*Web Code: MAB



Part No.	Manufacturer	Description	1	10	100
<b>16838</b>	BenchPro	DIP	\$2.95	\$2.59	\$1.95
<b>2173175</b>	BenchPro	PLCC	2.95	2.59	2.29
<b>16766</b>	Velleman	PLCC	3.95	3.49	2.95



## Magnifying Lamps



\*Web Code: DAW

For anyone working with precision assembly, inspection or design, these magnifying lamps are essential for the workbench. Whether with incandescent or LED light, our selection will have you choose what best suits your needs to help reduce eye strain and vision fatigue. Easily view the smaller details.



Part No.	Diopter	Lamp Size	Length	Shape	Type	# of Bulbs	Watts	Color	Wt. (lbs.)	1	5
<b>2238012</b>	3	3.5"Diameter	14.5"	Circular	LED	24	5.4	Black	1.9	\$44.95	\$39.95
<b>2238047</b>	3	3.5"Diameter	14.5"	Circular	LED	24	5.4	Black	2.6	44.95	39.95
<b>149981</b>	3	5"Diameter	45"	Circular	INC	1	22	White	7.3	59.95	54.95
<b>2120330</b>	3	7"Diameter	30"	Circular	LED	4	3.4	White	21	119.95	113.95
<b>2238039</b>	3	7"L x 5"W	36"	Rectangular	LED	36	7.6	White	9	129.95	119.95
<b>2238004</b>	3 & 5	5"Diameter	32"	Circular	LED	45	9.4	White	5.7	89.95	79.95
<b>2238021</b>	3	5"Diameter	32"	Circular	LED	45	9.4	Silver	7.0	99.95	89.95
<b>2196924</b>	5	5"Diameter	36"	Circular	LED	90	5.5	White	6.8	99.95	89.95
<b>2210600</b>	5	5"Diameter	39"	Circular	LED	45	9.4	White	5.4	94.95	84.95
<b>197456</b>	5	5"Diameter	40"	Circular	INC	1	22	White	7.1	84.95	74.95
<b>2210597</b>	5*	7"Diameter	36"	Circular	LED	102	16.8	White	10.8	239.95	224.95

\*Also contains 5 UV LEDs †INC = Incandescent

## TOP SELLING COMPONENT KITS

- Kits include plastic cabinet with 20 drawers
- Cabinet size: 6.0"L x 15.0"W x 7.9"H
- Includes ID labels for each drawer (except refills)

### 7400 Series IC Kit

Includes 350 pcs. (30 Types) 7400 (TTL) Integrated Circuits

20 each	10 each	10 each	10 each	10 each	10 each
7400	7402	7406	7416	7432	74121
7404	7405	7417	7438	74123	74160
7406	7408	7420	7447	74132	74174
7407	7410	7427	7485	74151	74175
7474	7414	7430	74107	74153	74279

Part No.	Description	1	5
<b>84953</b>	350 pcs. 7400 series IC kit	\$219.95	\$199.95

### 74LS00 Series IC Kit

Includes 420 pcs. (35 Types) 74LS00 (TTL) Integrated Circuits

20 each	10 each	10 each	10 each	10 each
74LS00	74LS05	74LS73	74LS125	74LS193
74LS02	74LS10	74LS75	74LS139	74LS240
74LS04	74LS11	74LS85	74LS151	74LS244
74LS08	74LS14	74LS86	74LS155	74LS245
74LS32	74LS20	74LS90	74LS157	74LS273
74LS74	74LS30	74LS93	74LS174	74LS373
74LS138	74LS47	74LS123	74LS175	74LS374

Part No.	Description	1	5
<b>84961</b>	420 pcs. 74LS series IC kit	\$169.95	\$153.95
<b>130391</b>	Refill for 84961 (420 pcs.)	154.95	139.95

\*For additional products, availability and specifications visit [Jameco.com](http://Jameco.com) and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)