

Panel Mount Indicators & Lamps



Panel Mount Indicators (Incandescent, LED, Neon)

* Web Code: SOL

These bright indicator lights come equipped with quick and easy connections. Available in many different types for your specific needs.

- .187"/.250" tabs; clamp screw; stripped & tin wires termination
- Red, amber, yellow, green, blue or white
- 22mm (0.88") mounting hole
- Lens and hex nut: polycarbonate
- UL/CUL/TUV/CE approved
- Diffuser: polyacetal
- Hex nut and panel seal mounting hardware
- Housing: PBT w/ 20% glass



Part No.	Mfr. Part No.	Fig.	Voltage (V)	Color	Mounting Hole	Type	Termination	1	10	100
2129457	3335-4-50-183-A-1001	1	14	Red (temperature Indicator)	0.375" x 1.38"	Incandescent	0.250" tabs	\$.39	\$.35	\$.29
2126424	KE12-4-03-01020	2	14	Amber (translucent lens)	0.63"	LED	0.250" tabs	.99	.89	.79
2126408	KE12-4-03-01050	2	14	Blue (translucent lens)	0.63"	LED	0.250" tabs	.99	.89	.79
2129545	4416-1-20-010-1	3	250	Red	0.250"	LED	9" wires	.49	.39	.35
2126512	2954-X-11-373-10	4	480	Red	0.50"	Neon	15" wires	.49	.39	.35



Fig. 4

Neon Bulb

* Web Code: NOB

Part No.	Mfr. Part No.	Fig.	Description	1	10	100
2129553	9950-X-00-00000-0002	5	125V Neon bulb with 46k resistor, 2" wires	\$.29	\$.25	\$.15



Fig. 5


JAMECO ValuePro LED Panel Mount Indicators

* Web Code: SOL

- Easy panel installation
- Panel/status/instrument indicators

141111/141129/141137: Chrome housing

NEW MARKED IN PINK



141111

141129/141137

637183

Part No.	Cross Ref. No.	Mfr.	LED Size	Color	Dimensions (in.)			Mounting Hole	VI @ IF	Pricing		
					L	A	B			1	10	100
141111	L922SRD	JVP	T1	Red	.56	.34	.25	.23"	2V @ 20mA	\$ 1.09	\$.99	\$.85
141129	L913RD	JVP	T1	Red	.56	.39	.32	.24"	2V @ 20mA	1.25	1.15	.99
141137	L917RD	JVP	T1 3/4	Red	.70	.55	.47	.31"	2V @ 20mA	1.25	1.09	.99
637183	UT2U1G-H113-R801-W05	JVP	T1 3/4	Green	.55	5.5	5.5	.24"	12V @ 10mA	1.09	.99	.89
2158936	UT2U1W-H113-R801-1739	LED	T1 3/4	White	.55	5.5	5.5	.24"	12V @ 30mA	1.09	.99	.89
2215427	11-2426B	LKG	T1 3/4	Green	.66	6.0	6.0	.25"	12-14V range	2.49	2.25	1.95
2230563	XPG1LCWD01M12VW6	JVP	10mm	White	.83	6.0	6.0	.55"	14V @ 8.6mA	3.95	3.49	2.95
2230571	XPG1LCBD01D12VW6	JVP	10mm	Blue	.83	6.0	6.0	.55"	14V @ 8.6mA	3.95	3.49	2.95
2230580	XPG1LMD01D12VW6	JVP	10mm	Red	.83	6.0	6.0	.55"	14V @ 8.6mA	3.95	3.49	2.95

† Has internal resistor to run 12V @ 10mA * Has 5.5" wire leads ‡ Additional panel mounting hardware, P/N 2182602 (pg 78)

JAMECO ValuePro Neon Panel Mount Lamps

- Input voltage: 120V
- Mounting hole dia.: 5/8" (16mm)
- Solder terminals: 0.196" (5mm)



215803

1585485:

- Rectangular
- 6" wire leads
- Size: .91"L x .38"W x .77"D



1585485

Part No.	Cross Ref. No.	Color	1	10	100
215803	R9-71N-05-120V-R	Red	\$ 1.95	\$ 1.75	\$ 1.49
215812	R9-71N-05-120V-Y	Yellow	1.95	1.75	1.49
215830	R9-71N-05-120V-G	Green	2.05	1.99	1.69
2202651	120VNEON	††	5.95	5.39	4.29
1585485	32501001714	Green	.29	.19	.15

†† 2 red, 1 yellow, 1 green

JAMECO ValuePro 12V Incandescent Panel Mount Lamps

- 215715: Solder terminals - 0.196" (5mm)

* Web Code: JBJ

Part No.	Cross Ref. No.	Fig.	Color	Mounting Hole	Wire Length	1	10	100
2181360	NN792-12V-12CM-RED	1	Red	9/32" (7mm)	4.7" (120mm)	\$ 1.55	\$ 1.39	\$ 1.25
2158506	F151-12G	1	Green	9/32" (7mm)	Terminals	.79	.69	.59
2181378	FNN792-12V-12CM-GRN	1	Green	9/32" (7mm)	4.7" (120mm)	1.49	1.25	1.09
215715	R9-71B-05-12V-R	2	Red	5/8" (16mm)	Terminals	2.25	1.95	1.79

§ Additional panel mounting hardware, P/N 2182688 (pg 78)



Fig. 1



Fig. 2

Incandescent/Neon Panel Mount Lamps

* Web Code: JBJ

- Mounting hole: .310" Dia. (except P/N 2228471: .495" Dia.)




Part No.	Voltage	Lead	1	10	100
2099788	2.7VDC @ 60mA#	10"	\$.39	\$.35	\$.29
2228463	14VDC @ 80mA#	10"	.79	.69	.59
2179737	125VAC @ 0.3W*†	6"	3.49	2.95	2.59
2228471	125VAC @ 0.3W†	6"	3.95	3.59	3.19

* Manufacturer: LKG Industrial #Incandescent † Neon

Dialight

Panel Mount Indicators



2183269

2182910

2182928

2182995

The panel mount indicator chart below shows a variety of lens and lamps to complete your lighting requirements.

Panel Indicators	2183269	2183437	2182881	2182872	2182910	2182899	2182928	2182995
	\$ 1.95	\$ 1.95	\$ 1.95	\$ 1.95	\$ 1.95	\$ 1.95	\$.99	\$.99
Voltage for Indicators	110-125VAC	110-125VAC	110-125VAC	110-125VAC	105-125 VAC/VDC	210-250 VAC/VDC	110-125VAC/30VDC	1-28VDC
Lens	2182952 2182830	2182952 2182830	2182864 2182848 2182944 2183445 2183584	2182864 2182848 2182944 2183445 2183584	2182864 2182848 2182944 2183445 2183584	2182864 2182848 2182944 2183445 2183584	2183621	2182987 2182979
2182864	\$.99	\$.99	\$.99	\$.99	\$.99	\$.99	\$.29	\$.25
Lamps	2203303	2203303	209437 209402	209437 209402	2203291	2203291	392690 392681 392702	392690 392681 392702
2203291	1 1.49 10 1.25	1 1.49 10 1.25	1 .49 10 .45	1 .49 10 .45	1 .95 10 .85	1 .95 10 .85	1 .95 10 1.75	1 .95 10 1.75

LED AND LED DISPLAY GRAB BAGS

JAMECO ValuePro 18041

Part No.	Description	Price
18041	100 assorted LEDs (all colors) (T1 & T1 1/2 round and rectangular)	\$ 6.95
2226943	100 assorted LEDs (red only)	4.95
2226951	100 assorted LEDs (green only)	4.95
2226960	100 assorted LEDs (yellow only)	4.95
135271	1800 assorted LEDs (all colors) #18041	59.95
2203311	100 assorted PCB housing colored LEDs (T1 & T1 1/2 single to multiple rt. angle LEDs)	4.95
18201	50 assorted sizes of colored displays (7-seg, LCD, dot-matrix, bar graph)	19.95

* For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box

3 LEVELS OF SAVINGS

NAME BRANDS	HOUSE BRANDS	SPECIAL BUY
-------------	--------------	-------------

Order by Phone at 1-800-831-4242 or Online at www.Jameco.com