

DC Brushless Tubeaxial Fans

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **SPECIAL BUY**



Call for additional OEM PRICING – we carry major manufacturers.

DC Brushless Tubeaxial Fans & Blowers

* 5V Web Code: TAS

* 12V Web Code: LBZ

NEW
 MARKED IN PINK



695050



2134125



2131944

mm to Inches Conversion Chart

mm	6	6.8	10	15	20	25	28	30	32	35	38	40	45	51	60	70	75	76	80	92	94	95	97	120	125	126	127	150	172
Inches	0.24	0.27	0.40	0.60	0.80	1.00	1.10	1.18	1.26	1.40	1.50	1.60	1.80	2.00	2.36	2.76	2.95	2.99	3.15	3.63	3.70	3.74	3.82	4.72	4.92	4.96	5.00	5.90	6.77

Fans

Part No.	Manufacturer	Mfr. Part No.	Voltage (VDC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Pricing			
												1	10	50	100
2134088	Adda	AD2005LX-K70	5	20 x 20 x 6	0.6	Hypro	60	0.3	TUV/CE	12	5.5"	\$10.95	\$9.95	\$8.95	\$7.95
2131872	Adda	AD0205MX-K53-LF	5	25 x 25 x 6	2.4	Hypro	120	0.6	CE	29	6" ¹	8.95	7.95	6.95	5.95
131247	Adda	AD0205LX-G50-LF	5	25 x 25 x 10	1.8	Hypro	100	0.5	UL/CSA/CE	15.6	5.5"	7.95	6.95	6.25	5.95
2132197	Adda	AD0205MB-G50GL	5	25 x 25 x 10	2.2	Ball	120	0.6	UL/CUL/TUV/CE	23	5.5"	8.95	7.95	6.95	6.25
695050	Sunon	GM0502PFV2-8	5	25 x 25 x 10	3.0	Vapo	80	0.4	UL/CUL	16	5.5"	9.95	8.95	7.95	6.95
2188924	Adda	AD0305HX-K70(TX)	5	30 x 30 x 6	3.5	Hypro	180	0.9	UL/CUL/TUV/CE	32	5.5"	6.95	5.95	5.49	4.95
2208905	Sunon	KDE0503PEB1-8	5	30 x 30 x 6	4.9	Ball	180	0.9	UL/CUL/TUV/CE	28	5.5"	4.95	4.49	3.95	3.49
2203354	Adda	AB3505LB-QB0 [†]	5	35 x 35 x 7	0.09	Ball	100	0.5	UL/CUL/TUV/CE	19	12"	6.95	5.95	4.95	3.95
2134096	Adda	AD3505MX-G53	5	35 x 35 x 10	6.0	Hypro	130	0.65	UL/CUL/TUV/CE	30	12" ¹	4.95	4.49	3.95	3.49
1708457	Sunon	KDE0504PEB3-8 (MS)	5	40 x 40 x 6.8	3.5	Ball	90	0.45	UL/CUL/TUV	20	6"	4.95	4.49	3.95	3.59
2167242	Adda	AD0405LB-K90(S)-LF	5	40 x 40 x 6.8	4.5	Ball/Sleeve	50	0.25	UL/CUL/TUV/CE	19.9	5.4"	7.95	6.95	6.25	5.95
2220200	Adda	AD0405MB-K90	5	40 x 40 x 6.8	5.2	Ball	90	0.45	UL/CUL/TUV/CE	23.8	5.5"	7.95	6.95	6.25	5.59
2133886	Adda	AD0405LX-G70	5	40 x 40 x 10	4.7	Hypro	80	0.40	UL/CUL/TUV/CE	21	11"	5.95	5.39	4.79	4.39
2258814	Adda	AD0405MB-G76	5	40 x 40 x 10	5.0	Ball	110	0.55	UL/CUL/TUV/CE	22	4" w/ conn ¹	4.95	4.49	3.95	3.49
2138628	Adda	AD0405MB-G70-LF	5	40 x 40 x 10	5.7	Ball	110	0.55	UL/CUL/TUV/CE	22	12"	7.95	6.95	5.95	5.49
2220091	Adda	AD0405MK-G70	5	40 x 40 x 10	5.7	Hypro	110	0.55	UL/CUL/TUV/CE	15.9	4"	5.95	5.39	4.79	4.29
2131928	Adda	AD0405MX-G76-LF	5	40 x 40 x 10	5.7	Hypro	110	0.55	UL/CUL/TUV/CE	15.9	11" ¹	4.95	4.49	3.95	3.49
1928353	Adda	AD0405HX-G70	5	40 x 40 x 10	6.7	Hypro	190	0.95	UL/CUL/TUV/CE	30	11"	5.95	5.39	4.79	4.29
2229933	Sunon	EE40100S1-0000-999	5	40 x 40 x 10	8.0	Sleeve	271	1.36	UL/CUL/TUV	32	12"	7.95	6.95	6.25	5.95
2132189	Adda	AD0405HB-G70	5	40 x 40 x 10	8.7	Ball	100	0.8	UL/CUL/TUV/CE	25	12" w/ conn	4.95	4.49	3.95	3.49
2230993	Delta	FBK04F05L	5	40 x 40 x 20	3.9	Ball	120	0.6	UL/UR	24	10"	6.95	6.25	5.59	4.95
2131910	Adda	AD0405MX-C50-LF	5	40 x 40 x 20	8.1	Hypro	160	0.8	UL/CUL/TUV/CE	27	13"	6.95	6.25	5.59	4.95
2134133	Adda	AP.505HB-J90	5	45 x 45 x 8	6.0	Hypro	120	0.6	UL/CUL/TUV/CE	31	5"	9.95	8.95	7.95	6.95
2134125	Adda	AP0505HB-J90 [§]	5	50 x 50 x 8	6.0	Ball	140	0.60	UL/CUL/CE	30	5"	3.95	3.49	2.95	2.49
136494	Delta	AFB0505LA	5	50 x 50 x 10	7.4	Ball	120	0.4	UL/CE/CSA/VDE	26	11"	5.95	4.95	3.95	3.49
2150774	Adda	AD0505MB-G70-LF	5	50 x 50 x 10	10.5	Ball	180	0.9	UL/CUL/TUV/CE	24	12"	9.95	8.95	8.49	7.95
2121324	Adda	AD0505MB-G76LF	5	50 x 50 x 10	10.5	Ball	180	0.9	UL/CUL/TUV/CE	24	11" ¹	7.95	6.95	5.95	4.95
2186241	Sunon	KDE0505PPV1.11.MS.A.GN	5	50 x 50 x 10	13	Vapo	270	1.4	UL/CUL/VDE	30	16" w/ conn	8.95	7.95	6.95	5.95
2132120	Adda	AD0605LB-A72GL	5	60 x 60 x 25	13.8	Ball	150	0.75	UL/CUL/TUV/CE	20.3	12" ¹	5.95	5.39	4.79	4.29
2131944	Adda	AD0605HB-A71-LF	5	60 x 60 x 25	23.2	Ball	450	2.25	UL/CUL/TUV/CE	32	11"	6.95	6.25	5.59	4.95
2131952	Adda	AD0605HB-A72GL	5	60 x 60 x 25	24.3	Ball	450	2.25	UL/CUL/TUV/CE	36	12" ⁵	6.95	6.25	5.59	4.95
2258671	Adda	AD0805HB-D71	5	80 x 80 x 15	29.9	Ball	430	2.1	UL/CUL/TUV/CE	33	12"	10.95	9.95	8.95	7.95
2095269	Adda	AD2012LX-G70(X)	12	20 x 20 x 10	0.6	Hypro	60	0.84	UL/CUL/CE	20	5.5"	7.95	6.95	5.95	4.95
2227655	Adda	AD0212MX-K50	12	25 x 25 x 6	2.4	Hypro	60	0.72	UL/CUL/TUV/CE	29	5.5"	11.95	10.95	9.95	8.95
2179454	Jamicon	KF0210S1H	12	25 x 25 x 10	2.57	Sleeve	120	1.44	UL/TUV/CE	27.4	12"	3.95	3.49	2.95	2.49
2121316	Adda	AD0212HB-G50GL	12	25 x 25 x 10	2.8	Ball	90	1.08	UL/CUL/CE	29	5.5"	5.95	5.39	4.79	4.29
2133958	Adda	AD0312DB-G50	12	30 x 30 x 10	2.18	Ball	50	0.6	UL/CUL/CE	17	12"	5.95	5.39	4.79	4.29
212741	Sunon	KDE1235PFB2-8	12	35 x 35 x 10	4.5	Ball	60	0.8	UL/CUL/TUV/CE/VDE	21	3" w/ conn	6.95	6.25	5.59	4.95
2179411	Sunon	MF35101V1-10000-A99	12	35 x 35 x 10	7.2	Vapo	60	0.72	UL/CUR/TUV/CE	28	5.5"	11.95	10.95	9.95	8.95
2186224	Delta	FFB03812VHN-F00	12	38 x 38 x 28	20.2	Ball	650	7.8	UL/CSA/VDE/CE	58.5	13" ¹	5.95	4.95	4.49	3.95
2215435	Adda	AD0412HX-K96 (X)	12	40 x 40 x 6	5.4	Hypro	140	0.96	UL/CUL/TUV/CE	30.5	5.5" ¹	8.95	7.95	6.95	6.25
2132162	Adda	AD0412LS-G70(T)	12	40 x 40 x 10	4.7	Sleeve	70	0.84	UL/CUL/TUV/CE	14	12"	4.95	4.49	3.95	3.49
2095314	Adda	AD0412LX-G70	12	40 x 40 x 10	4.7	Hypro	70	0.84	UL/CUL/TUV	14	11"	5.95	5.39	4.79	4.39
2224180	Adda	AD0412LX-G76	12	40 x 40 x 10	4.7	Hypro	70	0.84	UL/CUL/TUV	14	12" ¹	5.95	5.49	4.95	4.49
2167630	Sunon	HA40101V4-0000-999	12	40 x 40 x 10	5.3	Vapo	65	0.8	UL/TUV/CE	18.2	12"	6.95	6.25	5.59	4.95
2133915	Adda	AD0412MX-G70	12	40 x 40 x 10	5.7	Hypro	80	0.96	UL/CUL/TUV/CE	20	11.5"	4.95	4.49	3.95	3.49
2197530	JMC	4010-12-HBHA	12	40 x 40 x 10	6.4	Dual Ball	80	0.96	UL/CUL/TUV	25	8" w/ conn ¹	7.95	6.95	6.25	5.59
2205384	Adda	AD0412HB-G70(T)	12	40 x 40 x 10	6.7	Ball	100	1.2	UL/CUL/TUV/CE	25	12"	6.49	5.49	4.95	4.49
2167234	Sunon	ME40101V1-0000-A99	12	40 x 40 x 10	8.0	Vapo	90	1.08	UL/CUL/TUV	32	12"	4.95	4.49	3.95	3.49
1708473	Sunon	KDE1204PPVX11.MS.A	12	40 x 40 x 10	9.5	Vapo	150	1.8	UL/CUL/TUV	39	12"	5.95	4.95	4.49	3.95
2228181	Delta	AFB0412LD	12	40 x 40 x 20	3.88	Ball	50	0.6	UL/CE/CSA/TUV	25	13"	3.95	3.59	3.29	2.95
2133835	Adda	AD0412DX-C50	12	40 x 40 x 20	4.9	Hypro	50	0.6	UL/CUL/TUV/CE	10	11"	4.95	4.49	3.95	3.59

¹ 3 leads; speed sensor ⁵ 3 leads; alarm (All fans operate to their specs with or without the additional optional wire functions) [§] DC chip cooler [†] Blower

For case mounting screws, P/Ns 2188481 or 2188490, page 78