

# AC-to-AC Wall Adapters



## AC-to-AC Wall Adapters

Input: 120VAC @ 60Hz

\* Web Code: **ABQ**



**NEW**  
MARKED IN PINK

Call for Additional OEM pricing.

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call for details.



Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VAC)	Current (mA)							1	10	50	100
2082521	Arndt	5-2634	5	400	1.7mm x 5.5mm right angle F	2.0 x 1.4 x 1.3	White	6'	0.4	UL/CSA	\$1.95	\$1.75	\$1.49	\$1.25
2230651	ReliaPro	ABU050050R	5	500	2.1mm x 5.5mm F	2.7 x 1.9 x 1.7	Black	6'	0.9	UL/CUL	7.95	6.95	6.25	5.95
100061	ReliaPro	ACU090050	9	500	2.1mm x 5.5mm F	2.7 x 1.9 x 1.7	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	5.95
2202773	Bogen	PI-41-43A	9	780	2.1mm x 5.5mm right angle F	2.4 x 2.0 x 1.6	Black	6'	0.6	UL/CSA	7.95	6.95	6.25	5.59
102234	ReliaPro	ACU090100	9	1000	2.1mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	6.95
157041	ReliaPro	ACU090100E8942	9	1000	2.5mm x 5.5mm F	2.1 x 2.1 x 1.6	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	6.95
2227444	ReliaPro	ADU090150	9	1500	2.1mm x 5.5mm F	2.9 x 2.3 x 1.8	Black	6'	0.9	UL/CUL	10.95	9.95	8.95	7.95
112336	ReliaPro	ACU090150A2231	9	1500	2.5mm x 5.5mm F	2.5 x 2.2 x 2.0	Black	6'	0.9	UL/CUL	10.95	9.95	8.95	7.95
101258	ReliaPro	ACU120050	12	500	2.1mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	5.95
2179614	ReliaPro	ACU120050R	12	500	2.5mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.4	UL/CUL	8.95	7.95	6.95	5.95
10081	ReliaPro	AD-1201000AU1	12	1000	2.1mm x 5.5mm F	2.5 x 2.0 x 1.6	Black	6'	0.7	UL/CUL	9.95	8.95	7.95	7.29
100167	ReliaPro	ACU120100D0531	12	1000	2.5mm x 5.5mm F	3.2 x 2.4 x 2.0	Black	6'	0.7	UL/CUL	9.95	8.95	7.95	7.29
10428	ReliaPro	ACU120100Z9121	12	1000	3.5mm M	2.6 x 2.4 x 2.0	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	6.29
2167576	Arndt	AM-121200A	12	1200	2.1mm x 5.5mm right angle F	3.2 x 2.1 x 1.9	Black	6'	0.9	UL/CSA	6.95	6.25	5.49	4.95
167151	ReliaPro	ADU120150	12	1500	2.1mm x 5.5mm F	3.4 x 2.7 x 2.2	Black	6'	1.5	UL/CUL	11.95	10.95	9.95	8.95
307838	ReliaPro	ADU120160H4120	12	1600	2.5mm x 5.5mm F	2.9 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	12.95	11.95	10.95	9.95
206404	ReliaPro	MGT1220	12	1670	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	9.95	8.95	7.95	7.29
2197581	ReliaPro	GPU48120200WA00	12	2000	2.1mm x 5.5mm F	3.3 x 2.6 x 2.2	Black	6'	1.7	UL/CUL	14.95	13.49	11.95	10.49
2227604	ReliaPro	GPU48120200WA0-2.5	12	2000	2.5mm x 5.5mm F	3.3 x 2.6 x 2.2	Black	6'	1.7	UL/CUL	14.95	13.49	11.95	10.49
2197847	Arndt	A71235DC	12	3500	Stripped & tinned (Table-Top style)	3.9 x 2.7 x 2.2	Black	6'	2.1	UL/CSA	9.95	8.95	7.95	6.95
2202765	Arndt	240000000043	13.5	1000	2.1mm x 5.5mm F	2.8 x 2.2 x 1.8	Black	6'	0.6	UL/CUL	3.95	3.49	2.95	2.49
171408	ReliaPro	ACU140050	14	500	2.1mm x 5.5mm F	2.8 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	6.25
318684	ReliaPro	ACU140085	14	850	2.5mm x 5.5mm right angle F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	11.95	10.95	9.95	8.95
100108	ReliaPro	ADU160100	16	1000	2.1mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
2227612	ReliaPro	ADU160100-2.5	16	1000	2.5mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
2230635	ReliaPro	MGT1640#	16.5	2400	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	11.95	10.95	9.95	9.49
2217748	Arndt	ZMCE-014	18	300	Stripped/tinned	2.3 x 1.6 x 1.4	Black	6'	0.5	UL/CUL	4.95	4.49	3.95	3.49
2217916	Arndt	218054	18	500	2.1mm x 5.5mm F	2.7 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	5.95	4.95	4.49	3.95
121216	ReliaPro	ADU180100	18	1000	2.1mm x 5.5mm F	3.1 x 2.7 x 1.9	Black	6'	1.1	UL/CUL	11.95	10.95	9.95	8.95
2227621	ReliaPro	ADU180100-2.5	18	1000	2.5mm x 5.5mm F	3.1 x 2.7 x 1.9	Black	6'	1.1	UL/CUL	11.95	10.95	9.95	8.95
2179622	ReliaPro	AFU180200	18	2000	2.1mm x 5.5mm F	3.4 x 2.7 x 2.1	Black	6'	1.7	—	12.95	11.95	10.95	9.95
87581	ReliaPro	ADU240050	24	500	2.1mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95
140599	ReliaPro	ADU240100D5531	24	1000	2.1mm x 5.5mm F	3.0 x 2.2 x 1.9	Black	6'	1.2	UL/CUL	11.95	10.95	9.95	8.95
10102	ReliaPro	ADU240100E0461	24	1000	3.5mm M	3.0 x 2.2 x 1.9	Black	6'	1.2	UL/CUL	11.95	10.95	9.95	8.95
2100195	ReliaPro	GPU572401500WA00	24	1500	2.1mm x 5.5mm F	3.3 x 2.6 x 2.3	Black	6'	1.7	UL/CUL	14.95	13.49	11.95	10.95
2227639	ReliaPro	GPU572401500WA00-2.5	24	1500	2.5mm x 5.5mm F	3.3 x 2.6 x 2.3	Black	6'	1.7	UL/CUL	14.95	13.49	11.95	10.95
2230627	ReliaPro	MGT2440#	24	1600	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	11.95	10.95	9.95	9.49
2197548	ReliaPro	GPU572402000WA00	24	2000	2.1mm x 5.5mm F	3.3 x 2.6 x 2.2	Black	6'	1.7	UL/CUL	15.95	14.49	12.95	11.49
2229386	ReliaPro	MGT2450P	24	2100	Screw Terminal	3.2 x 2.2 x 1.9	White	—	0.9	UL	17.75	15.95	14.49	12.95

# Level VI efficiency

Power

## REGULATED SWITCHING AC-to-DC WALL ADAPTERS — NEW ARRIVALS

Part No.	Voltage	Current	Page	Price	Image	Part No.	Voltage	Current	Page	Price
2230408	5VDC	0.75A	90	\$6.95		2230264	12VDC	1.0A	90	\$7.95
2188713	5VDC	1.2A	90	5.95		2218142	12VDC	1.5A	90	8.95
2227735	5VDC	1.5A	90	7.95		2228922	12VDC	2.0A	91	10.95
2230133	6VDC	0.5A	91	8.95		2229845	12VDC	3.5A	91	12.95
2228965	9VDC	1.0A	90	8.95	2229888	24VDC	1.0A	91	12.95	
2229183	12VDC	1.0A	90	6.95	2230416	24VDC	1.0A	91	10.95	
2229765	12VDC	1.0A	90	8.95	2167613	24VDC	2.0A	91	15.95	

\* For additional products, availability and specifications visit [Jameco.com](http://Jameco.com) and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)