

AC-to-DC Regulated Switching Wall Adapters

Jameco carries the full line of Mean Well products. For additional Mean Well products visit www.Jameco.com/meanwellproducts




AC-to-DC Regulated Switching Wall Adapters (Continued)



★ Web Code: CDZ

Call for Additional OEM pricing.

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call for details.



Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ◆	Input VAC @ Hz	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing		
			Volt. (VDC)	Current (mA)								1	10	50
2215726	Arndt	P03WF-120B*	12	2500	2.1mm x 5.5mm F 2	100-240@50-60	3.0 x 1.4 x 2.0	Black	6'	0.3	UL/CUL/CEC	\$10.95	\$9.95	\$8.95
2173116	ReliaPro	KSAS0361200300HU-6†	12	3000	2.1mm x 5.5mm F 2	100-240@50-60	3.9 x 1.7 x 1.2	Black	6'	0.6	UL/CUL/CEC	13.49	11.95	11.49
2230643	ReliaPro	ST-123A#	12	3000	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	—	0.5	UL/CUL	17.95	16.49	14.95
196369	Mean Well	GSM06U15-P1J**	15	400	2.1mm x 5.5mm F 2	80-264@47-63	2.6 x 1.3 x 1.7	Black	6'	0.3	UL/CUL/TUV/CE	9.75	8.65	7.95
1952871	Mean Well	GS18U15-P1J	15	1200	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.4	Black	6'	0.4	UL/CUL/CEC	11.95	10.95	10.49
2225617	Mean Well	GST18U15-P1J#	15	1200	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	11.75	10.25	9.49
2225684	Mean Well	GST25U15-P1J#	15	1660	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	12.19	10.79	9.95
380173	Mean Well	GS25U15-P1J	15	1670	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CE	12.49	11.49	10.49
2173108	ReliaPro	EA1030CU†	15	2000	2.1mm x 5.5mm F 2	100-240@50-60	3.9 x 1.7 x 1.2	Black	6'	0.6	UL/CUL/CEC	13.95	12.95	11.95
380191	Mean Well	GS25U18-P1J	18	1380	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 1.2 x 1.3	Black	6'	0.5	UL/CUL/CEC	12.49	11.49	10.49
2225692	Mean Well	GST25U18-P1J#	18	1380	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	12.19	10.79	9.95
1952898	Mean Well	GS18U24-PIJ	24	750	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	11.95	10.95	10.49
2225545	Mean Well	GST18U24-P1J#	24	750	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	11.75	10.25	9.49
2121594	ReliaPro	ST-241A	24	1000	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	—	0.3	UL/CUL/CEC	15.95	14.49	12.95
2229888	ReliaPro	MTR-08395#	24	1000	2.1mm x 5.5mm F 2	100-240@50-60	3.4 x 2.7 x 2.2	Black	6'	0.5	UL/CUL/CEC	12.95	11.95	10.95
2230416	Phihong	PDA024A-1A0S-R	24	1000	2.1mm x 5.5mm F 2	110-120@50-60	3.4 x 2.1 x 1.2	Black	4'	0.3	UL/CUL	10.95	9.95	8.95
1953671	ReliaPro	MPC-2400107	24	1000	2.5mm x 5.5mm F 2	120-240@50-60	3.4 x 2.7 x 2.2	Black	6'	0.5	UL/CSA	14.95	13.49	11.95
380202	Mean Well	GS25U24-P1J	24	1040	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	12.49	11.49	10.49
2225561	Mean Well	GST25U24-P1J#	24	1040	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	12.19	10.79	9.95
2167613	ReliaPro	ST-242A	24	2000	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	6'	0.3	—	15.95	14.95	13.95
380220	Mean Well	GS25U28-P1J	28	890	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.6	UL/CUL/CEC	12.49	11.49	10.49
2225705	Mean Well	GST25U28-P1J#	28	900	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	12.19	10.79	9.95
2179391	ReliaPro	PA1024-360HU	36	670	2.5mm x 5.5mm F 2	90-264@47-63	2.7 x 1.8 x 1.3	Black	6'	0.3	UL/CUL/CEC	12.95	11.95	11.49
2225713	Mean Well	GST25U48-P1J#	48	520	2.1mm x 5.5mm F 2	85-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.3	UL/CUL/TUV/CE	12.49	12.19	10.79

†RFI filter on cord *Slimline **Medical rated # Level VI efficiency ✓ CEC

Power



AC-to-DC "Slimline" Regulated Switching Wall Adapters



Output connector: 2.1mm x 5.5mm F2 (center positive)

• 2-wire AC input • Output cord length: 6' • Color: black • Input volt.: 100 – 240VAC @ 47-63Hz



Part No.	Manufacturer	Output Rating		Size (in.) (H x W x D)	Wt. (lbs.)	Pricing				Part No.	Manufacturer	Output Rating		Size (in.) (H x W x D)	Wt. (lbs.)	Pricing			
		Volt. (VDC)	Curr. (mA)			1	10	50	100			Volt. (VDC)	Curr. (mA)			1	10	50	100
2173010	Phihong	5	400	1.9x1.4x0.9	0.1	\$4.95	\$4.49	\$3.95	\$3.59	1950841	ReliaPro	9	1000	2.5x1.1x1.7	0.2	\$10.95	\$9.95	\$8.95	\$7.95
252701	ReliaPro	5	500	2.9x1.1x1.7	0.3	6.95	6.25	5.59	4.95	252779	ReliaPro	9	1200	2.9x1.3x2.2	0.3	11.49	10.25	9.49	8.95
2126125	OEM	5	800	1.9x1.6x0.9	0.1	6.95	5.95	5.49	4.95	252786	ReliaPro	9	1500	2.9x1.3x2.2	0.3	12.95	11.95	10.95	9.95
252720	ReliaPro	5	1000	2.5x1.1x1.7	0.2	9.95	8.95	7.95	6.95	252795	ReliaPro	12	250	2.5x1.1x1.7	0.2	8.95	7.95	6.95	6.25
2211098	Phihong	5	1000	2.6x1.4x1.1	0.2	6.95	6.25	5.59	4.95	2150758	Arndt	12	500	2.5x1.7x1.1	0.2	7.95	6.95	6.25	5.95
1940660	Mean Well	5	1000	2.6x1.3x1.9	0.2	9.49	8.49	7.95	7.25	252808	ReliaPro	12	500	2.5x1.1x1.7	0.2	8.95	7.95	6.95	6.25
252728	ReliaPro	5	1500	2.5x1.1x1.7	0.2	10.95	9.95	8.95	7.95	1940694	Mean Well	12	500	2.6x1.3x1.9	0.2	9.49	8.49	7.95	7.25
210894	ReliaPro	5	2000	2.9x1.4x2.2	0.2	10.95	9.95	8.95	7.95	2232825	Arndt	12	1000	2.4x1.6x1.1	0.3	10.95	9.95	8.95	7.95
2217772	ReliaPro	5	2000	3.0x1.6x1.2	0.2	11.95	10.95	9.95	8.95	252824	ReliaPro	12	1000	2.9x1.3x2.2	0.3	12.95	11.49	9.95	8.95
2230336	DVE	5	2500	2.7x1.7x1.1	0.3	10.95	9.95	8.95	7.95	252833	ReliaPro	12	1250	2.9x1.3x2.2	0.3	13.95	12.95	11.95	10.95
252736	ReliaPro	5	2500	2.9x1.3x2.2	0.3	12.95	11.95	10.95	9.95	2228922	Arndt	12	2000	2.9x1.9x1.2	0.3	10.95	9.95	8.95	7.95
2224016	ReliaPro	5	3000	3.3x1.7x1.3	0.2	13.95	12.95	11.95	10.95	1950497	ReliaPro#	12	2000	2.9x2.1x1.3	0.4	15.95	14.49	12.95	11.49
2145078	Arndt	6	500	2.5x1.7x1.1	0.3	6.95	5.95	4.95	4.49	2229845	Arndt	12	3500	3.3x2.7x1.1	0.5	12.95	11.95	10.95	9.95
2230133	ReliaPro#	6	500	2.3x1.6x1.1	0.3	8.95	7.95	6.95	6.25	252904	ReliaPro	15	1000	2.9x1.3x2.2	0.3	12.95	11.95	10.95	9.95
1940678	Mean Well	7.5	800	2.6x1.3x1.9	0.2	9.49	8.49	7.95	7.25	2229941	ReliaPro#	24	500	2.9x2.2x0.3	0.3	11.95	10.95	9.95	8.95
252753	ReliaPro	9	500	2.5x1.1x1.7	0.2	10.95	9.95	8.95	7.95	2076341	ReliaPro	24	630	2.9x1.3x2.2	0.3	11.95	10.95	9.95	8.95
1940686	Mean Well	9	660	2.6x1.3x1.9	0.2	9.49	8.49	7.95	7.25	2208972	ReliaPro	24	1000	3.5x1.7x1.3	0.3	12.95	11.49	10.95	9.95

Level VI efficiency

*For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com