

Power Supplies, Wall Adapters & Power Cables

10-Watt Switching Wall Adapter

- Output voltage: 3, 4.5, 6, 7.5, 9, 12VDC selectable
- Output connectors: 2.5mm and 3.5mm male, 1mm x 3mm, 1.35mm x 3.5mm, 1.7mm x 4mm, 2.1 x 5mm, 2.5mm x 5.5mm, 1.5mm x 5.5mm female
- Input voltage: 100-230VAC, 50/60Hz • Output current: 0.8 to 1.5A

Part No.	Mfr. Part No.	Size (L x W x H)	1	10
2137182	PSSMV1USA	2.6" x 1.1" x 2.9"	\$15.95	\$14.49

30-Watt Switching Table-Top Power Supply

- Output voltage: 5VDC to 12VDC in 1V increments
- Output connectors: 2.5mm & 3.5mm male, 1mm x 3mm, 1.35mm x 3.5mm, 1.5mm x 5mm, 1.7mm x 4mm, 2.1mm x 5mm & 2.5mm x 5mm female
- Stabilized outputs, low ripple & interference
- High efficiency, low energy consumption
- Input voltage: 100-240VAC @ 50/60Hz
- Short-circuit, overload protection
- LED power indicator

Includes: AC power cord

Part No.	Mfr. Part No.	Output Current	Size (L x W x H)	1	5	25
2158354	PSSE13U	1.5A to 4A	3.5" x 1.8" x 1.2"	\$39.95	\$35.95	\$31.95

Regulated Desktop/Benchtop Power Supply

This is a high powered, regulated power supply that is perfect for hobbyists. Typical applications are model railroads, slot car racing, science projects and other applications requiring 12V @ 24A power source. Features output connections heavy duty binding posts and cigarette lighter plug with a 2.1 x 5.5mm female plug.

- Input voltage: 100VAC to 240VAC @ 50-60Hz
- Max. output voltage: 12V @ 24A • CUL/UL recognized

Includes: 6' IEC power cord, 6' coiled cigarette lighter plug cord with a 2.1mm x 5.5mm right angle female plug

Part No.	Mfr. Part No.	Size (L x W x H)	Wt. (lbs.)	1	5	25
2197599	PS24B	14.5" x 6" x 3.5"	9.0	\$54.95	\$49.95	\$46.95

BEST SELLING AC-to-DC MEDICAL TABLE-TOP POWER SUPPLIES

Part No.	Power (W)	VDC / Amps	1	10
2179606	15	6 / 2.5	\$12.95	\$11.49
230683	15.6	12 / 1.3	34.95	29.95



USB-A Power Cable w/ Interchangeable Tips

- 4' cable • 26 AWG
- USB-A male connector • UL/CSA approved
- Tips: 1.3mm x 5.5mm, 1.7mm x 4.0mm, 1.7mm x 4.8mm, 2.1mm x 5.5mm, 2.5mm x 5.5mm, 2.9mm x 6.3mm female 3.2mm x 5.0mm and 4.3mm x 6.0mm male
- For use with P/N 2138636 wall adapters (below)

Part No.	Cross Ref. No.	1	10	50	100
2081625	USBAC8	\$5.95	\$5.39	\$4.79	\$4.29



5VDC @ 200mA Wall USB Adapter

- Works with digital camera, cell phones, PDA, MP3 and other USB devices • LED indicator
- TUV/FCC approved • Output voltage: 5VDC @ 200mA
- Input volt.: 100-240VAC @ 50/60Hz
- Size: 2.5"H x 1.5"W x 0.8"D • Cable and tips use P/N 2081625 (above)

Part No.	Mfr. Part No.	1	10	50	100
2138636	SW013US-0500020US	\$2.95	\$2.59	\$2.25	\$1.95

5VDC @ 1 & 2A USB Wall Adapters

- Works with digital camera, cell phones, PDA, MP3 and other USB devices
- Input voltage: 100-240VAC @ 50/60Hz
- Flip up prongs
- UL FCC approved
- Cable and tips use P/N 2081625 (see Web)

Part No.	Mfr. Part No.	Output Curr.	Size (H" x W" x D")	1	10	50	100
2210888	1128	1A	2.6 x 1.3 x 1.5	\$3.95	\$3.49	\$2.95	\$2.59
2227786	XA1005-2U	2A	2.7 x 1.7 x 1.0	4.95	4.49	3.95	3.59



1A & 2.1A In-Car USB Charger/Adapter

- Input voltage: 12VDC to 24VDC
- Output voltage: 2158320: 5VDC @ 1A; 2228391: Dual 2.1A & 1A
- Output connector: USB type A
- Compatible with iPhone, iPod, Samsung

Part No.	Cross Ref. No.	Size (L" x D1" x D2")	Voltage	1	10	50
2158320	CC001-BLK	2.1 x 0.9 x 0.8	1A	\$3.95	\$3.59	\$3.25
2228391	CAR-D2A	2.23 x 1.26 x 0.8	2.1/1A dual	5.95	5.39	4.79



DC Cords with Pigtail – 6' length

- 18-24 AWG • Color: black

Part No.	Cross Ref. No.	Fig.	AWG	Type	ID x OD x L (mm)	1	10	100
2229731	DC-168	1	18	Plug	2.1 x 5.5 x 12	\$2.59	\$2.35	\$2.15
2229706	DC-169	1	18	Plug	2.5 x 5.5 x 12	2.59	2.35	2.15
2229722	DC-173	2	18	Jack	2.1 x 5.5 x 12	2.59	2.35	2.15
2229714	DC-175	2	18	Jack	2.5 x 5.5 x 12	2.95	2.59	2.29
2096763	DCCORD2.1	1	24	Plug	2.1 x 5.5 x 12	1.95	1.75	1.59
2096771	DCCORD2.5	1	24	Plug	2.5 x 5.5 x 12	1.95	1.75	1.59
2114600	6FT#245.5X2.1	2	24	Jack	2.1 x 5.5 x 12	1.95	1.75	1.59
2114597	6FT#245.5X2.5	2	24	Jack	2.5 x 5.5 x 12	1.95	1.75	1.59



DC Extension and Splitter (Y) Power Cables

- 18 AWG • Color: black

Part No.	Mfr.	Cross Ref. No.	Description (Barrel)	Cable Lgth	1	10	100
2099147	ValuePro	DCEXTCORD2.1-3FT	2.1 F x 2.1 M	3'	\$2.49	\$2.25	\$1.95
2099121	ValuePro	DCEXTCORD2.1-6FT	2.1 F x 2.1 M	6'	2.95	2.59	2.25
2099155	ValuePro	DCEXTCORD2.5-3FT	2.5 F x 2.5 M	3'	2.49	2.25	1.95
2099139	ValuePro	DCEXTCORD2.5-6FT	2.5 F x 2.5 M	6'	2.95	2.59	2.25
2230192	Arndt	EN-DCM-2	2.1M to (2) 2.1F	9'	3.95	3.59	2.95
2230205	Arndt	2505	2.1M to (5) 2.1F	13'	4.95	4.49	3.95
2230213	Arndt	2508	2.1M to (8) 2.1F	16'	6.95	6.25	5.59

* Web Code: MFP



Automobile Fused Power Plugs with Cords

- Accepts .25" x 1.25" fuse
- 115002: Screw assembly with strain relief (no cord)
- 124760: 3' cord with pigtail
- 2229773: 3' cord with 2.1mm x 5.5mm connector

Part No.	Fuse	1	10	100
115002	5A/250VAC	\$2.25	\$1.95	\$1.75
124760	3A/250VAC	2.49	2.25	1.95
2229773	2A/250VAC	2.75	2.49	2.25



Power Cord Adapters

- 2188545: Receptacle IEC plug C14 to Nema 5-15R
- 2188553: Receptacle CEE 7/7 to Nema 5-15R plug

Part No.	Cross Ref. No.	1	10	50
2188545	YL-3215	\$3.95	\$3.59	\$3.29
2188553	YL-2215	3.95	3.59	3.29

* For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com