

# AC Tubeaxial Fans & Power Cords

3 LEVELS OF SAVINGS  
**NAME BRANDS** **HOUSE BRANDS** **SPECIAL BUY**



Call for additional OEM PRICING - we carry major manufacturers.

## 120 & 220VAC Tubeaxial Fans



COMMONWEALTH™



\* Web Code: **ABJ**

2126096

2205405

102892

2228287

Part No.	Manufacturer	Mfr. Part No.	Voltage (VAC)	Size mm (W x H x D)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection	Pricing			
												1	10	50	100
213867	Fulltech	UF60D11BWH	120	60 x 60 x 30	10.2	Ball	35	4	UL/CUL/VDE/CE	28	12" leads	\$17.95	\$16.49	\$15.95	\$14.49
2231734	ADDA	AA8251HB-AT	120	80 x 80 x 25	21	Ball	70	5.8	UL/CUL/TUV/CE	27	Terminals	12.95	11.95	10.95	9.95
2230660	Thermocoool	G8025HAS	120	80 x 80 x 25	23	Sleeve	130	13	UL/CUL/TUV/CE	30	12" leads	10.95	9.95	8.95	7.95
146078	Common Wealth	FP108AX-S1-B	120	80 x 80 x 25	23	Ball	180	14	UL/CE	29	12" leads	15.95	14.49	12.95	11.95
300557	Fulltech	UF80B11SWH	120	80 x 80 x 25	24	Sleeve	140	14	UL/CUL/TUV/CE	35	12" leads	13.95	12.95	11.95	10.95
2133819	Adda	AA8381MS-AT	120	80 x 80 x 38	24	Sleeve	80	9.2	UL/CSA/TUV/CE	26.2	Terminals	13.95	12.49	10.95	9.95
2228279	Mechatronics	UF80A12BWL	120	80 x 80 x 38	25	Ball	110	9	UL/CSA	32	11" leads	14.95	13.49	11.95	10.95
300600	Fulltech	UF80A11BWH	120	80 x 80 x 38	29	Ball	120	12	UL/CUL/TUV/CE	36	12" leads	15.95	14.49	12.95	11.49
300389	Fulltech	UF80A11BTH	120	80 x 80 x 38	30	Ball	120	12	UL/CUL/TUV/CE	36	Terminals	15.95	14.49	12.95	11.49
2126096	Common Wealth	FP-108B**	120	92 x 92 x 25	22	Ball	60	8	UL/CSA	24	15" leads	9.95	8.95	7.95	6.95
2234169	NMB	3610PS-12T-B20	120	92 x 92 x 25	28	Ball	90	6	CSA	35	Terminals	8.95	7.95	6.95	6.25
2230678	Thermocoool	G9225HAS	120	92 x 92 x 25	34	Sleeve	140	13	UL/CUL/TUV/CE	40	Terminals	10.95	9.95	8.95	7.95
303467	Sunon	SF11592A-1092HBL.GN	120	92 x 92 x 25	37	Ball	110	12	UL/CSA/TUV/CE	40	12" leads	12.95	11.95	10.95	9.95
2135275	Common Wealth	FP-108JC	120	92 x 92 x 38	45	Sleeve	150	10	UL/CSA/CE	37	12" leads	13.95	12.49	10.95	9.95
2131830	Adda	AA1251MB-AW	120	120 x 120 x 25	65	Ball	240	22.3	UL/CSA/TUV/CE	39	12" leads	15.95	14.49	12.95	11.49
1810048	Sunon	SP101AT-1122HBL.GN	120	120 x 120 x 25	78	Ball	180	18	UL/CUL/TUV/CE	46	12" leads	16.95	15.49	13.95	12.49
124063	Sunon	SP101AT-1122HBT.GN	120	120 x 120 x 25	78	Ball	180	18	CSA/TUV/CE	46	Terminals	16.95	15.49	13.95	12.49
2230379	EBM PABST	4800N	120	120 x 120 x 38	57.1	Sleeve	78	9	UL/CSA/CE	32	Terminals	14.95	13.49	11.95	10.95
303361	Fulltech	UF12A11BTL1	120	120 x 120 x 38	64	Ball	80	15	UL/CUL/TUV/CE	37	Terminals	14.95	13.49	11.95	10.95
2205392	Adda	AA1281MB-AW	120	120 x 120 x 38	80	Ball	140	16.1	UL/CUL/TUV/CE	40	12" leads	12.95	11.49	9.95	8.95
2205405	Adda	AA1281MB-AT(CF)	120	120 x 120 x 38	80	Ball	250	16	UL/CUL/TUV/CE	40	Terminals	13.95	12.49	10.95	9.95
2230694	Thermocoool	G12038MAB	120	120 x 120 x 38	85	Ball	220	19	UL/CUL/TUV/CE	44	Terminals	12.95	11.95	10.95	9.95
2231718	Sunon	SP102A-1123MBL.GN	120	120 x 120 x 38	88	Ball	160	15	UL/CUR/TUV/CE	40	12" leads	14.95	13.49	11.95	10.95
2100427	Adda	AA1281HS-AW	120	120 x 120 x 38	91	Sleeve	250	16	UL/CUL/TUV/CE	43	12" leads	11.95	10.95	9.95	8.95
2230686	Thermocoool	G12038HAS	120	120 x 120 x 38	95	Sleeve	280	21	UL/CUL/TUV/CE	48	Terminals	11.95	10.95	9.95	8.95
106586	Common Wealth	FP108-1-S1/T	120	120 x 120 x 38	105	Sleeve	180	12	UL/CSA/CE	47	Terminals	12.95	11.95	10.95	9.95
16935	Common Wealth	FP108-1-S1-B/T	120	120 x 120 x 38	105	Ball	200	17	UL/CSA/TUV/CE	47	Terminals	13.95	12.49	11.95	10.49
1707163	Sunon	SP101A-1123HBL-GN	120	120 x 120 x 38	107	Ball	180	18	UL/CSA/TUV	50	12" leads	15.95	14.49	12.95	11.49
2125931	Common Wealth	FP108-1	120	120 x 120 x 38	112	Ball	250	19	UL/CUL/TUV/CE	45	Terminals	13.95	12.49	11.49	9.95
102884	Sunon	SP100A-1123XBT.GN	120	120 x 120 x 38	117	Ball	240	20	UL/CUL/TUV/CE	50	Terminals	14.95	13.95	12.95	11.95
2231726	Sunon	SP100A-1123XBL.GN	120	120 x 120 x 38	117	Ball	240	20	UL/CUR/TUV/CE	50	12" leads	17.95	16.49	14.95	13.49
2230141	Fulltech	UF13A11BTH	120	127 x 127 x 38	120	Ball	160	12	UL/CUL/TUV/CE	50	Terminals	19.95	17.95	15.95	14.49
2230707	Thermocoool	G13538HAS	120	135 x 135 x 38	122	Sleeve	340	25	UL/CUL/TUV/CE	53	12" leads	13.95	12.49	11.25	10.49
2230715	Thermocoool	G15050HAS	120	150 x 150 x 50	198	Sleeve	400	38	UL/CUL/TUV/CE	59	12" leads	20.95	18.95	16.95	15.49
2227701	ETRI	148VE0282030	120	172 x 150 x 38	122	Ball	100	11	UL/CSA/CE	36	Terminals	29.95	26.95	24.95	21.95
2230723	Thermocoool	G17050HASB	120	172 x 172 x 51	198	Ball	400	38	UL/CUL/TUV/CE	59	Terminals	20.95	18.95	16.95	15.49
189684	Fulltech	UF15PC11BTH	120	172 x 150 x 51	226	Ball	250	30	UL/CUL/TUV/CE	58	Terminals	32.95	29.95	26.49	23.95
212582	Fulltech	UF15PC11BWH	120	172 x 150 x 51	226	Ball	250	30	UL/CUL/TUV/CE	58	12" leads	32.95	29.95	26.49	23.95
2230117	ADDA	AA8252HB-AT	220	80 x 80 x 25	21	Ball	60	13.8	UL/CUL/TUV/CE	27.8	Terminals	12.95	11.95	10.95	9.95
2235241	Adda	AA8382HX-AT	220	80 x 80 x 38	24	Hypro	70	8.8	UL/CUL/TUV/CE	25	Terminals	11.95	10.95	9.95	8.95
355630	Fulltech	UF-80A23-BTH-R	220	80 x 80 x 38	30	Ball	60	12	UL/CSA/VDE/CE	36	Terminals	12.95	11.49	10.25	9.49
100918	Fulltech	SF23080A/2083HSL.GN	220	80 x 80 x 38	30	Sleeve	60	13.5	UL/CSA/TUV/CE	35	12" leads	15.95	13.95	12.49	10.95
2210837	EG&G Rotron	SU3G1	220	80 x 80 x 38	32	Sleeve	70	10	UL/CSA	39	12" leads	8.95	7.95	6.95	6.25
2234177	NMB	3115FS-23T-B10-A00	230	80 x 80 x 38	33	Ball	87	6	UL/CSA	36	Terminals	10.95	9.95	8.95	7.95
2234636	NMB	3610FS-23T-B10-A00	230	92 x 92 x 25	28	Ball	50	7	UL/CSA	35	Terminals	12.95	11.95	10.95	9.95
2231566	ADDA	AA1252MB-AT	220	120 x 120 x 25	65	Ball	100	21.6	UL/CUL/TUV/CE	38	Terminals	14.95	13.49	11.95	10.95
2258419	Fulltech	UF12A1223BWH*	115/230	120 x 120 x 38	92/106	Ball	260/120	23	UL/CUL/TUV/CE	42/46	12" leads	15.95	14.49	12.95	11.59
2231996	Adda	AA1282HB-AT	220	120 x 120 x 38	96.1	Ball	130	16	UL/CUL/TUV/CE	42.2	Terminals	16.95	14.95	13.49	11.95
2133801	Adda	AA1282UB-AT	220	120 x 120 x 38	103	Ball	120	21	UL/CUL/TUV/CE	46	Terminals	17.95	15.95	14.49	12.95
303459	Sunon	DP200A-2123XBL.GN	220	120 x 120 x 38	117	Ball	120	21	UL/CSA/TUV/CE	50	12" leads	15.95	14.95	13.95	12.95
102892	Sunon	DP200A-2123XBT.GN	220	120 x 120 x 38	117	Ball	120	21	UL/CSA/TUV/CE	50	Terminals	17.95	15.95	14.49	12.95
2228287	Papst	RER125-19/56	230	138 x 40	61.2	Ball	120	19	UL/CSA/TUV/CE	65	15" leads	39.95	35.95	32.95	29.95
2230424	Commonwealth	FP-108EX (S-1)	220	172 x 150 x 51	210	Ball	220	32	UL/CSA/TUV/CE	50	Terminals	29.95	26.49	23.95	21.49

\* 4 wire leads, dual voltage \*\* 24 AWG quick disconnect terminals

For case mounting screws, P/Ns 2188481 or 2188490, page 78

## DC & AC Plug Fan Power Cords

\* Web Code: **GAE**

For Fans with Terminal Connection

Fig. 1 Straight

Fig. 2 45°

Fig. 3 90°

Part No.	Description	Fig.	Length	1	10	100	250
28564	Straight pigtail fan cord	1A	24"	\$1.49	\$1.25	\$ .99	\$ .89
2076658	Straight pigtail fan cord	1A	36"	1.59	1.45	1.29	1.15
1952548	45° pigtail fan cord	2A	24"	1.59	1.35	1.09	.99
104192	90° pigtail fan cord	3A	24"	1.59	1.35	1.09	.99
1952572	Straight AC plug fan cord	1B	72"	3.95	3.59	3.19	2.49
1952581	45° AC plug fan cord	2B	72"	4.95	4.59	3.95	3.49