

# Open-Frame Switching AC-to-DC Power Supplies



## Open-Frame Switching AC-to-DC Power Supplies

- Universal AC input/full range
- Two-year warranty
- Short-circuit, overload and overvoltage protection
- † **PFC Model:** • Built-in active Power Factor Correction function, power factor >0.93
- Three-year warranty



PS-25

LPP-150

PT-45

For special versions and large quantities call us at 1-800-831-4242

Part No.	Manufacturer	Mfr. Part No.	Output		Input (VAC @ Hz)	Size (L"xW"xH")	Mounting Holes (L"xW"xDia.)	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%)§	Certification	Pricing		
			Voltage @ Current (min-max)	Power									1	10	
* 3.3-5.5V Web Code: OFI			* 7.5-13.8V Web Code: OTW			Single Output						* 15-24V Web Code: OFT		* 27-54V Web Code: OFE	
2210722	Pihong	PSA25-105	+5V @ 0-4A	20W	100-240 @ 47-63	4.0x3.0x1.3	3.6x2.6x0.16	50	2.0	1.0	70	UL/CSA/VE	\$6.95	\$6.25	
2227583	Power One	BLP30-1005G	+5V @ 0-5A	25W	100-250 @ 50-60	4.0x2.0x1.0	3.7x1.7x0.15	100	2.0	1.0	70	UL/CUL/TUV/CE	6.75	5.89	
2227567	Power One	BLP40-1005G	+5V @ 0-5A	25W	100-250 @ 50-60	5.0x3.0x1.0	4.5x2.5x0.16	100	2.0	1.0	70	UL/CUL/TUV/CE	6.75	5.89	
212354	MEAN WELL	PS-25-5	+5V @ 0-5A	25W	100-250 @ 50-60	5.0x3.0x1.0	4.5x2.5x0.16	100	2.0	1.0	70	UL/CUL/TUV/CE	9.95	8.95	
217332	MEAN WELL	PS-45-5	+5V @ 0-8A	40W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.2	100	3.0	1.0	74	UL/CUL/TUV/CE	12.80	10.49	
2188772	UMEC	UP0401S-09	+9V @ 0-4.4A	40W	90-264 @ 47-63	4.0x3.0x1.0	3.6x2.6x0.2	100	1.0	1.0	70	UL/CSA/TUV	6.95	5.95	
2227559	Power One	BLP30-1012G	+12V @ 0-2.1A	25W	100-250 @ 50-60	4.0x2.0x1.0	3.7x1.7x0.15	100	2.0	1.0	70	UL/CUL/TUV/CE	6.75	5.89	
148604	MEAN WELL	PS-25-12	+12V @ 0-2.1A	25.2W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	100	2.0	0.3	78	UL/CUL/TUV/CE	11.50	9.49	
2164332	MEAN WELL	EPS-25-12	+12V @ 0-2.1A	25.2W	85-264 @ 47-63	3.0x2.0x1.0	2.8x1.8x0.13	100	0.5	0.5	86	UL/CUL/TUV/CE/CB	10.60	8.99	
2234724	MEAN WELL	PS-45-12 ✓	+12V @ 0-3.7A	44.4W	100-240 @ 50-60	5.0x3.0x1.1	4.6x2.6x0.2	100	2.0	1.0	76	UL/CUL/TUV/CE	8.95	7.95	
213728	MEAN WELL	PS-45-12	+12V @ 0-3.7A	44.4W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.2	100	2.0	1.0	76	UL/CUL/TUV/CE	11.25	10.49	
2248641	MEAN WELL	EPS-45S-12	+12V @ 0-3.8A	45.6W	80-264 @ 47-63	3.0x2.0x1.0	2.8x1.8x0.13	120	2.0	0.5	88	UL/CUL/TUV/CE/CB	12.10	10.15	
252401	MEAN WELL	LPS-50-12	+12V @ 0-4.2A	50.4W	90-264 @ 47-63	7.6x2.1x0.9	7.3x1.7x0.1	80	2.0	1.0	82	UL/CUL/TUV/CE	14.60	12.25	
2205413	Astrodyne	ASM60-1380**	+12V @ 0-5A	60W	100-240 @ 50-60	4.0x2.0x1.7	3.7x1.7x0.1	100	3.0	1.0	84	UL/CUL/TUV/CE	4.95	4.49	
2234716	MEAN WELL	PS-65-12 ✓	+12V @ 0-5.2A	62.4W	100-240 @ 50-60	5.0x3.0x1.7	4.5x2.5x0.15	100	2.0	1.0	79	UL/CUL/TUV/CE	9.95	8.95	
148639	MEAN WELL	PS-65-12	+12V @ 0-5.2A	62.4W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.15	100	2.0	1.0	79	UL/CUL/TUV/CE	12.25	10.95	
2099981	ITE	SBU60-105	+12V @ 0-5.25A	63W	90-264 @ 47-63	5.0x3.0x1.1	4.6x2.6x0.15	120	3.0	0.5	80	UL/CUL/CE	7.95	6.95	
2122044	MEAN WELL	ELP-75-12	+12V @ 0-6.25A	75W	90-264 @ 47-63	6.9x2.4x1.1	2.8x1.8x0.13	120	1.0	0.5	89	UL/CUL/TUV/CE/CB	26.60	22.29	
2239429	MEAN WELL	EPS-120-12	+12V @ 0-10A	120W	80-264 @ 47-63	4.0x2.0x1.1	2.8x1.8x0.13	120	1.0	0.5	88	UL/CUL/TUV/CE/CB	19.30	16.19	
213681	MEAN WELL	LPP-150-12 ↑	+12V @ 0-12.5A	150W	85-264 @ 47-63	8.7x2.4x1.6	8.3x2.6x0.15	100	1.0	0.5	79	UL/CUL/TUV/CE	28.80	24.15	
2210731	Pihong	PSA25-115	+15V @ 0-1.6A	24W	100-240 @ 47-63	4.0x3.0x1.3	3.6x2.6x0.16	150	2.0	1.0	70	UL/CSA/VE	4.49	3.95	
216751	MEAN WELL	PS-65-15	+15V @ 0-4.2A	63W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	100	2.0	1.0	79	UL/CUL/TUV/CE	14.00	11.95	
216670	MEAN WELL	LPP-100-15 ↑	+15V @ 0-6.7A	100W	85-264 @ 47-63	8.7x2.4x1.3	8.3x2.0x0.14	100	0.5	0.5	80	UL/CUL/TUV/CE	27.20	22.79	
2239728	MEAN WELL	EPS-120-15	+15V @ 0-8A	120W	80-264 @ 47-63	4.0x2.0x1.1	3.8x1.8x0.13	120	1.0	0.5	88	UL/CUL/TUV/CE/CB	19.30	16.19	
212346	MEAN WELL	PS-25-24	+24V @ 0-1A	24W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	240	2.0	0.2	79	UL/CUL/TUV/CE	11.49	9.75	
2227575	Power One	BLP40-1024G	+24V @ 0-1.1A	26.4W	100-250 @ 50-60	5.0x3.0x1.0	4.5x2.5x0.16	100	2.0	1.0	70	UL/CUL/TUV/CE	6.75	5.89	
148647	MEAN WELL	PS-65-24	+24V @ 0-2.7A	64.8W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	100	2.0	1.0	80	UL/CUL/TUV/CE	12.25	10.95	
301429	MEAN WELL	PPS-125-24	+24V @ 0-4.2A	100.8W	90-264 @ 47-440	5.0x3.0x1.4	4.5x2.6x0.14	150	1.0	0.5	83	UL/CUL/TUV/CE/CB	43.95	38.49	
2253888	MEAN WELL	EPP-400-24	+24V @ 0-10.5A	252W	80-264 @ 47-63	5.0x3.0x1.4	4.6x2.6x0.14	200	1.0	0.5	93	UL/CUL/TUV/CE/CB	65.20	54.75	
668730	MEAN WELL	PPS-200-24 ↑	+24V @ 0-8.3A	199.2W	90-264 @ 47-63	5.0x3.0x1.4	3.7x7.8x0.14	150	1.0	0.5	89	UL/CUL/TUV/CE	47.49	44.95	
236882	MEAN WELL	LPP-100-27	+27V @ 0-3.8A	102.6W	85-264 @ 47-63	8.7x2.4x1.3	8.3x2.1x0.14	150	0.5	0.5	83	UL/CUL/TUV/CE/CB	27.20	22.79	
2100689	MEAN WELL	ASP-150-48	+48V @ 0-3.2A	153.6W	90-264 @ 47-63	6.7x2.1x1.1	4.2x2.0x0.7	89	0.5	0.5	89	UL/CUL/CE/CB	50.90	44.95	
Double Output												* Web Code: OFX			
212338	MEAN WELL	PD-25A	+5V @ 0.2-2.5A; +12V @ 0.1-1.5A	30.5W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.08x0.1	50;150	1.0	0.5	71	UL/CUL/TUV/CE	\$11.25	\$10.75	
375030	MEAN WELL	PT-45C	+5V @ 0-3A; +15 @ 1.6A; -15 @ 0.3A	43.5W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.15	50	3.0	1.0	75	UL/CUL/TUV/CE/CB	12.19	11.49	
194862	MEAN WELL	PD-45A	+5V @ 0.4-3.2A; +12V @ 0.2-2	40W	90-264 @ 47-440	5.0x2.5x1.5	4.5x2.5x0.2	50;120	3.0	1.0	77	UL/CSA	11.25	10.49	
2215697	Artesyn	NLP40-7629J	+5V @ 4A; +12V @ 0-2A	44W	90-264 @ 47-63	4.2x2.5x1.1	4.0x2.2x0.1	50;120	3.0	1.0	75	UL/CSA/CE	10.95	9.95	
2197741	Skynet	SNP-N563	+5V @ 1.0-8A; +3.3V @ 0.5-6A	60W	85-264 @ 47-63	5.0x3.0x1.1	4.6x2.6x0.2	50	3.0	1.0	70	UL	7.49	6.49	
194897	MEAN WELL	PD-65B	+5V @ 0.4-3.5A; +24V @ 0.2-2A	65.5W	90-264 @ 47-440	5.0x3.0x1.7	4.5x2.5x0.2	50;150	3.0	1.0	81	UL/CUL/TUV/CE	12.45	11.75	
148690	MEAN WELL	PD-2512	+12V @ 0.1-1.2A; -12V @ 0.1-1A	24W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	50	3.0	0.5	74	UL/CUL/TUV/CE	11.25	10.75	
2100857	MEAN WELL	PD-2515	+15V @ 0-1A, -15V @ 0-1A	30W	85-264 @ 47-63	4.2x2.4x1.1	3.7x2.1x0.1	50	3.0	0.5	75	UL/CUL/TUV/CE	11.25	10.75	
Triple Output												* Web Code: OFX			
2129676	Elpac	MSM40D**	+5.1V @ 0-4A; +24V @ 0-1A; -12V @ 0.4A	49.2W	100-240 @ 50-60	5.0x3.0x1.1	4.6x2.5x0.2	50	5.0	5.0	70	UL/CUL/CSA/CE	\$4.95	\$4.49	
88402	MEAN WELL	PT-45B	+5V @ 0.4-3A; +12V @ 0.2-2A; -12V @ 0-0.3A	42.6W	90-264 @ 47-440	5.0x3.0x1.1	4.6x2.6x0.2	50; 120;100	3.0	1.0	75	UL/CUL/TUV/CE	12.19	11.49	
216734	MEAN WELL	PT-65B	+5V @ 0.4-5.5A; +12V @ 0.2-2.5A; -12V @ 0-0.5A	63.5W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.2	50; 120;100	3.0	1.0	77	UL/CUL/TUV/CE	13.49	12.49	
216726	MEAN WELL	PT-65C	+5V @ 0.4-5.5A; +15V @ 0.2-2A; -15V @ 0-0.5A	65W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.2	50; 120;100	3.0	1.0	77	UL/CUL/TUV/CE	13.49	12.49	
215707	MEAN WELL	PT-65D	+5V @ 0.5-5A; +12V @ 0.2-4A; +24V @ 0.2-1.3A	104.2W	90-264 @ 47-440	5.0x3.0x1.7	4.6x2.6x0.2	50; 100;200	2.0	1.0	79	UL/CUL/TUV/CE	13.49	12.49	

\*Applies only to primary output \*\*Medical rated § Efficiency ✓ With removeable Molex connectors (with wires)

\*For additional products, availability and specifications visit [Jameco.com](http://www.Jameco.com) and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)