

Enclosed Switching AC-to-DC Power Supplies

3 LEVELS OF SAVINGS
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



Enclosed Switching AC-to-DC Power Supplies

• 100% full-load burn-in test • Wide AC input range • Manufacturer warranty varies



Complete specifications available online

*2.5-4.2V Web Code: ENT

*5-9V Web Code: ENF

*12-13.8V Web Code: ENW

*15-20V Web Code: ENI



SP-150



HRPG-150



HRP-300



RSP-1500



NES-75



SE-600

Part No.	Manufacturer	Mfr. Part No.	Output		Power	Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%)§	PFC	Certification	Pricing	
			Voltage @ Current (min-max)										1	10
Single Output														
2106685	MEAN WELL	RS-15-3.3	+3.3V @ 0-3A		9.9W	2.5 x 2.0 x 1.1	80	2.0	0.5	72	—	UL/CUL/TUV/CE/CB	\$7.40	\$6.19
1919043	MEAN WELL	RS-15-5	+5V @ 0-3A		15W	2.5 x 2.0 x 1.1	80	1.5	0.5	77	—	UL/CUL/TUV/CE/CB	7.40	6.19
323282	MEAN WELL	RS-25-5	+5V @ 0-5A		25W	3.1 x 2.0 x 1.1	80	1.0	0.5	77	—	UL/CUL/TUV/CE/CB	9.20	7.69
323329	MEAN WELL	RS-35-5	+5V @ 0-7A		35W	3.9 x 3.2 x 1.4	80	1	0.5	77	—	UL/CUL/TUV/CE	12.10	9.95
2257539	MEAN WELL	LRS-50-5	+5V @ 0-10A		50W	3.8 x 3.2 x 1.1	80	1.0	0.5	83	—	UL/CUL/TUV/CB/CE/CCC	11.70	9.75
323388	MEAN WELL	RS-50-5	+5V @ 0-10A		50W	3.9 x 3.8 x 1.4	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	13.50	11.25
194791	MEAN WELL	SP-100-5	+5V @ 0-20A		100W	7.0 x 3.9 x 1.8	100	1.0	0.5	76	✓	UL/CUL/TUV/CE/CB	35.49	33.25
323821	MEAN WELL	RS-150-5	+5V @ 0-26A		130W	7.8 x 3.9 x 1.5	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	23.40	19.49
123394	MEAN WELL	S-150-5	+5V @ 0-30A		150W	7.0 x 4.3 x 2.0	150	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	39.95	36.95
201912	MEAN WELL	SP-150-5	+5V @ 0-30A		150W	7.0 x 3.9 x 2.0	100	1.0	0.5	75	✓	UL/CUL/TUV/CE/CB	39.49	36.95
2219719	MEAN WELL	LRS-200-5	+5V @ 0-40A		200W	8.4 x 4.5 x 1.1	150	2.0	0.5	83	—	UL/CUL	26.10	21.89
202042	MEAN WELL	SP-200-5	+5V @ 0-40A		200W	7.0 x 3.9 x 2.0	100	1.0	0.5	71	✓	UL/CUL/TUV/CE/CB	45.95	42.95
244735	MEAN WELL	SP-320-5	+5V @ 0-55A at 230VAC; 0-44A at 115VAC		275W	8.5 x 4.5 x 2.0	150	1.0	0.5	79	✓	UL/CUL/TUV/CE/CB	56.95	53.95
2219794	MEAN WELL	LRS-350-5	+5V @ 0-60A		300W	8.5 x 4.5 x 1.2	150	2	0.5	83.5	—	UL/CUL	32.90	27.59
2149562	MEAN WELL	SE-350-5	+5V @ 0-60A		300W	8.5 x 4.5 x 2.0	150	2.0	0.5	78	—	UL/CUL	40.95	37.95
2172068	MEAN WELL	RSP-320-5	+5V @ 0-60A		300W	8.5 x 4.5 x 1.2	150	1.0	0.5	85	✓	UL/CUL/TUV/CB/CE	48.40	40.49
374002	MEAN WELL	SE-600-5	+5V @ 0-100A		500W	9.7 x 5.0 x 2.5	150	2.0	0.5	78	—	UL/CUL	72.20	60.49
394215	MEAN WELL	SP-320-7.5	+7.5V @ 0-40A		300W	8.5 x 4.5 x 2.0	150	1.0	0.5	83	✓	UL/CUL/TUV/CE/CB	56.95	52.95
1919051	MEAN WELL	RS-15-12	+12V @ 0-1.3A		15.6W	2.5 x 2.0 x 1.1	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	7.40	6.19
323300	MEAN WELL	RS-25-12	+12V @ 0-2.1A		25.2W	3.0 x 2.0 x 1.1	120	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	9.20	7.69
123255	MEAN WELL	S-25-12	+12V @ 0-2.1A		25.2W	3.9 x 3.8 x 1.4	100	0.5	0.5	76	—	UL/TUV/CE	20.95	18.95
2257475	MEAN WELL	LRS-35-12	+12V @ 0-3A		36W	3.8 x 3.2 x 1.1	120	0.5	0.5	82	—	UL/CUL/TUV/CB/CE/CCC	10.40	8.85
323337	MEAN WELL	RS-35-12	+12V @ 0-3A		36W	3.9 x 3.2 x 1.4	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	12.10	9.95
323396	MEAN WELL	RS-50-12	+12V @ 0-4.2A		50.4W	3.9 x 3.8 x 1.4	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	13.50	11.25
2257547	MEAN WELL	LRS-50-12	+12V @ 0-4.2A		50.4W	3.8 x 3.2 x 1.1	120	0.5	0.5	86	—	UL/CUL/TUV/CB/CE/CCC	11.20	9.39
123335	MEAN WELL	S-60-12	+12V @ 0-5A		60W	6.3 x 3.8 x 1.5	120	0.5	0.5	76	—	UL/CUL/TUV/CE/CB	27.95	24.95
2257601	MEAN WELL	LRS-75-12	+12V @ 0-6A		72W	3.8 x 3.8 x 1.1	120	0.5	0.5	89	—	UL/CUL/TUV/CB/CE/CCC	13.50	11.29
323599	MEAN WELL	RS-75-12	+12V @ 0-6A		72W	5.1 x 3.9 x 1.5	120	0.5	0.5	81	—	UL/CUL/TUV/CE/CB	16.20	13.49
2257678	MEAN WELL	LRS-100-12	+12V @ 0-8.5A		102W	5.0 x 3.8 x 1.1	120	0.5	0.5	88	—	UL/CUL/TUV/CB/CE/CCC	15.10	12.59
2105017	MEAN WELL	NES-100-12	+12V @ 0-8.5A		102W	6.3 x 3.8 x 1.5	120	0.5	0.5	83	—	UL/CUL/CE/CB	17.49	16.95
323716	MEAN WELL	RS-100-12	+12V @ 0-8.5A		102W	6.3 x 3.8 x 1.5	120	0.5	0.5	81	✓	UL/CUL/TUV/CE/CB	21.80	18.19
123386	MEAN WELL	S-100F-12	+12V @ 0-8.5A		102W	7.8 x 3.9 x 1.5	125	0.5	0.5	80	—	UL/TUV/CE/CB	27.95	25.95
194803	MEAN WELL	SP-100-12	+12V @ 0-8.5A		102W	7.0 x 3.9 x 1.8	100	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	28.95	27.95
2257723	MEAN WELL	LRS-150-12	+12V @ 0-12.5A		150W	6.0 x 3.8 x 1.2	150	0.5	0.5	87.5	—	UL/CUL/TUV/CE	18.70	15.69
2257782	MEAN WELL	LRS-150F-12	+12V @ 0-12.5A		150W	6.3 x 3.8 x 1.2	150	0.5	0.5	87.5	—	UL/CUL/TUV/CE/CB	20.90	17.55
323839	MEAN WELL	RS-150-12	+12V @ 0-12.5A		150W	7.8 x 3.9 x 1.5	120	0.5	0.5	83	—	UL/CUL/TUV/CE/CB	23.40	19.49
123423	MEAN WELL	S-150-12	+12V @ 0-12.5A		150W	7.0 x 4.3 x 2.0	180	0.3	0.3	82	—	UL/CUL/TUV/CE/CB	39.95	36.95
173421	MEAN WELL	SP-150-12	+12V @ 0-12.5A		150W	7.0 x 3.9 x 2.0	100	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	39.49	36.95
194774	MEAN WELL	SP-200-12	+12V @ 0-16.7A		200.4W	7.0 x 3.9 x 2.0	100	0.5	0.5	79	✓	UL/CUL/TUV/CE/CB	45.95	42.95
2219727	MEAN WELL	LRS-200-12	+12V @ 0-17A		204W	8.5 x 4.5 x 1.2	150	1	0.5	87.5	—	UL/CUL	24.80	20.95
2101497	MEAN WELL	SP-240-12	+12V @ 0-20A		240W	7.5 x 3.7 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	50.90	42.95
244743	MEAN WELL	SP-320-12	+12V @ 0-25A at 230VAC; 0-20A @ 115VAC		300W	8.5 x 4.5 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	56.95	52.95
2102203	MEAN WELL	HRP-300-12	+12V @ 0-27A		324W	7.8 x 4.1 x 1.6	120	0.5	0.3	88	✓	UL/CUL/TUV/CE/CB	68.90	57.75
2219807	MEAN WELL	LRS-350-12	+12V @ 0-29A		348W	8.5 x 4.5 x 1.2	150	1.0	0.5	85	—	UL/CUL	31.10	25.95
2149503	MEAN WELL	SE-350-12	+12V @ 0-29A		348W	8.5 x 4.5 x 2.0	150	1.0	0.5	83	—	UL/CUL	40.95	37.95
2094928	MEAN WELL	SE-450-12	+12V @ 0-37.5A		450W	8.9 x 4.9 x 2.0	200	1.0	0.5	83	✓	UL/CUL	58.50	48.95
374011	MEAN WELL	SE-600-12	+12V @ 0-50A		600W	9.7 x 5.0 x 2.5	150	0.5	0.5	83	—	UL/CUL	72.20	60.49
374214	MEAN WELL	PSP-600-12	+12V @ 0-50A		600W	6.7 x 4.7 x 3.7	240	0.5	0.5	84	✓	UL/CUL/TUV/CE/CB	119.00	99.95
2101542	MEAN WELL	SE-1000-12	+12V @ 0-83.3A		999.6W	10.9 x 5.0 x 2.5	150	0.5	0.5	85	—	UL/CUL	157.00	131.75
694911	MEAN WELL	RSP-1500-12	+12V @ 0-125A		1500W	10.9 x 5.0 x 3.3	150	0.5	0.5	87	✓	EN/TUV/UL	297.00	249.49
212410	MEAN WELL	SP-200-13.5	+13.5V @ 0-14.9A		201.1W	7.0 x 3.9 x 2.0	100	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	50.90	42.95
693599	MEAN WELL	SP-320-13.5	+13.5V @ 0-22A		297W	8.5 x 4.5 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	63.00	52.95
2106079	MEAN WELL	PSP-600-13.5	+13.5V @ 0-44.5A		600W	6.7 x 4.7 x 3.7	240	0.5	0.5	85	✓	UL/CUL/TUV/CE/CB	119.00	94.95
2105439	MEAN WELL	AD-155A†	+13.8V @ 0-11.5A or 13.3V @ 0-0.5A		145W	7.8 x 4.3 x 2.0	150	0.5	0.5	80	✓	UL/CUL/TUV/CE/CB	46.95	44.95
323302	MEAN WELL	RS-25-15	+15V @ 0-1.7A		25.5W	3.0 x 2.0 x 1.1	120	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	9.20	7.69
323345	MEAN WELL	RS-35-15	+15V @ 0-2.4A		36W	3.9 x 3.2 x 1.4	120	0.5	0.5	83	—	UL/CUL/TUV/CE/CB	12.10	9.95
323409	MEAN WELL	RS-50-15	+15V @ 0-4A		60W	3.9 x 3.8 x 1.4	120	0.5	0.5	88	—	UL/CUL/TUV/CB/CE/CCC	13.50	11.25

*Applies only to primary output †UPS function § Efficiency