

Enclosed Switching AC-to-DC Power Supplies

Jameco carries the full line of MEAN WELL Power products. For additional products visit www.Jameco.com/meanwellproducts



Enclosed Switching AC-to-DC Power Supplies (Continued)

- 100% full-load burn-in test
- Wide AC input range
- Manufacturer warranty varies



RS-25



* 15-20V Web Code: ENI

* 24-30V Web Code: ENE

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%) §	PFC	Certification	Pricing		
			Voltage @ Current (min-max)	Power								1	10	
Single Output (Continued)														
323602	MEAN WELL	RS-75-15	+15V @ 0-5A	75W	5.1 x 3.9 x 1.5	120	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	\$16.20	\$13.49	
2257686	MEAN WELL	LRS-100-15	+15V @ 0-7A	105W	5.1 x 3.82 x 1.2	120	0.5	0.5	88.5	—	UL/CUL/TUV/CB/CE/CCC	15.10	12.59	
323724	MEAN WELL	RS-100-15	+15V @ 0-7A	105W	6.3 x 3.8 x 1.5	120	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	21.80	18.19	
2257791	MEAN WELL	LRS-150F-15*	+15V @ 0-10A	150W	6.3 x 2.7 x 1.5	150	0.5	0.5	89	—	UL/CUL/TUV/CB/CE/CCC	20.90	17.55	
323847	MEAN WELL	RS-150-15	+15V @ 0-10A	150W	7.8 x 3.9 x 1.5	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	23.40	19.49	
123432	MEAN WELL	S-150-15	+15V @ 0-10A	150W	7.0 x 4.3 x 2.0	180	0.3	0.3	85	—	UL/CUL/TUV/CE/CB	39.95	36.95	
693610	MEAN WELL	SP-320-15	+15V @ 0-20A	300W	8.5 x 4.5 x 2.0	150	0.5	0.3	86	✓	UL/CUL/TUV/CE/CB	56.95	52.95	
291522	MEAN WELL	SE-600-15	+15V @ 0-40A	600W	9.7 x 5.0 x 2.5	150	0.5	0.5	84	—	UL/CUL	72.20	60.49	
694920	MEAN WELL	RSP-1500-15	+15V @ 0-100A	1500W	10.9 x 5.0 x 3.3	150	0.5	0.5	87	✓	UL/CUL/TUV/CE/CB	297.00	249.49	
1919078	MEAN WELL	RS-15-24	+24V @ 0-0.625A	15W	2.5 x 2.0 x 1.1	200	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	7.40	6.19	
323311	MEAN WELL	RS-25-24	+24V @ 0-1.1A	26.4W	3.0 x 2.0 x 1.1	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	9.20	7.69	
123272	MEAN WELL	S-25-24	+24V @ 0-1.1A	26.4W	3.9 x 3.8 x 1.4	100	0.5	0.5	80	—	UL/TUV/CE	20.95	18.95	
2257491	MEAN WELL	LRS-35-24	+24V @ 0-1.5A	36W	3.9 x 3.2 x 1.2	150	0.5	0.5	88	—	UL/CUL/TUV/CB/CE/CCC	9.90	8.25	
323353	MEAN WELL	RS-35-24	+24V @ 0-1.5A	36W	3.9 x 3.2 x 1.4	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	12.10	9.95	
123319	MEAN WELL	S-40-24	+24V @ 0-1.8A	43W	5.1 x 3.9 x 1.5	100	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	19.95	18.95	
323417	MEAN WELL	RS-50-24	+24V @ 0-2.2A	52.8W	3.9 x 3.8 x 1.4	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	13.50	11.25	
2257563	MEAN WELL	LRS-50-24	+24V @ 0-2.2A	52.8W	3.9 x 3.8 x 1.4	150	0.5	0.5	88	—	UL/CUL/TUV/CB/CE/CCC	10.60	8.95	
123352	MEAN WELL	S-60-24	+24V @ 0-2.5A	60W	6.3 x 3.8 x 1.5	150	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	27.95	24.95	
2257627	MEAN WELL	LRS-75-24	+24V @ 0-3.2A	76.8W	3.9 x 3.8 x 1.2	150	0.5	0.5	90	—	UL/CUL/TUV/CB/CE/CCC	12.80	10.75	
323620	MEAN WELL	RS-75-24	+24V @ 0-3.2A	76.8W	5.1 x 3.9 x 1.5	120	0.5	0.5	85	—	UL/CUL/TUV/CE/CB	16.20	13.49	
2257694	MEAN WELL	LRS-100-24	+24V @ 0-4.5A	108W	5.1 x 3.8 x 1.2	150	0.5	0.5	90	—	UL/CUL/TUV/CB/CE/CCC	14.40	12.09	
323732	MEAN WELL	RS-100-24	+24V @ 0-4.5A	108W	6.3 x 3.8 x 1.5	120	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	21.80	18.19	
201971	MEAN WELL	S-100F-24	+24V @ 0-4.5A	108W	7.8 x 3.9 x 1.5	150	0.5	0.5	83	—	UL/TUV/CE/CB	32.95	29.95	
173404	MEAN WELL	SP-150-24	+24V @ 0-6.25A	150W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	39.49	36.95	
2257740	MEAN WELL	LRS-150-24	+24V @ 0-6.5A	156W	6.0 x 3.8 x 1.2	200	0.5	0.5	89	—	UL/CUL/TUV/CE	17.60	14.75	
2257803	MEAN WELL	LRS-150F-24	+24V @ 0-6.5A	156W	6.3 x 3.8 x 1.2	200	0.5	0.5	89	—	UL/CUL/TUV/CE/CB	19.80	16.75	
323855	MEAN WELL	RS-150-24	+24V @ 0-6.5A	156W	7.8 x 3.9 x 1.5	120	0.5	0.5	86	—	UL/CUL/TUV/CE/CB	23.40	19.49	
123450	MEAN WELL	S-150-24	+24V @ 0-6.5A	156W	7.0 x 4.3 x 2.0	240	0.2	0.2	85	—	UL/CUL/TUV/CE/CB	39.95	36.95	
2094864	MEAN WELL	HRPG-150-24	+24V @ 0-6.5A	156W	6.3 x 3.8 x 1.5	150	0.5	0.3	87	✓	UL/CUL/TUV/CE/CB	52.00	43.65	
194782	MEAN WELL	SP-200-24	+24V @ 0-8.4A	201.6W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	45.95	42.95	
2219743	MEAN WELL	LRS-200-24	+24V @ 0-8.8A	211.2W	8.5 x 4.5 x 1.2	150	0.5	0.5	89.5	—	UL/CUL	23.40	19.75	
2101518	MEAN WELL	SP-240-24	+24V @ 0-10A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	45.95	42.95	
244752	MEAN WELL	SP-320-24	+24V @ 0-13A	312W	8.5 x 4.5 x 2.0	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	56.95	52.95	
2102220	MEAN WELL	HRP-300-24	+24V @ 0-14A	336W	7.7 x 4.1 x 1.6	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	68.90	57.75	
2219823	MEAN WELL	LRS-350-24	+24V @ 0-14.6A	350.4W	8.5 x 4.5 x 1.2	150	0.5	0.5	88	—	UL/CUL	29.90	24.95	
2146564	MEAN WELL	SE-350-24	+24V @ 0-14.6A	350.4W	8.5 x 4.5 x 2.0	150	0.5	0.5	87	—	UL/CUL	41.25	37.95	
2101606	MEAN WELL	SE-450-24	+24V @ 0-18.8A	451.2W	8.9 x 4.9 x 2.0	200	0.5	0.2	86	—	UL/CUL	58.50	48.95	
2122335	MEAN WELL	HRP-450-24	+24V @ 0-18.8A	451.2W	8.6 x 4.1 x 1.6	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	111.00	93.19	
301322	MEAN WELL	SP-480-24	+24V @ 0-20A	480W	10.9 x 5.0 x 1.7	150	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	123.95	115.95	
147054	MEAN WELL	SP-500-24	+24V @ 0-20A	480W	6.7 x 4.7 x 3.7	240	0.5	0.5	85.5	✓	UL/CUL/TUV/CE/CB	138.95	129.95	
2197994	MEAN WELL	RSP-500-24	+24V @ 0-21A	504W	9.1 x 5.0 x 1.6	150	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	86.40	72.49	
295902	MEAN WELL	SE-600-24	+24V @ 0-25A	600W	9.7 x 5.0 x 2.5	150	0.5	0.5	87	—	UL/CUL	72.20	61.25	
374231	MEAN WELL	PSP-600-24	+24V @ 0-25A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	86	✓	UL/CUL/TUV/CE/CB	119.00	94.95	
2100961	MEAN WELL	HRP-600-24	+24V @ 0-27A	648W	8.6 x 4.1 x 2.5	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	115.00	97.75	
2172121	MEAN WELL	RSP-750-24	+24V @ 0-31.3A	751.2W	9.8 x 5.0 x 1.6	150	0.5	0.5	90.5	✓	EN/TUV/UL	169.00	141.95	
320048	MEAN WELL	SP-750-24	+24V @ 0-31.3A	751.2W	10.9 x 5.0 x 2.5	120	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	185.49	173.95	
1585717	MEAN WELL	RSP-1000-24	+24V @ 0-40A	960W	11.6 x 5.0 x 1.6	150	0.5	0.5	88	✓	UL/CUL/TUV/CE/CB	200.00	167.95	
2101569	MEAN WELL	SE-1000-24	+24V @ 0-41.7A	1000.8W	10.9 x 5.0 x 2.5	200	0.5	0.5	88	—	UL/CUL	157.00	131.75	
694938	MEAN WELL	RSP-1500-24	+24V @ 0-63A	1512W	10.9 x 5.0 x 3.3	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	297.00	249.49	
693513	MEAN WELL	SP-150-27	+27V @ 0-5.6A	151.2W	7.8 x 3.9 x 2.0	15	0.5	0.5	84	—	UL/CUL/CE/CB/PFC	39.49	38.49	
693548	MEAN WELL	SP-200-27	+27V @ 0-7.5A	202.5W	7.0 x 3.9 x 2.0	150	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	49.95	42.95	
693628	MEAN WELL	SP-320-27	+27V @ 0-11.7A	315.9W	8.5 x 4.5 x 2.0	200	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	56.95	52.95	
190706	MEAN WELL	SP-500-27	+27V @ 0-18A	486W	6.7 x 4.7 x 3.7	200	0.5	0.5	86.5	✓	UL/CUL/TUV/CE/CB	169.95	151.95	
295911	MEAN WELL	SE-600-27	+27V @ 0-22.2A	599.4W	9.7 x 5.0 x 2.5	150	0.5	0.5	87	—	UL/CUL	72.20	60.49	
374257	MEAN WELL	PSP-600-27	+27V @ 0-22.2A	599.4W	6.7 x 4.7 x 3.7	240	0.5	0.5	86	✓	UL/CUL/TUV/CE/CB	119.00	94.95	
1585709	MEAN WELL	RSP-1000-27	+27V @ 0-37.0A	999W	11.6 x 5.0 x 1.6	150	0.5	0.5	88	✓	UL/CUL/TUV/CE/CB	200.00	167.95	
694946	MEAN WELL	RSP-1500-27	+27V @ 0-56A	1512W	10.9 x 5.0 x 3.3	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	297.00	249.49	
2146118	MEAN WELL	AD-155B	+27.6V @ 0-5.5A or 27.1V @ 0-0.5A	152W	7.8 x 4.3 x 2.0	150	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	46.95	44.95	
2102473	MEAN WELL	SP-240-30	+30V @ 0-8A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	88	✓	UL/CUL/TUV/CE/CB	45.95	42.95	

*Applies only to primary output § Efficiency

*For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com