

Enclosed Switching AC-to-DC Power Supplies

3 LEVELS OF SAVINGS
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



Enclosed Switching AC-to-DC Power Supplies (Continued)

• 100% full-load burn-in test • Wide AC input range • Manufacturer warranty varies



SP-200



* 36-54V Web Code: ENH

* Multiple Output WC: ENM

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L" x W" x H")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	EFF (%)§	PFC	Certification	Pricing		
			Voltage @ Current (min-max)	Power								1	10	
Single Output (Continued)														
2102730	MEAN WELL	SP-320-36	+36V @ 0-8.8A	316.8W	8.5 x 4.5 x 2.0	220	0.5	0.2	87	✓	UL/CUL/TUV/CE/CB	\$63.00	\$52.95	
693206	MEAN WELL	RS-25-48	+48V @ 0-0.57A	27.4W	3.1 x 2.0 x 1.1	200	0.5	0.5	85	—	UL/CUL/TUV/CE/CB	9.20	7.69	
693290	MEAN WELL	RS-100-48	+48V @ 0-2.3A	110.4W	6.3 x 3.8 x 1.5	200	0.5	0.5	84	—	UL/CUL/TUV/CE/CB	21.80	18.19	
201930	MEAN WELL	SP-150-48	+48V @ 0-3.2A	153.6W	7.0 x 3.9 x 2.0	250	0.5	0.5	83	✓	UL/CUL/TUV/CE/CB	39.49	36.95	
323863	MEAN WELL	RS-150-48	+48V @ 0-3.3A	158.4W	7.8 x 3.9 x 1.5	200	0.5	0.5	87	—	UL/CUL/TUV/CE/CB	23.40	19.49	
202068	MEAN WELL	SP-200-48	+48V @ 0-4.2A	201.6W	7.0 x 3.9 x 2.0	250	0.5	0.5	84	✓	UL/CUL/TUV/CE/CB	50.90	42.95	
2102481	MEAN WELL	SP-240-48	+48V @ 0-5A	240W	7.5 x 3.7 x 2.0	150	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	45.95	43.25	
2229466	Arndt	SP-300-48	+48V @ 0-6.25A	300W	8.1 x 4.5 x 2.0	240	0.5	0.2	85	✓	UL/CUL/TUV/CE	36.95	33.94	
244770	MEAN WELL	SP-320-48	+48V @ 0-6.7A	321.6W	8.5 x 4.5 x 2.0	240	0.5	0.2	89	✓	UL/CUL/TUV/CE/CB	56.95	53.49	
2219840	MEAN WELL	LRS-350-48	+48V @ 0-7.3A	350W	8.5 x 4.5 x 1.2	200	0.5	0.5	89	—	UL/CUL	31.10	25.95	
2149554	MEAN WELL	SE-350-48	+48V @ 0-7.3A	350W	8.5 x 4.5 x 2.0	240	0.5	0.5	87.5	—	UL/CUL	40.95	37.95	
2231558	Arndt	S-400-48	+48V @ 0-8.3A	400W	7.5 x 4.5 x 1.9	150	0.5	0.5	83	—	CE	39.95	34.95	
2105164	MEAN WELL	SE-450-48	+48V @ 0-9.4A	451.2W	8.9 x 4.9 x 2.0	200	0.5	0.2	88	—	UL/CUL	58.50	48.95	
161796	MEAN WELL	SP-500-48	+48V @ 0-10A	480W	6.7 x 4.7 x 3.7	300	0.5	0.5	87	✓	UL/CUL/TUV/CE/CB	138.95	132.95	
295929	MEAN WELL	SE-600-48	+48V @ 0-12.5A	600W	9.7 x 5.0 x 2.5	200	0.5	0.5	88	—	UL/CUL	72.20	60.49	
374249	MEAN WELL	PSP-600-48	+48V @ 0-12.5A	600W	6.7 x 4.7 x 3.7	240	0.5	0.5	87	✓	UL/CUL/TUV/CE/CB	119.00	94.95	
2101577	MEAN WELL	SE-1000-48	+48V @ 0-20.8A	998.4W	10.9 x 5.0 x 2.5	200	0.5	0.5	89	—	UL/CUL	157.00	131.75	
1585725	MEAN WELL	RSP-1000-48	+48V @ 0-21.0A	1008W	11.6 x 5.0 x 1.6	150	0.5	0.5	90	✓	UL/CUL/TUV/CE/CB	200.00	167.95	
694954	MEAN WELL	RSP-1500-48	+48V @ 0-32.0A	1536W	10.9 x 5.0 x 3.3	200	0.5	0.5	91	✓	UL/CUL/TUV/CE/CB	297.00	249.49	
2108921	MEAN WELL	RSP-3000-48	+48V @ 0-62.5A	3000W	10.9 x 7.0 x 2.5	200	0.5	0.5	90.5	✓	UL/CUL/TUV/CE/CB	410.00	343.95	
Double Output														
323362	MEAN WELL	RD-35A	+5V @ 0.3-4A; +12V @ 0.2-1A	32W	3.9 x 3.2 x 1.4	80	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	\$11.95	\$10.95	
323380	MEAN WELL	RD-35B	+5V @ 0.3-4A; +24V @ 0.2-1.3A	51.2W	3.9 x 3.2 x 1.4	80	0.5	0.5	82	—	UL/CUL/TUV/CE/CB	11.95	10.95	
323425	MEAN WELL	RD-50A	+5V @ 0.3-6A; +12V @ 0.3-3A	54W	3.9 x 3.8 x 1.4	80	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	14.49	12.95	
323433	MEAN WELL	RD-50B	+5V @ 0.3-6A; +24V @ 0.2-2A	54W	3.9 x 3.8 x 1.4	80	0.5	0.5	80	—	UL/CUL/TUV/CE/CB	14.49	12.95	
323505	MEAN WELL	RD-65A	+5V @ 0.3-8A; +12V @ 0.2-4A	66W	5.1 x 3.9 x 1.5	80	0.5	0.5	79	—	UL/CUL/TUV/CE/CB	15.95	14.49	
323513	MEAN WELL	RD-65B	+5V @ 0.3-8A; +24V @ 0.2-3A	68W	5.1 x 3.9 x 1.5	80	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	15.95	14.49	
323741	MEAN WELL	RD-125A	+5V @ 2.0-15A; +12V @ 0.5-10A	130.9W	7.8 x 3.9 x 1.5	80	3.0	1.0	82	—	UL/CUL/TUV/CE/CB	23.25	22.95	
323759	MEAN WELL	RD-125B	+5V @ 2.0-10A; +24V @ 0.4-5A	133.4W	7.8 x 3.9 x 1.5	80	3.0	1.0	82	—	UL/CUL/TUV/CE/CB	24.95	22.95	
2106124	MEAN WELL	RD-125-1224	+12V @ 1.0-3.7A; +24V @ 0.4-3.7A	133.2W	7.8 x 3.9 x 1.5	120	1.0	0.5	85	—	UL/CUL/TUV/CE/CB	24.95	22.95	
Triple Output														
323460	MEAN WELL	RT-50B	+5V @ 0.5-4A; +12V @ 0.2-2A; -12V @ 0.1-0.5A	50W	3.9 x 3.8 x 1.4	80	1.0	0.5	77	—	UL/CUL/TUV/CE/CB	\$15.49	\$14.49	
323468	MEAN WELL	RT-50C	+5V @ 0.4A; +15V @ 0.2-1.5A; -15V @ 0.1-0.5A	50W	3.9 x 3.8 x 1.4	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	15.49	14.49	
323476	MEAN WELL	RT-50D	+5V @ 0.5-5A; +12V @ 0.1-1A; +24V @ 0.2-1.5A	51W	3.9 x 3.8 x 1.4	80	1.0	0.5	80	—	UL/CUL/TUV/CE/CB	15.49	14.49	
123482	MEAN WELL	T-60B	+5V @ 0.5-5A; +12V @ 0.2-2.5A; -12V @ 0-0.5A	61W	6.3 x 3.8 x 1.5	100	1.0	0.5	72	—	UL/CUL/TUV/CE/CB	33.95	30.95	
323540	MEAN WELL	RT-65B	+5V @ 0.5-8A; +12V @ 0.2-3.5A; -12V @ 0-1A	64.6W	5.1 x 3.9 x 1.5	80	1.0	0.5	77	—	UL/CUL/TUV/CE/CB	17.49	16.49	
323548	MEAN WELL	RT-65C	+5V @ 0.5-8A; +15V @ 0.2-3A; -15V @ 0-1A	65.5W	5.1 x 3.9 x 1.5	80	1.0	0.5	78	—	UL/CUL/TUV/CE/CB	17.49	16.49	
323555	MEAN WELL	RT-65D	+5V @ 0.5-8A; +12V @ 0.1-1A; +24V @ 0.2-2A	68W	5.1 x 3.9 x 1.5	80	1.0	0.5	79	—	UL/CUL/TUV/CE/CB	17.49	16.49	
323775	MEAN WELL	RT-125B	+5V @ 2-15A; +12V @ 0.5-6A; -12V @ 0.1-1A	132W	7.8 x 3.9 x 1.5	80	1.0	0.5	80	—	UL/CUL/TUV/CE/CB	26.49	25.49	
323783	MEAN WELL	RT-125C	+5V @ 2-15A; +15V @ 0.5-6A; -15V @ 0.1-1A	132.5W	7.8 x 3.9 x 1.5	80	1.0	0.5	81	—	UL/CUL/TUV/CE/CB	26.49	25.49	
323792	MEAN WELL	RT-125D	+5V @ 2-15A; +12V @ 0.1-2A; +24V @ 0.4-4A	136W	7.8 x 3.9 x 1.5	80	1.0	0.5	82	—	UL/CUL/TUV/CE/CB	26.49	25.49	
Quad Output														
323484	MEAN WELL	RQ-50B	+5V @ 0.5-5A; +12V @ 0.2-1.0A; -5V @ 0-0.5A; -12V @ 0-0.5A	45.5W	3.9 x 3.8 x 1.4	80	0.5	0.5	74	—	UL/CUL/TUV/CE/CB	\$16.95	\$15.95	
323564	MEAN WELL	RQ-65B	+5V @ 0.5-6A; +12V @ 0.2-2A; -5V @ 0.1-0.5A; -12V @ 0-0.5A	62.5W	5.1 x 3.9 x 1.5	80	0.5	0.5	76	—	UL/CUL/TUV/CE/CB	18.49	17.49	
323572	MEAN WELL	RQ-65D	+5V @ 0.5-4A; +12V @ 0.2-1.5A; +24V @ 0.1-1A; -12V @ 0-0.5A	68W	5.1 x 3.9 x 1.5	80	0.5	0.5	78	—	UL/CUL/TUV/CE/CB	18.49	17.49	
323812	MEAN WELL	RQ-125D	+5V @ 2-8A; +12V @ 0.5-2.5A; +24V @ 0.1-2A; -12V @ 0-0.5A	124W	7.8 x 3.9 x 1.5	80	1.0	0.5	82	—	UL/CUL/TUV/CE/CB	28.95	26.95	
213648	MEAN WELL	QP-150F	+5V @ 3-10A; +15V @ 0-3A; +24V @ 0.4-2A; -15V @ 0-0.6A	152W	7.8 x 3.9 x 1.5	120	2.0	1.0	78	✓	UL/CUL/TUV/CE/CB	77.49	74.49	
213752	MEAN WELL	QP-200D	+5V @ 3-15A; +12V @ 0-4A; +24V @ 0.4-3A; -12V @ 0-0.7A	204.9W	7.8 x 3.9 x 2.0	100	2.0	1.0	75	✓	UL/CUL/TUV/CE/CB	81.49	77.49	
668764	MEAN WELL	QP-320D	+5V @ 2.5-20A; +12V @ 0-10A; +24V @ 0.2-3A; -12V @ 0.2-2A	316W	8.5 x 4.5 x 2.0	100	2.0	1.0	83	✓	UL/CUL/TUV/CE	103.49	97.95	

*Applies only to primary output

§ Efficiency