



Meters & Testers



* Web Code: EMT



Part No.	Manufacturer	Mfr. Part No.	Description	1	5
2264543	BenchPro	23437	Pen style non-contact AC voltage detector with alarm and LED light	\$6.95	\$6.49
2130749	Velleman	VTLAN4	LAN tester, tests RJ-45, 10 Base-T, Token Ring, RJ11/12 cables	16.95	15.49
2206037	Dawson	DDM30	Smart SMD Tweezer Tester	27.95	24.95
198678	Extech	LCR Meter	Passive Component LCR Meter	210.95	199.95
2075946	P3	P4400	Kill-A-Watt® Energy Consumption Meter	29.95	26.95
2222483	Dawson	DET301	3-wire socket AC polarity/open	5.95	5.35



3MHz Direct Digital Synthesis Signal Generator with Voltage Display

* Web Code: BLT

This economical function generator with high accuracy and high stability output is based on Direct Digital Synthesis technology and offers a frequency range of 3MHz and you can select Sine, Square, Triangle and TTL waveform outputs. The DDS platform also provides user friendly operation.

- Frequency range: 0.1Hz - 3MHz (sine, square); 0.1Hz - 1MHz (triangle)
- Low distortion Sine wave: -55dBc, 0.1Hz to 200kHz
- Constant current source circuit
- Attenuator: -40dB ±1dB
- 6-digit LED display
- Impedance: 50Ω ±10%



Part No.	Mfr. Part No.	Bandwidth	# of waveforms	Price
2244050	SFG-1013	3MHz	4	\$189.95

Function Generators



* Web Code: DEJ



Part No.	Manufacturer	Mfr. Part No.	Features	Bandwidth	# of Waveform Types	Size (in.)	Wt. (lbs.)	Includes*	Price
2160411	Instek	SFG-1003	DDS with FPGA design and 6-digit LED display	3MHz	4	9.9 x 3.6 x 11.5	4.6	1, 2, 3	\$143.95
2112831	SKMI	SK5200	Rotary switch control with built-in 60MHz counter	5MHz	6	11.8 x 3.5 x 10.8	5.5	1, 3	209.95
2135814	Uniteq	US-9170A	Maximum resolution 0.01Hz, 100mVpp ~20Vpp Sweep range 1Hz ~ 10MHz	10MHz	5	14.6 x 13.8 x 6.9	28.7	1, 3	849.95

* 1. Power cord 2. BNC cable 3. User's manual

Oscilloscopes



* Web Code: RCG

Part No.	Manufacturer	Mfr. Part No.	Bandwidth	Features	Size (in.)	Wt. (lbs.)	Includes	Price
2205915	Gobotronics	GT-0005	200kHz	Mixed signal plug-in DIP package, 2MSa/s, 2.42" OLED	3.3 x 1.75	0.065	Two 10-pin headers	\$69.95
2205931	Gobotronics	GT-0015	200kHz	Mixed signal handheld, 2MSa/s, 2.42" OLED, 750mAh Li-Ion	3.17 x 2.22 x 0.7	0.4	Header, USB cable, 2 test clip leads	117.95
2217393	Seed Studio	TOL01241P	200kHz	USB PC-based scope, 2.8" LCD display, built-in signal generator	4.1 x 2.1 x 0.3	0.4	Carrying case, stand, 2 grabbers, wrench	99.95
2187454	Velleman	PCSU200	12MHz	USB PC-Based scope, function generator, transient recorder, bode plotter and spectrum analyzer	3.9 x 3.9 x 1.4	0.54	USB cable, user's manual	146.95
2137422	Velleman	PCSGU250	12MHz	All-in-One PC lab with o-scope, spectrum analyzer, recorder, function generator, bode plotter	2.2 x 8.2 x 7	2.1	Scope probe, BNC-to-RCA adaptor, USB cable, CD software, manual	199.95
2218273	Uniteq	OS-5030A	30MHz	2-Channel dual trace, sensitivity 1mV/div, alt, triggering function (vert mode), 6" rectangular CRT display, sweep mag. (x10)	16.1 x 12.4 x 5.2	17.2	Probes not included	444.95
2171655	Uniteq	DS-1065	60MHz	2-Channel, 500MSa/s, built-in delay sweep function, 320x240 pixel high-resolution 5.7" display, USB storage	11.8 x 5.9 x 5.1	8.0	2 probes, DB9 cable, USB cable, power cord, user's manual, CD software	549.95
2143401	Instek	GDS-1152A-U	150MHz	2-Channel, 1GSa/s, 2Mpoint record length	12.2 x 5.6 x 5.5	7.9	Test probe, AC cord, user's manual	599.95

Oscilloscope Probe Sets

- Input resistance at x10 ratio: 10MΩ
- Accessories may include: tips, ground lead, hooks, protection caps, trimmer screwdriver



* Web Code: RAC



Part No.	Manufacturer	Mfr. Part No.	Bandwidth	Attenuation Ratio	Description	Length (ft.)	1	5
2130781	Velleman	PROBE60S	60MHz	1:1 or 10:1	IEC-1010 CAT II, 600V max	4.0	\$11.75	\$11.25
2145342	EZ Digital	T5060	60MHz	1:1 or 10:1	300VDC max.	4.0	22.95	20.95
22892	BenchPro	LF101E	60MHz	1:1 or 10:1	600VDC max.	5.0	19.95	17.95
2189880	BenchPro	P6100*	100MHz	1:1 or 10:1	600VDC max.	4.0	19.95	17.95
2130618	Velleman	PROBE100	100MHz	1:1 or 10:1	IEC-1010 CAT II, 600V max	4.0	24.95	22.49

* 2 probes included

* For additional products, availability and specifications visit [Jameco.com](http://www.Jameco.com) and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com