

# Cutters, Strippers, Crimpers & Tool Kits

Xcelite

JAMECO  
BenchPro



Wire Cutters/Strippers/Crimpers

molex

\* Web Code: GBU



Part No.	Manufacturer	Mfr. P/N	Description	Functions			Size (L" x W")	Pricing	
				Cut	Strip	Crimp		1	5
179902	BenchPro	GPL-171	4" leaf spring cutters with flush side cutting, forged steel, cushion grip	✓			4.0 x 2.6	\$3.95	\$3.59
2123320	BenchPro	GPL-101	4.5" spring return cutters with flush side cutting, carbon steel, vinyl grip	✓			4.5 x 2.6	4.95	4.49
35482	BenchPro	AX103	4.3" Diagonal wire cutters, rubber handles, 0.5" cutting blade, 45° angle	✓			4.3 x 2.1	7.95	6.95
2203750	Plato	175LX	5.6" Ergonomic, ESD-safe shear lead cutter with guard, blue grips	✓			5.6 x 2.0	9.95	8.95
146712	Xcelite	170M	5" general purpose shearcutters, flush cutting, red cushioned grips	✓			5.0 x 2.5	7.49	7.25
217921	Xcelite	MS54J	4" oval head-flush diagonal cutters, flush cut, green cushioned grips	✓			4.3 x 1.8	21.49	20.49
217904	Xcelite	MS549JV	4" tapered head diagonal cutters, flush cut, green cushioned grips	✓			4.2 x 1.8	21.49	20.49
2112292	BenchPro	TTK-061	UTP/STP wire stripper, 3-24 AWG, shielded/unshielded/twisted pair cable		✓		3.5 x 1.3	2.95	2.59
159185	Hanlong	HT-332D	2-blade rotary coax cable strippers, 4 settings for cable sizes 4-12mm		✓		3.9 x 0.7	12.95	11.49
114535	Hanlong	HT-336G	Ratcheted BNC crimper, for RG58, RG59, RG62, RG174, and fiber optic			✓	8.5 x 2.5	25.95	23.49
78992	Hanlong	HT-108	5" cutter/strippers, 10-30 AWG, spring return, screw-adjustable wire gauge	✓	✓		5.0 x 3.0	5.95	5.49
215889	BenchPro	JE-2022C	5" cutter/strippers, 10-24 AWG, spring return, dial to adjust wire gauge	✓	✓		5.0 x 3.0	5.95	4.95
159274	Hanlong	HT-1091	5" cutter/strippers, 20-24 AWG, spring-loaded, insulated grips, 45° angle	✓	✓		5.0 x 3.0	5.95	4.95
2236666	Hanlong	HT-206	6-1/2" cable cutter, cuts copper to 3/8" Dia. closed lock	✓			6.5 x 2.5	12.95	11.95
2112284	BenchPro	GTA-002	Automatic wire strippers, 10-24 AWG, spring-loaded handle with wire stopper	✓	✓		6.8 x 3.2	9.95	8.95
159291	Hanlong	HT-5023	6.6" cutter/strippers, 20-30 AWG, cuts steel wire, scale markings in AWG/mm	✓	✓		6.6 x 2.0	10.95	9.95
99443	Hanlong	HT-202A	Non-insulated terminal crimper, for D-sub and non-insulated connectors	✓		✓	7.3 x 1.5	9.95	8.95
159266	Hanlong	HT-213	D-sub crimper, crimps D-sub pins and sockets, works with 20-28 AWG wire	✓		✓	7.0 x 4.0	15.95	14.49
161218	Ideal	45-121	6" cutter/strippers, strips 16-26 AWG stranded, 14-24 AWG solid, plier nose	✓	✓		6.0 x 2.0	17.95	15.95
175098	BenchPro	GTA-006H	Automatic strippers, 8-22 AWG, spring-loaded handle with wire stopper	✓	✓		7.0 x 3.5	18.95	16.95
2236851	Cal Term	1209	8.0" self adjusting stripper/crimper 8-22 AWG	✓	✓	✓	8.0 x 2.0	11.95	10.95
18797	Hanlong	HT-1041	7-in-1 wire-handling tool, 10-18 AWG, steel wire cutter, wire loop, red	✓	✓	✓	6.6 x 3.0	6.95	6.25
127862	Hanlong	HT-1042	7-in-1 wire-handling tool, 16-26 AWG, steel wire cutter, wire loop, blue	✓	✓	✓	6.6 x 3.0	7.95	6.95
127871	Hanlong	HT-1043	7-in-1 wire-handling tool, 22-30 AWG, steel wire cutter, wire loop, orange	✓	✓	✓	6.6 x 3.0	7.95	6.95
2153078	BenchPro	GRK-42N	8.5" cutter/crimper/stripper, ergonomic grip, 10-22 AWG, wire gauge markings	✓	✓	✓	8.5 x 3.0	7.95	6.95
2192376	BenchPro	HT-N5684	7.5" modular crimping tool, 8P8C/RJ45, 6P6C/RJ12, 6P4C/RJ11, 4P4C and 4P2C	✓	✓	✓	7.5 x 3.0	16.95	14.95
304928	Molex	63811-10007	Crimp tool for rectangular contacts, 14-24 AWG side entry, Mini Fit Jr. series	✓	✓	✓	7.5 x 3.0	54.95	50.95
304936	Molex	11-03-0044	Extraction hand tool, terminal housing and extraction, Mini Fit Jr. series	✓	✓	✓	7.5 x 3.0	20.95	19.95

Test/Tools

JAMECO  
BenchPro

## 26-Piece SAE Hobby Tool Set

- 4-1/2" long nose pliers
- #1 & #2 Phillips bits\*
- #1 & #2 pozi bits\*
- 3/16" & 1/4" slotted bits\*
- Hex to 1/4" driver adapter\*
- Compact carrying case
- 4-1/2" diagonal cutting pliers
- T-10, T-15, and T-20 Torx bits\*
- 3" extension bar for 1/4" drive
- 3 slotted and 3 screw driver precision set
- 3/16", 1/4", 11/32" and 3/8" sockets for 1/4" drive
- Size: 12.0"L x 9.0"W x 2.0"H • Weight: 1.5 lbs.



Part No.	Description	1	5	25
170069	26-pc. SAE tool set ...	\$12.95	\$11.49	\$9.95
2231321	10-pc. SAE bit set w/ ...	3.95	3.59	3.29

\* Tool Kits — Enter Web Code CAA

\* Crimping Tools — Enter Web Code GBU

JAMECO  
BenchPro

## 95-Piece Pro-Tech Tool Kit

- Kit includes:
  - Navy blue storage box
  - 7-piece hex key set
  - 5-piece needle file set
  - 10-piece wrench set
  - 30W soldering iron
  - 8 different pliers
  - Hammer
  - 6-piece precision screwdriver set
  - Wire stripper/crimper
  - 29-pc. socket wrench set
  - Inspecting mirror
  - Digital multimeter
  - Lead-free solder core
  - Desolder pump
  - 6" chrome-plated wrench
  - Stainless steel tweezer
  - Size: 18.4"L x 13.4"W x 6.4"H
- Tape measure
- Aluminum flashlight
- Plastic flip-top box
- Cleaning brushes
- Mini drill with drill bits
- Mini hobby vise
- Elastic wrist strap
- IC extractor
- Electrical tape



Part No.	Description	Wt. (lbs.)	Price
2153756	95-piece tool kit	20.6	\$199.95

JAMECO  
BenchPro

## 100-Piece Professional Electronics Tool Kit

- Kit includes:
  - Soldering iron
  - 12 screwdrivers
  - Crimper/Stripper
  - Adjust. wrench
  - 6-piece screwdriver set
  - 3-piece soldering aid kit
  - 7-piece hex key set
  - Flashlight
  - Solder pen
  - 5-piece file set
  - Desoldering pump
  - Voltage tester
  - Vacuum cleaner
  - Cordless screwdriver kit (bits included)
  - Aluminum case features removable pallets, surface-type locks, and black plastic handle
  - Size: 18.0"L x 14.0"W x 6.0"H • Weight: 20 lbs.
- 4 Pliers
- Tape
- Vise
- Brush
- Storage box
- Soldering stand
- 10-piece wrench set
- 2 bottles cleaning liquid
- Extractor
- Blade cutters
- Multimeter
- Wrist strap
- Tweezers
- Scissors



Part No.	Description	1	5
242851	100-piece tool kit	\$159.95	\$149.95

\* For additional products, availability and specifications visit [Jameco.com](http://Jameco.com) and enter the Web Code in the product search box

3 LEVELS OF SAVINGS		
NAME BRANDS	HOUSE BRANDS	SPECIAL BUY

Order by Phone at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)