

Screwdrivers, Calipers & Miscellaneous Tools

JAMECO BenchPro Ball-End, Hex Key, Screwdriver & Socket Sets

These small screwdriver and hex-key hand tool sets are great for working on small-scale jobs like electronics, computer repair, craft or models. The tools are stored in clam shell boxes or internally for convenience and organization. Get it right the first time around with these reliable tools.

- Delivers perfect balance between tip strength and working angle
- Ergonomically designed anti-roll handle
- Bondhus: Made in USA, ball-end inserts quickly into screw head up to 25 degrees

*Web Code: CAQ

Part No.	Mfr.	Description	1	10
34059	BenchPro	6-pc. precision screwdriver set (Phillips #0 - 1/16", 5/64", 3/32", #1 - 1/8", 9/64")	\$3.95	\$3.59
168735	Xcelite	XP600 6-pc. ESD-safe screwdriver set, slotted & philps, vanadium steel w/ black oxide tips and case	27.95	26.95
226106	BenchPro	6-pc. precision 50 mm torx screwdriver set (Torx - T5, T6, torx hex - T7, T8, T9, T10)	11.95	10.95
226094	BenchPro	11-pc. magnetic AWL prec. screwdriver set (slotted -.9, 1.2, 1.4, 1.8, 2.4, 3 mm, Phillips - #00, #0, #1)	3.95	3.59
2096173	Bondhus	12-pc. ball-end hex key set (.05"; 1/16"; 5/64"; 3/32"; 7/64"; 1/8"; 9/64"; 5/32"; 3/16"; 7/32"; 1/4"; 5/16")	13.95	12.49
2231339	BenchPro	4-pc. metric 1/4" 6 point socket set (5mm, 6mm, 8mm, 10mm)	6.95	6.25
127271	BenchPro	6"L pocket screwdriver	1.95	1.59



JAMECO BenchPro 5-Piece Needle File Set

- Round, square, tri-square, half-round, flat
- Color: black with red handle
- Made of heavy duty hardened steel • Each 7" long

Part No.	Description	1	10	25
2157589	5-piece file set	\$5.95	\$5.39	\$4.79

JAMECO BenchPro 30 AWG Wire Wrap/Strip Tool

Recommended for use on 0.025" (0.63mm) square posts on 0.100" (2.54mm) center grids. The first 1-1/2 loop on the modified tool has wire insulation.

- Modified wrap for 30 gauge Kynar wire (pg 41)
- Knurled handle for easy grip • 5" long
- Wire stripper stored in handle

Part No.	Description	1	5
2150361	Modified wrap tool	\$19.95	\$17.95

JW Strip-Wrap-Unwrap Tools

- Tool tip made of tempered steel
- Spring steel cutter
- Use with 30 AWG wire on .025" square posts
- No solder necessary, see pg 41 for wire • 4.5" long
- 34585: wraps 1 to 2 turns of insulated portion of wire for secure connections

Part No.	Mfr.	Part No.	1	5
236785	HSR30 (Regular)		\$27.95	\$25.95
34585	HSM30 (Modified)		29.95	27.95

1/4 & 1/2-Watt Resistor & Capacitor Lead Forming Tool

- Watt size indicates appropriate package size
- Bends lead length in 0.05" increments
- Lead spacing: 1/4W: 0.4"-1.5"; 1/2W: 0.5"-1.5"

Part No.	Description	Size (L" x W")	1	10
106884	1/4W & 1/2W	5.4 x 1.5	\$4.95	\$4.49

JAMECO BenchPro PLCC & DIP IC Extractors

- 16838: BenchPro DIP IC extractor
- 2173175: BenchPro PLCC IC extractor
- 16766: Velleman PLCC IC extractor

Part No.	Manufacturer	Description	1	10	100
16838	BenchPro	DIP	\$2.95	\$2.59	\$1.95
2173175	BenchPro	PLCC	2.49	2.25	1.95
16766	Velleman	PLCC	2.95	2.75	2.49

JAMECO BenchPro Tweezers

- 252929: Straight round, fine-point tip, stainless steel
- 253092: Curved fine-point tip
- 252938: Self-closing reverse-action tweezers; medium point tip; stainless steel
- 253113: Fine-point tip, insulated, anti-static
- 2235129: Fine-point angled tip, stainless steel

JAMECO BenchPro 4-Pcs. Steel Tweezer Set

- 4 styles of stainless steel tweezers, one self-locking
- | Part No. | Description | 1 | 10 | 100 |
|----------|---------------------|--------|--------|--------|
| 10735 | 4-piece tweezer set | \$5.95 | \$5.49 | \$4.95 |

Xytronic Vacuum Tweezers

- Easy interchangeable tips
 - ESD safe body
- | Part No. | Mfr. | Includes | 207239 | 1 | 5 |
|----------|----------|-------------|--------|---------|---------|
| 207239 | Xytronic | 4 tips/cups | | \$15.95 | \$14.49 |
| 2183939 | Xytronic | 3 tips/cups | | 24.95 | 22.49 |

22"L Anti-Static Plastic DIP IC Storage Rails & Rubber Rail Stops

- 29524 (ICs not included)
 - 29583
- Note: previously used
- | Part No. | Description | Pins | 1 | 10 | 100 |
|----------|-------------|----------------------|-------|-------|-------|
| 29516 | .300"W rail | 8,14,16,18,20,22 ... | \$.29 | \$.25 | \$.22 |
| 29524 | .600"W rail | 24,28,36,40 | .29 | .25 | .22 |
| 29583 | Rubber stop | — | * | .09 | .07 |

JAMECO BenchPro IC Pin Straightener

- Straightens 8/14/16/18/20/24/28/40/42-pin ICs
 - Includes: Ground terminal
- | Part No. | Size (L x W x H) | 1 | 10 | 100 |
|----------|--------------------|--------|--------|--------|
| 99363 | 3.3" x 1.5" x 0.4" | \$7.95 | \$6.95 | \$5.95 |

Anti-Static Work Mats and Foam

These mats are made of attractive semi-conductive vinyl that provide adequate discharging yet will not short leads or pins.

Part No.	Dimensions	Wt. (lbs.)	1	10	25
10576	11.3" x 22"	0.7	\$9.95	\$8.95	\$7.95
10584	19.5" x 23.5"	1.1	12.95	11.49	9.55
2130853	19.7" x 23.6"	1.1	14.95	13.49	11.95
2152075	24" x 48"	3.9	69.95	64.95	59.95
2237896	12" x 6"*	—	4.95	4.49	3.95
13864	24" x 12"*	—	12.95	11.95	10.95

*Foam

*Anti-Static — Enter Web Code XAA

Anti-Static Wrist Straps

- Comfortable, adjustable black Velcro wrist strap
- The coiled grounding cord has banana plug and alligator clips
- Extended cord: 9'L (2131266: 6'L)

Part No.	Mfr.	Color	1	10	100
34552	BenchPro	Black/yellow	\$4.79	\$4.29	\$3.89
2202087	3M	Disposable	1.49	1.25	1.09

JAMECO BenchPro Field Service Static Kit

- 4 pockets for ESD safe storage
 - 10' ground strap and 6' wrist strap share on one ground point
 - Size: 2' x 2.13'
- | Part No. | Cross Ref. No. | 1 | 5 | 25 |
|----------|----------------|---------|---------|---------|
| 2113720 | 8PK-AS07-1 | \$14.95 | \$13.95 | \$12.95 |

JAMECO BenchPro Digital Display Calipers

- Hardened stainless steel
 - Display: inches to 0.001; mm to 0.01
 - Instructions for making internal, external, depth and step measurements
 - One-year warranty
- Includes: Fitted case and 1.5V LR44 battery (replacement battery, P/N 140783, pg 111)
- | Part No. | Description | 1 | 5 |
|----------|---------------------|---------|---------|
| 127482 | Measures 6" (150mm) | \$27.95 | \$25.95 |
| 2153545 | Measures 8" (203mm) | 34.95 | 31.95 |

*For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box

