

Heat Guns & Soldering Equipment

3 LEVELS OF SAVINGS
 NAME BRANDS HOUSE BRANDS SPECIAL BUY

Weller® 12-Watt Li-Ion Battery Powered Soldering Iron

Provides 45 minutes of continuous soldering.
 • Li-Ion battery charges in about 3 hours

- Cordless, round, co-molded handle designed for comfort
 - Stable heat shield base with built-in side stand
 - 12 watt performance, up to 1070°F/580°C
 - LED illumination and modular tips
- Includes:** BL60 iron, 0.031" conical tip, charger base, foot stand and plug-in power supply.



Part No.	Mfr.	Part No.	Description	Price
2246493	BL60MP	12W solder iron	\$68.95
2246506	BL10	0.031" conical tip	9.95
2246522	BL12	0.047" conical tip	9.95
2246514	BL11	0.125" chisel tip	9.95

XYTRONIC® 16 to 30-Watt Variable Soldering Iron & Stand

116572: Length: 7.5"

- Black anodized steelbase - 5.3"L x 3.3"W
- See below for replacement sponge (P/N 134631)
- Fits most soldering irons .85" dia.



Includes: Sponge

Part No.	Description	1	5	25
116572	258VL soldering iron ...	\$17.95	\$15.95	\$14.49
36329	Soldering stand	4.95	4.49	3.95
134631	Sponge (for P/N 36329)	2.95	2.59	2.29

Weller® 18-Watt Pro Series Soldering Iron

- Heats up to working temperature in just 35 seconds
- Up to 900°F temperature
- Co-molded grip for a comfortable feel
- Performance equivalent to a 60 watt iron
- Designed be self-standing, no stand is needed
- Tips use a phono jack and plug for easy tip exchange • UL and CUL listed
- Ideal for hobbies, kits, radios and electronics



Includes: Charger and WPS10 soldering tip

Part No.	Mfr.	Part No.	Description	1	5
2153810	WPS18MP	18-watt iron	\$28.95	\$27.95
2158637	WPS11	0.03125" chisel tip	9.95	8.95
2158629	WPS10	0.03125" conical tip	9.95	8.95

Weller® 25 & 35-Watt High-Quality Soldering Irons

- 120VAC @ 60Hz
- Interchangeable heater elements
- Lightweight handle with cushioned grip
- Quick change knurled collar • Length: 9"



Includes: Power cord & ST3 tip (pg 123)

Part No.	Mfr.	Part No.	Description	1	5
170587	WP25	25W solder iron	\$44.95	\$43.95
192102	WP35	35W solder iron	55.95	53.95
146608	ST1	Screwdriver tip 1/16"	3.69	3.49
146616	ST3	Screwdriver tip 1/8"	4.95	4.75
192145	ST6	Screwdriver tip .031"	3.95	3.69
146624	ST7	Conical tip 1/32"	3.95	3.69

NTE® Heat Guns and Strippers

Heat guns are ideally suited for drying, heating, welding, shrinking, soldering, desoldering and many other applications where heat is required.



Part No.	Mfr.	Product No.	Description	Watts	Heat Setting (°F)	Temp. (°F max.)	1	5
2232796	BenchPro	TT79001	Compact heat gun for light duty	350	494-575	575	\$17.95	\$15.95
2117413	NTE	HG300-D	Mini heat gun	350	482-662	662	24.95	22.49
254925	BenchPro	1001A	Economical heat gun	1200	600 & 1000	1000	42.95	39.95
2244480	BenchPro	866B	Adjustable heat gun	1800	140-1112	1112	19.95	18.95
2007062	BenchPro	1004	Accessory kit for P/N 254925	—	—	—	11.95	10.95

Weller® 20-Watt Soldering Iron

A high-quality, mains-powered soldering iron for general purposes.

- Power supply: 20W/110VAC
- UL approved
- Cord length: 5 feet

Includes: Iron stand

Part No.	Mfr.	Part No.	1	5
2131151	VTS20U	\$6.95	\$6.25

XYTRONIC® 25-Watt Thermally Balanced Soldering Iron

The XY200GX is a thermally balanced soldering iron for the professional or hobbyist.

- 120VAC; 6' cord • Length: 8.0"
- 25-watt power consumption
- Interchangeable tips (pg 124)
- One-year warranty

Includes: 1.6mm conical tip

Part No.	Mfr.	Part No.	1	5	25
129040	200GX-25W	\$9.95	\$8.95	\$7.95

JAMECO® BenchPro 35-Watt Soldering Iron

A high quality, mains powered soldering iron for general purposes.

- 110-120VAC • 35-watt
- Long life tip
- Cord length: 5'
- 5' solder tube
- UL/CUL approved

Part No.	Cross Ref. No.	1	5	25	
2228367	CL-1	\$9.95	\$8.95	\$7.95

JAMECO® BenchPro Glue Gun and Glue Sticks

- Adheres to PCBs, cardboard, wires, metal and cloth
- Silicon nozzle
- Electronic heating
- Trigger action
- Utilizes 100mm long gluesticks (2 sticks included) • Size: 7.3"L x 6.3"W

Part No.	Description	1	5	25	
72696	Glue gun	\$8.95	\$7.95	\$6.95
78633	Glue sticks (6/pk)	2.95	2.59	2.29

Weller® LED Soldering Irons

- 3 high-temperature LEDs with 25 lumen light intensity
- Each iron includes soldering aid tool, tip and user's manual
- 2174901/2174928 includes soldering aid tool, lead-free solder and 2 spare soldering tips

Part No.	Mfr.	Part No.	Description	1	5
2174901	SP25NKUS	25W soldering iron kit	\$19.95	\$18.95
2174936	SP40NUS	40W soldering iron	19.95	18.95
2174928	SP40NKUS	40W soldering iron kit	23.95	22.95

XYTRONIC® 40 & 60W High-Performance, Economical Soldering Irons

- Iron length: 9"
- 120VAC; 6' cord with 3-prong plug
- High-performance double-wound nichrome heating element
- Flexible, burn-resistant silicon cable

Part No.	Description	1	5	25	
224602	40W soldering iron	\$9.95	\$8.95	\$7.95
195223	60W soldering iron	10.95	9.95	8.95
226018	Conical tip for P/N 224602	3.95	3.59	3.29

XYTRONIC® 60-Watt Replacement Soldering Iron

- Compatible with the following XYtronic soldering stations: 168-3C, 168-3CD, 9-60A and 9-60D.

Part No.	Mfr.	Part No.	1	5
2144649	XY-207ESD	\$34.95	\$31.95

* Soldering Stands — Enter Web Code YAU

Weller® 100-Watt Soldering Iron

- "Closed loop" method of controlling max. tip temperature
- Nominal heat-up time with 700°F tip is 110 seconds
- Length: 6"
- 120VAC @ 60Hz input • Weight: 0.7 lbs.

Includes: CT6F7 (0.375" screwdriver tip; 700°F)

Part No.	Mfr.	Part No.	Description	1	5
192081	W100PG	Solder iron	\$64.95	\$62.95
192090	CT6F7	.375" screwdriver tip	6.95	6.75

Replacement Sponges

For XY-60D, XY-379 & XYT379-C

Part No.	Mfr.	Part No.	Size (in.)	1	5	25
134631	78-465715	1.7 x 2.1	\$2.95	\$2.59	\$2.29
236460	78-744615	1.8 x 2.9	2.95	2.59	2.29

* Prototyping Boards — Enter Web Code PBH

* Soldering Irons — Enter Web Code QAS

- Cord strain relief for extended life
- Durable cable with 5-foot reach

