

Soldering Equipment, Solder Kits & Tips

3 LEVELS OF SAVINGS
NAME BRANDS HOUSE BRANDS SPECIAL BUY

80-Watt SMD Rework Stations



2120541

- Thermocouple sensor for stable temp.
- Rapid heat-up and recovery

2120541 • Size: 7.4"L x 5.0"W x 3.3"H • Wt.: 2.6 lbs.
• Adjustable temperature: 482°F-842°F (250°C-450°C)
2099219 • Size: 8.8"L x 6.0"W x 4.5"H • Wt.: 6.8 lbs.
• Adjustable temperature: 392°F-896°F (200°C-480°C)

Includes: Base power unit, sponge, stand, surface mount tweezer iron and stand for tweezers

Part No.	Description	1	5
2120541	SMD rework tweezer station	\$59.95	\$54.95
2099219	Soldering & tweezer combo station ...	124.95	114.95
156814	SMD conical tip (1/32")	3.95	3.59

30-Watt Solder Tool Kit

Includes: Soldering iron with stand, long nose pliers, wire strippers, side cutters & sponge



Part No.	Description	1	5
358598	7-piece tool soldering kit	\$15.95	\$14.95

6-Piece Solder Aid Tool Kit

Includes: Various tips: chip holder, spacer, reamer, lever, needle, knife, fork shaft, hook and brush



Part No.	Cross Ref. No.	1	5
2096000	GSR-107	\$6.95	\$6.25

600 & 1000-Watt Lead-Free Hot Air SMD Rework Stations

- Incorporates the largest pump in the industry
- Long life ceramic heater insures accurate and sufficient heat where you need it
- Automatic cooling mode protects the heating element
- Adjustable air-flow: **2128032:** 1.5-40L/min; **2174741:** 1.5-7.L/min.
- Nichrome heating element
- Power supply: 100-120VAC @ 60Hz or 220-240VAC @ 50Hz
- Electronically controlled temperature system with digital readout in preset and actual temperature
- Hot air temp. range: 100°C - 480°C (212°F - 896°F)
- Temp lock-out feature, password protected
- Sensor/pump failure detection
- Static-free circuit design
- 25W diaphragm pump
- Size: 7.3"W x 5.3"H x 9.6"D • Weight: 10.8 lbs.



2128032



2174741

2128032 includes: Extra 600W heater, 4 focus hood tips, 5 stainless steel anti-magnetic tweezers, IC popper for IC extraction
2174741 includes: 2 focus hood tips, 5 stainless steel anti-magnetic tweezers, IC extractor

Part No.	Mfr. P/N	Description	1	5
2128032	LF-852D	600W station	\$199.95	\$179.95
2174741	LF-852D-II	1000W station	219.95	199.95

*SMD Rework Stations — Enter Web Code NAT

900-Watt Lead-Free, ESD-Safe Soldering Rework Station

- 3-in-1 design: soldering, desoldering and hot air station
- 2 LED displays
- Temperature and air pressure settings
- Temperature-lock feature
- Heater and sensor failure detection
- Input voltage: 100-120VAC @ 60Hz
- Soldering iron temperature range: 302°F - 896°F
- Desoldering iron temperature range: 572°F - 842°F
- Hot air temperature range: 212°F - 896°F
- Fume extractor air volume: 95/115 CFM



Includes: Soldering iron, desoldering iron, hot-air iron, fume extractor, extra heating element, 2 soldering iron stands, 4 hood tips and 5 tweezers

Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
2128041	LF-853D	26.5	\$474.95	\$459.95

Heat Sink Clip

Heat sink absorbs and dissipates heat during soldering & desoldering of sensitive parts



Part No.	Description	1	10	25
100378	Clip-on heat sink	\$1.49	\$1.25	\$0.99

Solder Super Combo

Includes: 6 oz. pump bottle, 6pc scraper set, 6" acid brush, heat sink clip, 35W solder iron, solder and solder wick.



Part No.	Mfr. Part No.	1	5	25
2244033	JESC-2000	\$26.95	\$24.49	\$21.95

Tips & Replacement Parts for XYtronic Soldering and Desoldering Products


*Web Code: NAB



156814



207327



156822




207298




127642



2095509



2095517



Part No.	Mfr. P/N	Description	For XYtronic Model Numbers (* Legacy Models)										Pricing								
			163, 2359L JS232*	139E3D 319-C, 369D LF-1600	XY90A 379*	168 2009X DESD 166-3C	960D*	968	9995DA*	LF-2000, 165D	LF-700, 200PAG	2000, LF-5000	L307A, LF-5000	LF-3550, LF-5000	LF-3200	1	10	25			
35318	XY48	Assembly - 60W w/ nichrome heater																	\$24.95	\$22.49	\$19.95
35326	XY401	Soldering tip - conical bevel 1/32"																	3.59	3.25	2.95
35078	XY402	Soldering tip - semi-chisel 1/32"																	3.59	3.25	2.95
35334	XY403	Soldering tip - conical sharp 1/64"																	3.59	3.25	2.95
35115	XY404	Soldering tip - conical chisel 1/16"																	3.59	3.25	2.95
35238	XY405	Soldering tip - semi-chisel wide 1/8"																	3.59	3.25	2.95
207335	XY406	Soldering tip - long conical chisel 3/64"																	2.95	2.75	2.49
207351	XY410	Soldering tip - chisel 3/16"																	3.59	3.25	2.95
156814	XYB01	Soldering tip - sharp conical chisel 1/32"																	3.95	3.59	3.25
207327	XYB03	Soldering tip - conical sharp 1/64"																	3.95	3.59	3.25
156822	XYB04	Soldering tip - conical sharp 1/16"																	3.95	3.59	3.25
207298	XYB05	Soldering tip - semi-wide chisel 1/8"																	3.95	3.59	3.25
127642	XYD12	Desoldering tip - 1.2mm (.0472")																	6.95	6.25	5.59
2095509	XY12	Desoldering tip - 1.2mm (.0472")																	7.95	7.19	6.49
2095517	XY15	Desoldering tip - 1.5mm (.0586")																	7.95	7.19	6.49
2135136	44-710654	Soldering tip - conical 0.2mm (.007")																	3.95	3.59	3.25
2135152	44-710662	Soldering tip - chisel 2.4mm (.094")																	3.95	3.59	3.25
2144171	44-413081	Soldering tip - conical 0.5mm																	3.59	3.25	2.95
2144163	44-413072	Soldering tip - semi-chisel 0.8mm																	3.59	3.25	2.95
2144155	44-413069	Soldering tip - flat 1.6mm																	3.59	3.19	2.89