

# Vises, Soldering Accessories & Tape Products

3 LEVELS OF SAVINGS		
NAME BRANDS	HOUSE BRANDS	SPECIAL BUY

## PANAVISE Multi-Purpose Work Center

- Jaws open to 9°
- Double action extra wide self-centering heads allow fast opening and closing; centered weight allows jaws to hold heavier objects; plates can be reversed to close together; reversible jaw pads feature ribbing on one side and a V groove on the other
- Base has three 1/4" countersunk mounting holes
- Overall base diameter is 8.5"



Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
<b>684852</b>	350	5.0	\$94.95	\$89.95

## Electronic Work Center

- Size: 8.5"W x 7.8"H
- Includes: Circuit board holder, standard base, tray base mount and wire holder



Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
<b>27060</b>	324	5.3	\$94.95	\$89.95

## PANAVISE Rapid Assembly Circuit Board Holder

- 8 positions rotating adjustment, six positive lock positions in the vertical plane and height adjustment for quick board rotation speeds
- Holds circuit boards from 1/8" (3.2mm) to 12" (304.8mm) wide and up to 5/32" (4mm) thick
- Arms move independently • 10" high



Part No.	Mfr. Part No.	Wt. (lbs.)	1	5
<b>684844</b>	333	6.4	\$86.95	\$79.95

## JAMECO BenchPro Vacuum Base Vise

- Features the patented "split ball" that tilts, turns and rotates through three planes
- Powerful suction pad for quick and easy set-up
- Nylon jaws open 2.25"
- Size: 5.0"L x 4.0"W x 6.3"H



Part No.	Product No.	Wt. (lbs.)	1	5
<b>262116</b>	GV-300	3.3	\$34.95	\$31.49

\* Vises — Enter Web Code TAD

## JAMECO BenchPro Solder Spool Stand

- 12 pc. solder spool stand (some assembly required)
- Size: 3.6"W x 3.9"D x 4.3"H
- Shaft diameter: 0.6"



Part No.	Description	Wt. (lbs.)	1	5	25
<b>141761</b>	Solder stand	1.6	\$12.95	\$11.49	\$9.95

## Soldering Tip Cleaner with Stand

- For cleaning soldering iron tips without the use of water and sponge
- Metal wool for cleaning
- Rubberized base for stability



Part No.	Description	Wt. (lbs.)	1	5	25
<b>156777</b>	Tip cleaner and stand	0.5	\$6.95	\$6.39	\$5.79
<b>160004</b>	Metal wool replacement	0.1	2.95	2.59	2.29



## Solder Bars, Rolls and Pocket Packs

Due to extraordinary price fluctuations, solder prices are subject to change.

\* Web Code: ABD

Part No.	Manufacturer	% Composition				Diameter Inches/mm	Weight	Type†	Pricing	
		Tin	Lead	Silver	Copper				1	10
<b>2210132</b>	Kester	60	40	—	—	0.025/0.64	1.0 lbs.	1	\$31.49	\$29.95
<b>2238135</b>	BenchPro	60	40	—	—	0.025/0.64	1.1 lbs.	1	29.95	26.95
<b>73576</b>	Kester	60	40	—	—	0.031/0.787	0.5 oz.	2	2.59	2.45
<b>32117</b>	Kester	60	40	—	—	0.031/0.787	1.08 lbs.	1	29.95	28.49
<b>2184616</b>	Kester	60	40	—	—	0.062/1.57	1.03 lbs.	1	34.95	29.95
<b>141786</b>	BenchPro	60	40	—	—	0.031/0.787	1.13 lbs.	1	26.95	23.95
<b>176057</b>	BenchPro	60	40	—	—	12.5x0.75x0.44	1.1 lbs.	3	29.95	27.95
<b>2188220</b>	Kester	60	40	—	—	0.05/1.27	1.0 lbs.	1	32.95	29.95
<b>94570</b>	Kester	60	40	—	—	0.05/1.27	1.3 oz.	2	4.29	4.09
<b>2210124</b>	Kester	60	40	—	—	0.040/1.02	1.0 lbs.	1	29.95	28.49
<b>73605</b>	Kester	62	36	2.0	—	0.02/0.51	0.35 oz.	2	2.95	2.75
<b>2177694</b>	BenchPro	63	37	—	—	0.015/0.38	1.0 lbs.	1	29.95	25.95
<b>2237571</b>	Kester	63	37	—	—	0.020/0.51	1.0 lbs.	1	39.95	36.95
<b>2210116</b>	Kester	63	37	—	—	0.025/0.64	1.0 lbs.	1	32.49	30.95
<b>2237626</b>	Kester	63	37	—	—	0.031/0.79	0.5 oz.	2	3.59	3.29
<b>2210087</b>	Kester	63	37	—	—	0.031/0.79	1.0 lbs.	1	31.49	28.95
<b>2238143</b>	BenchPro	63	37	—	—	0.031/0.79	1.1 lbs.	1	27.95	24.95
<b>151474</b>	Kester*	63	37	—	—	0.031/0.787	1.0 lbs.	1	30.95	29.49
<b>2188246</b>	Kester	63	37	—	—	0.031/0.787	1.0 lbs.	1	31.49	29.95
<b>2237589</b>	Kester	63	37	—	—	0.040/1.02	1.0 lbs.	1	30.95	29.49
<b>2158178</b>	Kester	63	37	—	—	0.05/1.27	1.0 lbs.	1	30.95	29.49
<b>2237600</b>	Kester	63	37	—	—	0.062/1.57	1.0 lbs.	1	30.49	28.95
<b>668262</b>	BenchPro	96.3	—	3.2	0.5	0.04/1.02	7.2 oz.	1	39.95	35.95
<b>2113172</b>	Kester	96.5	—	3.0	0.5	0.031/0.787	0.43 oz.	2	4.49	4.25
<b>170457</b>	BenchPro	99.3	—	—	0.7	0.031/0.787	0.8 oz.	2	3.25	2.95
<b>668078</b>	BenchPro	99.3	—	—	0.7	0.04/1.02	9.15 oz.	1	26.95	23.95
<b>209075</b>	BenchPro	99.3	—	—	0.7	0.031/0.787	1.0 lbs.	1	34.95	31.95

\*Organic core †1. Roll; 2. Packet; 3. 13" Bar



141786



2188220



2237626



2238143



2113172



170457

## TECHSPRAY Chemtronics 5' Desolder Braids

Part No.	Manufacturer	Product No.	Description	Width (in.)	1	10
<b>2188748</b>	Philips	ZW050-5	Zip wick, Military/NASA certified, 5'	.005	\$2.49	\$2.25
<b>2192430</b>	Philips	ZW100-5	Zip Wick Military/NASA certified, 5'	.100	2.95	2.39
<b>2203776</b>	Techspray	1821-5F*	No-Clean, Military/NASA certified, 5'	.055	2.49	2.25
<b>124126</b>	Techspray	1815-5F	No-Clean, Military/NASA certified, 5'	.055	4.95	4.49
<b>2203784</b>	Techspray	1822-5F*	No-Clean, Military/NASA certified, 5'	.075	2.95	2.65
<b>124118</b>	Techspray	1816-5F	No-Clean, Military/NASA certified, 5'	.075	4.49	3.95
<b>2203792</b>	Techspray	1823-5F*	No-Clean, Military/NASA certified, 5'	.098	2.95	2.59
<b>263708</b>	Techspray	1817-5F	No-Clean, Military/NASA certified, 5'	.098	4.95	4.49
<b>2203805</b>	Techspray	1825-5F*	No-Clean, Military/NASA certified, 5'	.193	3.95	3.59
<b>2203768</b>	Techspray	1810-5F*	Pro Wick, pure rosin 5'	.075	2.75	2.49
<b>263695</b>	Techspray	1803-5F	Pro Wick, pure rosin, type R, 5'	.075	3.95	3.59
<b>263599</b>	Techspray	1804-5F	Pro Wick, pure rosin, 5'	.098	4.49	3.95
<b>41082</b>	BenchPro	GISW20	Desolder braid, solder wick, 5'	.079	1.95	1.75
<b>41100</b>	BenchPro	GISW25	Desolder braid, solder wick, 5'	.098	1.95	1.75
<b>153462</b>	BenchPro	GSR104D	Desolder braid, solder wick, 5'	.120	2.49	2.25
<b>2113130</b>	Chemtronics	60-3-5	Soder-Wick® no clean size 3, 5'	0.08	4.95	4.49
<b>2113148</b>	Chemtronics	60-4-5	Soder-Wick® no clean size 4, 5'	0.11	4.95	4.49

\* Anti static

\* Web Code: DAG



263708



263695



2113148

## 3M Tape Products

\* Web Code: TPS

Part No.	Description	Color	Width	Length	Thickness	1	10	50
<b>285587</b>	Vinyl electrical tape, Tartan 1710, UL	Black	.75"	20 yards	.007"	\$1.49	\$1.35	\$1.19
<b>2153764</b>	Vinyl electrical tape, temflex	Black	.75"	20 yards	.007"	1.39	1.25	1.09
<b>1643551</b>	Embossed copper foil, 1245 tape	Copper	.50"	18 yards	.004"	20.95	19.49	18.95
<b>2235663</b>	Polyimide film and silicone tape	Amber	.50"	36 yards	.007"	39.95	38.95	37.95



285587