

JAMECO ValuePro



Metal and Plastic Enclosures

The prototype builder boards on pg 131 are designed to fit into our ABS plastic and aluminum enclosures, metal cabinets and heavy-duty instrument cases. The pre-cut boards have 2 or 4 mounting holes compatible with the PC board mounting hardware (P/N 106551, pg 131) and adhesive standoff (P/N 2191592).

Board description: Laminated glass epoxy 1/16" thick fire retardant per FR-4 specs. Copper-clad and solder mask one side. Drilled holes: .035" diameter on .080" square pad. Pads spaced on .10" x .10" grid.

See page 39 for Knobs and page 77 for Hardware

*Web Code: UAL



ABS Plastic Enclosures

Lid for precision fit (adds 0.4" height). Complete with four screws and lid. All sizes below are interior dimensions. **18893**

Part No.	Cross Ref. No.	Size (L x W x H)	1	10	50	100
18922	H2855	3.1" x 2.0" x 0.9"	\$3.49	\$3.19	\$2.89	\$2.49
18914	H2853	4.9" x 2.5" x 1.5"	3.95	3.59	3.19	2.75
18893	H2851	6.0" x 3.5" x 1.9"	4.95	4.49	3.95	3.49
18906	H2852	7.5" x 4.3" x 2.3"	6.49	5.95	5.39	4.79
2234687	RP1240*	6.5" x 4.9" x 2.9"	17.95	15.95	14.49	12.95

*Polycarbonate

ABS Enclosures with Clear Top

Includes screws for mounting boards, rubber gasket for a tight seal on your equipment & drilled holes for mounting. **141841**

Part No.	Cross Ref. No.	Size (L x W x H)	1	10	50	100
141832	203C1	4.9" x 3.4" x 2.4"	\$9.95	\$8.95	\$7.95	\$6.95
141841	203D1	6.5" x 3.4" x 2.2"	9.95	8.95	7.95	6.95
141859	203F1	7.3" x 5.7" x 3.0"	14.95	13.95	12.95	11.95

ABS Heavy-Duty Instrument Cases

P/N 18877 includes ventilation and speaker sound slots. **18869**

Part No.	Cross Ref. No.	Size (L x W x H)	1	10	50	100
18869	H2505	7.9" x 6.3" x 2.5"	\$7.95	\$6.95	\$6.25	\$5.59
18877	H2507	10.0" x 7.5" x 3.1"	8.95	7.95	6.95	6.25

ABS Plastic Lip Top Enclosure

PCB standoffs molded into the case with a lip top for a precision fit. Painted black with a satin texture finish and protection against dust and splashing water. Assembly screws and lid included.

Part No.	Mfr. Part No.	Size (L x W x H)	Color	1	10	50
2138206	1551GBK	2.0" x 1.4" x 0.8"	Black	\$1.95	\$1.75	\$1.49

SERPAC

Specialty Enclosures



C Series — with Pinch-Fit for PCBs

- Simple 2-piece design
- 2-insert areas for customized I-plates

Please Note: Images used are representative. Color and shapes may vary by model.

Part No.	Mfr. Part No.	Color	Size (L" x W" x H")	1	10	25
675331	C-4-BK	Black	2.13 x 1.38 x 0.58	\$2.95	\$2.59	\$2.29

H Series — Four Piece Design

- Holds 4-AA batteries (contactors included)
- Circuit board mounting bosses
- Assembly with 6 screws RoHS compliant
- ABS plastic black

Part No.	Mfr. Part No.	Color	Size (L" x W" x H")	1	10	25
222778	H754AA	Black	7.20 x 3.65 x 1.26	\$8.95	\$7.95	\$6.95

S Series — Two-piece Standard Enclosures

- 2-piece design
- 2-insert areas for customized I-plates
- With screws

Part No.	Mfr. Part No.	Color	Batt. Holder	Size (L" x W" x H")	1	10	25
675462	111-BK	Black	None	3.61 x 2.27 x 1.51	\$4.95	\$4.39	\$3.95
2202108	341BLK*	Black	None	4.38 x 3.25 x 1.51	3.49	2.95	2.59
675489	131-BK	Black	None	4.38 x 3.25 x 1.51	6.95	5.95	5.39
675542	173-BK	Black	None	6.88 x 4.88 x 2.51	10.95	9.95	8.95
675551	193-BK	Black	None	9.50 x 6.34 x 2.51	14.95	12.95	10.95

*Drilled, ValuePro

Metal Enclosures

- Mounting screws and rubber feet included
- Glossy black textured steel top cover and ivory aluminum base

Part No.	Cross Ref. No.	Size (L x W x H)	1	10	50	100
208901	B2741A	4.0" x 3.3" x 2.2"	\$6.95	\$6.25	\$5.59	
208911	CMC11922	5.9" x 5.3" x 3.0"	9.95	8.95	7.95	
209350	B2746A	6.3" x 7.8" x 2.5"	9.95	8.95	7.95	
208929	B2744A	7.3" x 6.3" x 2.8"	10.95	9.95	8.95	
209358	SY0207	7.5" x 9.8" x 3.2"	15.95	14.49	12.95	

Die-Cast Aluminum Enclosures

Made from aluminum, an excellent heat sink, these cases are great for high temp circuits (up to 600°C). Includes screws. **11973**

Part No.	Cross Ref. No.	Size (L x W x H)	1	10	50	100
11957	B5002	3.9" x 2.0" x 1.0"	\$6.95	\$6.25	\$5.59	\$4.95
11965	03-125B	4.7" x 2.6" x 1.4"	9.95	8.95	7.95	6.95
2191867	BOX3-1455N-BK	6.3" x 4.6" x 2.1"	23.95	22.95	21.95	20.95
11973	03-125C	7.5" x 4.3" x 2.4"	19.95	18.95	17.95	16.95

Aluminum Enclosures

The enclosure comes in two pieces that slide together. **11870**

Part No.	Cross Ref. No.	Size (L x W x H)	1	10	50	100
11870	H2300	4.0" x 2.0" x 2.8"	\$5.95	\$5.49	\$4.95	\$4.49
11886	H2320	5.0" x 4.0" x 3.0"	6.95	6.29	5.59	5.49

Rugged Diecast Aluminum Alloy Enclosures

Protects from dust and splashing water, while also providing EMI/RFI shielding. Designed to meet IP54 rating. Unpainted with a vibra finish. Assembly screws included.

Part No.	Mfr. Part No.	Size (L x W x H)	Cover	1	10	50
2138169	1550A	3.5" x 1.4" x 1.2"	Lid top	\$5.95	\$4.95	\$4.25
2138290	1590B	4.4" x 2.3" x 1.1"	Lip top	7.25	6.45	5.39
2138302	1590BB	4.7" x 3.7" x 1.2"	Lip top	8.95	8.49	7.95



Black Plastic Mounting Enclosure w/ PCB Grooves



- Rear panels must be ordered separately
- Size: 5.65"W x 4.82"D x 2.83"H
- Material: noryl rosin

- 2228025 includes:
 - Enclosure with PCB grooves (NGS7411)
 - Front panel, plain (NGS7411P)
 - Front panel frame (NGS74PF)
- Screw clamps NGS-NK 2 3/4" (L)
- Self tapping screws (8)

Part No.	Description	1	10
2228025	Enclosure with PCB grooves and front panel	\$6.95	\$6.25
2228050	Rear panel, unpunched ABS, plain, black	3.95	3.59
2228041	Screw clamps for screw fitting enclosure (2) NGS-NK	2.95	2.59
263207	P.C. protoboard - 674 plated thru hole pads	7.95	6.95

Design your own kit and earn \$\$
www.ClubJameco.com