

Rack Mount Enclosures, Surge Protectors & USB Products

JAMECO
ValuePro

19" Rack Mount Enclosures

- Ventilation holes all side
- Finish: Flat black
- Front and back panels are steel with aluminum, pre-punched face plates
- 0.12" thick black front panel
- Need to assemble
- Top, bottom and sides are durable 0.035" steel
- All enclosures have handles



Includes: Mounting screws

Part No.	RU	Dimensions (In.)			Wt. (lbs.)	Pricing	
		H1	H2	D		1	5
132840	2U	3.46	2.88	11.75	9.1	\$59.95	\$53.95
2203590†	2U	3.50	3.50	15.50	9.1	29.95	26.95
132848	3U	5.22	4.75	11.75	10.6	69.95	62.95

† Assembled with 2 fans

* Rack Mount Products — Enter **Web Code GAT**

Wireless Keyboard with Touchpad

Connect with PCs, tablets, Android TV, Google TV boxes, XBOX360 & PS3 game consoles, Raspberry Pi and more.



- 92 keys, audio and web buttons
- 2.4-2.48 GHz, ≤45 ft. range
- Slick, compact design
- Mini wireless QWERTY keyboard with touchpad

Includes: Li-ion battery, charging cable and USB receiver

Part No.	Mfr. Part No.	1	5
2240112	DFR0330	\$24.95	\$22.49

PS-2/USB PC Trackball

- 51mm opto-mech ball
- 3 large buttons
- Windows® 98SE/2000/ME/XP/Vista




Part No.	Mfr. Part No.	DPI	Color	Price
305082	Libra-90	6400	White	\$29.95

JAMECO
ValuePro

Computer Switchbox

- 2-port switchbox
- DB25 female (2 PCs to 1 printer)
- Size: 6.0"L x 5.8"W x 2.3"H
- Weight: 1.4 lbs.

* Web Code: **CAK**



Part No.	Cross Ref. No.	1	10
20095	40D3-17602	\$17.95	\$15.95

JAMECO
ValuePro

Panel Bracket Cable Assembly

- Standard back panel bracket
- Length: 12"
- Ribbon cable with header connector
- One serial port



Part No.	Description	1	10	100
355688	DB9M to 10-pin header F ..	\$1.49	\$1.35	\$1.19

* Computer Brackets — Enter **Web Code RAX**

JAMECO
ValuePro

USB-A Cable with Bracket

- Add additional USB ports to your PC
- Dual USB-A female ports
- Supports data transfer rates of 12Mbps
- 8'L cable



Part No.	Description	1	10	25
144813	(2) 1x5-pin connectors ...	\$4.95	\$4.49	\$3.95

Analog DIN-Rail Timer

- DIN rail/ back panel mount (17.5mm)
- 10 time ranges • 13 timing functions
- Output contact: SPDT (1C/0)
- Contact rating: 5A (NO), 3A @ 250VAC (NC)
- Faceplate (IP50), housing (IP40), terminals (IP20)



Part No.	Size	1	5	25
2193862	17.5mm	\$29.95	\$26.95	\$24.95

* DIN Mounting Rails Accessories — **Web Code MBM**

APC 8-Outlet Surge Protector

- Protection rating: 1120 joules
- 8 outlets • RoHS
- UL 1363, UL 1449
- Phone/Fax/Modem protection
- Building wiring fault (red LED)
- On/Off power button (green LED)
- Electrical rating: 120VAC, 15A 50/60Hz
- Reset button - 15A circuit breaker for overloads
- Voltage protection: L-N 400V, L-G 500V, N-G 400V
- Voltage/current spike: 6kV @ 200A, 100kHz max.
- Includes 6 foot RJ9 telephone cord



NEW
MARKED IN PINK

Part No.	Mfr. Part No.	1	10	100
2233975	PR08T2	\$19.95	\$17.95	\$16.49

SPI 300-Watt AT Power Supply

- +12V @ 12A, -12V @ 0.5A
- +5V @ 30A, -5V @ 0.5A
- 2x floppy connector
- 4x peripheral (4P Molex)
- Input: 100/220VAC selectable
- 2x 6P power connector ("P8" & "P9")
- Quick connect terminals for main switch
- AC cord not included, recommend P/N 38050

NEW
MARKED IN PINK



Part No.	Mfr. Part No.	1	5
2208219	SPI-300G-B (no plug)	\$64.95	\$59.95

Pixy Cam Vision Sensor – CMUcam5

- Track hundreds of objects simultaneously
- Color and shape recognition
- Arduino, Pi, BeagleBone compatible
- Use with pan/tilt assembly (sold separately, see below)



Part No.	Mfr. Part No.	Price
2239381	1/4" 1280x800, 264k RAM, M12 lens	\$69.95
2239390	Pan & tilt kit assembly for pixy, 2x servo ..	39.95



Mini Pan & Tilt Kit

- For horizontal surface mount
- Aluminum multifunction bracket
- 15kg/cm @ 4.8V
- Rotation: 0-180°



Part No.	Mfr. Part No.	1	5
2157870	RS002B	\$15.95	\$13.95

JAMECO
ValuePro

6-Outlet Surge Protector

- 4' cord
- Heavy-duty power cord (14AWG x 3)
- Size: 9.5"L x 1.7"W x 1.4"H
- Clamping voltage: 400V
- Max. spike current: 4500A, 150 joules
- Max. surge voltage: 6500V
- RESET/OFF switch with built-in 15A circuit breaker



Part No.	Cross Ref. No.	1	10	25
216485	51W1-10206	\$9.95	\$8.95	\$7.95

6-Outlet Power Strips

- 10 ft. 14/3 AWG power cord
- 6 grounded outlets
- Combination circuit
- Breaker ON/OFF switch
- 125V/15A/1875W



2258460/2132200:	6 ft. cord	
2258697:	10 ft. cord	2132200

Part No.	Mfr. Part No.	1	10	25
2258460	PS08-12-WHITE*	\$4.95	\$4.49	\$3.95
2258697	PS08-12-BEIGE	6.95	6.25	5.59
2132200	ALG242**	2.95	2.59	2.39

* Protective socket covers plugs into IISAC wall plug ** Wall mount

* Surge Protectors — Enter **Web Code CAC**

JAMECO
ValuePro

USB 2.0 4-Port Hub

Add multiple high performance USB 2.0 devices to your computer or laptop. Unique design allows for easy storage and use.

- Stylish compact size and light weight
- USB 2.0 up to 480 Mbps
- Plug-and-play, bus powered
- 1 upstream, 4 downstream ports



Part No.	Cross Ref. No.	1	5
2184085	HU2Z40	\$9.95	\$8.95

JAMECO
ValuePro

Waterproof USB Video Borescope

Allows for easy surveying of hard-to-reach places with 4 adjustable LEDs on the top on the camera.

- Flexible 16' cord
- 9.8mm camera
- Webcam and photo snap function
- Works with Windows® XP, 7, Vista and Mac iOS



Part No.	Cross Ref. No.	1	5
2177707	INSPECTOR-T1	\$34.95	\$31.95

Computer Cables on page 134

DIN-RAIL POWER SUPPLIES

- Universal AC input/full range
- Use TS-35/7.5 or 15 rails
- Ideal for industrial applications



Part No.	Mfr. Part No.	Output	Power	1	10
1943385	MDR-20-24	24V/1A	24W ..	\$12.80	\$10.75
192681	DR-4524	24V/2A	48W	19.10	15.95
1943465	MDR-60-24	24V/2.5A	60W	18.40	15.25
212266	DR-120-24	24V/5A	120W	38.70	31.95

* For additional products, availability and specifications visit [Jameco.com](http://www.Jameco.com) and enter the Web Code in the product search box

3 LEVELS OF SAVINGS
NAME BRANDS HOUSE BRANDS SPECIAL BUY

Order by Phone at 1-800-831-4242 or Online at www.Jameco.com