

# Computer Cables & Smartphone Chargers

Due to extraordinary copper market price fluctuations, cable & wire prices are subject to change.

3 LEVELS OF SAVINGS  
NAME BRANDS HOUSE BRANDS SPECIAL BUY

## Computer Cables and Adapters

NEW MARKED IN PINK

\*Web Code: CCS



### Extension Cables

• All lines connected straight through

#### Male to Female

Part No.	Description	Lgth (ft.)	Color	1	10	100
199639	DB9*	6	Black	\$3.95	\$3.59	\$3.25
25701	DB9*	6	Beige	3.69	3.39	2.95
148516	DB9*	10	Beige	5.95	5.59	4.79
181359	DB15	6	Gray	5.95	5.39	4.75
175291	DB25*	3	Black	3.95	3.59	3.29
67257	DB25*	6	Gray	4.95	4.49	3.95
177279	DB25*	15	Gray	6.95	6.25	5.59
2236535	DB25*	25	Gray	7.95	6.95	5.95
181295	DB37	6	Gray	6.95	6.25	5.59

#### Male to Male

181666	DB9	10	Beige	\$4.95	\$4.49	\$3.95
2155188	HDD15*	6	Black	1.95	1.75	1.49
148523	HDD15	10	Beige	5.95	5.35	4.79
174001	DB25*	3	Black	3.95	3.59	3.29
65788	DB25*	6	Gray	5.95	5.39	4.75

\*with thumbscrews

#### Serial Cables w/ Thumbscrews

132346	DB9 F to F	6	Beige	\$3.95	\$3.59	\$3.29
--------	------------	---	-------	--------	--------	--------

#### AT F-M Adapter Serial Cables

31722	DB9 F to DB25 M	6	Beige	\$3.95	\$3.59	\$3.29
-------	-----------------	---	-------	--------	--------	--------

#### Serial Null Modem Cables

• Gray • Pin-outs in ( )

Part No.	Description	Length (ft.)	1	10	100
181404	DB9 F to F (1 & 6-4; 2-3; 3-2; 4-6 & 1; 5-5; 7-8; 8-7)	6	\$3.95	\$3.59	\$3.29
180698	DB9 F to F (1 & 6-4; 2-3; 3-2; 4-6 & 1; 5-5; 7-8; 8-7)	10	4.95	4.49	3.95

#### Disk Drive Cables

32686	40-pin (IDE)	1.5	\$1.95	\$1.75	\$1.49
-------	--------------	-----	--------	--------	--------

#### Ribbon Cable Assemblies

12408	DB25 M to F (28 AWG)	4	\$6.95	\$6.25	\$5.59
208582	DB9 M to F (28 AWG)	6	4.95	3.95	3.59

#### 6-Pin Mini DIN PS/2 & AT Cables

Part No.	Description	Lgth (ft.)	Color	1	10	100
112628	Male to male	10	Beige	\$4.95	\$4.49	\$3.95
28549	Male to female	6	Beige	3.95	3.59	3.29

#### IEEE 488

73155	24-pin GPIB	3.3	Gray	\$24.95	\$22.49	\$19.95
115782	24-pin GPIB	6.6	Gray	29.95	26.95	23.95

\*HDMI Cables & Adapters — Enter Web Code DEM

\*Ethernet & Bidirectional Converters — Web Code KEM

Audio Cables & Connectors  
on pages 46-47

### DIN Male Printer & Keyboard Cables for Mac®

Part No.	Description	Lgth (ft.)	Color	1	10	25
10604	8-pin	6	Gray	\$3.95	\$3.49	\$2.95
130025	8-pin	10	Gray	4.49	3.95	3.49

### USB-A to DB9 Male Serial Cable/Adapters

387954	w/ jackscrews	2	Gray	\$16.95	\$14.95	\$13.49
--------	---------------	---	------	---------	---------	---------

### USB Cables 2.0 & 3.0

\*Web Code: NAV

Part No.	Description	Lgth (ft.)	Color	1	10	25
326474	A M to M (2.0)	3	Beige	\$1.95	\$1.75	\$1.49
2150985	A M to M (2.0)	6	Blue	.99	.89	.75
222033	A M to M (2.0)	6	Black	2.95	2.59	1.95
2234257	A M to (2) A F (2.0)	1	Black	7.95	6.95	6.25
326482	A M to F (2.0)	3	Beige	1.75	1.59	1.39
222068	A M to F (2.0)	6	Black	1.95	1.75	1.49
222076	A M to F (2.0)	10	Black	2.95	2.59	2.29
222084	A M to F (2.0)	15	Black	3.25	2.95	2.59
229711	A M to B M (2.0)	3	Beige	1.95	1.75	1.59
222608	A M to B M (2.0)	3	Black	1.75	1.49	1.25
229730	A M to B M (2.0)	6	Beige	2.95	2.49	1.95
2227874	A M to B M (2.0)	6	White	1.75	1.47	1.25
222010	A M to B M (2.0)	6	Black	2.95	2.49	1.95
229594	A M to B M (2.0)	6	Clear	2.95	2.49	1.95
229738	A M to B M (2.0)	10	Beige	2.95	2.59	2.29
222018	A M to B M (2.0)	10	Black	2.95	2.49	2.25
2230862	A M to B M (2.0)	14	Beige	2.75	2.59	2.25
222026	A M to B M (2.0)	15	Black	3.49	2.95	2.49
2258478	A M to B M (3.0)	3	Black	1.75	1.59	1.35
2228877	A M to 5-pin mini B	3	Black	2.49	2.25	1.95
673694	A M to 5-pin mini B	6	Black	2.95	2.59	2.29
2230512	A F to micro-B (2.0)	6"	Black	2.75	2.49	2.25
2135064	A M to micro-B (2.0)	3	Black	2.49	2.25	1.95
2196086	A M to micro-B (2.0)	3.2	White	1.95	1.75	1.49
2223945	A M to micro-B (2.0)*	5	Black	4.95	4.49	3.95

\*RFI filter A = USB-A; B = USB-B; M = male; F = female

### USBtinyISP AVR Programmer

The USBtinyISP is a low-cost, simple solder kit, and has both 6 and 10-pin standard ISP cables. Works with AVRdude and AVRStudio-compatible & tested under Windows® XP, Linux & MacOS X. It does not do JTAG or high voltage programming.

- Max clock rate: 400kHz
- Read/write speed: 2kb/s, 1kb/s
- 2 status LEDs: "USB/Power Good" and "Busy"
- I/O buffering allows programming of 2V-6V targets
- Powered via 5V USB bus @ <100mA

Includes: 6 & 10-pin ISP cable and kit (PCB, enclosure, MCU & components)

Requires: USB-A to USB-B cable (P/N 222608, not included, see above)

Part No.	Mfr. Part No.	1	5
2136788	46	\$24.95	\$22.95

Hook-Up Wire on page 41

## Chargers and Accessories for Android and Apple Products

NEW MARKED IN PINK



Part No.	Description	Price
2196078	iPhone4 USB-A to 30-pin cable, 3'*	\$3.95
2196078	iPhone4 30-pin to 8-pin lighting adapter*	2.95
2158320	Single port USB cigarette car adapter 5V @ 1A, black*#	3.95
2228391	Dual Port USB cigarette car adapter, 5V @ 2A/5VDC @ 1A, white*#	5.95
2244359	Dual port USB AC charger, 5V @ 2.1A, white*#	6.95
2227786	Dual port USB AC charger, 5V @ 2A, black*#	4.95
2259420	iPhone 5/6/7 AC charger with 3' USB-A to 8-pin lighting cable*	14.95
2135064	USB cable, USB male to micro-B, 3'*	2.49
2196060	iPhone 5/6/7 adapter, USB micro-B 8-pin lighting*	2.95
2228519	iPhone 5/6/7 USB MFi lighting cable, 3' white*	6.95
2232315	iPhone 5/6/7 USB MFi lighting cable, 6' white*	7.95
2229693	Viper earbuds with mic*#	4.95
2228527	Power bank, 4000mAh, dual output: 2A/1A @ 5V, 12' cable*#	19.95

\*Apple # Android

## GETTING STARTED WITH ARDUINO BOOK, 3RD EDITION

An introduction for the popular, open-source prototyping platform. Learn about what Arduino is and how it works; all while teaching yourself how to code. By the end, you'll be thinking about what kind of inputs you can read to control some other output.

O'REILLY



Part No.	ISBN	Price
2222053	978-1-4493-6333-8	\$14.95

## CAR ADAPTER SOCKET SPLITTER

Turn a single cigarette lighter socket in your car or truck into three with this convenient adapter.

- 3 food cable
- 3 output sockets
- Mounting hardware included.



Part No.	Mfr. Part No.	Price
2231419	TV/003/5-3	\$8.95