

## 74LS Series

\* Web Code: NBS

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
46252	◆	74LS00**	DIP-14	Quad 2-input pos. NAND gate ....	\$ .79	\$ .69	\$ .49
283725	◆	SN74LS00N	DIP-14	Quad 2-input pos. NAND gate .....	.99	.89	.65
46287	◆	74LS02**	DIP-14	Quad 2-input pos. NOR gate .....	.49	.39	.25
283741	◆	SN74LS02N	DIP-14	Quad 2-input pos. NOR gate .....	.59	.45	.29
46308	◆	74LS03	DIP-14	Quad 2-input pos. NAND gate (O.C.)	.69	.59	.39
46316	◆	74LS04**	DIP-14	Hex inverter .....	.59	.45	.35
283792	◆	SN74LS04N	DIP-14	Hex inverter .....	.65	.49	.39
46341	◆	74LS05*	DIP-14	Hex inverter (O.C.) .....	.79	.69	.49
46359	◆	74LS06	DIP-14	Hex inverter buffer/driver .....	.79	.69	.59
46367	◆	74LS07	DIP-14	Hex buffer/driver .....	.89	.79	.59
46375	◆	74LS08**	DIP-14	Quad 2-input pos. AND gate .....	.69	.59	.49
295401	◆	SN74LS08N	DIP-14	Quad 2-input pos. AND gate .....	.59	.49	.35
46404	◆	74LS10*	DIP-14	Triple 2-input pos. NAND gate .....	.69	.59	.39
46439	◆	74LS11*	DIP-14	Triple 3-input pos. AND gate .....	.69	.59	.39
46640	◆	74LS14*	DIP-14	Hex schmitt-trigger inverter .....	.55	.45	.29
47095	◆	74LS20*	DIP-14	Dual 4-input NAND gate .....	.79	.69	.59
47108	◆	74LS21	DIP-14	Dual 4-input AND gate .....	.59	.49	.35
47378	◆	74LS27	DIP-14	Triple 3-input NOR gate .....	.99	.79	.65
47458	◆	74LS30*	DIP-14	8-input NAND gate .....	.79	.69	.49
47466	◆	74LS32**	DIP-14	Quad 2-input pos. OR gate .....	.49	.39	.27
295515	◆	SN74LS32N	DIP-14	Quad 2-input pos. OR gate .....	.55	.45	.29
47693	◆	74LS38	DIP-14	Quad 2-input NAND buffer .....	.69	.59	.49
47773	◆	74LS42	DIP-14	4 line BCD to 10 line decimal decoder	2.09	1.75	1.49
47790	◆	74LS47*	DIP-16	BCD-to-7 seg. decoder/driver ....	1.59	1.39	1.15
295582	◆	SN74LS47N	DIP-16	BCD-to-7 seg. decoder/driver ....	1.75	1.49	1.19
47811	◆	74LS48	DIP-16	BCD-to-7 seg. decoder/driver ....	5.95	5.39	4.79
47992	◆	74LS73*	DIP-14	Dual J-K neg-edge-triggered flip-flop	1.79	1.59	1.29
48004	◆	74LS74**	DIP-14	Dual D-type flip-flop .....	.49	.39	.25
295726	◆	SN74LS74AN	DIP-14	Dual D-type flip-flop .....	.55	.45	.29
48021	◆	74LS75*	DIP-16	4-bit bi-stable latch .....	1.89	1.59	1.29
48063	◆	74LS83	DIP-16	4-bit binary full adder .....	2.95	2.59	2.29
48071	◆	74LS85*	DIP-16	4-bit magnitude comparator .....	1.19	.99	.79
48098	◆	74LS86*	DIP-14	Quad 2-input exclusive OR gate .	1.19	1.09	.95
295751	◆	SN74LS86AN	DIP-14	Quad 2-input exclusive OR gate .	1.39	1.25	1.09
48119	◆	74LS90*	DIP-14	Asynchronous decade counter ...	1.95	1.59	1.45
48143	◆	74LS92	DIP-14	Divide-by-12 decade counter .....	2.49	2.19	1.85
48151	◆	74LS93	DIP-14	4-bit binary counter .....	1.75	1.59	1.29
46412	◆	74LS107	DIP-14	Dual J-K flip-flop with clear .....	1.75	1.49	1.25
46421	◆	74LS109	DIP-16	Dual J-K bar flip-flop .....	1.19	1.09	.89
46447	◆	74LS112	DIP-16	Dual J-K neg-edge-triggered flip-flop	.69	.59	.39
46471	◆	74LS122	DIP-14	Retriggerable monostable multivib. ....	.99	.79	.59
46480	◆	74LS123*	DIP-16	Dual monostable multivibrator .....	.69	.59	.39
46501	◆	74LS125*	DIP-14	Tri-state quad bus buffer .....	.69	.55	.39
46527	◆	74LS126	DIP-14	Tri-state quad bus buffer .....	.69	.59	.39
46551	◆	74LS132	DIP-14	Quad 2-input NAND schmitt trigger	.69	.55	.49
46607	◆	74LS138*	DIP-16	3-to-8 decoder/demultiplexer .....	.69	.59	.39
301233	◆	SN74LS138N	DIP-16	3-to-8 decoder/demultiplexer .....	.79	.65	.45
46623	◆	74LS139*	DIP-16	Dual 2-to-4 decoder/demultiplexer	.69	.59	.39
46666	◆	74LS145	DIP-16	BCD-to-decimal decoder/driver .....	.89	.75	.59
46682	◆	74LS148	DIP-16	8-to-3 line priority encoder .....	1.19	.99	.79
46703	◆	74LS151*	DIP-16	1-to-8 data selector/multiplexer ...	.79	.69	.55
46720	◆	74LS153	DIP-16	Dual 4-to-1 data selector/multiplexer	.79	.69	.55
46754	◆	74LS155*	DIP-16	Dual 2-to-4 line decoder/demultiplexer	1.29	1.09	.89
46771	◆	74LS157*	DIP-16	Quad 2-to-1 line data selector .....	.69	.59	.39
46800	◆	74LS160	DIP-16	Synchronous decade counter .....	2.49	2.25	2.05
46818	◆	74LS161	DIP-16	4-bit synchronous binary counter	.79	.65	.45
46842	◆	74LS163	DIP-16	Synchronous 4-bit binary counter	.69	.59	.39
46851	◆	74LS164	DIP-14	8-bit serial shift register .....	.69	.59	.49
46877	◆	74LS165	DIP-16	8-bit parallel load shift register .....	.65	.49	.39

\*10 pcs./ \*\*20 pcs. in 74LS series IC cabinet kit, right

◆ Major Brands

## 74LS Series (Continued)

\* Web Code: NBS

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
46906	◆	74LS169	DIP-16	Synch. 4-bit binary up/down counter	\$1.39	\$1.19	\$ .99
46922	◆	74LS173*	DIP-16	4-bit D-type register w/ 3-state output	1.39	1.19	.79
46931	◆	74LS174*	DIP-16	Hex D-type flip-flop with clear .....	.49	.39	.35
46957	◆	74LS175*	DIP-16	Quad D-type flip-flop with clear ....	.79	.69	.49
46973	◆	74LS181	DIP-24	Arithmetic logic unit/function generator	4.95	4.49	3.95
46990	◆	74LS190	DIP-16	Synchronous up/down decade counter	3.95	3.59	3.29
47001	◆	74LS191	DIP-16	Synch. 4-bit up/down binary counter	.89	.79	.59
47010	◆	74LS192	DIP-16	Synch. 4-bit up/down decade counter	3.95	3.59	3.25
47036	◆	74LS193	DIP-16	Synch. 4-bit up/down binary counter	.89	.79	.69
47052	◆	74LS194	DIP-16	4-bit bi-directional shift register	1.29	1.09	.89
47061	◆	74LS195	DIP-16	4-bit parallel-access shift register	1.95	1.75	1.49
47141	◆	74LS240*	DIP-20	Octal buffer/line driver .....	.69	.59	.49
47167	◆	74LS241	DIP-20	Tri-state octal buffer/line driver ....	.69	.59	.49
47183	◆	74LS244*	DIP-20	Tri-state octal buffer/line driver ....	.79	.69	.59
308312	◆	SN74LS244N	DIP-20	Tri-state octal buffer/line driver ....	.79	.69	.55
47212	◆	74LS245*	DIP-20	Tri-state octal bus transceiver .....	.79	.69	.55
47247	◆	74LS247	DIP-16	BCD to 7-seg. decoder/driver .....	1.75	1.49	1.19
47298	◆	74LS257B**	DIP-16	Tri-state quad 2-data selector/m ..	.79	.69	.55
47327	◆	74LS259	DIP-16	8-bit addressable latch .....	.99	.89	.69
47360	◆	74LS266	DIP-14	Quad 2-input exclusive NOR gate (O.C.)	.99	.89	.69
47386	◆	74LS273*	DIP-20	Octal D-type flip-flop .....	.75	.65	.49
47407	◆	74LS279	DIP-16	Quad S-R latch .....	.99	.89	.79
47423	◆	74LS283	DIP-16	4-bit binary full add w/ fast carry	2.95	2.59	2.29
47562	◆	74LS367	DIP-16	Tri-state hex buffer .....	.99	.89	.69
309286	◆	74LS368	DIP-16	Tri-state hex bus driver .....	1.19	.89	.59
47600	◆	74LS373*	DIP-20	Octal D-type transparent latch .....	.69	.59	.45
308460	◆	SN74LS373N	DIP-20	Octal D-type transparent latch .....	.79	.69	.49
47634	◆	74LS374*	DIP-20	Octal D-type flip-flop .....	.79	.69	.45
47669	◆	74LS377	DIP-20	Octal D-type flip-flop .....	1.29	1.09	.89
47722	◆	74LS390	DIP-16	Dual 4-bit decade counter .....	1.19	.99	.79
47731	◆	74LS393	DIP-14	Dual 4-bit binary counter .....	1.09	.89	.75
47870	◆	74LS541	DIP-20	Tri-state octal buffer/line driver ....	.95	.89	.75
64418	◆	74LS573	DIP-20	Tri-state octal D-type flip flop ....	1.95	1.49	1.25
47976	◆	74LS670	DIP-16	4 x 4 register file .....	1.95	1.75	1.49
309260	◆	74LS682	DIP-20	8-bit magnitude/identity comp. ...	1.95	1.75	1.49

\*10 pcs./ \*\*20 pcs. in 74LS series IC cabinet kit, below

## 74LS Series IC Kit

\* Web Code: CKS

Includes: 20-drawer component cabinet (319600), 20 clear plastic drawers (319601), 20 clear dividers (319611) and 30 adhesive labels for drawers to identify parts in kit



10 each: 74LS05, 74LS10, 74LS11, 74LS14, 74LS20, 74LS30, 74LS47, 74LS73, 74LS75, 74LS85, 74LS86, 74LS90, 74LS123, 74LS125, 74LS138, 74LS139, 74LS151, 74LS155, 74LS157, 74LS173, 74LS174, 74LS175, 74LS240, 74LS244, 74LS245, 74LS273, 74LS373, 74LS374  
74LS00, 74LS02, 74LS04, 74LS08, 74LS32, 74LS74, 74LS257

Part No.	Description	Wt. (lbs.)	1	5
84961	420 pcs. 74LS IC kit	6.7	\$229.95	\$209.95
130391	Refill for 84961 (420 pcs.)	2.0	214.95	199.95

## 74S Series

Please Note: Manufacturer may vary

\* Web Code: NCK

Part No.	Product No.	Pkg.	Description	1	10	100
676959	74S00	DIP-14	Quad 2-input NAND gate .....	\$ .39	\$ .29	\$ .25
48266	74S02	DIP-14	Quad 2-input NOR gate .....	.25	.19	.15
48750	74S32	DIP-14	Quad 2-input positive OR gate .....	.29	.19	.15
676991	74S74	DIP-14	Dual D-type flip flop .....	.59	.49	.39
677003	74S138	DIP-16	3 to 8 decoder/demultiplexer .....	.49	.45	.39
48506	74S175	DIP-16	Quad D-type flip flop with clear .....	.49	.45	.39
64696	74S194	DIP-16	4-bit bi-directional shift register .....	.45	.35	.29
48776	74S374J	DIP-20	Dual D-type flip flop .....	.49	.39	.29
52513	74S428	DIP-28	System controller/bus driver (8228) .....	4.95	4.49	3.95

3 LEVELS OF SAVINGS  
**NAME BRANDS** **HOUSE BRANDS** **SPECIAL BUY**

\*For additional products, availability and specifications visit [Jameco.com](http://www.Jameco.com) and enter the Web Code in the product search box