


Electrolytic, Dipped Tantalum & Ceramic Capacitors

3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **SPECIAL BUY**

JAMECO ValuePro Aluminum Axial-Lead Electrolytic Capacitors (±20%) 85°C

*Web Code: GAA

Operating temperature range	-40°C to +85°C
Leakage Current (After 2 minutes 20°C)	0.02CV or 2µA, whichever is greater



Passives

Part No.	Product No.	*Mfr.	Value (µF)	Volt (V)	Size (mm)* D x H	Pricing			
						1	10	100	500
10866	A1/50	JVP	1.0	50	5 x 13	\$.35	\$.29	\$.25	\$.22
93569	A2.2/50	JVP	2.2	50	6 x 13	.39	.35	.29	.27
2215638	A2.0/35	ADT	2.5	35	6 x 13	.25	.12	.09	.07
11076	A4.7/50	JVP	4.7	50	6 x 13	.39	.35	.29	.27
1946199	A10/16	JVP	10	16	4 x 7	.39	.35	.29	.27
10882	A10/50	JVP	10	50	6 x 12	.49	.45	.39	.37
331425	AB10/450	JVP	10	450	13 x 25	1.75	1.49	1.09	.99
199268	A22J/25	JVP	22	25	6 x 12.5	.39	.35	.29	.27
2202520	A22/35#	VHS	22	35	6 x 13	.35	.29	.19	.15
10997	A22/50	ILC	22	50	16 x 12	.49	.39	.35	.25
331433	AB22/450	JVP	22	450	16 x 26.5	1.75	1.49	1.09	.99
135319	A47/25	JVP	47	25	8 x 16	.49	.39	.32	.27
11105	A47/50	JVP	47	50	8 x 16	.55	.49	.45	.39
199188	A100J/16	JVP	100	16	6 x 12.5	.55	.49	.45	.39
93551	A100/35	JVP	100	35	8 x 16	.59	.55	.49	.45
10911	A100/50	JVP	100	50	8 x 20	.79	.75	.69	.59
331417	AB100/250	JVP	100	250	18 x 39	1.49	1.25	.99	.85
2150811	A220/16	JVP	220	16	10 x 21	.39	.35	.29	.25
11019	A220/50	JVP	220	50	10 x 17	.79	.69	.59	.55

*Capacitor dimensions and styles may vary #105°C

Part No.	Product No.	*Mfr.	Value (µF)	Volt (V)	Size (mm)* D x H	Pricing			
						1	10	100	500
2234943	A330/50	ILC	330	50	10 x 25	\$1.35	\$1.19	\$0.99	\$0.89
2235794	A470/16	MST	470	16	8 x 21	.49	.39	.29	.25
199381	A470J/35	JVP	470	35	10 x 21	1.25	1.09	.99	.89
11123	A470/50	JVP	470	50	13 x 22	1.35	1.19	.99	.89
2215689	T200V680UF	ADT	680	200	25 x 50	2.95	2.75	2.49	2.25
10954	A1000/25	JVP	1000	25	13 x 26	.95	.85	.75	.65
93649	A1000/35	JVP	1000	35	13 x 31	1.49	1.09	.99	.85
147256	A1000/50	JVP	1000	50	16 x 31	1.75	1.49	1.09	.99
11033	A2200/16	JVP	2200	16	16 x 40	1.09	.99	.89	.79
93658	A2200/35	JVP	2200	35	16 x 30	1.49	1.25	1.09	.95
199479	A2200J/50	JVP	2200	50	18 x 33	1.95	1.75	1.25	1.09
2144972	A3300/16	JVP	3300	16	16 x 26	1.49	1.25	1.09	.89
199487	A3300J/50	JVP	3300	50	22 x 43	2.49	2.09	1.85	1.59
2229538	A4700/16	ADT	4700	16	16 x 36	.99	.89	.79	.69
93673	A4700/25	JVP	4700	25	19 x 36	2.09	1.75	1.49	1.25
158650	A4700A25	JVP	4700	25	22 x 40	1.25	1.09	.89	.79
158811	A4700A50	JVP	4700	50	22 x 40	2.95	2.59	2.29	2.09
93681	A10000/16	JVP	10000	16	22 x 51	2.95	2.39	2.09	1.89
2215671	16V22000	ADT	22000	16	25 x 60	2.95	2.75	2.49	2.25

*Capacitor dimensions and styles may vary

JAMECO ValuePro Resin Dipped Solid Tantalum Capacitors (±10%) 85°C

- Operating temperature range: -55°C to +85°C (+125°C with derating)
- Exceptional temperature stability
- Flame retardant coating
- Designed for entertainment and commercial equipment
- Rated voltage DC: ≤ +85°C
- Moisture-resistant
- Low leakage current
- † P/Ns 2178726/2167357/2178785/2178769: ±20%

*Web Code: VAE



Part No.	Product No.	*Mfr.	Value (µF)	Volt (V)	Size (mm)* D x H x L.S.	Pricing			
						1	10	100	500
545561	TAP104K035SCS	JVP	.10	35	4.0 x 6.0 x 2.5	\$.39	\$.29	\$.25	\$.19
33486	TM.1/35	JVP	.10	35	4.5 x 7.0 x 5.2	.35	.25	.19	.15
33507	TM.22/35	JVP	.22	35	4.5 x 7.0 x 5.0	.39	.29	.25	.19
2178726	TM.33/35/20†	ADT	.33	35	3.4 x 6.5 x 5.0	.25	.15	.12	.09
33523	TM.33/35	JVP	.33	35	4.5 x 7.0 x 2.5	.29	.25	.19	.15
33531	TM.47/35	JVP	.47	35	4.5 x 7.0 x 2.7	.39	.25	.19	.15
545588	TAP105K025SCS	JVP	1	25	4.3 x 7.0 x 2.5	.35	.25	.19	.15
154860	TM1/25	JVP	1	25	4.5 x 7.0 x 4.7	.35	.25	.19	.15
545596	TAP105K035SCS	JVP	1	35	4.3 x 7.0 x 2.5	.35	.25	.19	.15
33662	TM1/35	JVP	1	35	4.5 x 7.0 x 2.7	.39	.29	.19	.15
545609	TAP105K050SCS	JVP	1	50	4.7 x 7.5 x 2.5	.69	.55	.39	.29
2167357	TAP155M035BRS†	AVX	1.5	35	4.5 x 8.0 x 5.0	.29	.25	.19	.15
94001	TM2.2/16	JVP	2.2	16	4.5 x 7.0 x 4.7	.45	.35	.29	.25
33736	TM2.2/35	JVP	2.2	35	5.0 x 8.0 x 2.5	.49	.45	.35	.29
545941	TAP335K025SCS	JVP	3.3	25	4.3 x 7.0 x 2.5	.49	.39	.29	.25
94035	TM4.7/16	JVP	4.7	16	5.0 x 8.0 x 2.5	.39	.35	.29	.25
546071	TAP475K025SCS	JVP	4.7	25	4.3 x 7.0 x 2.5	.49	.39	.29	.25
546089	TAP475K035SCS	JVP	4.7	35	4.7 x 7.5 x 2.5	.55	.45	.35	.25
33806	TM4.7/35	JVP	4.7	35	5.5 x 9.5 x 2.5	.55	.45	.35	.25

*Capacitor dimensions and styles may vary Note: Above case sizes may have ±20% tolerances

Part No.	Product No.	*Mfr.	Value (µF)	Volt (V)	Size (mm)* D x H x L.S.	Pricing			
						1	10	100	500
33873	TM6.8/35	JVP	6.8	35	6.5 x 9.0 x 4.7	\$.59	\$.49	\$.39	\$.29
545625	TAP106K010SCS	JVP	10	10	4.7 x 7.5 x 2.5	.45	.39	.35	.29
94060	TM10/16	JVP	10	16	4.6 x 7.5 x 3.2	.45	.35	.25	.19
94062	TM10/16-R	JVP	10	16	5.0 x 8.0 x 2.5	.45	.35	.25	.19
545633	TAP106K020SCS	JVP	10	20	5.4 x 8.0 x 2.5	.69	.59	.49	.39
2178785	TM10/25/20†	ADT	10	25	6.0 x 5.0 x 5.0	.45	.35	.25	.19
545641	TAP106K025SCS	JVP	10	25	5.4 x 8.0 x 2.5	.59	.49	.45	.39
94078	TM10/25	JVP	10	25	5.5 x 9.5 x 2.8	.55	.45	.39	.35
33689	TM10/35	JVP	10	35	6.5 x 11.0 x 4.7	1.19	.99	.79	.65
33719	TM15/25	JVP	15	25	4.5 x 8.0 x 2.5	1.59	1.39	1.25	.99
33751	TM22/6.3	JVP	22	6.3	4.7 x 7.5 x 2.5	.29	.25	.19	.15
545852	TAP226K016SCS	JVP	22	16	5.4 x 8.0 x 2.5	.69	.59	.49	.39
94094	TM22/16	JVP	22	16	5.5 x 9.5 x 4.1	.69	.59	.49	.39
2040196	TAP226K035SCS	AVX	22	35	8.5 x 12.5 x 2.5	2.25	1.95	1.75	1.49
33785	TM33/25	JVP	33	25	8.5 x 13.0 x 4.7	1.75	1.49	1.25	1.09
94123	TM47/16	JVP	47	16	5.2 x 8.2 x 2.0	1.25	1.09	.99	.89
546118	TAP476K016SCS	JVP	47	16	6.0 x 9.4 x 2.5	.79	.69	.59	.49
33822	TM47	JVP	47	25	9.5 x 16.5 x 2.5	1.95	1.75	1.49	1.25
597450	TAP107K016CCS	JVP	100	16	7.0 x 11.0 x 2.5	2.49	2.25	1.95	1.75
2178769	TAP157M016CCS†	ADT	150	16	7.5 x 10.7 x 4.5	1.49	1.25	1.09	.99

JAMECO ValuePro Axial Leaded Ceramic Capacitors (±5 & ±10%)

50, 100 and 200 Volt, NPO and X7R Temperature Coefficient

- Operating temperature range: -55°C to +125°C

*Web Code: ACC

* Order in multiples 10

Part No.	Product No.	*Mfr.	Value	Volt (V)	Temp Co-eff.	Tol.	Pricing		
							1	10	100
2229790	SA102A150JAA	AVX	15pF	200	NPO	5	\$.19	\$.17	\$.15
2229802	SA101A181KAA	AVX	180pF	100	NPO	10	.17	.15	.12
2229829	SA101C471KAA	AVX	470pF	100	X7R	10	.19	.17	.15

Part No.	Product No.	*Mfr.	Value	Volt (V)	Temp Co-eff.	Tol.	Pricing		
							1	10	100
1069763	SA101C222KAA	JVP	2200pF	100	X7R	10	*	\$.12	\$.09
2229837	SA101C472KAA	AVX	4700pF	100	X7R	10	.19	.17	.15
2229811	SA205C473KAA	AVX	.047µF	50	X7R	10	.19	.17	.15
546290	P10R103K5	JVP	.01µF	50	X7R	10	*	.12	.09
536542	P20R104K5	JVP	.1µF	50	X7R	10	.45	.39	.35

* ADT = Arndt Electronics | AVX = AVX Corp. | ILC = Illinois Capacitor | JVP = Jameco ValuePro | MST = Matsushita Electronic Comp. | VSH = Vishay