

# Coaxial, Multi-Conductor, Paired & Speaker Cable

3 LEVELS OF SAVINGS  
 NAME BRANDS HOUSE BRANDS SPECIAL BUY



JAMECO ValuePro

## Coaxial Cable

Common Coax Cables:

RG-#/U (RG = Radio Grade; U = Universal)

RG-58: Radio communication, amateur radio, 50Ω

RG-174: Wi-Fi pigtails, more flexible but higher loss than RG-58, 50Ω

- Color: black
- PVC jacket
- Polyethylene insulated

Part No.	Mfr.	Product No.	Fig.	Length	AWG	Type	Nom. Imp (Ω)	Bare Copper	Braid Shield	Pricing	
										1	5
644754	JVP	RG58/U-100	1	100' Reel	20 Solid	RG58/U	50	0.015"	38	\$26.95	\$24.95
644818	JVP	RG174/U-100	2	100' Reel	26 Stranded	RG174/U	50	0.020"	98	19.95	17.95
644826	JVP	RG174/U-1000	2	1000' Reel	26 Stranded	RG174/U	50	0.020"	98	164.95	149.95

\* Web Code: CLC



Fig. 1



Fig. 2



JAMECO ValuePro

## Multi-Conductor Cable

\* Web Code: MCC

Part No.	Mfr.	Product No.	Fig.	AWG (stranded)	# of Cond.	Length	Jacket (Color/Material)	Wire Color	Insul.	Nom. O.D.	Pricing	
											1	5
2234901	BDN	8442 06025	1	22 <sup>1</sup>	2	25' Unreel	Chrome/PVC	Black, Red	A	0.170"	\$14.95	\$13.95
732996	BDN	8442 060100	1	22 <sup>1</sup>	2	100' Reel	Chrome/PVC	Black, Red	A	0.170"	39.95	37.95
733008	BDN	8442 060500	1	22 <sup>1</sup>	2	500' Reel	Chrome/PVC	Black, Red	A	0.170"	169.95	159.95
733024	BDN	8443 060100	2	22 <sup>1</sup>	3	100' Reel	Chrome/PVC	Black, Red, Green	A	0.172"	55.95	49.95
733032	BDN	8443 060500	2	22 <sup>1</sup>	3	500' Reel	Chrome/PVC	Black, Red, Green	A	0.172"	229.95	219.95
733059	BDN	8444 060100	3	22 <sup>1</sup>	4	100' Reel	Chrome/PVC	Black, Red, White, Green	A	0.185"	64.95	61.95
733067	BDN	8444 060500	3	22 <sup>1</sup>	4	500' Reel	Chrome/PVC	Black, Red, White, Green	A	0.185"	279.95	259.95
2119494	JVP	5411-100	4	22 <sup>1</sup>	5	100' Reel	Gray/PVC	Blk, Red, Wh, Grn, Brn	A	0.190"	44.95	42.95
2119558	JVP	5578-100	5	18/20 drain wire <sup>2</sup>	3	100' Reel	Chrome/PVC	Black, Red, White	B	0.230"	49.95	44.95
2119531	JVP	5576-100	5	22/22 drain wire <sup>2</sup>	3	100' Reel	Gray/PVC	Black, Red, White	B	0.190"	29.95	28.49
644383	JVP	SC4-25	6	24 drain wire <sup>2</sup>	4	25' Reel	Gray/PVC	Multi-Colored	A	0.200"	9.95	8.95
644391	JVP	SC4-100	6	24 drain wire <sup>2</sup>	4	100' Reel	Gray/PVC	Multi-Colored	A	0.200"	26.95	24.49
644404	JVP	SC4-1000	6	24 drain wire <sup>2</sup>	4	1000' Reel	Gray/PVC	Multi-Colored	A	0.200"	219.95	199.95
644412	JVP	SC-925	6	24 drain wire <sup>2</sup>	9	25' Unreel	Gray/PVC	Multi-Colored	A	0.230"	13.95	12.49
644421	JVP	SC9-100	6	24 drain wire <sup>2</sup>	9	100' Reel	Gray/PVC	Multi-Colored	A	0.230"	44.95	39.95
644447	JVP	SC15-25	6	24 drain wire <sup>2</sup>	15	25' Unreel	Gray/PVC	Multi-Colored	A	0.280"	19.95	17.95
644455	JVP	SC15-100	6	24 drain wire <sup>2</sup>	15	100' Reel	Gray/PVC	Multi-Colored	A	0.280"	59.95	53.95
644471	JVP	SC25-25	6	24 drain wire <sup>2</sup>	25	25' Unreel	Gray/PVC	Multi-Colored	A	0.370"	29.95	26.95
644480	JVP	SC25-100	6	24 drain wire <sup>2</sup>	25	100' Reel	Gray/PVC	Multi-Colored	A	0.370"	99.95	89.95



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

- 1 = Unshielded
- 2 = 100 Aluminum/ Mylar Shield 100%
- A = PVC B = Polyethylene
- Blk = Black Brn = Brown
- Grn = Green Wh = White



JAMECO ValuePro

## Paired Cable

\* Web Code: HCS

Part No.	Mfr.	Product No.	Fig.	AWG/Drain Wire	# of Pairs	Length	Jacket (Color/Material)	Wire Color	Insul.	Pricing	
										1	5
2119515	JVP	5574-100	1	18 / 24	1	100' Reel	Chrome/PVC	Black/White	A	\$39.95	\$35.95
733112	BDN	8451 010100	2	22 / 22	1	100' Reel	Black/PVC	Black/Red	B	29.95	28.49
734063	BDN	8451 010U500	2	22 / 22	1	500' Unreel	Black/PVC	Black/Red	B	129.95	124.95
2234898	BDN	8723 06025	3	22 / 24	2	25' Unreel	Chrom/PVC	Black/Red, Green/White	B	19.95	18.95
734180	BDN	8723 060100	3	22 / 24	2	100' Reel	Chrome/PVC	Black/Red, Green/White	B	64.95	59.95
734184	BDN	8723 060U500	3	22 / 24	2	500' Unreel	Chrome/PVC	Black/Red, Green/White	B	279.95	259.95



Fig. 1



Fig. 2



Fig. 3

- A = Polyethylene
- B = Polypropylene



## 2-Conductor Power/ Speaker Cable

\* Web Code: VAL

- Black wire has white polarity stripe
- Temp. rating: 20°C to 60°C
- Stranded copper wire (7 x 32)
- Operating voltage: 300V
- 24 AWG
- White wire has textured jacket for polarity




Part No.	Cross Ref. No.	Color	Length	1	5	10
100280	CAR45B-100	Black	100'	\$9.95	\$8.95	\$7.95
100299	CAR45B-1K	Black	1000'	69.95	62.95	56.95
2208391	CAR45W-1K	White	1000'	59.95	53.95	48.95



## Zip Automotive Speaker Cable

- Good for automotive or language labs
- High definition, low loss
- Red/black color coded PVC
- Voltage: 300VAC, 60VDC
- Annealed stranded bare copper wire (16 x 30)



2173845

Part No.	AWG	Strands	Length	1	5
2206299	18	16 x 30	25' ....	\$10.95	\$9.95
2173845	18	16 x 30	100' ....	29.95	27.95



## Modular Telephone Cable - 28 AWG

- Color coded conductors
- Flat modular cable
- PVC jacket
- 7 x 43 stranded
- 6 conductors
- Color: gray



\* Web Code: LCG

Part No.	Cross Ref. No.	Length	1	5	10
644691	300-860SL-100	100 ...	\$9.95	\$9.49	\$8.95
644703	300-860SL-1000	1000 ...	89.95	81.95	73.95

\* BDN = Belden | JVP = Jameco ValuePro



## ALL YOUR POWER CORD NEEDS

2 & 3 Conductor Fan, Pigtail, Detachable & Hospital Grade Power Cords at Industry Low Prices! See Page 102 for Complete Selection.

\* Web Code: UBF

