

Pushbutton Switches

3 LEVELS OF SAVINGS
 NAME BRANDS HOUSE BRANDS SPECIAL BUY

Pushbutton Switches (Continued)

See page 61 for figures

For additional Pushbutton Switches, visit Jameco.com and use Web Code

*Web Code: UBU

Part No.	Manufacturer	Product No.	Fig.	Pins	Contact Form () Momentary	Contact Rating (A @ VAC)	Mounting Hole Dia.	Dimension (L" x W" x D")	Lead Spacing	Terminal Type	Button Color	Pricing		
												1	10	100
315660	ValuePro	R13-502A-05-BR	18	2	SPST off-(on)	3 @ 125	.500"	.82 (D) x 1.02 (T)	.22"	Solder lugs	Red	\$1.49	\$1.25	\$1.09
315580	ValuePro	R13-40B-B	2	2	SPST off-(on)	3 @ 125	.480"	.87 (D) x 1.4 (T)	.20"	Solder lugs	Black	1.49	1.25	1.09
164486	ValuePro	R13-84A	3	2	SPST off-(on) ³	3 @ 125	.406"	.59 (D) x 1.2 (T)	.175"	Solder lugs	Red	1.75	1.59	1.39
315678	ValuePro	R13-502A-05-BG	18	2	SPST off-(on)	3 @ 125	.500"	.82 (D) x 1.02 (T)	.20"	Solder lugs	Green	1.95	1.75	1.49
315651	ValuePro	R13-502A-05-BB	18	2	SPST off-(on)	3 @ 125	.500"	.82 (D) x 1.02 (T)	.23"	Solder lugs	Black	1.95	1.75	1.49
106112	Mountain Switch	DS-412-RED	5	2	SPST off-(on)	3 @ 125	.734"	.66 (D) x .63 (T)	.275"	Solder lugs	Red	2.25	1.95	1.75
315820	ValuePro	R13-508AL-05-BRR	4	4	SPST off-(on)	3 @ 125	.630"	.93 (D) x 1.14 (T)	.21"	Solder w/LED	Red illum.	2.49	2.25	1.95
164582	Mountain Switch	112-R13-502MA-BLB	19	2	SPST off-(on) ⁴	3 @ 125	.490"	.90 (D) x 1.0 (T)	.19"	Solder lugs	Black	2.95	2.75	2.49
2267879	Mountain Switch	107-3039-EVX	1	2	SPST off-(on)	3 @ 125 & 1 @ 250	.393"	.393 Dia. x .77	.181"	Solder lugs	Silver	2.49	2.25	1.95
2267887	Mountain Switch	107-3040-EVX	1	2	SPST off-(on)	3 @ 125 & 1 @ 250	.393"	.393 Dia. x .77	.181"	Solder lugs	Silver [#]	2.49	2.25	1.95
2267895	Mountain Switch	107-3041-EVX	1	2	SPST off-(on)	3 @ 125 & 1 @ 250	.393"	.393 Dia. x .77	.181"	Solder lugs	Silver	2.49	2.25	1.95
2267903	Mountain Switch	107-3042-EVX	1	2	SPST off-(on)	3 @ 125 & 1 @ 250	.393"	.393 Dia. x .77	.181"	Solder lugs	Silver [#]	2.49	2.25	1.95
2267823	Mountain Switch	107-3027-EVX	3	2	SPST off-(on)	3 @ 125 & 1 @ 250	.393"	.393 Dia. x .77	.181"	Solder lugs	Silver	3.49	3.15	2.79
2267839	Mountain Switch	107-3029-EVX	3	2	SPST off-(on)	3 @ 125 & 1 @ 250	.393"	.393 Dia. x .77	.181"	Solder lugs	Silver [#]	3.49	3.15	2.79
2268327	ValuePro	R13-509A-05-BB	20	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.280"	.28 Dia. x .60	.19"	Solder lugs	Black	.89	.79	.69
2268087	ValuePro	R13-509A-05-BB	20	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.280"	.417 Dia. x 1.14L	.181"	Solder lugs	Red	.89	.79	.69
2269679	Mountain Switch	R13-23A-05-B/BL	1	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.470"	.47 Dia. x 1.13 (T)	.21"	Solder lugs	Blue	1.49	1.25	1.09
2269671	Mountain Switch	R13-23A-05-BY	1	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.470"	.47 Dia. x 1.13 (T)	.21"	Solder lugs	Yellow	1.49	1.25	1.09
2268295	Mountain Switch	103-1022-EVX	21	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.280"	.28 Dia. x .58	.19"	Solder lugs	Red	1.25	1.09	.99
2268135	ValuePro	R13-23A-05-BL	1	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.480"	.47 Dia. x .90 (T)	.181"	Solder lugs	Blue	1.95	1.75	1.49
2269631	ValuePro	R13-508A-R	4	2	SPST off-(on)	3 @ 125 & 1.5 @ 250	.63L x .59W	.63 Dia. x .94 (T)	.23"	Solder lugs	Red illum.	2.95	2.59	2.29
2231822	Apem Inc.	1413NC2	22	2	SPST off-(on)	3 @ 12VDC	.57L x .63W	.71 x .71 x .51	.29"	Solder lugs	Black	1.95	1.75	1.49
2217553	Seeed Studio	TEM12123B	23	2	SPST off-(on)	3 @ 250	.620"	.70 x .70 x .90	.20"	Solder lugs	Black	4.49	3.95	3.59
2217570	Seeed Studio	TEM12127B	23	2	SPST off-(on)	3 @ 250	.620"	.70 x .70 x .90	.20"	Solder lugs	Blue	4.49	3.95	3.59
2217561	Seeed Studio	TEM12125B	23	2	SPST off-(on)	3 @ 250	.620"	.70 x .70 x .90	.20"	Solder lugs	Red	4.49	3.95	3.59
22218	Judco	J1882	12	2*	SPST off-(on)	4 @ 14VDC	.375"	.65 x .52 x .40	.25"	5" Pigtail	Red	1.59	1.35	1.19
2267679	Mountain Switch	104-0015-EVX	24	2	SPST on-(off)	5 @ 125	.290"	.374 (D) x 1.12 (T)	.181"	Solder lugs	Red illum.	.89	.79	.69
2228906	Arndt	MGPB-SPST-3A(iridite)	24	2	SPST on-(off) ¹	3 @ 125	.299"	.36 (D) x 1.13 (T)	.17"	Solder lugs	Black	.79	.69	.59
26649	ValuePro	R18-29B (chrome)	9	2	SPST on-(off) ¹	3 @ 125	.299"	.36 (D) x 1.13 (T)	.181"	Solder lugs	Black	.89	.79	.69
2266815	Mountain Switch	103-1024-EVX	21	2	SPST on-(off)	3 @ 125	.283"	.395 (D) x 1.34 (T)	.16"	Solder lugs	Red	1.09	.99	.89
2266839	Mountain Switch	103-1219-EVX	20	2	SPST on-(off)	3 @ 125 & 1.5 @ 250	.280"	.42 (D) x .69 (T)	.16"	Solder lugs	Black	.99	.89	.79
2266831	Mountain Switch	103-1218-EVX	20	2	SPST on-(off)	3 @ 125 & 1.5 @ 250	.280"	.42 (D) x .69 (T)	.16"	Solder lugs	Red	.99	.89	.79
2181386	ValuePro	WJ-DS03	25	3	SPDT on-(off)	16 @ 125 & 10 @ 250	.335"	1.6 x 1.0 x .54	.20"	250° quick conn.	White	1.49	1.25	1.09
22200	Judco	J1881	12	2*	SPST on-off, Alt [†]	2 @ 14VDC	.375"	.65 x .52 x .40	.25"	5" Pigtail	White	2.25	1.95	1.75
2269655	ValuePro	PA102A1-BR	6	3	SPDT on-on	6 @ 125 & 3 @ 250	.240"	.51 x .32 x .87	.18"	Solder lugs	Red	1.95	1.75	1.49
2269663	ValuePro	112-PA106A1-R/BL	6	3	SPDT (on)-on	6 @ 125 & 3 @ 250	.240"	.24 Dia. x .87 (T)	.18"	Solder lugs	Red	1.95	1.75	1.49
2267783	Mountain Switch	107-3016-EVX	27	3	SPDT on-(on)	4 @ 20VAC/VDC	.185"	.79 x .33 x .22	.12"	PC right angle	Black	2.95	2.59	2.29
2267791	Mountain Switch	107-3018-EVX	25	3	SPDT on-(on)	4 @ 20VAC/VDC	.185"	.32 x .35 x .24	.12"	SMD/SMT	White	2.95	2.59	2.29
2227524	NKK	DB2511V	26	3	SPDT on-(on)	4 @ 28VDC	.240"	.60 x .58 x .28	.10"	PC right angle	Silver	.99	.85	.75
2182080	C&K Switch	8121J81ZGE99	28	3	SPDT on-(on)	1 @ 120	.250"	.50 x .27 x .41	.185"	Solder lugs	Gray	5.95	5.39	5.55
2182098	C&K Switch	8125J85ZBE225	29	5	SPDT on-(on)	1 @ 120	.50L x .60W	.50 x .37 x .37	.145"	Solder lugs	Black	7.95	6.95	6.25
28063	ValuePro	PB126	30	3	SPDT on-(on) ²	3 @ 120	.250"	.52 x .28 x .38	.185"	Solder lugs	Red	3.59	3.25	2.95
121305	ValuePro	GPB006-WH	30	3	SPDT on-(on) ²	3 @ 120	.250"	.52 x .27 x .38	.185"	Solder lugs	White	3.59	3.25	2.95
2267703	Mountain Switch	107-3001-EVX	31	3	SPDT on-(on)	3 @ 120/28VDC	.250"	.50 x .26 x .41	.185"	Solder lugs	White	3.95	3.49	2.95
2267719	Mountain Switch	107-3003-EVX	17	3	SPDT on-(on)	3 @ 120 & 1 @ 250	.185"	.62 x .32 x .66	.19"	PC terminal	White	3.95	3.49	2.95
2267735	Mountain Switch	107-3005-EVX	26	3	SPDT on-(on)	3 @ 120 & 1 @ 250	.250"	.27 x .52 x .50	.185"	PC right angle	White	3.95	3.49	2.95
2267711	Mountain Switch	107-3002-EVX	32	3	SPDT on-(on)	3 @ 120 & 1 @ 250	.250"	.50 x .50 x .26	.20"	PC terminal	White	3.95	3.49	2.95
2267727	Mountain Switch	107-3004-EVX	28	3	SPDT on-(on)	3 @ 120 & 1 @ 250	.250"	.50 x .27 x .63	.185"	Solder lugs	Red	2.95	2.59	2.29
2267743	Mountain Switch	107-3007-EVX	28	3	SPDT on-(on)	3 @ 120 & 1 @ 250	.62L x .50W	.98 x .48 x .72	.185"	Solder lugs	Red	3.95	3.49	2.95
2267751	Mountain Switch	107-3008-EVX	28	3	SPDT on-(on)	3 @ 120 & 1 @ 250	.62L x .50W	.98 x .48 x .72	.185"	Solder lugs	Red	3.95	3.49	2.95
2182101	C&K Switch	8168SHABE2	33	3	SPDT on-(on)	6 @ 120	.300"	.50 x .27 x .45	.185"	PC right angle	Black	6.95	6.25	5.59
2182240	Alcoswitch	MSP105F	34	3	SPDT (on)-off-(on)	5 @ 115	.250"	.50 x .26 x .66	.14"	Solder lugs	Silver	1.95	1.75	1.49
2215785	C&K Switch	PVA1-0A-H1-1.2N	35	6	DPST on-(on)	1 @ 32VDC	.21L x .22W	.36 x .34 x .30	.10"	PC pin	Red	.99	.89	.79
2181407	ValuePro	01-690C	36	6	DPDT off-on [†]	4 @ 125	.472"	1.7 x .71 x .98	.35"	Solder lugs	Silver	4.49	3.95	3.59
2267967	Alpha	SF1202F-0202-20R-L-051	37	6	DPDT on-off	6 @ 125 & 3 @ 250	.470"	.53 x .47 x .65	.18"	Solder lugs	Silver	5.95	5.39	4.79
594718	C&K Switch	PVA2EEH21.7N	35	6	DPDT on-(on)	1 @ 32VDC	.21L x .22W	.36 x .36 x .43	.10"	PC pin	White	.99	.89	.79
2267759	Mountain Switch	107-3009-EVX	31	6	DPDT on-(on)	3 @ 120 & 1 @ 250	.250"	.50 x .45 x .59	.185"	Solder lugs	White	4.95	4.49	3.95
2267767	Mountain Switch	107-3011-EVX	17	6	DPDT on-(on)	3 @ 120 & 1 @ 250	.250"	.62 x .32 x .82	.185"	PC terminal	White	4.95	4.49	3.95
2267775	Mountain Switch	107-3012-EVX	28	6	DPDT on-(on)	3 @ 120 & 1 @ 250	.62L x .50W	.98 x .48 x .72	.185"	Solder lugs	Red	2.95	2.59	2.29
2181415	ValuePro	01-690DB-RH	38	9	3PDT off-on [†]	4 @ 125	.472"	1.7 x .68 x .77	.185"	Solder lugs	Silver	4.49	3.95	3.59
2203055	LKG	SW-CAP	39		Red pushbutton switch cap, round, .30"Dia. x .30"H x .12"ID, snap fit							.35	.29	.25
2202132	Alcoswitch	C22004	39		Black pushbutton switch cap (for P/N 71643), round, .402"Dia x .315"H x .099"ID, snap fit							.25	.12	.09
578591	C&K Switch	894102000	39		Black pushbutton switch cap, round, .395"Dia. x .325"H							.25	.19	.15

*Lead wires #Silver body †Alt = alternate action Additional panel mounting hardware: 1 2182688; 2 2182477; 3 2183242; 4 2182733, see pg 78