

# Toggle Switches

3 LEVELS OF SAVINGS  
**NAME BRANDS** | **HOUSE BRANDS** | **SPECIAL BUY**



## Miniature Toggle Switches (Continued)

See page 63 for figures

\* Web Code: PAJ

Part No.	Mfr.	Product No.	Fig.	Pins	Contact Form ( ) Momentary	Contact Rating (A @ VAC)	Dimensions (L" x W" x D")	Lead Spacing		Terminal Type	Lever Type	Pricing		
								A"	B"			1	10	100
2135857	JVP	GTS103 <sup>1</sup>	1	3	SPDT on-on	5 @ 120 & 2 @ 250	.50 x .28 x .35	—	0.185	Solder lugs	Round	\$1.49	\$1.25	\$1.09
217236	JVP	1MS1T1B1M1QE <sup>1</sup>	1	3	SPDT on-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	Solder lugs	Round	1.79	1.59	1.45
26332	JVP	MPC123R <sup>1</sup>	4	3	SPDT on-on	5 @ 120 & 2 @ 250	.52 x .32 x .37	—	0.185	PC straight	Round	1.75	1.49	1.25
22833	JVP	MS102F1-R <sup>1</sup>	2	3	SPDT on-on	5 @ 125 & 2 @ 250	.52 x .28 x .36	—	0.185	Solder lugs	Flat	1.95	1.75	1.49
2258486	NKK	M2012SS1W01	1	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .37	—	0.185	Solder lugs	Round	2.95	2.59	2.29
71597	JVP	MTS-102-C4	3	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.133	PC right angle	Round	1.75	1.49	1.25
2258777	NKK	M2015SS1W01	1	3	SPDT on-(on)	6 @ 125 & 3 @ 250	.52 x .32 x .37	—	0.185	Solder lugs	Round	2.49	2.25	1.95
21910	JVP	JMT121 <sup>1</sup>	1	3	SPDT on-off-on	5 @ 120 & 2 @ 250	.52 x .32 x .38	—	0.185	Solder lugs	Round	1.25	1.09	.99
317308	JVP	1MS3T6B11M1QE <sup>1</sup>	2	3	SPDT on-off-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	Solder lugs	Flat	1.79	1.59	1.45
317244	JVP	1MS3T1B1M1QE <sup>1</sup>	1	3	SPDT on-off-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	Solder lugs	Round	1.79	1.59	1.45
26315	JVP	MPC121 <sup>1</sup>	4	3	SPDT on-off-on	5 @ 125 & 2 @ 250	.52 x .32 x .37	—	0.185	PC straight	Round	1.49	1.25	1.09
2181765	JVP	TS-5-120VAC	4	3	SPDT on-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	Solder lugs	Round	1.09	.99	.89
317252	JVP	1MS4T1B1M1QE <sup>1</sup>	1	3	SPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	Solder lugs	Round	1.79	1.59	1.45
317316	JVP	1MS4T6B11M1QE <sup>1</sup>	2	3	SPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	Solder lugs	Flat	1.95	1.75	1.49
2180893	ALC	A105SYZB	4	3	SPDT (on)-off-(on)	5 @ 125 & 2 @ 250	.50 x .27 x .36	—	0.185	Solder lugs	Round	3.95	3.59	3.29
75889	JVP	SWM129 <sup>1</sup>	1	3	SPDT (on)-off-(on)	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	Solder lugs	Round	1.95	1.75	1.49
2181642	C&K	7101MD9ABI	3	3	SPDT on-none-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	PC right angle	Round	2.95	2.59	2.29
21979	JVP	T201T1B1A1QN <sup>1</sup>	6	6	DPDT on-on	5 @ 120 & 2 @ 250	.52 x .52 x .38	0.20	0.185	Solder lugs	Round	1.75	1.49	1.25
317472	JVP	1MD1T6B11M1QE <sup>1</sup>	5	6	DPDT on-on	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	Solder lugs	Flat	1.95	1.75	1.49
26367	JVP	GTS112-p <sup>1</sup>	6	6	DPDT on-on	5 @ 120 & 3 @ 250	.52 x .50 x .41	0.20	0.157	PC straight	Round	1.75	1.49	1.25
22859	JVP	GTS172BLK <sup>1</sup>	5	6	DPDT on-on	5 @ 120 & 3 @ 250	.52 x .52 x .38	0.20	0.185	Solder lugs	Flat	1.95	1.75	1.49
26358	JVP	MPC221 <sup>1</sup>	6	6	DPDT on-off-on	5 @ 120 & 3 @ 250	.52 x .52 x .38	0.20	0.185	PC straight	Round	1.75	1.49	1.25
21952	JVP	GTS114 <sup>1</sup>	6	6	DPDT on-off-on	5 @ 120 & 3 @ 250	.52 x .52 x .38	0.20	0.185	Solder lugs	Round	1.75	1.49	1.25
22841	JVP	GTS164BLK <sup>1</sup>	5	6	DPDT on-off-on	5 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	Solder lugs	Flat	1.95	1.75	1.49
317498	JVP	1MD4T6B11M1QE <sup>1</sup>	5	6	DPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	Solder lugs	Flat	2.95	2.59	2.29
75951	JVP	SWM130 <sup>1</sup>	6	6	DPDT (on)-off-(on)	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	Solder lugs	Round	1.75	1.49	1.25
620576	GCE	35-009 <sup>1</sup>	6	6	DPDT on-on-on	5 @ 120 & 2 @ 250	.50 x .45 x .40	0.23	0.150	Solder lugs	Round	3.95	3.59	3.29
2181212	C&K	E201MD1CBE	6	6	DPDT on-none-on	5 @ 125 & 3 @ 250	.50 x .45 x .35	—	0.185	PC straight	Round	1.95	1.75	1.49
2182477	C&K	1/4-40HDWR	7	—	Additional 1/4-40 UNS threaded panel mounting hardware (4 pcs.) for above switches indicated with 1							.89	.79	.69
2182506	C&K	15/32-32HDWR	7	—	Additional 15/32-32 UNS threaded panel mounting hardware (4 pcs.) for P/N 2235735 indicated with 2							.99	.89	.79

Electromech

## Subminiature Toggle Switches

**NEW**  
MARKED IN PINK

Additional Toggle Switches, visit [Jameco.com](http://Jameco.com) and use Web Code

\* Web Code: NAN

- Mounting hole diameter: .7/32 (.21")
  - Round toggle
  - Thread: 10-48 UNS
  - Metal construction
  - Pre-tinned leads
- Includes:** Panel mounting hardware



Part No.	Mfr.	Product No.	Fig.	Pins	Contact Form ( ) Momentary	Contact Rating (A @ VAC)	Dimensions (L" x W" x D")	Lead Spacing		Terminal Type	Pricing			
								A"	B"		1	10	100	
2269519	MSW	108-0047-EVX	1	3	SPST off-on	3 @ 125 & 1 @ 250	.32 x .24 x .47	—	.10	PC terminal		\$2.49	\$2.25	\$1.95
2267943	MSW	108-0038-EVX	3	2	SPST off-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	.18	Solder lugs		3.49	3.29	2.96
2267935	MSW	108-0040-EVX	3	2	SPST off-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	.18	Solder lugs		3.49	3.29	2.96
2267959	MSW	1055-TA2120-EVX	1	2	SPST off-on	6 @ 125 & 3 @ 250	.51 x .29 x .62	—	.19	Solder lugs		2.49	2.25	1.95
2269623	MSW	108-0050-EVX	1	2	SPST on-off	3 @ 125 & 1 @ 250	.32 x .24 x .47	—	.10	PC terminal		2.49	2.25	1.95
72161	JVP	SW1501 <sup>§</sup>	1	2	SPST on-off	5 @ 120 & 1.5 @ 250	.33 x .21 x .33	.10	—	Solder lugs		1.49	1.25	1.09
106067	JVP	SWP124	2	3	SPDT on-on	.4VA max.	.25 x .33 x .40	.20	.10	PC right angle		1.95	1.75	1.49
2202757	ESW	A123S1D9AB	2	3	SPDT on-on	.5VA @ 28VDC/AC	.50 x .37 x .26	.17	—	PC right angle		3.95	3.59	3.29
2269551	MSW	108-0048-EVX	1	3	SPDT on-on	3 @ 120 & 1 @ 250	.32 x .20 x .47	—	.10	PC terminal		2.95	2.59	2.29
75969	JVP	SWM136 <sup>§</sup>	1	3	SPDT on-on	3 @ 125 & 1.5 @ 250	.33 x .21 x .33	.10	—	Solder lugs		1.49	1.25	1.09
2268287	MSW	103-0017-EVX	4	3	SPDT on-on	6 @ 125 & 3 @ 250	.63 x .63 x .72	—	.19	Solder lugs		1.95	1.75	1.49
2268663	MSW	103-4023-EV	5	3	SPDT on-on	6 @ 125 & 3 @ 250	.585 x .534 x .76	.185	—	Solder lugs		2.25	1.95	1.75
2269527	MSW	108-1MS2T2B4M6QE	2	3	SPDT on-(on)	5 @ 125 & 2 @ 250	.50 x .50 x .40	—	.20	PC right angle		2.49	2.25	1.95
2269599	MSW	108-1MS2T2B3M1QE	3	3	SPDT on-(on)	5 @ 125 & 2 @ 250	.50 x .27 x .51	—	.19	Solder lugs		2.49	2.25	1.95
2269535	MSW	1055-TA2135-EVX	3	3	SPDT on-off-on	6 @ 125 & 3 @ 250	.51 x .29 x .62	—	.19	Solder lugs		2.49	2.25	1.95
2268103	MSW	108-0002-EVX	3	3	SPDT on-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .51	—	.19	Solder lugs		2.95	2.59	2.29
2268399	MSW	108-0023-EVX	2	3	SPDT (on)-off-(on)	5 @ 125 & 2 @ 250	.50 x .27 x .62	.18	—	PC terminal		2.95	2.59	2.29
2269615	MSW	108-0043-EVX	1	6	DPDT on-on	3 @ 120 & 1 @ 250	.36 x .32 x .47	.20	.10	PC terminal		2.95	2.59	2.29
2269607	MSW	108-2MD1T1B1M1QE	3	6	DPDT on-on	3 @ 120 & 1 @ 250	.36 x .32 x .49	.16	.10	Solder lugs		2.95	2.59	2.29
75977	JVP	66-1005	3	6	DPDT on-on	3 @ 125	.33 x .37 x .33	.17	.10	Solder lugs		1.49	1.25	1.09
2267975	MSW	108-0029-EVX	3	6	DPDT on-on	5 @ 120 & 2 @ 250	.50 x .45 x .51	.19	.19	Solder lugs		2.95	2.59	2.29
2269567	MSW	108-1MD1T6B11M2QE	3	6	DPDT on-on	5 @ 125 & 2 @ 250	.50 x .45 x .60	.20	.19	PC terminal		3.49	3.29	2.96
2269559	MSW	108-1MD2T2B3M1QE	1	6	DPDT on-(on)	5 @ 125 & 2 @ 250	.50 x .45 x .50	.19	.18	Solder lugs		2.95	2.59	2.29

§ Mounting hardware P/N 2182549 on pg 65

