

AC-to-AC Wall Adapters



AC-to-AC Wall Adapters

Input: 120VAC @ 60Hz

* Web Code: ABQ



We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call 1-800-831-4242 for details.

Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VAC)	Current (mA)							1	10	50	100
2230651	ReliaPro	ABU050050R	5	500	2.1mm x 5.5mm F	2.7 x 1.9 x 1.7	Black	6'	0.9	UL/CUL	\$7.95	\$6.95	\$6.25	\$5.95
2236834	ReliaPro	ACU060100R	6	1000	2.1mm x 5.5mm F	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CUL	9.95	8.95	7.95	6.95
2236842	ReliaPro	ADU060200R	6	2000	2.1mm x 5.5mm F	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CUL	10.95	9.95	8.95	7.95
100061	ReliaPro	ACU090050	9	500	2.1mm x 5.5mm F	2.7 x 1.9 x 1.7	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	7.19
102234	ReliaPro	ACU090100	9	1000	2.1mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	10.95	9.95	8.95	7.95
157041	ReliaPro	ACU090100E8942	9	1000	2.5mm x 5.5mm F	2.1 x 2.1 x 1.6	Black	6'	0.6	UL/CUL	10.95	9.95	8.95	7.95
2231574	ReliaPro	ACU090100-3.5M	9	1000	3.5mm M	2.5 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	6.25
2227444	ReliaPro	ADU090150	9	1500	2.1mm x 5.5mm F	2.9 x 2.3 x 1.8	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
112336	ReliaPro	ACU090150A2231	9	1500	2.5mm x 5.5mm F	2.5 x 2.2 x 2.0	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
2234222	Arndt	A35100300	10	300	2.5mm x 5.0mm F	2.4 x 1.7 x 1.6	Black	6'	0.4	UL	6.95	6.25	5.49	4.95
2234185	Arndt	41A-12-500	12	500	2.1mm x 5.5mm F	2.3 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	6.95	6.25	5.95	4.95
101258	ReliaPro	ACU120050	12	500	2.1mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	6.95
2179614	ReliaPro	ACU120050R	12	500	2.5mm x 5.5mm F	2.5 x 2.0 x 1.7	Black	6'	0.4	UL/CUL	9.95	8.95	7.95	6.95
2234214	Arndt	AC9084-BK01	12	830	3.5mm M	2.7 x 1.9 x 1.5	Black	10'	0.8	UL/CSA	7.95	6.95	6.25	5.49
10081	ReliaPro	AD-1201000A1	12	1000	2.1mm x 5.5mm F	2.5 x 2.0 x 1.6	Black	6'	0.7	UL/CUL	10.95	9.95	8.95	7.95
100167	ReliaPro	ACU1201000D0531	12	1000	2.5mm x 5.5mm F	3.2 x 2.4 x 2.0	Black	6'	0.7	UL/CUL	10.95	9.95	8.95	7.95
10428	ReliaPro	ACU12010029121	12	1000	3.5mm M	2.6 x 2.4 x 2.0	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	6.95
2167576	Arndt	AM-121200A	12	1200	2.1mm x 5.5mm right angle F	3.2 x 2.1 x 1.9	Black	6'	0.9	UL/CSA	6.95	6.25	5.49	4.95
167151	ReliaPro	ADU120150	12	1500	2.1mm x 5.5mm F	3.4 x 2.7 x 2.2	Black	6'	1.5	UL/CUL	12.95	11.95	10.95	9.95
307838	ReliaPro	ADU120160H4120	12	1600	2.5mm x 5.5mm F	3.9 x 2.3 x 1.9	Black	6'	1.0	UL/CUL	13.95	12.95	11.95	10.95
206404	ReliaPro	MGT1220	12	1670	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	10.95	9.95	8.95	7.95
2236455	ReliaPro	A1220NNL#	12	1670	Screw terminals	3.2 x 2.2 x 1.9	White	—	1.0	UL	11.95	10.95	9.95	8.95
2197581	ReliaPro	GPU48120200WA00	12	2000	2.1mm x 5.5mm F	3.3 x 2.6 x 2.2	Black	6'	1.7	UL/CUL	15.95	14.49	12.95	11.49
2227604	ReliaPro	GPU481202000WA0-2.5	12	2000	2.5mm x 5.5mm F	3.3 x 2.6 x 2.2	Black	6'	1.7	UL/CUL	15.95	14.49	12.95	11.49
2197847	Arndt	A71235DC	12	3500	Stripped/tinned (Table-Top style)	3.9 x 2.7 x 2.2	Black	6'	2.1	UL/CSA	9.95	8.95	7.95	6.95
171408	ReliaPro	ACU140050	14	500	2.1mm x 5.5mm F	2.8 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	9.95	8.95	7.95	6.95
318684	ReliaPro	ACU140085	14	850	2.5mm x 5.5mm right angle F	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	10.95	9.95	8.95	7.95
100108	ReliaPro	ADU160100	16	1000	2.1mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	12.95	11.95	10.95	9.95
2227612	ReliaPro	ADU160100-2.5	16	1000	2.5mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
2230635	ReliaPro	MGT1640#	16.5	2400	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	12.95	11.95	10.95	9.95
2231591	ReliaPro	ACU180050	18	500	Stripped/tinned	2.5 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	6.25
121216	ReliaPro	ADU180100	18	1000	2.1mm x 5.5mm F	3.1 x 2.7 x 1.9	Black	6'	1.1	UL/CUL	12.95	11.95	10.95	9.95
2227621	ReliaPro	ADU180100-2.5	18	1000	2.5mm x 5.5mm F	3.1 x 2.7 x 1.9	Black	6'	1.1	UL/CUL	11.95	10.95	9.95	8.95
2179622	ReliaPro	AFU180200	18	2000	2.1mm x 5.5mm F	3.4 x 2.7 x 2.1	Black	6'	1.7	—	13.95	12.95	11.95	10.95
87581	ReliaPro	ADU240050	24	500	2.1mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	10.95	9.95	8.95	7.95
2234193	ReliaPro	ADU240050-2.5	24	500	2.5mm x 5.5mm F	2.5 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95
140599	ReliaPro	ADU240100D0531	24	1000	2.1mm x 5.5mm F	3.0 x 2.2 x 1.9	Black	6'	1.2	UL/CUL	12.95	11.95	10.95	9.95
10102	ReliaPro	ADU240100E0461	24	1000	3.5mm M	3.0 x 2.2 x 1.9	Black	6'	1.2	UL/CUL	12.95	11.95	10.95	9.95
2100195	ReliaPro	GPU572401500WA00	24	1500	2.1mm x 5.5mm F	3.3 x 2.6 x 2.3	Black	6'	1.7	UL/CUL	15.95	14.49	12.95	11.95
2227639	ReliaPro	GPU572401500WA00-2.5	24	1500	2.5mm x 5.5mm F	3.3 x 2.6 x 2.3	Black	6'	1.7	UL/CUL	15.95	14.49	12.95	11.95
2230627	ReliaPro	MGT2440#	24	1600	Screw terminals with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	12.95	11.95	10.95	9.95
2197548	ReliaPro	GPU572402000WA00	24	2000	2.1mm x 5.5mm F	3.3 x 2.6 x 2.2	Black	6'	1.7	UL/CUL	16.95	15.49	13.95	12.49
2229386	ReliaPro	MGT2450P#	24	2100	Screw terminal with green LED	3.2 x 2.2 x 1.9	White	—	0.9	UL	18.95	16.95	15.49	13.95

Level VI efficiency




AC-to-DC Regulated Switching Wall Adapters



* Web Code: CDZ

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call 1-800-831-4242 for details.



Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ♦	Input VAC @ Hz	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing		
			Volt. (VDC)	Current (mA)								1	10	50
2138636	Emerson	SW013US-0500020US*	5	200	USB type-A F	100-240@50-60	2.3 x 1.8 x 0.9	Black	—	0.2	TUV/FCC	\$2.95	\$2.59	\$2.25
2234097	Phihong	PLA02A-050*	5	400	1.7mm x 3.0mm RA F 2	100-240@50/60	1.9 x 1.3 x 1.0	Black	6'	0.2	UL/CUL	4.95	4.49	3.95
2230408	Phihong	PSM04A-050	5	750	2.1mm x 5.5mm F 2	100-240@50/60	2.7 x 1.8 x 1.0	Black	6'	0.3	UL/CUL	6.95	6.25	5.95
2234601	Arndt	MU05-050100-A1-10	5	1000	2.1mm x 5.5mm F 2	100-240@50/60	2.6 x 1.3 x 1.5	Black	10'	0.2	UL/CUL	5.95	5.49	4.95
2229440	Arndt	TSA1-050120WA*	5	1200	Stripped/tinned	100-240@50/60	2.1 x 1.8 x 1.1	Black	6'	0.2	UL/CUL	6.95	6.25	5.95
2229503	Arndt	YFAF22073001	5	1200	Stripped/tinned	100-240@50-60	3.2 x 1.2 x 1.3	Black	6'	0.2	UL/CUL	6.95	6.25	5.95
2227735	Arndt	EDF0500150A1BA*	5	1500	1.3mm x 3.5mm F 2	100-120@50-60	2.8 x 1.6 x 1.3	Black	6'	0.2	UL/CUL	7.95	6.95	6.25

* Slimline

Continued on next page

* For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com