

AC-to-DC Linear Wall Adapters


3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **SPECIAL BUY**

JAMECO ReliaPro AC-to-DC Regulated & Unregulated Linear Wall Adapters



Input: 120VAC @ 60Hz

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call 1-800-831-4242 for details.



Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ◆	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing				
			Voltage (VDC)	Current (mA)							1	10	50	100	
Regulated Linear Wall Adapters												*Web Code: WAZ			
1953612	ReliaPro	DDU050100	5	1000	2.1mm x 5.5mm F 2	3.2 x 2.2 x 1.8	Black	6'	1.2	UL/CUL	\$10.95	\$9.95	\$8.95	\$7.95	
168605	ReliaPro	DBU0501000	5	1000	2.5mm x 5.5mm F 2	3.3 x 2.2 x 1.9	Black	6'	1.2	UL/CUL	10.95	9.95	8.95	7.95	
2265887	Arndt	41-9-300R	9	300	2.1mm x 5.5mm F 2	2.5 x 2.0 x 1.6	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95	
1953639	ReliaPro	DCU09050	9	500	2.1mm x 5.5mm F 2	2.4 x 2.0 x 1.6	Black	6'	0.9	UL/CUL	10.95	10.49	9.95	8.95	
1953647	ReliaPro	GPU410900500WDOO	9	500	2.5mm x 5.5mm F 2	3.0 x 2.0 x 1.6	Black	6'	0.9	UL/CUL	10.95	10.49	9.95	8.95	
220898	ReliaPro	DCU120020	12	200	2.1mm x 5.5mm F 1	2.5 x 2.0 x 1.7	Black	6'	0.5	UL/CUL	8.95	7.95	6.95	6.25	
2236789	Ever Glow	DCU120020	12	200	2.1mm x 5.5mm F 1	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CUL	8.95	7.95	6.95	6.25	
162996	ReliaPro	DDU120050	12	500	2.1mm x 5.5mm F 2	3.2 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95	
170245	ReliaPro	DDU120100	12	1000	2.1mm x 5.5mm F 2	3.2 x 2.3 x 2.0	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95	
1953663	ReliaPro	DCU1201000	12	1000	2.5mm x 5.5mm F 2	3.3 x 2.3 x 2.0	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95	
249244	ReliaPro	DFU120150/G9760	12	1500	2.1mm x 5.5mm F 2	3.1 x 2.6 x 2.2	Black	6'	1.6	UL/CUL	15.95	14.49	12.95	11.49	
174861	ReliaPro	DFU240050	24	500	2.1mm x 5.5mm F 2	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	14.95	13.49	11.95	10.95	
174879	ReliaPro	DCU090025	24	500	2.5mm x 5.5mm F 2	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	14.95	13.49	11.95	10.95	
Unregulated Linear Wall Adapters												*Web Code: UAP			
2231443	Arndt	950-00143	5	800	2.5mm x 5.5mm F 2	3.0 x 2.2 x 1.8	Black	6'	0.9	UL/CSA	\$6.95	\$6.25	\$5.59	\$4.95	
2179745	DVE	DV-6100-3508	6	100	2.1mm x 5.5mm F 1	2.4 x 1.5 x 1.0	Black	6'	0.3	UL/CUL	2.95	2.59	2.29	1.95	
101266	ReliaPro	DBU060050E3860	6	500	2.1mm x 5.5mm F 2	2.4 x 1.9 x 1.6	Black	6'	0.4	UL/CUL	6.95	6.25	5.59	4.95	
2234741	ReliaPro	DBU060050-2.5	6	500	2.5mm x 5.5mm F 2	2.4 x 1.9 x 1.6	Black	6'	0.4	UL/CUL	7.95	6.95	6.25	5.95	
2234610	Arndt	H00AAA	6	600	2.1mm x 5.5mm F 1	2.4 x 2.1 x 1.5	Black	6'	0.5	UL/CSA	7.95	6.95	5.95	4.95	
147707	ReliaPro	DBU060080C6962	6	800	2.1mm x 5.5mm F 2	2.3 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	5.95	
1953719	ReliaPro	DCU060100-S0070	6	1000	2.1mm x 5.5mm F 2	2.5 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	6.25	
220943	ReliaPro	DCU060120G2401	6	1200	2.1mm x 5.5mm F 1	2.5 x 2.0 x 1.7	Black	6'	0.7	UL/CUL	9.95	8.95	7.95	6.95	
2229271	OEM	AD0780	7.5	800	2.5mm x 5.5mm F 2	2.3 x 2.3 x 1.8	Black	6'	0.8	UL/CSA	8.95	7.95	6.95	6.25	
2215460	Fujitsu	MA14L-2001-0012	9	200	1.3mm x 3.5mm right angle F 2	2.4 x 1.7 x 1.5	Black	6'	0.4	UL/CSA	4.95	3.95	3.49	2.95	
2234628	Arndt	DV-9200	9	200	2.1mm x 5.5mm F 1	2.1 x 1.7 x 1.4	Black	6'	0.4	UL/CSA	5.95	5.49	4.95	4.95	
100845	ReliaPro	DBU090020E0850	9	200	2.1mm x 5.5mm F 2	2.1 x 1.7 x 1.5	Black	6'	0.4	UL/CUL	6.95	5.95	5.49	4.59	
133891	ReliaPro	DBU090030-C1110	9	300	2.1mm x 5.5mm F 2	2.0 x 1.5 x 1.5	Black	6'	0.4	UL/CUL	6.95	5.95	5.49	4.95	
2230432	Arndt	35-9-300C	9	300	2.5mm x 5.5mm F 2	2.2 x 1.7 x 1.5	Black	6	0.4	UL/CUL	5.95	5.49	4.49	3.95	
189238	ReliaPro	DBU090030H4540	9	300	2.5mm x 5.5mm F 2	2.2 x 1.7 x 1.5	Black	6'	0.4	UL/CUL	6.95	5.95	4.95	4.49	
163628	ReliaPro	DCU090050-Z7483	9	500	2.1mm x 5.5mm F 1	2.5 x 1.9 x 1.7	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
100853	ReliaPro	DCU090050-Z7480	9	500	2.1mm x 5.5mm F 2	2.5 x 1.9 x 1.7	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
236937	ReliaPro	DCU090050G6440	9	500	2.5mm x 5.5mm right angle F 2	2.5 x 2.0 x 1.7	Black	6'	0.4	UL/CUL	7.95	6.95	6.25	5.95	
15561	ReliaPro	DCU090050A2011	9	500	3.5mm M 2	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CSA	7.95	6.95	6.25	5.95	
202180	ReliaPro	DCU090060F2091	9	600	2.1mm x 5.5mm F 2	3.3 x 2.9 x 2.3	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
100175	ReliaPro	DCU090060Z6652	9	600	2.5mm x 5.5mm F 2	2.7 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
164929	ReliaPro	DDU090100C2550	9	1000	2.1mm x 5.5mm F 1	2.7 x 2.3 x 1.8	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95	
364576	ReliaPro	DDU090100J0490	9	1000	2.1mm x 5.5mm F 2	2.9 x 2.3 x 1.9	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95	
2227428	Arndt	MT12-Y090100-A1	9	1000	2.5mm x 5.5mm F 2	2.6 x 1.5 x 1.3	Black	6'	0.2	UL/CUL	8.95	7.95	6.95	6.25	
2229280	OEM	AD091AL	9	1000	2.5mm x 5.5mm F 2	2.9 x 2.1 x 1.9	Black	6'	0.9	UL/CUL	7.95	6.95	6.25	5.49	
127505	ReliaPro	DDU090100-N1600	9	1000	2.5mm x 5.5mm F 2	2.6 x 2.4 x 2.0	Black	6'	0.9	UL/CUL	9.95	8.95	7.95	6.95	
100095	ReliaPro	DBU120020-B1850	12	200	2.1mm x 5.5mm F 2	2.1 x 1.8 x 1.5	Black	6'	0.4	UL/CUL	5.95	5.49	4.95	4.49	
158043	ReliaPro	DBU120020E2261	12	200	2.1mm x 5.5mm right angle F 2	2.2 x 1.7 x 1.5	Black	6'	0.4	UL/CUL	5.95	5.49	4.95	4.49	
2167226	Arndt	4292A	12	200	2.5mm x 5.5mm F 2	2.3 x 2.1 x 1.6	Black	6'	0.5	UL/CSA	4.95	4.49	3.95	3.59	
2231689	Arndt	41-12-300	12	300	2.1mm x 5.5mm F 2	2.6 x 1.8 x 1.6	Black	6'	0.5	UL/CSA	5.95	5.49	4.95	4.49	
127976	ReliaPro	DCU120030-D1762	12	300	2.1mm x 5.5mm F 2	2.6 x 1.8 x 1.6	Black	6'	0.7	UL/CUL	7.95	6.95	6.25	5.95	
2227743	Arndt	MW41-1230	12	300	2.1mm x 5.5mm F 1/F 2	2.6 x 1.8 x 1.6	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	6.25	
2230301	Arndt	RAD-1200400C	12	400	2.1mm x 5.5mm F 2	2.9 x 1.9 x 1.6	Black	6'	0.7	UL/CUL	7.95	6.95	6.25	5.49	
114825	ReliaPro	DCU120050D4740	12	500	Stripped/tinned	2.5 x 2.0 x 1.7	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
2227840	DVE	DV-1250	12	500	2.1mm x 5.5mm F 2	2.3 x 1.9 x 1.6	Black	12'	0.6	UL/CSA	6.95	5.95	5.49	4.95	
2227858	Arndt	L4D-120050R	12	500	2.1mm x 5.5mm F 2	2.3 x 1.9 x 1.6	Black	6'	0.6	UL/CUL	5.95	5.39	4.79	4.29	
2228893	CUI	DPD120050-P5	12	500	2.1mm x 5.5mm F 2	2.3 x 1.9 x 1.6	Black	6'	0.6	UL/CSA	6.95	5.95	5.49	4.95	
2229781	CUI	91-54909	12	500	2.1mm x 5.5mm F 2	2.5 x 2.0 x 1.6	Black	6'	0.6	UL/CUL	6.95	6.25	5.95	4.95	
15368	ReliaPro	DCU120050-Z8693	12	500	2.1mm x 5.5mm F 1	2.5 x 1.9 x 1.6	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
102496	ReliaPro	DCU120050E8601	12	500	2.1mm x 5.5mm F 2	2.5 x 1.9 x 1.6	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	
102277	ReliaPro	DCU120050U-Z8694	12	500	2.5mm x 5.5mm F 2	2.5 x 2.1 x 1.7	Black	6'	0.6	UL/CUL	7.95	6.95	6.25	5.95	

§ Reversible polarity (±)

More AC-to-DC Wall Adapters listed on pages 91-93 & 95