

AC-to-DC Switching Table-Top Power Supplies


3 LEVELS OF SAVINGS
NAME BRANDS **HOUSE BRANDS** **SPECIAL BUY**

Jameco carries the full line of MEAN WELL Power products. For additional products visit www.Jameco.com/meanwellproducts



AC-to-DC Unregulated Linear & Regulated Switching Table-Top Power Supplies

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call 1-800-831-4242 for details.



See page 101 for International Power Cords

Part No.	Manufacturer	Product No.	Output Rating Volts (VDC)/ Current (A)	Output Connector ID x OD/F = female; M = male; Polarity ◆	Input VAC@Hz	Output Power (W)	LED Ind.	Size (L" x W" x H")	Cords* (DC/AC)	Wt. (lbs.)	Agency Approvals	Pricing		
												1	10	
2-Wire AC Input – Unregulated Linear Table-Top													* Web Code: TBE	
2231451	ENG	3A-122DU12	+12/1	2.1mm x 5.5mm F 2	100-120@50/60	12	No	2.9 x 1.8 x 1.0	6/2'	0.3	UL/CUL	\$9.95	\$8.95	
140880	ReliaPro	DC1215ST	+12/1.5	Stripped/tinned	120@60	18	No	3.1 x 2.1 x 1.9	6/6'	1.5	UL	11.95	10.95	
2234484	ReliaPro	EDU120150RA222	+12/1.5	2.5mm x 5.5mm F 2	120@60	18	No	3.1 x 2.1 x 1.9	6/6'	1.4	—	12.95	11.95	
143722	ReliaPro	DC1220F5	+12/2.0	2.5mm x 5.5mm F 2	120@60	24	No	3.8 x 2.8 x 2.3	6/6'	2.2	UL/CUL	15.95	14.49	
2197898	Arndt	MKD66123400	+12/3.4	5-pin DIN M	120@60	40	No	5.1 x 3.6 x 2.6	6/6'	3.0	UL/CUL	9.95	8.95	
2099569	Arndt	57-1607-U4D	+5/4/0.7	2.5mm x 5.5mm F 2	120@60	19	No	3.6 x 2.7 x 3.6	6/6'	1.3	UL	4.95	4.49	
139096	ReliaPro	EHU240120	+24/1.2	2.1mm x 5.5mm F 2	120@60	29	No	4.4 x 3.1 x 2.6	6/6'	2.5	—	13.95	12.95	
2197572	ReliaPro	EHU240200	+24/2.0	2.1mm x 5.5mm F 2	120@60	48	No	4.4 x 3.1 x 2.6	6/6'	2.5	—	14.95	13.49	
2-Wire AC Input – Regulated Switching Table-Top – Single Output													* Web Code: TTZ	
2179577	Delta	ADP-12GB	+5/2.5	2.5mm x 5.5mm F 2	100-240@50-60	12	No	3.4 x 2.2 x 1.2	6/6'	0.5	UL/CUL	\$5.95	\$5.39	
2202870	Arndt	EADP-20NB	+5/4.0	2.1mm x 5.5mm F 2	100-120@50-60	20	No	4.4 x 2.1 x 1.3	6/4'	0.7	UL/CUL/CEC	9.95	8.95	
2202626	Arndt	PS-2.1-5-4DAC	+5/4.0	2.1mm x 5.5mm F 2	100-120@50-60	20	No	4.4 x 2.1 x 1.3	6/6'	0.7	UL/CUL/CEC	9.95	8.95	
2203848	Arndt	G32DD-050400-A†	+5/4.0	2.1mm x 5.5mm F 2	100-120@50-60	20	No	4.0 x 2.2 x 1.3	6/6'	0.8	UL/CUL	11.95	10.95	
2203821	Arndt	AD8048	+5/4.0	2.5mm x 5.5mm F 2	100-240@50-60	20	No	4.7 x 2.3 x 1.2	6/6'	0.8	UL/CUL	10.95	9.95	
2234249	Arndt	FY0506000	+5/6	2.5mm x 5.5mm F 2	100-240@50/60	30	No	4.6 x 2.0 x 1.2	4/6'	0.7	UL/CUL/TUV/CE	13.95	12.95	
2231435	Arndt	094-0224-000	+9/1.1	2.1mm x 5.5mm F 2	100-240@50/60	10	No	3.3 x 2.2 x 1.0	6/1'	0.4	UL/CUL/TUV/CE	9.95	8.95	
2227381	Delta	EADP-24MB	+12/2.0	2.5mm x 5.5mm F 2	100-240@50-60	24	No	4.5 x 1.9 x 1.2	6/1'	0.4	UL/CUL	10.95	9.95	
2188570	Arndt	MPGS-U0241202000D2	+12/2.0	2.5mm x 5.5mm F 2	100-240@50-60	24	No	4.2 x 1.7 x 1.2	6/6'	0.5	UL/CUL/FCC	10.95	9.95	
2224075	Arndt	HK-HA-U12-L†	+12/2.5	2.1mm x 5.5mm F 2	100-120@50-60	30	Yes	4.3 x 1.7 x 1.2	6/6'	0.8	UL/CUL/CEC	9.95	8.95	
2236754	Arndt	PS-2.1-12-3-DC-S1	+12/3.0	2.1mm x 5.5mm F 2	100-120@50/60	36	No	4.4 x 2.1 x 1.3	6/6'	0.8	UL/CUL	10.95	9.95	
2227401	Arndt	ADA017	+12/3.0	2.1mm x 5.5mm F 2	100-240@50-60	36	No	5.1 x 2.2 x 1.2	6/1'	0.6	UL/CUL	10.95	9.95	
2230168	Arndt	EADP-36FB	+12/3.0	2.1mm x 5.5mm F 2	100-240@50-60	36	No	5.3 x 2.4 x 1.4	3/1'	0.6	UL/CUL	10.95	9.95	
2167445	ReliaPro	K36V120300E2	+12/3.0	2.1mm x 5.5mm F 2	100-240@50-60	36	No	3.6 x 1.6 x 1.1	5/1'	0.4	UL/CUL/CE/CSA	14.95	13.49	
2205456	Arndt	AD7212A	+12/5.0	2.1mm x 5.5mm F 2	100-240@50-60	60	Yes	4.2 x 2.4 x 1.2	7/1'	0.7	UL/CUL/TUV/CE	12.95	11.95	
2214230	MEAN WELL	GSM60B12-PIJ	+12/5.0	2.1mm x 5.5mm F 2	80-264@47-63	60	Yes	4.9 x 2.0 x 1.2	3/1'	0.7	UL/CUL/TUV/CE	20.70	17.35	
1940547	MEAN WELL	GS25B24-P1J	+24/1.04	2.1mm x 5.5mm F 2	80-264@47-63	25	Yes	3.1 x 2.1 x 1.3	6/1'	0.5	UL/CUL/TUV/CE	13.95	12.95	
1707139	MEAN WELL	ES25B48-P1J	+48/0.52	2.1mm x 5.5mm F 2	90-264@47-63	25	Yes	3.1 x 2.1 x 1.3	6/1'	0.4	UL/CUL/TUV/CE	10.95	9.95	
* 3-9V Web Code: TTF													* 12-14V Web Code: TTW	
196218	GlobTek	GT-21089-1305T3	+5/2.0	2.1mm x 5.5mm F 2	120-240@50-60	10	No	3.4 x 1.9 x 1.3	6/2'	0.4	UL/CUL/TUV/CE	\$17.95	\$15.95	
2235760	GlobTek	GT-21089-1305	+5/2.6	2.1mm x 5.5mm F 2	100-240@50-60	13	No	3.4 x 1.8 x 1.2	6/2'	0.5	UL/CUL/CE	11.95	10.95	
2227815	GlobTek	TR9CA2000LLP-YD**	+5/2.6	2.5mm x 5.5mm F 2	100-240@50-60	13	No	3.4 x 1.8 x 1.2	6/2'	0.5	UL/CUL/CE	12.95	11.95	
1940387	MEAN WELL	GS18A05-P1J	+5/3.0	2.1mm x 5.5mm F 2	90-264@47-63	15	Yes	3.7 x 2.1 x 1.4	4/2'	0.5	UL/CUL/TUV/CE	12.95	11.95	
1940571	MEAN WELL	GS25A05-P1J	+5/4.0	2.1mm x 5.5mm F 2	90-264@47-63	20	Yes	3.7 x 2.1 x 1.4	4/2'	0.5	UL/CUL/TUV/CE	13.95	12.95	
2227807	Sceptre Power	PS5050AP-LO5	+5/5.0	2.1mm x 5.5mm F 2	100-240@50-60	25	Yes	4.1 x 2.6 x 1.4	6/6'	1.1	UL/CUL/CE	15.95	14.49	
1952337	MEAN WELL	GS40A05-P1J	+5/5.0	2.1mm x 5.5mm F 2	90-264@47-63	25	Yes	4.9 x 2.0 x 1.2	4/2'	0.7	UL/CUL/TUV/CE	15.95	14.95	
2224059	Sparkle Power	AD025DGA11-J25	+5/5.0	2.5mm x 5.5mm F 2	90-264@47-63	25	Yes	4.3 x 2.0 x 1.2	4/2'	0.7	UL/CUL/TUV/CE	14.95	13.49	
2224358	MEAN WELL	GST60A05	+5/6.0	2.1mm x 5.5mm F 2	90-264@47-63	30	Yes	4.9 x 1.9 x 1.2	3/2'	0.4	UL/CUL/TUV/CE	16.20	13.49	
2144956	ReliaPro	GQ65-060330-EI	+6/3.3	2.1mm x 5.5mm F 2	90-264@47-63	20	No	3.6 x 2.0 x 1.3	6/3'	0.3	UL/TUV/CE	12.95	11.49	
2173036	Phihong	PSA18U-090	+9/2.0	2.1mm x 5.5mm F 2	90-264@47-63	18	No	3.9 x 2.2 x 1.2	5/2'	0.5	UL/CUL/TUV/CE	9.95	8.95	
1940408	MEAN WELL	GS18A09-P1J	+9/2.0	2.1mm x 5.5mm F 2	90-264@47-63	18	Yes	3.7 x 2.1 x 1.4	6/2'	0.6	UL/CUL/TUV/CE	12.95	11.95	
1954244	MEAN WELL	GS15A-3P1J	+12/1.25	2.1mm x 5.5mm F 2	90-264@47-63	15	No	3.9 x 2.3 x 1.3	6/2'	0.4	UL/CUL/TUV/CE	14.20	11.89	
2227823	Globtek	TR9CE1250-LCP-7	+12/1.25	2.5mm x 5.5mm F 2	100-240@50-60	15	No	3.4 x 1.8 x 1.2	6/2'	0.5	UL/CUL/CE	15.95	14.49	
2229491	DVE	DSA-0151D-12-2.1	+12/1.5	2.1mm x 5.5mm F 2	100-125@50-60	18	No	3.9 x 1.9 x 1.3	6/2'	0.4	UL/CSA/TUV/CE	11.95	10.95	
2229482	DVE	DSA-0151D-12-2.5	+12/1.5	2.5mm x 5.5mm F 2	100-125@50-60	18	No	3.9 x 1.9 x 1.3	6/2'	0.4	UL/CSA/TUV/CE	11.95	10.95	
1940416	MEAN WELL	GS18A12-P1JU	+12/1.5	2.1mm x 5.5mm F 2	90-264@47-63	18	Yes	3.7 x 2.1 x 1.4	6/6'	0.5	UL/CUL/TUV/CE	14.49	12.95	
1940601	MEAN WELL	GS25A12-P1JU	+12/2.08	2.1mm x 5.5mm F 2	90-264@47-63	25	Yes	3.7 x 2.1 x 1.4	4/6'	0.5	UL/CUL/TUV/CE	12.95	11.95	
2197927	ReliaPro	DZ036DL120300G	+12/3.0	2.1mm x 5.5mm F 2	100-240@50-60	36	No	4.3 x 1.9 x 1.3	6/2'	0.5	UL/CUL/CE	12.95	11.95	
2234329	ReliaPro	DZ036DL120300G-2.5	+12/3.0	2.5mm x 5.5mm F 2	100-240@50/60	36	No	4.3 x 1.9 x 1.3	6/2'	0.5	UL/CUL/CE	13.95	12.49	
2230387	Arndt	LSE0107A1240	+12/3.33	2.5mm x 5.5mm F 2	100-240@50-60	40	Yes	4.5 x 2.0 x 1.2	4/2'	0.5	UL/CUL/TUV/CE	11.95	10.95	
2224307	MEAN WELL	GST40A12-P1J#	+12/3.34	2.1mm x 5.5mm F 2	90-264@47-63	40	Yes	4.9 x 1.2 x 2.0	3.3/2'	0.6	UL/CUL/TUV/CE	14.60	12.19	

* See accessory table-top power cord chart on page 95 when AC cord needed; refer to 1, 2 or 3 in "Cords (DC/AC)" column above for correct power cord
 ** Locking connector # Level VI efficiency

† Attached cord

Continued on next page