

AC-to-DC Regulated Switching Table-Top Power Supplies

JAMECO ReliaPro MW GlobTek® AC-to-DC Regulated Switching Table-Top Power Supplies See page 101 for International Power Cords

We are happy to change any listed wall adapter or table-top power plug to overmolding on a connector of your choice for \$4.00 each. A 100 piece minimum order applies. Please call 1-800-831-4242 for details.



♦ Polarity 1 (+) (-) (-) (center negative)
Polarity 2 (-) (-) (+) (center positive)



Part No.	Manufacturer	Product No.	Output Volts (VDC)/Current (A)	Output Connector ID x OD/F = female; M = male; Polarity ♦	Input VAC@Hz	Output Power (W)	LED Ind.	Size (L" x W" x H")	Cords* (DC/AC)	Wt. (lbs.)	Agency Approvals	Pricing	
												1	10

*** 12-14V Web Code: TTW * 15-24V Web Code: TTR 3-Wire AC Input – Regulated Switching Table-Top – Single Output (Continued) * 27-54V Web Code: TTT**

1952345	MEAN WELL	GS40A12-P1J	+12/3.34	2.1mm x 5.5mm F 2	90-264@47-63	40	Yes	4.9 x 2.0 x 1.3	4/2	0.7	UL/CUL/TUV/CE	\$17.95	\$16.49
2079357	MEAN WELL	GS40A12-P1M	+12/3.34	2.5mm x 5.5mm F 2	90-264@47-63	40	Yes	4.9 x 2.0 x 1.3	4/2	0.7	UL/CUL/TUV/CE	16.95	15.49
2234661	ReliaPro	MP65-120350-E11	12/3.5	2.1mm x 5.5mm F 2	100-240 @ 50/60	42	Yes	4.7 x 2.1 x 1.2	4/2	0.6	UL/CUL/CE/GS	13.95	12.59
2265599	Globtek	TRCE4000LCP-Y	12/4.17	2.5mm x 5.5mm F 2	100-240@50/60	50	No	4.6 x 2.4 x 1.4	6/2	0.6	UL/CUL/TUV/CE	14.95	13.49
2208956	ReliaPro	KPL-060F#	+12/5.0	2.1mm x 5.5mm F 2	100-240@50-60	60	No	4.5 x 2.0 x 1.2	4/2	0.9	UL/CUL/TUV/CE	15.95	14.49
2224382	MEAN WELL	GST60A12-P1J#	+12/5.0	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 2.0 x 1.2	3.3/2	0.7	†† (See below)	16.20	13.49
1952370	MEAN WELL	GS60A12-P1J	+12/5.0	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 1.9 x 1.2	4/2	0.7	UL/CUL/TUV/CE	20.95	18.95
2218151	Net Gear	AD8180LF	+12/5.0	2.5mm x 5.5mm F 2	100-240@50-60	60	No	4.6 x 2.4 x 1.4	6/2	0.6	UL/CUL/CE	15.95	14.49
2236543	Lite-On	PA-1600-2A-LF	12/5.0	2.5mm x 5.5mm F 2	100-240 @ 50/60	60	No	5.9 x 2.1 x 1.6	6/2	0.9	UL/CUL/TUV/CE	16.95	15.49
2236447	Seasonic	SSA-0601D-12	12/5.0	2.5mm x 5.5mm F 2	100-240 @ 50/60	60	Yes	4.5 x 1.8 x 1.4	3.3/2	0.6	UL/CUL/TUV/CE	17.95	15.95
2230230	Arndt	RX-SP-5012-6	+12/6.0	2.1mm x 5.5mm F 2	100-240@50-60	72	Yes	4.7 x 2.3 x 1.4	4/4	0.6	CE/FCC	17.95	15.95
2223460	MEAN WELL	GST90A12-P1M#	+12/6.67	2.5mm x 5.5mm F 2	90-264@47-63	80	Yes	5.7 x 2.4 x 1.3	3.3/2	1.4	†† (See below)	26.60	22.19
2078291	MEAN WELL	GS90A12-P1M	+12/6.67	2.5mm x 5.5mm F 2	90-264@47-63	80	Yes	5.7 x 2.3 x 1.3	4/2	0.9	UL/CUL/TUV/CE	31.95	28.95
2129211	MEAN WELL	GS120A12-R7B	+12/8.5	4-pin DIN M	85-264@47-63	102	Yes	6.6 x 2.6 x 1.4	4/2	1.4	UL/CUL/TUV/CE	38.95	37.25
2229950	EDAC Power	EA11011H(33)#	+12/10	4-pin DIN M	100-240@50-60	120	Yes	5.4 x 2.3 x 1.3	4/2	1.0	UL/CUL/CE/CEC	49.95	45.95
2099294	MEAN WELL	GS220A12-R7B	+12/15	4-pin DIN M	90-264/127-370@47-63	180	Yes	8.3 x 3.4 x 1.8	3.3/2	1.0	UL/CUL/TUV/CE	73.95	64.49
1940619	MEAN WELL	GS25A15-P1J	+15/1.66	2.1mm x 5.5mm F 2	90-264@47-63	25	Yes	3.7 x 2.1 x 1.4	6/2	0.5	UL/CUL/TUV/CE	12.95	11.95
2171559	MEAN WELL	GS40A15-P1JU	+15/2.67	2.1mm x 5.5mm F 2	90-264@47-63	40	Yes	4.9 x 2.0 x 1.2	3.3/6	0.6	UL/CUL/TUV/CE	16.95	15.49
2224391	MEAN WELL	GST60A15-P1J#	+15/4.0	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 2.0 x 1.3	3.3/2	0.7	UL/CUL/TUV/CB/CE/CCC/FC	16.20	13.49
1954295	MEAN WELL	GS60A15-P1J	+15/4.0	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 2.0 x 1.2	4/2	0.7	UL/CUL/TUV/CE	20.95	18.95
2078320	MEAN WELL	GS90A15-P1M	+15/6.0	2.5mm x 5.5mm F 2	90-264@47-63	90	Yes	5.7 x 2.3 x 1.3	3.3/2	0.8	UL/CUL/TUV/CE	28.95	25.95
2154951	MEAN WELL	GS60A18-P1JU	+18/3.33	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 2.0 x 1.2	6/6	0.8	UL/CUL/TUV/CE	18.95	16.95
2224331	MEAN WELL	GST40A24-P1J#	+24/1.67	2.1mm x 5.5mm F 2	90-264@47-63	40	Yes	4.9 x 2.0 x 1.2	6/2	0.6	UL/CUL/TUV/CB/CE/CCC/FC	14.60	12.19
2223494	MEAN WELL	GST90A24-P1M#	+24/1.67	2.5mm x 5.5mm F 2	90-264@47-63	40.1	Yes	5.7 x 2.4 x 1.3	3.9/2	0.9	UL/CUL/TUV/CB/CE/CCC/FC	26.60	22.19
1940635	MEAN WELL	GS25A24-P1JU	+24/1.04	2.1mm x 5.5mm F 2	90-264@47-63	25	Yes	3.7 x 2.1 x 1.4	6/6	0.5	UL/CUL/TUV/CE	12.95	11.95
2197919	ReliaPro	DZ036DL240150G	+24/1.5	2.1mm x 5.5mm F 2	100-240@50-60	36	No	4.3 x 1.9 x 1.3	6/2	0.5	UL/CUL/CE	11.95	10.95
1952353	MEAN WELL	GS40A24-P1J	+24/1.67	2.1mm x 5.5mm F 2	90-264@47-63	40	Yes	4.9 x 2.0 x 1.2	6/2	0.7	UL/CUL/TUV/CE	17.95	16.49
2229984	ReliaPro	KPL-060M-2.1-VI#	+24/2.5	2.1mm x 5.5mm F 2	100-240@50-60	60	Yes	4.5 x 2.0 x 1.2	4/2	0.9	UL/CUL/TUV/CE	14.95	13.95
2224411	MEAN WELL	GST60A24-P1J#	+24/2.5	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 1.2 x 2.0	6/2	0.7	UL/CUL/TUV/CE	16.20	13.49
1952214	MEAN WELL	GS60A24-P1J	+24/2.5	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 2.0 x 1.3	6/2	0.7	UL/CUL/TUV/CE	20.95	18.95
2229992	ReliaPro	KPL-060M-2.5-VI#	+24/2.5	2.5mm x 5.5mm F 2	100-240@50-60	60	Yes	4.8 x 2.4 x 1.4	4/2	0.9	UL/CUL/TUV/CE	17.95	16.49
2078338	MEAN WELL	GS90A24-P1M	+24/3.75	2.5mm x 5.5mm F 2	90-264@47-63	90	Yes	5.9 x 2.3 x 1.2	4/2	0.9	UL/CUL/TUV/CE	28.95	25.95
2208892	MEAN WELL	GS120A24-HQU \$	+24/5.0	2.5mm x 5.5mm F 2	90-264@47-63	120	Yes	6.6 x 2.6 x 1.4	4/2	1.4	UL/CUL/TUV/CE	32.95	29.95
2223646	MEAN WELL	GST120A24-P1M#	+24/5.0	2.5mm x 5.5mm F 2	85-264@47-63	120	Yes	6.6 x 2.7 x 1.4	3.9/2	1.4	UL/CUL/TUV/CB/CE/CCC/FC	38.90	38.89
2135208	MEAN WELL	GS120A24-P1M	+24/5.0	2.5mm x 5.5mm F 2	85-264@47-63	120	Yes	6.6 x 2.6 x 1.4	4/2	1.4	UL/CUL/TUV/CE	39.95	35.95
2223611	MEAN WELL	GST120A24-R7B#	+24/5.0	4-pin DIN M	85-264@47-63	120	Yes	6.6 x 2.7 x 1.4	3.9/2	1.4	UL/CUL/TUV/CB/CE/CCC/FC	38.90	38.89
2122212	MEAN WELL	GS160A24-R7B	+24/6.67	4-pin DIN M	85-264@47-63	160	Yes	6.9 x 2.8 x 1.4	4/2	1.5	UL/CUL/TUV/CE	51.95	45.95
2226505	MEAN WELL	GST220A24-R7B#	+24/9.2	4-pin DIN M	85-264@47-63	220.8	Yes	8.3 x 3.4 x 1.8	3.3/2	2.2	UL/CUL/TUV/CB/CE/CCC/FC	66.60	55.89
2099286	MEAN WELL	GS220A24-R7B	+24/9.2	4-pin DIN M	90-264@47-63	220	Yes	8.3 x 3.4 x 1.8	3.3/2	2.4	UL/CUL/TUV/CE	79.95	73.95
2202562	Phihong	PSA18U-480	+48/0.38	2.5mm x 5.5mm F 2†	100-240@50-60	18	No	3.9 x 2.1 x 1.2	6/2	0.5	UL/CUL/CE	4.95	4.49
2228931	FSP	FSP025-1AD207A	+48/0.52	2.5mm x 5.5mm F 2	100-240@50-60	25	No	3.3 x 2.0 x 1.3	6/2	0.4	UL/CUL/CE	9.95	8.95
1952396	MEAN WELL	GS60A48-P1JU	+48/1.25	2.1mm x 5.5mm F 2	90-264@47-63	60	Yes	4.9 x 2.0 x 1.2	6/6	0.7	UL/CUL/TUV/CE	18.95	16.95

3-Wire AC Input – Regulated Switching Table-Top – Double & Triple Output * Web Code: TTN

196270	ReliaPro	PSU25A13	+5/2.5, +12/1.0	4-pin mini DIN M	100-240@47-63	25	No	4.2 x 2.6 x 1.4	6/6	1.2	UL/CUL/TUV/CE	\$31.95	\$28.95
2230740	ReliaPro	GPSN25A-13#	+5/2.5, +12/1.5	4-pin mini DIN M	100-240@50-60	30	No	4.2 x 2.6 x 1.4	6/6	1.2	UL/CUL/TUV/CE	34.95	31.49
2229511	Ault	SC200	+5/4.0, +12/1.0	5-pin DIN M	100-240@50-60	32	No	5.0 x 3.0 x 1.6	6/2	1.2	UL/CSA/CE/TUV	19.95	17.95
221720	MEAN WELL	P25A14E-R1BU	+5/2.5, +15/0.3 -15/0.3	5-pin DIN M	90-264@47-63	25	Yes	4.3 x 2.6 x 1.4	6/6	0.8	UL/CUL/TUV/CE	33.95	30.95
190960	MEAN WELL	P25A13D-R1B	+5/2.5, +12/0.8 -12/0.3	5-pin DIN M	90-264@47-63	26	Yes	4.1 x 2.6 x 1.4	6/2	1.1	CUL/TUV/CE	32.95	29.95
237367	MEAN WELL	P50A14E-R1B	+5/4.0, +15/1.5 -15/0.5	5-pin DIN M	90-264@47-63	42	Yes	5.8 x 3.0 x 1.7	4/2	1.2	UL/CUL/TUV/CE	54.95	49.95
2217844	Arndt	T40-9312A	+5/5.0, +12/1.2 -12/0.3	6-pin DIN M	90-264@47-63	43	No	6.0 x 3.3 x 1.9	4/2	1.2	UL/CUL/TUV/CE	19.95	17.95
221702	MEAN WELL	P50A13D-R1BU	+5/4.0, +12/2.0 -12/0.5	5-pin DIN M	90-264@47-63	50	Yes	5.7 x 3.0 x 1.7	4/6	1.5	UL/CUL/TUV/CE	49.95	44.95
2250951	MEAN WELL	GP50A13D-R1B#	+5/4.0, +12/2.0 -12/0.5	5-pin DIN M	90-264@47-63	50	Yes	5.7 x 3.0 x 1.7	4/2	1.5	UL/CUL/TUV/CE	39.60	33.65

* See accessory table-top power cord chart on page 95 when AC cord needed; refer to 1, 2 or 3 in "Cords (DC/AC)" column above for correct power cord

† Right angle †† UL/CUL/TUV/BSMI/CCC/FCC/CE \$ HQU = C Tick Austria approval # Level VI efficiency CEC

*For additional products, availability and specifications visit [Jameco.com](http://www.Jameco.com) and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com