

Transformers, Wall Adapters & Power Cables

EMERSON 5VDC @ 200mA Wall USB Adapter

- Works with digital camera, cell phones, PDA, MP3 and other USB devices
- LED indicator
- TUV/FCC approved
- Output voltage: 5VDC @ 200mA
- Input volt.: 100-240VAC @ 50/60Hz
- Size: 2.5"H x 1.5"W x 0.8"D

Part No.	Mfr. Part No.	1	10	50	100
2138636	SW013US-0500020US	\$2.95	\$2.59	\$2.25	\$1.95



5VDC @ 1 & 2A USB Wall Adapters

* Web Code: WFV

- Works with digital camera, cell phones, PDA, MP3 and other USB devices
- Input voltage: 100-240VAC @ 50/60Hz
- Flip up prongs
- UL/FCC approved

Part No.	Mfr. Part No.	Output Curr.	Size (H" x W" x D")	1	10	50	100
2210888	1128	1.0A	2.6 x 1.3 x 1.5	\$3.95	\$3.49	\$2.95	\$2.59
2227786	XA1005-2U*	2.0A	2.7 x 1.7 x 1.0	4.95	4.49	3.95	2.49
2244359	XS-0502/00FU	2.1A	2.0 x 1.9 x 1.1	6.95	6.25	5.59	4.95



JAMECO ValuePro 320VA Variable AC Transformer

- Input voltage: 110VAC @ 50-60Hz
- Max. current: 2.5A
- Matching input/output terminals: P/N 103668 and 109112 (disconnect .25" solderless terminals), see Web
- Panel mount
- One-year warranty
- Shaft length: 0.5"

Includes: 3 disconnect .25" solderless terminals

Part No.	Cross Ref. No.	Weight	Size (Dia. x H)	1	5	25
149324	PSV-203-R	2.5 lbs.	2.8" x 2.1"	\$64.95	\$59.95	\$54.95



JAMECO ValuePro Transformer Isolation

- Output: 120VAC/4A, 60Hz
- Input: 110VAC 60Hz, 1800VA
- Primary: Current: 14 Amps fuse
- Direct AC#1: 110VAC 60Hz, 900VA
- Direct AC#2: 110VAC 60Hz, 900VA
- Secondary: Current: 7 Amps fuse
- Isolated AC#1: 110VAC 60Hz, 450VA
- Isolated AC#2: 110VAC 60Hz, 450VA
- Dimension: 5"L x 6"W x 9"H

Part No.	Cross Ref. No.	1	5	25
2214336	GRP-1200	\$99.95	\$89.95	\$84.95



JAMECO ValuePro 500 to 2000VA Variable Transformers

Variable transformers are suitable for changing the brightness of a room, speeds of electric motor, or other testing systems in diverse conditions.

- Input: 110VAC or 220VAC
- Power: 500, 1000 or 2000VA
- Output: 0-240VAC
- Banana/screw input terminals
- Universal US/European output plugs
- Lighted on/off power switch

121276



Part No.	Fuse	Size (W" x D" x H")	Wt. (lbs.)
121276	3A/250V (P/N 69439)	5.3 x 7.3 x 7.0	10.4
129008	5A/250V	9.4 x 6.5 x 7.7	14.8
152582	10A/250V (P/N 69462)	9.0 x 7.0 x 7.7	19.8

Part No.	Description	1	5
121276	500VA transformer	\$129.95	\$119.95
129008	1000VA transformer	169.95	154.95
152582	2000VA transformer	224.95	199.95

* Variable Transformers — Enter Web Code MAR

* AC Power Cords — Enter Web Code UBF

JAMECO ValuePro 300VA Isolation Transformer 120VAC to 120VAC

- Output voltage: 120VAC @ 2.5A (isolated)
- Input connector: 5.5" cord with 2-prong plug
- Input voltage: 120VAC @ 60Hz
- Size: 3.2"W x 4.6"D x 4.2"H
- Weight: 7.0 lbs.

Part No.	Cross Ref. No.	1	5	25
181315	ITR300	\$49.95	\$44.95	\$39.95



JAMECO ValuePro DC Cords with Pigtail — 6' length

- 18-24 AWG
- Color: black

Part No.	Cross Ref. No.	Fig.	AWG	Type	ID x OD x L (mm)	1	10	100
2229731	DC-168	1	18	Plug	2.1 x 5.5 x 12	\$2.59	\$2.35	\$2.15
2229706	DC-169	1	18	Plug	2.5 x 5.5 x 12	2.59	2.35	2.15
2229722	DC-173	2	18	Jack	2.1 x 5.5 x 12	2.59	2.35	2.15
2229714	DC-175	2	18	Jack	2.5 x 5.5 x 12	2.95	2.59	2.29
2231401	DC20AWG-RA-2.5	3	20	Plug	2.5 x 5.5 x 12	1.59	1.45	1.29
2096763	DCCORD2.1	1	24	Plug	2.1 x 5.5 x 12	1.95	1.75	1.59
2096771	DCCORD2.5	1	24	Plug	2.5 x 5.5 x 12	1.95	1.75	1.59
2114600	6FT#245.5X2.1	2	24	Jack	2.1 x 5.5 x 12	1.95	1.75	1.59
2114597	6FT#245.5X2.5	2	24	Jack	2.5 x 5.5 x 12	1.95	1.75	1.59
2230791	DC-6-2.1-CUT	1	24	Plug	2.1 x 5.5 x 10	1.49	1.35	1.19
2231380	DC-6-2.5-CUT	1	24	Plug	2.5 x 5.5 x 10	1.49	1.35	1.19

* Web Code: MFP



JAMECO ValuePro DC Extension and Splitter (Y) Power Cables

- 18 AWG/26AWG
- Color: black

Part No.	Mfr.	Cross Ref. No.	Description (Barrel)	ID x OD (mm)	Cable Lgth	1	10	100
2099147	ValuePro	DCEXTCORD2.1-3FT	2.1 F x 2.1 M	2.1	3'	\$2.49	\$2.25	\$1.95
2099121	ValuePro	DCEXTCORD2.1-6FT	2.1 F x 2.1 M	2.1	6'	2.95	2.59	2.25
2099155	ValuePro	DCEXTCORD2.5-3FT	2.5 F x 2.5 M	2.5	3'	2.49	2.25	1.95
2099139	ValuePro	DCEXTCORD2.5-6FT	2.5 F x 2.5 M	2.5	6'	2.95	2.59	2.25
2230192	Arndt	EN-DCM-2*	2.1M to (2) 2.1F	2.1	9'	3.95	3.59	2.95
2230205	Arndt	2505	2.1M to (5) 2.1F	2.1	13'	4.95	4.49	3.95
2230213	Arndt	2508	2.1M to (8) 2.1F	2.1	16'	6.95	6.25	5.59

*26 AWG



PC Mount Audio Transformer

- Impedance matching: 10% over frequency range
- 6-pin PC mount
- Output: 100mW
- Impedance (Ω): 600CT/600CT
- Primary DC Unbalance: 15mA
- Dimensions: 13/16"W x 9/32"D x 5/8"H

Part No.	Mfr. Part No.	1	10	100
630459	TY-145P	\$5.95	\$5.49	\$4.49



EMI Suppression Cores with Case

Reduce Electromagnetic Interference (EMI) with a snap of these suppression cores around a power cord or data cord. Easy to install and an affordable way to reduce EMI without redesigning your product.

- Impedance at 100MHz between 75-225Ω min.
- Color: black

Part No.	InDia.	OutDia.	Length	1	10	100
218174	.20"	.64"	1.15"	\$1.25	\$.99	\$.75
217842	.34"	.78"	1.40"	1.49	1.25	.99
2202600	.38"	.87"	1.34"	.99	.85	.69
2081810	.38"	1.0"	0.65"	1.25	.99	.75



JAMECO ValuePro Automobile Fused Power Plugs with Cords

- Accepts .25" x 1.25" fuse

- 115002: Screw assembly with strain relief (no cord)
- 124760: 3' cord with pigtail
- 2229773: 3' cord with 2.1mm x 5.5mm connector
- 2234396: Screw assembly with strain relief (no cord)

Part No.	Fuse	1	10	100
2229773	2A/250VAC	\$2.75	\$2.49	\$2.25
124760	3A/250VAC	2.49	2.25	1.95
115002	5A/250VAC	2.25	1.95	1.75
2234396	10A/250VAC	2.95	2.75	2.49



REGULATED SWITCHING WALL ADAPTERS

Part No.	Voltage @ Current	Page	Price
2232825	12V @ 1.0A	93	\$8.95
2233983	12V @ 1.0A level 6 efficiency	93	10.95



*For additional products, availability and specifications visit Jameco.com and enter the Web Code in the product search box



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com