



[Click Here to Request a Large Quantity Quote](#)

[AC-to-AC-Wall Transformers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Output Voltage (VAC)	Output Current (A)	Power Rating (VA)	Input Voltage (VAC)	Primary Frequency	Output Connector Type	Output Connector Diameters	Primary Side Connection	Secondary Side Connection	Output Cord Length (feet)	Price 1
2230651	Jameco Reliapro	ABU050050R	5	0.5	2.5	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$6.95
2236834	Jameco Reliapro	ACU060100R	6	1	6	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$8.95
2236842	Jameco Reliapro	ADU060200R	6	2	12	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
100061	Jameco Reliapro	ACU090050A4542	9	0.5	4.5	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$9.95
2289183	Arndt	A9500	9	0.5	12	120	62 Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug		\$8.95
102234	Jameco Reliapro	ACU090100	9	1	9	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
2270815	Jameco Reliapro	GPU480901000WAOO	9	1	9	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$11.95
157041	Jameco Reliapro	ACU090100E8942	9	1	9	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
2231574	Jameco Reliapro	ACU090100-3.5M	9	1	9	120	50-60Hz	Male plug	3.5mm	NEMA15-P	3.5mm Plug	6	\$10.95
2227444	Jameco Reliapro	ADU090150	9	1.5	13.5	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
112336	Jameco Reliapro	ADU090150A2231	9	1.5	13.5	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
2234222	Arndt	A35100300	10	0.3	3	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$3.95
2272999	Condor Power Supplies Inc.	A9300-04	12	0.2	6	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$5.95
101258	Jameco Reliapro	ACU120050F4031	12	0.5	6	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$9.95

Jameco Part #	Manufacturer	Manufacturer Part #	Output Voltage (VAC)	Output Current (A)	Power Rating (VA)	Input Voltage (VAC)	Primary Frequency	Output Connector Type	Output Connector Diameters	Primary Side Connection	Secondary Side Connection	Output Cord Length (feet)	Price 1
2179614	Jameco Reliapro	ACU120050R	12	0.5	6	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$9.95
2234214	Arndt	AC9084-BK01	12	0.83	9.96	120	50-60Hz	3.5mm Male Plug	3.5mm	NEMA15-P	3.5mm Plug	10	\$5.95
10428	Jameco Reliapro	ACU120100Z9121	12	1	12	120	50-60Hz	3.5mm Male Plug	3.5mm	NEMA15-P	3.5mm Plug	6	\$10.95
10081	Jameco Reliapro	ACU120100	12	1	12	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
2270823	Jameco Reliapro	GPU481201000WAOO	12	1	12	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$11.95
100167	Jameco Reliapro	ACU120100D0531	12	1	12	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
167151	Jameco Reliapro	ADU120150E1012	12	1.5	18	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$12.95
307838	Jameco Reliapro	ADU120160H4120	12	1.6	19.2	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$12.95
2236455	Jameco Reliapro	A1220NNNL	12	1.67	20	120	50-60Hz	Screw terminals	Screw terminals	NEMA15-P	Screw Terminals		\$10.49
2197581	Jameco Reliapro	GPU481202000WAOO	12	2	24	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$14.95
2227604	Jameco Reliapro	GPU481202000WA00-2.5	12	2	24	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$14.95
171408	Jameco Reliapro	ACU140050C6951	14	0.5	7	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$9.95
318684	Jameco Reliapro	ACU140085H5780	14	0.85	11.9	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm right angle	NEMA15-P	DC Power Plug	6	\$9.95
2271271	Jameco Reliapro	ACU150050R	15	0.5	7.5	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
2271279	Jameco Reliapro	ADU150100R	15	1	15	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$11.95
100108	Jameco Reliapro	ADU160100Z5401	16	1	16	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$12.95
2227612	Jameco Reliapro	ADU160100-2.5	16	1	16	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$12.95

Jameco Part #	Manufacturer	Manufacturer Part #	Output Voltage (VAC)	Output Current (A)	Power Rating (VA)	Input Voltage (VAC)	Primary Frequency	Output Connector Type	Output Connector Diameters	Primary Side Connection	Secondary Side Connection	Output Cord Length (feet)	Price 1
2271087	Jameco Reliapro	AFU160200R-2.1	16	2	32	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$15.95
2271095	Jameco Reliapro	AFU160200R-2.5	16	2	32	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$15.95
2230635	Jameco Reliapro	MGT1640	16	2.4	38.4	120	50-60Hz	Screw terminals	Screw terminals	NEMA15-P	Screw Terminals		\$9.49
2231591	Jameco Reliapro	ACU180050	18	0.5	9	120	50-60Hz	Wires		NEMA15-P	Wires	6	\$7.95
121216	Jameco Reliapro	ADU180100	18	1	18	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$11.95
2227621	Jameco Reliapro	ADU180100-2.5	18	1	18	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$11.95
2179622	Jameco Reliapro	AFU180200	18	2	36	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$14.95
2271103	Jameco Reliapro	AFU180200R	18	2	36	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$14.95
87581	Jameco Reliapro	ADU240050	24	0.5	12	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$9.95
2270831	Jameco Reliapro	GPU412400500WAOO	24	0.5	12	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$11.95
2234193	Jameco Reliapro	ADU240050-2.5	24	0.5	12	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$10.95
10102	Jameco Reliapro	ADU240100E0461	24	1	24	120	50-60Hz	3.5mm Male Plug	3.5mm	NEMA15-P	3.5mm Plug	6	\$12.95
140599	Jameco Reliapro	ADU240100D5531	24	1	24	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$12.95
2271111	Jameco Reliapro	ADU240100R	24	1	24	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$12.95
2100195	Jameco Reliapro	GPU572401500WA00	24	1.5	36	120	50-60Hz	Female barrel plug	2.1mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$13.95
2227639	Jameco Reliapro	GPU572401500WA00-2.5	24	1.5	36	120	50-60Hz	Female barrel plug	2.5mm x 5.5mm	NEMA15-P	DC Power Plug	6	\$13.95
2230627	Jameco Reliapro	MGT2440	24	1.6	38.4	120	50-60Hz	Screw terminals	Screw terminals	NEMA15-P	Screw Terminals		\$12.95

