



[Click Here to Request a Large Quantity Quote](#)

[Axial Leaded Ceramic Capacitors](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance Value	Voltage	Tolerance	Dielectric	Construction	Price 1
<a href="#">2229790</a>	AVX	SA102A150JAA	0.000015 uF	200	5%	C0G (NP0)	Axial	\$0.25
<a href="#">2229802</a>	AVX	SA101A181KAA	0.000180 uF	100	10%	C0G (NP0)	Axial	\$0.25
<a href="#">2229829</a>	AVX	SA101C471KAA	0.00047 uF	100	10%	X7R	Axial	\$0.25
<a href="#">1069763</a>	Jameco Valuepro	314J222K100VATTQY22	0.0022 uF	100	10%	X7R	Axial	\$0.25
<a href="#">2229837</a>	AVX	SA101C472KAA	0.0047 uF	100	10%	X7R	Axial	\$0.25
<a href="#">546290</a>	Jameco Valuepro	SA105C103KAA	0.01 uF	50	10%	X7R	Axial	\$0.25
<a href="#">2229811</a>	AVX	SA205C473KAA	0.047 uF	50	10%	X7R	Axial	\$0.25
<a href="#">536542</a>	Jameco Valuepro	P20R104K5-F	0.1 uF	50	10%	X7R	Axial	\$0.25
<a href="#">2296367</a>	AVX	SA105E104MAA	0.1 uF	50	20%	Z5U	Axial	\$0.25