



[Click Here to Request a Large Quantity Quote](#)

Blowers-DC

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage Rating	Height	Width	Depth	Air Flow (CFM)	Bearing	Current Rating	Agency Approvals	Noise (dBA)	Termination	Price 1
2315303	ADDA Corporation	AB0312HB-GA6	12 VDC	30 mm	30 mm	10 mm	1.2	Ball	100 mA	UL, CUL, TUV, CE	33	5.5" Wires (3), speed sensor	\$19.95
2315335	ADDA Corporation	AB3512HB-GA6	12 VDC	35 mm	35 mm	10 mm	1.52	Ball	120 mA	UL, CUL, TUV, CE	30.7	5.5" Wires (3), speed sensor	\$15.95
2233561	ADDA Corporation	AB3512MX-QB0	12 VDC	35 mm	35 mm	7 mm	1.11	Hypro	120 mA	UL, CUL, TUV, CE	23	5.5" Wires	\$14.95
2315863	ADDA Corporation	AB4512HX-QA0	12 VDC	45 mm	45 mm	7 mm	2.1	Hypro	100 mA	UL, CUL, TUV, CE	31.2	5.5" Wires	\$15.95
2303631	Stinger Electronics	SGJ78	12 VDC	46 mm	46 mm	210 mm	54	N/A	220 mA	UL	37	4" Wires	\$19.95
2315807	ADDA Corporation	AB05012MX15100	12 VDC	50 mm	50 mm	15 mm	4.9	Hypro	130 mA	UL, CUL, TUV, CE	38.8	12" Wires	\$12.95
2133843	ADDA Corporation	AB5012MB-C03	12 VDC	50 mm	50 mm	20 mm	4.6	Ball	90 mA	UL, CUL, TUV, CE	32.5	12" Wires (3)	\$14.95
2315679	ADDA Corporation	AB07512DB300100	12 VDC	75 mm	75 mm	30 mm	5.31	Ball	80 mA	UL, CUL, TUV, CE	26.5	12" Wires	\$11.95
2099446	ADDA Corporation	AD7512LB(2A)	12 VDC	75 mm	75 mm	30 mm	6.9	Ball	110 mA	UL, CUL, TUV, CE	29	15" Wires	\$9.95
2315687	ADDA Corporation	AB07512MB300200	12 VDC	75 mm	75 mm	30 mm	7.78	Ball	150 mA	UL, CUL, TUV, CE	34.9	12" Wires (3), speed sensor	\$11.95
2315399	ADDA Corporation	AD7512MB(NBA)	12 VDC	75 mm	75 mm	30 mm	7.8	Ball	150 mA	UL, CUL, TUV, CE	34.9	19" Wires	\$9.95
2233035	ADDA Corporation	AD7512MS	12 VDC	75 mm	75 mm	30 mm	7.8	Sleeve	200 mA	UL, CUL, CE	34.9	15" Wires	\$7.95
2320263	ADDA Corporation	AD7512HX	12 VDC	75 mm	75 mm	30 mm	13	Hypro	520 mA	UL, CUL, TUV, CE	38.5	12" Wires	\$13.95
2315311	ADDA Corporation	AB0912MB-Z01(N)	12 VDC	94 mm	94 mm	33 mm	31.4	Ball	90 mA	UL, CUL, TUV, CE	51.5	12" Wires	\$11.95
2315319	ADDA Corporation	AB1224HB-Y01	24 VDC	120 mm	120 mm	32 mm	31.4	Ball	49 mA	UL, CUL, TUV, CE	55	12" Wires	\$19.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage Rating	Height	Width	Depth	Air Flow (CFM)	Bearing	Current Rating	Agency Approvals	Noise (dBA)	Termination	Price 1
2320247	ADDA Corporation	AD7524MB(NBA)	24 VDC	75 mm	75 mm	30 mm	7.8	Ball	140 mA	UL, CUL, TUV, CE	35	7" Wires w/ conn.	\$11.95
2316151	ADDA Corporation	AB07524DB300300(21)	24 VDC	75 mm	75 mm	30 mm	8.7	Ball	90 mA	UL, CUL, TUV, CE	33	12" Wires (3), FG	\$110.95
2315519	ADDA Corporation	AD7524HB(NBA)	24 VDC	75 mm	75 mm	30 mm	9.11	Hypro	160 mA	UL, CUL, TUV, CE	38.5	12" Wires	\$10.95
2306703	NMB Technologies	FAL5F24LH	24 VDC	76 mm	76 mm	28 mm	10.6	Hydro Wave	100 mA	UL, CSA	36	12" Wires	\$7.95
2302279	ADDA Corporation	AB09424LB330300	24 VDC	94 mm	94 mm	33 mm	28	Dual Ball	300 mA	CE	48.4	11" Wires (4), speed sensor + alarm	\$14.95
2313359	NMB Technologies	09533GA-24M-AT	24 VDC	94 mm	94 mm	33 mm	28.6	Ball	490 mA	UL, CUL, VDE, CE	54.5	8" Wires (3), speed sensor	\$11.95
2306607	Orion Fans	ODB9733-24HB	24 VDC	97 mm	97 mm	35 mm	33	Ball	350 mA	UL, CUL	56	12" Wires	\$14.95
2235250	ADDA Corporation	AB3505LB-GAO	5 VDC	35 mm	35 mm	10 mm	1	Ball	90 mA	UL, CUL, TUV, CE	23.8	5" Wires	\$12.95
2315551	ADDA Corporation	AB3505HX-QB6(TX)	5 VDC	35 mm	35 mm	7 mm	1.3	Hypro	230 mA	UL, CUL, TUV, CE	28.3	5.5" Wires (3), speed sensor	\$13.95
2316015	ADDA Corporation	AB05012DX200300	5 VDC	50 mm	50 mm	20 mm	3.7	Hypro	70 mA	UL, CUL, TUV, CE	21	12" Wires (3), speed sensor	\$12.95
2315855	ADDA Corporation	AB0505MB-RB3(A)	5 VDC	50 mm	50 mm	9 mm	3	Ball	170 mA	UL, CUL, TUV, CE	30.5	5.5" Wires (3), speed sensor	\$12.95
2306663	Sunon	GB0507PGV1-A	5 VDC	70 mm	70 mm	12 mm	4.6	Vapo	310 mA	UL, CUL, TUV	27	2.5" Wires (3)	\$11.95