



[Click Here to Request a Large Quantity Quote](#)

Special Function LEDs

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Luminous Intensity - Iv (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Mounting	Price 1
2152163	Jameco Valuepro	MCDL-10003RGBW-B	10mm, T3-1/4	RGB Auto Blinking	800/900/600	Diffused White	20	3	30 mA	625 nm, 525 nm, 470 nm	13.2	0.1"	\$1.95
2129625	Jameco Valuepro	LDUV3333	10mm, T3-1/4	UV	450	Water Clear	20	3.5	30 mA	400 nm	8.6	0.1"	\$0.99
2305751	Jameco Valuepro	5BR4-O-T-12V-SB	5mm, T-1 3/4	Blue	7500	Water Clear	30	12	120 mA	465 nm	8.6	0.1"	\$0.59
2305791	Jameco Valuepro	5GR4-O-T-360-SB	5mm, T-1 3/4	Green	1100	Water Clear	360	3.3	20 mA	530 nm	6.8	0.1"	\$0.59
2305727	Jameco Valuepro	5GR4-O-T-12V-SB	5mm, T-1 3/4	Green	13000	Water Clear	30	12	120 mA	530 nm	8.6	0.1"	\$0.59
2157271	Jameco Valuepro	MCDL-5013RGBW-B	5mm, T-1 3/4	RGB Auto Blinking	300	Diffused	40	3	20 mA	630 nm, 525 nm, 470 nm	8.6	0.1"	\$1.49
2299479	Jameco Valuepro	2P-RGB-S-335-S	5mm, T-1 3/4	RGB Auto Blinking	4,000/4,500/8,000	Water Clear	35	3.1	80 mA	630 nm, 525 nm, 470 nm	7.6	0.1"	\$0.49
2299463	Jameco Valuepro	2P-RGB-F-335-F	5mm, T-1 3/4	RGB Auto Blinking	4,000/4,500/8,000	Water Clear	35	3.1	80 mA	630 nm, 525 nm, 470 nm	7.6	0.1"	\$0.59
2299455	Jameco Valuepro	0.3W-2P-RGB-F-335-F	5mm, T-1 3/4	RGB Auto Blinking	8,000/11,000/18,000	Water Clear	35	3.1	80 mA	630 nm, 525 nm, 470 nm	7.6	0.1"	\$0.35
2299471	Jameco Valuepro	0.3W-2P-RGB-S-335-S	5mm, T-1 3/4	RGB Auto Blinking	8,000/11,000/18,000	Water Clear	35	3.1	80 mA	630 nm, 525 nm, 470 nm	7.6	0.1"	\$0.49
2305719	Jameco Valuepro	5RR4-O-T-12V-SB	5mm, T-1 3/4	Red	13000	Water Clear	30	12	120 mA	630 nm	8.6	0.1"	\$0.59
34690	Jameco Valuepro	LFH3360	5mm, T-1 3/4	Red	2.8	Diffused	30	3 to 12	60 mA	697 nm	8.6	0.1"	\$0.39
2305799	Jameco Valuepro	5RR4-O-T-360-SB	5mm, T-1 3/4	Red	600	Water Clear	360	2	20 mA	630 nm	6.8	0.1"	\$0.59
2186558	Lite-On Electronics	MSB557DA-OHM	5mm, T-1 3/4	Red	80	Diffused	40	3	28 mA	660 nm	8.7	0.1"	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Luminous Intensity - Iv (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Mounting	Price 1
2274823	Jameco Valuepro	5WUV4-Y-T	5mm, T-1 3/4	UV	1000	Water Clear	30	3.2	20 mA	405 nm	8.6	0.1"	\$0.45
2305807	Jameco Valuepro	5WR4-O-T-360-SB	5mm, T-1 3/4	White	1100	Water Clear	360	3.2	20 mA	7000 K	6.8	0.1"	\$0.59
2305735	Jameco Valuepro	5WR4-O-T-12V-SB	5mm, T-1 3/4	White	12000	Water Clear	30	12	120 mA	6500 K	8.6	0.1"	\$0.59
2299439	Jameco Valuepro	F-3-1HZ-600-W	5mm, T-1 3/4	White	12000	Water Clear	35	3.1	20 mA	6500 K	4.1	0.1"	\$0.49
2299447	Jameco Valuepro	FLI-5-5922-Y	5mm, T-1 3/4	Yellow	220	Water Clear	35	2	20 mA	590 nm	7.6	0.1"	\$0.49