



[Click Here to Request a Large Quantity Quote](#)

Ceramic Radial Capacitors

Jameco Part #	Manufacturer	Manufacturer Part #	Body Width (mm)	Capacitance (pF)	Capacitance (uF)	Dielectric	Lead Length (mm)	Lead Spacing (mm)	Tolerance (%)	Price 1	Price 10
81543	Jameco Valuepro	MD10	3	10	0.00001	Z5U	26	5	20	\$0.25	\$0.17
2296855	Jameco Valuepro	CRC215COG560J100	3	56	0.000056	NP0	13	3	5	\$0.39	\$0.29
2296847	Jameco Valuepro	CRC115C0G101J100	3	100	0.0001	NP0	15	3	5	\$0.39	\$0.29
544825	Jameco Valuepro	SR151C102KAA	3	1000	0.001	X7R	26	3	10	\$0.29	\$0.19
2284663	Jameco Valuepro	FG28C0G1H391JNT	3.3	390	0.00039	Z5U	41	3	20	\$0.25	\$0.15
2302191	Jameco Valuepro	MD.0056	3.3	5600	0.0056	Z5U	38	3	20	\$0.25	\$0.15
332541	Jameco Valuepro	COG22/100-R	3.5	22	0.000022	NP0	30	3	5	\$0.29	\$0.22
332567	Jameco Valuepro	COG47/100-R	3.5	47	0.000047	NP0	30	3	5	\$0.39	\$0.29
2302151	Jameco Valuepro	MD180	3.5	180	0.00018	Z5U	40	3	20	\$0.25	\$0.15
2302215	Jameco Valuepro	MD270	3.5	270	0.00027	Z5U	38	3	20	\$0.49	\$0.39
2080340	PDC / PROSPERITY DIELECTRIC CO.	RD15CG-331J-500RR	3.5	330	0.00033	Z5U	40	5	20	\$0.25	\$0.15
2302175	Jameco Valuepro	MD560	3.5	560	0.00056	Z5U	36	5	20	\$0.25	\$0.15
81517	Jameco Valuepro	MD.001	3.5	1000	0.001	Z5U	24	3	20	\$0.25	\$0.15
2302183	Jameco Valuepro	MD.0027	3.5	2700	0.0027	Z5U	40	3	20	\$0.25	\$0.15
544833	Jameco Valuepro	SR151C103KAA	3.5	10000	0.01	X7R	28	3	10	\$0.25	\$0.19
332647	Jameco Valuepro	MOC10000/100-R	3.5	10000	0.01	X7R	28	3	10	\$0.25	\$0.19
544905	Jameco Valuepro	SR211C333KAA	3.5	33000	0.033	X7R	30	5	10	\$0.35	\$0.25
332523	Jameco Valuepro	COG10/100	4	10	0.00001	NP0	30	5	5	\$0.29	\$0.19
2281199	Jameco Valuepro	F5NP01C150K	4	15	0.000015	NP0	26	6	5	\$0.39	\$0.29
2280815	Jameco Valuepro	CPC-C1-100V-18P	4	18	0.000018	NP0	16	5	2	\$0.39	\$0.29
81533	Jameco Valuepro	MD22	4	22	0.000022	Z5U	26	3	20	\$0.25	\$0.17
332583	Jameco Valuepro	MOC100/100	4	100	0.0001	X7R	40	3	10	\$0.25	\$0.19
2288527	Jameco Valuepro	220PF50VRAD	4	220	0.00022	X7R	28	3	10	\$0.25	\$0.19
332592	Jameco Valuepro	MOC220/100-R	4	220	0.00022	Y5P	28	5	10	\$0.39	\$0.35
332612	Jameco Valuepro	MOC470/100-R	4	470	0.00047	X7R	28	3	10	\$0.25	\$0.19
138182	Jameco Valuepro	MD.0022-VP	4	2200	0.0022	Z5U	30	3	20	\$0.25	\$0.15

Jameco Part #	Manufacturer	Manufacturer Part #	Body Width (mm)	Capacitance (pF)	Capacitance (uF)	Dielectric	Lead Length (mm)	Lead Spacing (mm)	Tolerance (%)	Price 1	Price 10
<a href="#">332655</a>	Jameco Valuepro	MOC22000/100-R	4	22000	0.022	X7R	28	3	10	\$0.39	\$0.29
<a href="#">544913</a>	Jameco Valuepro	SR211C473KAA	4	47000	0.047	X7R	9	6	10	\$0.29	\$0.19
<a href="#">2295911</a>	Jameco Valuepro	RD16YV104M500RR	4	100000	0.1	Y5V	25	5	20	\$0.25	\$0.06
<a href="#">25525</a>	Jameco Valuepro	MD.1-VP-R	4	100000	0.1	Z5U	40	3	20	\$0.25	\$0.15
<a href="#">57621</a>	Jameco Valuepro	MD.047	4.5	47000	0.047	Z5U	24	5	20	\$0.39	\$0.29
<a href="#">332689</a>	Jameco Valuepro	MOC150000/100	4.6	150000	0.15	Z5U	38	3	+80/-20	\$0.29	\$0.25
<a href="#">81525</a>	Jameco Valuepro	MD100	5	100	0.0001	Z5U	13	5	20	\$0.25	\$0.15
<a href="#">2296935</a>	Murata	RPE122-905COG151K050V	5	150	0.00015	NP0	25	7	10	\$0.29	\$0.19
<a href="#">2159816</a>	Siemens Corporation	B37986N5102K	5	1000	0.001	NP0	36	3	5	\$0.25	\$0.15
<a href="#">2280823</a>	AVX	URSUJC222KA-CRIMP	5	2200	0.0022	X7R	26	7	10	\$0.29	\$0.19
<a href="#">138202</a>	Jameco Valuepro	MD.0047	5	4700	0.0047	Z5U	16	6	20	\$0.25	\$0.19
<a href="#">25507</a>	Jameco Valuepro	MD.01	5	10000	0.01	Z5U	26	3.5	20	\$0.29	\$0.22
<a href="#">2302199</a>	Jameco Valuepro	MD.056	5	56000	0.056	Z5U	39	6	20	\$0.25	\$0.15
<a href="#">332672</a>	Jameco Valuepro	MOC100000/100	5	100000	0.1	X7R	25	3	10	\$0.29	\$0.25
<a href="#">544921</a>	Jameco Valuepro	SR215C104KAA	5	100000	0.1	X7R	30	5	10	\$0.25	\$0.19
<a href="#">2280335</a>	Jameco Valuepro	ECU-S1J104KBB	5	100000	0.1	X7R	34	5	10	\$0.25	\$0.15
<a href="#">767834</a>	AVX	SR211C104KAR	5	100000	0.1	X7R	36	4	10	\$0.29	\$0.19
<a href="#">25523</a>	Jameco Valuepro	MD.1	5	100000	0.1	Z5U	14	3	20	\$0.25	\$0.15
<a href="#">544868</a>	Jameco Valuepro	SR205E104MAA	5	100000	0.1	Z5U	38	3	20	\$0.29	\$0.19
<a href="#">2302207</a>	Jameco Valuepro	MD.12	5	120000	0.12	Z5U	36	3	20	\$0.39	\$0.29
<a href="#">25540</a>	Jameco Valuepro	MD.22	5	220000	0.22	Z5U	35	6	20	\$0.39	\$0.25
<a href="#">544930</a>	Jameco Valuepro	SR215E334MAA	5	330000	0.33	Z5U	30	6	20	\$0.29	\$0.19
<a href="#">138237</a>	Jameco Valuepro	MD.33	5	330000	0.33	Z5U	38	5	20	\$0.39	\$0.25
<a href="#">2239162</a>	Jameco Valuepro	FK22X7R1H335K	5	3.3 Meg	3.3	X7R	30	5	10	\$1.09	\$0.95
<a href="#">2280719</a>	AVX	MD015X104MMA	6	100000	0.1	Z5U	4	8	20	\$0.79	\$0.69
<a href="#">544948</a>	Jameco Valuepro	SR305C474KAA	6	470000	0.47	X7R	38	5	10	\$0.99	\$0.85
<a href="#">25558</a>	Jameco Valuepro	MD.47	6	470000	0.47	Z5U	12	6	20	\$0.39	\$0.29
<a href="#">544956</a>	Jameco Valuepro	SR305E105MAA	6	1 Meg	1	Z5U	28	5	20	\$0.49	\$0.35
<a href="#">768183</a>	AVX	SR305E105MAR	6	1 Meg	1	Z5U	40	5	20	\$0.59	\$0.45
<a href="#">2280111</a>	Jameco Valuepro	HCFE2G102MAA	7	1000	0.001	X7R	28	7	20	\$0.29	\$0.25
<a href="#">2280831</a>	AVX	URSUHC472KA-CRIMP	7	4700	0.0047	X7R	8	7	10	\$0.39	\$0.29

Jameco Part #	Manufacturer	Manufacturer Part #	Body Width (mm)	Capacitance (pF)	Capacitance (uF)	Dielectric	Lead Length (mm)	Lead Spacing (mm)	Tolerance (%)	Price 1	Price 10
<a href="#">2112911</a>	AVX	C320C473K5R5CA	7.3	47000	0.047	X7R	25	5	10	\$0.39	\$0.35
<a href="#">2280575</a>	AVX	SV53222KAA	7.5	2200	0.0022	X7R	34	7	10	\$0.29	\$0.19
<a href="#">81509</a>	Jameco Valuepro	MD1	7.5	1 Meg	1	Z5U	37	5	20	\$0.49	\$0.35
<a href="#">2301663</a>	Jameco Valuepro	MY.022/630	21	22000	0.022	NP0	25	10	10	\$0.99	\$0.89