



[Click Here to Request a Large Quantity Quote](#)

[Slim Line Regulated Switching Wall Adapters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
2138636	Emerson Network Power	SW013US-0500020US	5	0.2	100 to 240	50 to 60	USB Port	USB Type A	N/A	2.5 x 0.8 x 1.5	TUV/FCC	\$1.95
2234097	Phihong	PLA02A-050-1.7	5	0.4	90 to 264	47 to 63	Cylindrical Female	1.7mm x 3.0mm right angle	Center Positive	2 x 1 x 1.4	UL/CUL	\$3.25
2126125	Arndt	ADS0051-W050080	5	0.8	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	1.9 x 1.6 x 0.9	UL/CUL/FCC	\$5.95
2289127	Arndt	DSC-6PFA-05FU	5	1	100 to 240	50 to 60	Cylindrical Female	1.3mm x 3.5mm	Center Positive	2.4 x 1.0 x 1.6	UL/CUL/TUV/FCC	\$5.95
252720	Jameco Reliapro	HK-AP-050A100-US	5	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.3 x 1.1 x 1.7	UL/CUL/CEC	\$8.95
2120090	Arndt	MU05-J050100-A1-2.1	5	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.3 x 1.3 x 1.5	UL/CUL/CEC	\$4.95
2234601	Arndt	MU05-050100-A1-10	5	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.6 x 1.3 x 1.5	UL/CUL	\$3.95
2289807	Jameco Reliapro	TC006	5	1	100 to 240	50 to 60	USB Port	USB Type A	N/A	1.0 x 1.0 x 1.1		\$3.95
2210888	Arndt	1128	5	1	100 to 240	50 to 60	USB Port	USB Type A	N/A	2.6 x 1.3 x 1.5	UL/CUL	\$2.49
1940660	MEAN WELL	GS06U-1P1J	5	1	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.6 x 1.3 x 1.7	UL/CUL/FCC/EAC	\$9.90
2211098	Phihong	PLA05A-050-R	5	1	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.1 x 1.3 x 1.6	UL/CUL	\$4.95
2229440	Arndt	TSA1-050120WA	5	1.2	100 to 240	50 to 60	Stripped & Tinned Pigtail Wires	N/A	N/A	1.8 x 1.1 x 2.1	UL/CUL	\$4.49
2289479	Jameco Reliapro	JTA0302A	5	2	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	1.8 x 1 x 2.5	UL/CUL/TUV	\$5.95
2217772	Jameco Reliapro	HK-AR-050A200-US	5	2	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3 x 1.6 x 1.2	UL/CUL/CEC	\$10.95
2244359	Jameco Reliapro	US2018	5	2.1	100 to 240	50 to 60	USB Port	USB Type A	N/A	2 x 1.1 x 2	UL	\$6.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
2217617	Seed Studios	313990002	5	2.1	100 to 240	50 to 60	USB Port	USB Type A	N/A	2.3 x 1.3 x 1.6	UL/FCC	\$9.95
2230336	Dee Van Enterprise Usa	DSA-15P-05 US	5	2.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.7 x 1.1 x 1.7	UL/CUL	\$9.95
2292431	Arndt	FJ-SW0503000U	5	3	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.4	UL/CUL	\$6.49
2224016	Jameco Reliapro	KSAS0150500300VU-VI	5	3	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.3 x 1.3 x 1.7	UL/CUL/CEC	\$11.95
2135451	MG Electronics	SPS-054000D	5	4	90 to 132	47 to 63	Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	3.0 x 1.3 x 1.8	UL/CUL/CE	\$10.95
2225932	MEAN WELL	SGA40U05-P1J	5	5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$19.00
2226003	MEAN WELL	SGA60U05-P1J	5	6	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90
2230133	Jameco Reliapro	GQ05-060050-CU	6	0.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.3 x 1.1 x 1.6	UL/CUL	\$6.49
2145078	Arndt	MGT-6500SPS	6	0.5	90 to 264	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.5 x 1.1 x 1.8	UL/CUL/CEC	\$6.95
2236498	Jameco Reliapro	KSAS0050900050VUD	9	0.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.1 x 0.9 x 1.3	UL/CUL/CE	\$8.95
2203741	Arndt	CYSC24-090100-P	9	1	100 to 120	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	2.4 x 1.3 x 1.9	UL/CUL	\$7.95
2234100	Jameco Reliapro	MTR-16110	9	1	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.5 x 1.1 x 1.7	UL	\$9.95
252779	Jameco Reliapro	HK-AR-090A120-US	9	1.2	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/CE/CEC	\$10.95
252786	Jameco Reliapro	HK-AW-090A150-US	9	1.5	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/TUV	\$11.95
2236412	Jameco Reliapro	GQ05-120025-CU	12	0.25	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.2 x 1 x 1.7	UL/CUL	\$7.95
252808	Jameco Reliapro	HK-AP-120A050-US	12	0.5	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.5 x 1.1 x 1.7	UL/CUL/CE/CEC	\$8.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
2150758	Arndt	MGT-12500SPS	12	0.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.5 x 1.1 x 1.7	UL/CUL/TUV/CE	\$6.95
2270847	Arndt	PSU-C9-ELEV6	12	0.75	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	2.7 x 1.1 x 1.7	UL/CUL/CEC	\$5.95
2233983	Arndt	DSA-12PFT-12FUS	12	1	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.7 x 1.1 x 1.5	UL	\$7.95
252824	Jameco Reliapro	HK-AR-120A100-US	12	1	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.1 x 1.6	UL/CUL/TUV	\$9.95
2232825	Arndt	SPS121	12	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.3 x 1.2 x 1.6	UL/CUL	\$6.95
2303159	Jameco Valuepro	PEA-120100VA	12	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.2 x 1.7	UL/CUL	\$7.95
252833	Jameco Reliapro	HK-AW-120A125-US	12	1.25	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/TUV	\$10.95
2236501	Jameco Reliapro	KSA-24W-120150VU	12	1.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.3 x 1.3 x 1.7	UL/CUL	\$11.95
1950497	Jameco Reliapro	GQ30-120200-BU	12	2	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/FCC	\$13.95
2236738	Jameco Reliapro	GQ30-120200-BU-2.5	12	2	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.1	UL/CUL	\$10.95
2247277	MEAN WELL	SGA25U12-P1J	12	2.08	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$12.95
2280167	Arndt	PS-2.1-12-24WTM	12	2.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.1 x 2.1 x 1.3	UL/CSA/CEC	\$8.95
2295551	Jameco Reliapro	KSA-30W-120250VU	12	2.5	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	2.8 x 1.2 x 1.7	UL/CUL	\$12.95
2225959	MEAN WELL	SGA40U12-P1J	12	3.33	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$19.00
2229845	Arndt	AD898F20	12	3.5	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.3 x 1.1 x 2.7	UL/CUL	\$9.95
2226038	MEAN WELL	SGA60U12-P1J	12	5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
2265647	Arndt	PS15V1300MA-003	15	1.3	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.8 x 1.4 x 2.2	UL/CUL/FCC	\$7.95
2229941	Jameco Reliapro	HK-AW-240A050-US	24	0.5	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/TUV/CE	\$8.95
2247154	MEAN WELL	SGA12U24-P1J	24	0.5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.45 x 1.08 x 1.56	UL/CUL/CB/FCC/EAC	\$10.60
2076341	Jameco Reliapro	HK-AW-240A063-US	24	0.63	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/CEC	\$9.95
2230416	Phihong	PDA024A-1A0S-R	24	1	100 to 120	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.4 x 1.4 x 2.1	UL/CUL	\$8.95
2208972	Jameco Reliapro	KSA-24W-240100VU	24	1	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.5 x 1.3 x 1.7	UL/CUL/CECV	\$10.95
2271063	Jameco Reliapro	MTR-18028	24	1	100 to 240	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	2.9 x 1.3 x 2.3	UL/CUL/CEC	\$12.95
2247306	MEAN WELL	SGA25U24-P1J	24	1.04	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$14.80
2226062	MEAN WELL	SGA60U24-P1J	24	2.5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90
2226071	MEAN WELL	SGA60U48-P1J	48	1.25	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90