



[Click Here to Request a Large Quantity Quote](#)

[Rectangular Connectors-.165" \(4.20mm\) Series](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Contact Gender	Number of Rows	Number of Contacts	Product Depth (mm)	Product Length (mm)	Mounting Type	Maximum Current Rating	Maximum Voltage Rating	Maximum Contact Resistance	Price 1
2232884	Molex	39-01-3129	Plug	2	12	23.9	9.6	Cable End	N/A	N/A	N/A	\$0.49
881004	Molex	39-01-3023	Plug	2	2	23.9	7.4	Cable End	N/A	N/A	N/A	\$0.29
303685	Molex	39-01-2021	Plug	2	2	23.9	10.8	Cable End	N/A	N/A	N/A	\$0.29
147379	Jameco Valuepro	CW4201SA-20	Plug	2	20	16	43	PCB	7	250	1000 Mohm	\$0.25
881135	Molex	39-01-3049	Plug	2	4	23.9	11.6	Cable End	N/A	N/A	N/A	\$0.45
798307	Molex	39-01-3089	Plug	2	8	23.9	18	Cable End	N/A	N/A	N/A	\$0.49
880870	Molex	39-01-2125	Receptacle	2	12	19.6	26.4	Cable End	N/A	N/A	N/A	\$0.59
303562	Molex	39-01-2020	Receptacle	2	2	19.6	5.4	Cable End	N/A	N/A	N/A	\$0.25
303571	Molex	39-01-2040	Receptacle	2	4	19.6	9.6	Cable End	N/A	N/A	N/A	\$0.25
880790	Molex	39-01-2065	Receptacle	2	6	19.6	13.8	Cable End	N/A	N/A	N/A	\$0.49